



Bottom view



| SYMBOL | DIMENSIONS | | |
|--------|------------|------|------|
| | MIN. | NOM. | MAX. |
| A | - | - | 1.3 |
| A1 | 0.15 | 0.25 | 0.35 |
| D | 6 BSC | | |
| E | 6 BSC | | |
| Øb | 0.2 | 0.3 | 0.4 |
| eD | 0.5 BSC | | |
| eE | 0.5 BSC | | |

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []