



Bottom view



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.55
A1	0.16	-	-
D	4.91 BSC		
E	5.85 BSC		
$\varnothing b$	0.2	0.25	0.3
eD	0.4 BSC		
eE	0.4 BSC		
f1	0.235 BSC		
f2	0.413 BSC		
f3	0.272 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []