

- 1) Does not include plastic protrusion which shall not exceed 0.15mm max. per side.
- 2) Dambar protrusion shall be maximum 0.1mm per side.
- 3) Fillet and radii: unless otherwise noted all radii are 0.3mm max.
- 4) All metal surfaces are plated, except area of cut.
- 5) Datum A & B to be determined at datum H.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [ Drawing according to ISO 8015, general tolerances ISO 2768-mK

