


| SYMBOL    | DIMENSIONS |       |       |
|-----------|------------|-------|-------|
|           | MIN        | NOM   | MAX   |
| A         | -          | -     | 0.514 |
| A1        | 0.169      | -     | -     |
| D         | 2.443 BSC  |       |       |
| E         | 2.51 BSC   |       |       |
| D1        | 2 BSC      |       |       |
| E1        | 2.078 BSC  |       |       |
| Øb        | 0.235      | 0.265 | 0.295 |
| eD        | 0.4 BSC    |       |       |
| eE        | 0.693 BSC  |       |       |
| eDs / eEs | 0.4 BSC    |       |       |

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]