





| SYMBOL   | DIMENSIONS |      |      |
|----------|------------|------|------|
|          | MIN.       | NOM. | MAX. |
| A        | -          | -    | 1.7  |
| A1       | 0.05       | -    | 0.15 |
| b        | 0.17       | 0.22 | 0.27 |
| c        | 0.09       | -    | 0.2  |
| D        | 30 BSC     |      |      |
| D1       | 28 BSC     |      |      |
| e        | 0.5 BSC    |      |      |
| E        | 30 BSC     |      |      |
| E1       | 28 BSC     |      |      |
| L        | 0.45       | 0.6  | 0.75 |
| $\theta$ | 0°         | -    | 8°   |

1) Dimensions D1 and E1 do not include mold protrusion. allowable protrusion is 0.25mm per side.

2) Dimension b does not include dambar protrusion. the dambar protrusion(s) shall not cause the lead width to exceed b maximum by more than 0.08mm.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]