



Pin 1 up to pin 16 omitted for clarity

Bottom view





Pin 1 corner side




Punched-mold along this equator side
Mold flash along side of leads

0.12 Max. per side



Pin 17 up to pin 24 omitted for clarity

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0.1/\pm 1^\circ$