






SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	4.1
A1	0.25	-	0.5
b	0.25	0.32	0.4
c	0.14	-	0.22
D	31.2 BSC		
D1	28 BSC		
e	0.65 BSC		
E	31.2 BSC		
E1	28 BSC		
θ	0°	-	8°
L	0.73	0.88	1.03

1) Dimensions D1 and E1 do not include mold protrusion. allowable protrusion is 0.25mm per side.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []