







1) All dimensions refer to JEDEC standard TO261-AA do not include mold flash or protrusions, body length including mold protrusions shall not exceed 6.7mm.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances ISO 2768-mK