





SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.05	-	0.15
D	12 BSC		
D1	10 BSC		
D2	7.17 REF		
D3	6.1 REF		
E	12 BSC		
E1	10 BSC		
E2	7.17 REF		
E3	6.1 REF		
θ	0°	4°	8°
c	0.09	-	0.2
b	0.27	0.32	0.37
L	0.45	0.6	0.75
e	0.65 BSC		

- 1) Dimensions D1 and E1 do not include mold protrusion. allowable protrusion is 0.25mm pre side.
- 2) Dimension b does not include dambar protrusion. the dambar protrusion(S) shall not cause the lead width to exceed b maximum by more than 0.08mm.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 