

CIPURSE™ Security Controller

Short Product Overview



SLS 32TLC100(M)

Features

- Compliant to CIPURSE™ T Profile Specification Revision 2.0
 - 8 and 16 applications (ADF) configurable
 - 4 and 8 PxSE ADF configurable
- 8 kByte user memory for application data storage
- Optional support of 1 kByte or 4 kByte NRG™ (ISO/IEC 14443-3 type A with CRYPTO1) emulation
- NFC Forum Type 4 Tag configurable
- Contactless interface ISO/IEC 14443 Type A
- CC EAL 5+ (high)

Applications

- Weekly or seasonal cards for Automatic Fare Collection (AFC)
- Event ticketing
- Access Control
- Micropayment

Description

The CIPURSE™ Security Controller is a dedicated contactless security controller for cost optimized tickets and cards in transport ticketing multi-applications. It is featuring the CIPURSE™ T profile and is compliant to the OSPT™ Alliance CIPURSE™ V2 specification. The Open Standard CIPURSE™ V2 provides interoperability and easy integration of CIPURSE™ V2 compliant products.

The CIPURSE™ Security Controller incorporates the CIPURSE™ V2 security architecture and is compliant to the CIPURSE™ V2 cryptographic protocol specification using AES-128, augmented by a combination of hardware and software security measures. Commands and transmitted data can be secured using the CIPURSE™ V2 cryptographic protocol which is inherently resistant against physical attacks like DPA and DFA. A typical CIPURSE™ secured transaction will take less than 100 ms.

On top, 1 kByte or 4 kByte NRG™ (ISO/IEC 14443-3 type A with CRYPTO1) emulation for legacy systems and NFC Forum Type 4 Tag operation for NFC applications can be supported.

CIPURSE™ Security Controller is the ideal product to support migration from existing none security or NRG™ (ISO/IEC 14443-3 type A with CRYPTO1) legacy systems towards a more advanced and state-of-the-art security architecture like CIPURSE™.

Description

Product name	CIPURSE™ Security Controller - SLS 32TLC100(M)
Product description	Contactless Security Controller with featuring the CIPURSE™T profile and is compliant to the OSPT™ Alliance CIPURSE™V2 specification
Interfaces	ISO/IEC 14443 Type A, Optional NRG™ (ISO/IEC 14443-3 type A with CRYPTO1) interface
Memory	8 kByte user memory for application data storage
CPU	16-bit
Symmetrical cryptography	Mutual authentication using AES 128
Ambient temperature	Operating temperature range: -25°C to +85°C Storage temperature range: -25°C to +125°C
System Features	CIPURSE™T Profile compliant Security Controller Secured communication using AES 128 and session key derivation 16 applications (ADF) configurable CIPURSE™ certified
Delivery forms	Sawn wafer 75 or 150 μm NiAu bump 20 μm MCC8-2-6
Typical applications	Weekly or seasonal cards for Automatic Fare Collection (AFC) Event ticketing, Access Control, Micropayment
Certification level	CC EAL5+ high Robust protection against potential security attacks CIPURSE™V2 certified NFC Tag device Type 4A Tag certified

For further information on technology, delivery forms and conditions please contact your nearest Infineon Technologies sales representative (www.infineon.com)

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-11-30

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2022 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email:

CSSCustomerService@infineon.com

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.