


- 1) Measured at the bottom parting line; does not include mold flash or metal protrusions;
Flash or protrusions shall not exceed 0.15 mm per side for dimension 12.5 and 0.25 for dim. 6.1 .
- 2) Does not include dambar protrusion of 0.08 max. in excess of leadwidth at max. material
Condition; min. space between protrusion and an adjacent lead to be 0.08 mm .

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances ISO 2768-mK