


Position tolerance for all pads:

14x	$\oplus 0.1(M)$	A	B	C
	$\oplus 0.05(M)$	C		

All dimensions are in units mm  
 The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]  
 Drawing according to ISO 8015, general tolerances ISO 2768-mK