


Bottom view



Position tolerance for all pads:

14x	⊕ 0.1 (M)	A	B	C
	⊕ 0.05 (M)	C		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Drawing according to ISO 8015, general tolerances ISO 2768-mK