



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	0.8	0.85	0.9
A1	0	0.02	0.05
b	0.15	0.2	0.25
D	9 BSC		
E	9 BSC		
D1	6.4 BSC		
E1	6.3 BSC		
D2	3.2 BSC		
E2	3.1 BSC		
e	0.4 BSC		
L	0.325	0.4	0.475

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []