

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [

SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
А	0.8	0.85	0.9
A1	0	0.02	0.05
b	0.15	0.2	0.25
D	10 BSC		
E	10 BSC		
D1	6.8 BSC		
E1	6.8 BSC		
е	0.4 BSC		
L	0.35	0.4	0.45