TLF50281EL

2.2 MHz Step-Down Regulator 500 mA low quiescent current

Application Board



TLF50281EL Application Board Introduction



This application board shall enable testing of the TLF50281EL

- 2.2 MHz Step-Down Regulator 500 mA, low quiescent current
- Fixed output voltage (5 V)
- The board offers the possibility to modify the circuit
- (please refer to datasheet for TLF50281EL details)

TLF50281EL Application Board How to start




Connect the Application Board as shown below for a basic Test:




TLF50281EL Application Board Connections: details (Refer to Datasheet)





TLF50281EL Application Board Schematic





TLF50281EL Application Board Bill Of Material



Reference Designator	Characteristics
	TLF50281EL
R1	330 kΩ
R2	100 kΩ
Rз	16 kΩ
R_wo	16 kΩ
R_freq	47 kΩ
Rs	510 Ω
CIN1	10 µF / 50 V
CIN2	10 µF / 50 V
CIN3	100 nF / 50 V
COUT1	10 µF / 16 V
COUT2	100 nF / 16 V
Lin2	XAL6060-103 10 μH
LBU1	XAL6060-103 10 μH
DRV	MURS360 3A/600V

TLF50281EL Application Board Bill Of Material



Reference Designator	Characteristics
D1	10BQ100 1A/100V
Cs	100 pF
JP1	2 pins
JP2	3 pins
VBB	Banana Jack red
GND	2 x Banana Jack black
WI	Banana Jack red
ENA	Banana Jack red
SYNC	Banana Jack red
OUT	Banana Jack red
RO	Banana Jack red
WO	Banana Jack red

TLF50281EL Application Board Reset adjustment



The reset generator consists of an internal comparator with a reset threshold V_{RO,T}. By adding an external resistor divider between the output voltage V_{CC} and ground (GND) and connecting the point between the upper (R1) and lower (R2) resistor to pin RTADJ the desired reset threshold VRT (where the reset generator indicates an under voltage) might be adjusted. If reset function is not used please connect pin RTADJ to V_{CC}.


Desired reset threshold =
$$V_{RO, T} \left(\frac{R1 + R2}{R2} \right) = V_{RT}$$

TLF50281EL Application Board Watchdog mode selection



- The watchdog offers two operation modes:
 - ¬ Slow watchdog timing
 - ¬ Fast watchdog timing.


For <u>slow</u> watchdog timing please connect pin WMSEL to Vcc (output voltage) using JP2. For <u>fast</u> watchdog timing please connect WMSEL to ground (GND) using JP2.



 Pin 1 of JP2 is connected to OUT.
Vcc is called Vbb at JP2.
Please consider
Vbb as Vcc, as described and listed in the datasheet.

TLF50281EL Application Board PCB Layout





TLF50281EL Application Board



Edition 2012-04-05

Published by Infineon Technologies AG 81726 Munich, Germany

© 2012 Infineon Technologies AG All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.



ENERGY EFFICIENCY MOBILITY SECURITY

Innovative semiconductor solutions for energy efficiency, mobility and security.

