



## Product brief

# 6EDL7141


## 3-phase smart gate drive controller IC

The 6EDL7141 is Infineon's latest 3-phase motor control gate driver IC that enables development of high performance battery operated products using BLDC or PMSM motors. Ideal applications include cordless power tools, gardening products, and automated guided vehicles. With over 50 programmable parameters using built-in digital SPI interface, 6EDL7141 is fully configurable to drive a wide range of MOSFET's to yield the best possible system efficiency.

The 6EDL7141 is also designed for maximum flexibility. With an operating voltage from 5.5-70 V and configurable gate drive sink and source current up to 1.5 A, it has the ability to drive a wide range of MOSFETs effectively to best fit the application. It has adjustable gate driver supply voltage setting between 7 V, 10 V, 12 V and 15V even at low battery voltage thanks to built-in dual charge pumps. The 6EDL7141 also has adjustable gate driver parameters to enable control of the slew rate to minimize system EMI. All of the 6EDL7141 settings can be quickly changed with the available easy-to-use GUI.

The integrated buck regulator requires only an external capacitor and inductor to provide power for both the microcontroller and the Hall sensors in the motor, further reducing peripheral components and required PCB area. In addition, with a full suite of system protection features such as OCP, UVLO, over-temperature, and locked rotor detection, this dedicated motor controller will increase reliability and robustness in severe operating fault conditions.

EVAL\_6EDL7141\_TRAP\_1SH  
Single shunt evaluation board  
for trapezoidal commutation of  
BLDC motors with 40 V OptiMOS™ 5 PQFN  
and XMC1404 MCU  
On-board programming dongle  
Featured IC: 6EDL7141



### Key features

- › Integrated power supplies
- › Adjustable slew rate
- › Programmable gate drive parameters
- › 3x current shunt amplifier
- › Complete dedicated motor control protection suite

### Key benefits


- › Reduced external components and PCB area
- › Optimized efficiency and EMI
- › Maximum flexibility to use different inverter FET's
- › Highly accurate current sense while saving external components
- › Higher dynamic range to increase signal resolution
- › Improve reliability and fault detection



# 6EDL7141

## 3-phase smart gate drive controller IC

### Block diagram



### Product portfolio

Part number	Package	Voltage [V]	$R_{DS(on)}$ max. [mΩ]
6EDL7141	PG-VQFN-48-78	5.5 – 70 V	2.2 Ω

Published by  
Infineon Technologies Austria AG  
9500 Villach, Austria

© 2021 Infineon Technologies AG.  
All Rights Reserved.

#### Please note!

This document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

#### Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

#### Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.