


Thermally-Enhanced High Power RF LDMOS FET 320 W, 28 V, 2110 – 2200 MHz

Description

The PXAC213308FV is a 320-watt (P_{3dB}) LDMOS FET with an asymmetrical design intended for use in multi-standard cellular power amplifier applications in the 2100 to 2200 MHz frequency band. Features include dual-path design, broadband matching, high gain and thermally-enhanced package with earless flanges. Manufactured with Infineon's advanced LDMOS process, this device provides excellent thermal performance and superior reliability.



PXAC213308FV
Package H-37275G-6/2



Features

- Broadband internal input and output matching
- Asymmetrical Doherty design
 - Main : $P_{1dB} = 140\text{ W Typ}$
 - Peak : $P_{1dB} = 190\text{ W Typ}$
- Typical Pulsed CW performance, 2170 MHz, 28 V, combined outputs
 - Output power at $P_{3dB} = 320\text{ W}$
 - Efficiency = 53% @ P_{3dB}
 - Gain = 16 dB @ P_{3dB}
- Capable of handling 10:1 VSWR @ 28 V, 170 W CW output power
- Integrated ESD protection
- Low thermal resistance
- Pb-free and RoHS compliant

RF Characteristics

Single-carrier WCDMA Specifications (tested in Infineon Doherty production test fixture)

$V_{DD} = 28\text{ V}$, $I_{DQ} = 820\text{ mA}$, $V_{GSPEAK} = 1.3\text{ V}$, $P_{OUT} = 55\text{ W avg}$, $f = 2170\text{ MHz}$, 3GPP signal, channel bandwidth = 3.84 MHz, peak/average = 10 dB @ 0.01% CCDF

Characteristic	Symbol	Min	Typ	Max	Unit
Linear Gain	G_{ps}	15.5	16.5	—	dB
Drain Efficiency	η_D	40	43.5	—	%
Adjacent Channel Power Ratio	ACPR	—	-31	-27	dBc

All published data at $T_{CASE} = 25^\circ\text{C}$ unless otherwise indicated

ESD: Electrostatic discharge sensitive device—observe handling precautions!

DC Characteristics (each side)

Characteristic	Conditions	Symbol	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	$V_{GS} = 0\text{ V}$, $I_{DS} = 10\text{ mA}$	$V_{(BR)DSS}$	65	—	—	V
Drain Leakage Current	$V_{DS} = 28\text{ V}$, $V_{GS} = 0\text{ V}$	I_{DSS}	—	—	1	μA
	$V_{DS} = 63\text{ V}$, $V_{GS} = 0\text{ V}$	I_{DSS}	—	—	10	μA
Gate Leakage Current	$V_{GS} = 10\text{ V}$, $V_{DS} = 0\text{ V}$	I_{GSS}	—	—	1	μA
On-State Resistance (Main)	$V_{GS} = 10\text{ V}$, $V_{DS} = 0.1\text{ V}$	$R_{DS(on)}$	—	0.08	—	Ω
	(Peak) $V_{GS} = 10\text{ V}$, $V_{DS} = 0.1\text{ V}$	$R_{DS(on)}$	—	0.06	—	Ω
Operating Gate Voltage (Main)	$V_{DS} = 28\text{ V}$, $I_{DQ} = 850\text{ mA}$	V_{GS}	2.5	2.67	2.8	V
	(Peak) $V_{DS} = 28\text{ V}$, $I_{DQ} = 0\text{ mA}$	V_{GS}	1	1.30	1.5	V





Maximum Ratings



Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	65	V
Gate-Source Voltage	V_{GS}	-6 to +10	V
Junction Temperature	T_J	225	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	-65 to +150	$^{\circ}\text{C}$
Thermal Resistance (Main, $T_{CASE} = 70^{\circ}\text{C}$, 56 W CW)	$R_{\theta JC}$	0.50	$^{\circ}\text{C/W}$
	(Peak, $T_{CASE} = 70^{\circ}\text{C}$, 140 W CW)	$R_{\theta JC}$	0.24

Ordering Information

Type and Version	Order Code	Package Description	Shipping
PXAC213308FV V1 R0	PXAC213308FVV1R0XTMA1	H-37275G-6/2, earless flange	Tape & Reel, 50 pcs
PXAC213308FV V1 R2	PXAC213308FVV1R2XTMA1	H-37275G-6/2, earless flange	Tape & Reel, 250 pcs

Typical RF Performance (data taken in production test fixture)




Typical RF Performance (cont.)

Load Pull Performance
Main Side Load Pull Performance – Pulsed CW signal: 10 μs , 10% duty cycle, 28 V, $I_{DQ} = 850 \text{ mA}$, class AB

Freq [MHz]	Z_s [Ω]	P_{1dB}									
		Max Output Power					Max PAE				
		Z_l [Ω]	Gain [dB]	P_{OUT} [dBm]	P_{OUT} [W]	PAE [%]	Z_l [Ω]	Gain [dB]	P_{OUT} [dBm]	P_{OUT} [W]	PAE [%]
2110	3.1 -j3.95	1.35 -j3.44	17.9	52.54	180	55.0	2.48 -j2.92	19.9	51.25	133	63.0
2140	3.24 -j3.84	1.3 -j3.49	17.7	52.53	179	54.7	2.31 -j2.77	19.8	51.20	131	63.0
2170	3.53 -j3.59	1.25 -j3.52	17.6	52.60	182	54.5	2.23 -j2.82	19.7	51.10	129	62.4
2200	3.6 -j2.99	1.28 -j3.56	17.7	52.44	176	54.0	2.11 -j2.92	19.6	51.17	131	61.5

Peak Side Load Pull Performance – Pulsed CW signal: 10 μs , 10% duty cycle, 28 V, $V_{GS(PEAK)} = 1.3 \text{ V}$, class C

Freq [MHz]	Z_s [Ω]	P_{1dB}									
		Max Output Power					Max PAE				
		Z_l [Ω]	Gain [dB]	P_{OUT} [dBm]	P_{OUT} [W]	PAE [%]	Z_l [Ω]	Gain [dB]	P_{OUT} [dBm]	P_{OUT} [W]	PAE [%]
2110	2.57 -j8	5.37 -j1.04	18.6	53.90	245	54.0	2.11 -j1.23	20.2	51.99	158	62.9
2140	3.27 -j8	3.3 -j8.07	18.5	53.81	240	54.4	2.55 -j1.2	19.9	52.39	174	62.6
2170	4.78 -j8.8	5.54 -j0.9	18.4	53.70	238	53.2	2.15 -j1.72	20.0	51.76	150	62.7
2200	7.5 -j8.4	4.4 -j1.47	17.94	53.70	236	50.5	2.62 -j1.49	19.8	52.29	169	62.7

Reference Circuit, 2110 – 2170 MHz



Reference circuit assembly diagram (not to scale)


Reference Circuit (cont.)

Reference Circuit Assembly


DUT	PXAC213308FV V1
Test Fixture Part No.	LTA/PXAC213308FV V1
PCB	Rogers 4350, 0.508 mm [0.020"] thick, 2 oz. copper, $\epsilon_r = 3.66$, $f = 2110 - 2170$ MHz
Find Gerber files for this test fixture on the Infineon Web site at http://www.infineon.com/rfpower	

Components Information

Component	Description	Manufacturer	P/N
Input			
C101, C104, C105, C109	Capacitor, 18 pF	ATC	ATC100A180JW150XB
C102, C106	Capacitor, 10 μ F	Taiyo Yuden	UMK325C7106MM-T
C103	Capacitor, 0.9 pF	ATC	ATC100A0R9CW150XB
C107	Capacitor, 0.4 pF	ATC	ATC100A0R4CW150XB
C108	Capacitor, 0.2 pF	ATC	ATC100A0R2CW150XB
R101, R102	Resistor, 5.1 Ω	Panasonic Electronic Components	ERJ-8GEYJ5R1V
R103	Resistor, 50 Ω	Richardson	C8A50Z4A
U1	Hybrid coupler	Anaren	X3C21P1-04S
Output			
C201, C202, C203, C204, C205, C206, C207, C208, C209, C210, C211, C212, C215, C216, C224, C217, C218, C225	Capacitor, 10 μ F	Taiyo Yuden	UMK325C7106MM-T
C213, C219	Capacitor, 220 μ F	Panasonic Electronic Components	ECA-2AHG221
C214, C226	Capacitor, 220 μ F	Panasonic Electronic Components	EEE-FP1V221AP
C220	Capacitor, 0.4 pF	ATC	ATC100A0R4CW150XB
C221	Capacitor, 0.2 pF	ATC	ATC100A0R2CW150XB
C222, C227	Capacitor, 20 pF	ATC	ATC100A200JW150XB
C223, C228, C229	Capacitor, 18 pF	ATC	ATC100A180JW150XB

Pinout Diagram (top view)

Lead connections for PXAC213308FV

Package Outline Specifications



Find the latest and most complete information about products and packaging at the Infineon Internet page <http://www.infineon.com/rfpower>

Revision History


Revision	Date	Data Sheet Type	Page	Subjects (major changes since last revision)
01	2015-07-23	Advance	All	Data Sheet reflects advance specification for product development
02	2016-05-04	Production	All	Data Sheet reflects released product specification

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all?
Your feedback will help us to continuously improve the quality of this document.
Please send your proposal (including a reference to this document) to:

highpowerRF@infineon.com

To request other information, contact us at:
+1 877 465 3667 (1-877-GO-LDMOS) USA
or +1 408 776 0600 International



Edition 2016-03-16

**Published by
Infineon Technologies AG
85579 Neubiberg, Germany**

**© 2014 Infineon Technologies AG
All Rights Reserved.**

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com/rfpower).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.