



**Please note that Cypress is an Infineon Technologies Company.**

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

**Continuity of document content**

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

**Continuity of ordering part numbers**

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

# Cypress Semiconductor Product Qualification Report

**QTP# 062201 VERSION\*A**  
**June, 2014**

<b>MoBL ADM DUAL PORT STATIC RAM FAMILY R52LD-3 TECHNOLOGY, FAB4</b>	
<b>CYDMX256A16 CYDMX128A16 CYDMX064A16</b>	<b>4K/8K/16K x 16 MoBL® ADM Asynchronous Dual-Port Static RAM</b>

**FOR ANY QUESTIONS ON THIS REPORT, PLEASE CONTACT**  
[reliability@cypress.com](mailto:reliability@cypress.com) or via a CYLINK CRM CASE

**Prepared By:**  
Josephine Pineda  
Reliability Engineer

**Reviewed By:**  
Zhaomin Ji  
Reliability Manager

**Approved By:**  
Richard Oshiro  
Reliability Director

## PRODUCT QUALIFICATION HISTORY

<b>QUAL REPORT</b>	<b>DESCRIPTION OF QUALIFICATION PURPOSE</b>	<b>DATE COMP.</b>
99075	New Technology R52LD-3 / New Slow Low Power MoBL SRAM, CY62137V	Apr 99
052103	Qualify 256K Dual Port (Split Voltage) Device Family, R52LD3 Technology from Fab4	Nov 05
062201	Qualification of Device 7C02638A (MoBL ADM Dual Port) in R52LD-3 Technology at Fab 4	Sep 06

<b>PRODUCT DESCRIPTION (for qualification)</b>	
Qualification Purpose: To qualify 3 <sup>rd</sup> Generation MoBL DP ADM on existing package and qualified technology, R52LD-3.	
Marketing Part #:	CYDMX256A16, CYDMX128A08, CYDMX064A16
Device Description:	1.8/2.5/3V 256K/128K/64K (16K/8K/4K x 16) MoBL ADMux Dual port
Cypress Division:	Cypress Semiconductor Corporation – Data Communication Division
Overall Die (or Mask) REV:	Rev. A
What ID markings on Die:	7C02638A

<b>TECHNOLOGY/FAB PROCESS DESCRIPTION – R52LD3</b>			
Number of Metal Layers:	2	Metal Composition:	Metal 1: 500 Å-TiW/6000 Å Al-Cu/500 Å TiW Metal 2: 300 Å-Ti/8000 Å Al-Cu/300 Å TiW
Passivation Type and Materials:	1,000Å TEOS + 9,000Å SiN		
Free Phosphorus contents in top glass layer (%):	0%		
Die Coating(s), if used:	N/A		
Number of Transistors in Device:	2932342		
Number of Gates in Device:	733086		
Generic Process Technology/Design Rule ( μ-drawn):	R52 TDR (01-30065), 0.25um Technology		
Gate Oxide Material/Thickness (MOS):	55Å		
Name/Location of Die Fab (prime) Facility:	Cypress Semiconductor – Bloomington Minnesota		
Die Fab Line ID/Wafer Process ID:	7C02638A		

### PACKAGE AVAILABILITY

<b>PACKAGE</b>	<b>ASSEMBLY FACILITY SITE</b>
<b>100-Ball VFBGA</b>	ASE Taiwan (TAIWN-G), CML-RA

**Note: Package Qualification details upon request.**

<b>MAJOR PACKAGE INFORMATION USED IN THIS QUALIFICATION</b>	
<b>Package Designation:</b>	BZ100
<b>Package Outline, Type, or Name:</b>	100-Ball, Very Fine Ball Grid Array (VFBGA)
<b>Mold Compound Name/Manufacturer:</b>	KE-G2270
<b>Mold Compound Flammability Rating:</b>	V-O per UL94
<b>Oxygen Rating Index:</b>	N/A
<b>Substrate Material:</b>	CCL-HL832NX
<b>Lead Finish, Composition / Thickness:</b>	SnAgCu
<b>Die Backside Preparation Method/Metallization:</b>	Backgrind
<b>Die Separation Method:</b>	100%
<b>Die Attach Supplier:</b>	Ablestik
<b>Die Attach Material:</b>	2025D
<b>Die Attach Method:</b>	Epoxy
<b>Bond Diagram Designation:</b>	001-08055
<b>Wire Bond Method:</b>	Thermosonic
<b>Wire Material/Size:</b>	Au, 0.8mil
<b>Thermal Resistance Theta JA and JC °C/W:</b>	44.21 , 19
<b>Package Cross Section Yes/No:</b>	N/A
<b>Assembly Process Flow:</b>	001-06964
<b>Name/Location of Assembly (prime) facility:</b>	ASE Taiwan (TAIWN-G)

<b>ELECTRICAL TEST / FINISH DESCRIPTION</b>	
<b>Test Location:</b>	CML-R
<b>Fault Coverage:</b>	100%

**Note:** Please contact a Cypress Representative for other packages availability.

**RELIABILITY TESTS PERFORMED PER SPECIFICATION REQUIREMENTS**

<b>Stress/Test</b>	<b>Test Condition (Temp/Bias)</b>	<b>Result P/F</b>
Alpha Particle Emission	0.001 CPH/Cm <sup>2</sup>	P
Data Retention (Hermetic)	250 °C, non-biased	P
Data Retention (Plastic)	150 °C, non-biased	P
Electrostatic Discharge Charge Device Model (ESD-CDM)	500V JESD22-C101	P
Electrostatic Discharge Human Body Model (ESD-HBM)	2,200V JEDEC EIA/JESD22-A114	P
High Accelerated Saturation Test (HAST)	JEDEC STD 22-A110: 140 °C, 3.63V, 85%RH  Precondition: JESD22 Moisture Sensitivity Level (192 Hrs., 30°C, 60% RH, 260°C Reflow)	P
High Temperature Operating Life Early Failure Rate	Dynamic Operating Condition, Vcc Max=3.45V, 125 °C Dynamic Operating Condition, Vcc Max=3.45V, 150 °C Dynamic Operating Condition, Vcc Max=3.8V, 150 °C JESD22-A108	P
High Temperature Operating Life Latent Failure Rate	Dynamic Operating Condition, Vcc Max=3.45V, 125 °C Dynamic Operating Condition, Vcc Max=3.45V, 150 °C Dynamic Operating Condition, Vcc Max=3.8V, 150 °C JESD22-A108	P
High Temperature Steady State Life	Static Operating Condition, Vcc Max = 3.63V, 150 °C JESD22-A108	P
High Temperature Storage	JESD22-A103:165 °C, no bias	P
Long Life Verification	Dynamic Operating Condition, Vcc Max = 3.8V, 150 °C JESD22-A108	P
Low Temperature Operating Life	Dynamic Operating Condition, Vcc = 3.8V, -30 °C, f = 8 MHz JESD22-A108	P
Pressure Cooker	JESD22-A102, 121 °C, 100%RH, 15 PSIG Precondition: JESD22 Moisture Sensitivity Level (192 Hrs., 30°C, 60% RH, 260C Reflow)	P
Static Latch-up	125C, ± 200mA  In accordance with JEDEC 17	P
Temperature Cycle	MIL-STD-883, Method 1010, Condition C, -65 °C to 150 °C Precondition: JESD22 Moisture Sensitivity Level (192 Hrs., 30°C, 60% RH, 260C Reflow)	P
Thermal Series	MIL-STD-883-5005, D3	P

### RELIABILITY FAILURE RATE SUMMARY

Stress/Test	Device Tested/ Device Hours	# Fail	Activation Energy	Acceleration Factor <sup>3</sup>	Failure Rate
High Temperature Operating Life Early Failure Rate	1078 Devices	0	N/A	N/A	0 PPM
High Temperature Operating Life <sup>1,2</sup> Long Term Failure Rate	400,500 HRs	1	0.7	170	30 FITs

<sup>1</sup> Assuming an ambient temperature of 55 °C and a junction temperature rise of 15 °C.

<sup>2</sup> Chi-squared 60% estimations used to calculate the failure rate.

<sup>3</sup> Thermal Acceleration Factor is calculated from the Arrhenius equation

$$AF = \exp \left[ \frac{E_A}{k} \left[ \frac{1}{T_2} - \frac{1}{T_1} \right] \right]$$

where:

$E_A$  =The Activation Energy of the defect mechanism.

$k$  = Boltzmann's constant =  $8.62 \times 10^{-5}$  eV/Kelvin.

$T_1$  is the junction temperature of the device under stress and  $T_2$  is the junction temperature of the device at use conditions.



## Reliability Test Data

QTP #: 99075

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
<b>STRESS: ESD-CHARGE DEVICE MODEL, 500V</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	COMP	3	0	
CY62137V-ZSIB	4851023	619907600	CSPI-R	COMP	3	0	
<b>STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE (150C, 3.8V, &gt;Vcc Max)</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	48	1505	0	
CY62137V-ZSIB	4902501	619905577	CSPI-R	48	1504	0	
<b>STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-LATENT FAILURE RATE (150C, 3.8V, &gt;Vcc Max)</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	80	405	0	
CY62137V-ZSIB	4852210	619903364	CSPI-R	500	405	1	UNKNOWN
CY62137V-ZSIB	4902501	619905577	CSPI-R	80	396	0	
CY62137V-ZSIB	4902501	619905577	CSPI-R	500	396	0	
<b>STRESS: LONG LIFE VERIFICATION, (150C, 3.8V, &gt;Vcc Max)</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	1000	404	0	
<b>STRESS: HIGH TEMP DYNAMIC STEADY STATE LIFE TEST, (150C, 3.63V, &gt;Vcc Max)</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	80	80	0	
CY62137V-ZSIB	4852210	619903364	CSPI-R	168	80	0	
<b>STRESS: LOW TEMPERATURE OPERATING LIFE, (-30C, 3.8V, 8 MHZ)</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	500	45	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-B, 2,200V</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	COMP	3	0	
CY62137V-ZSIB	4851023	619907600	CSPI-R	COMP	3	0	
<b>STRESS: HIGH TEMPERATURE STORAGE, 165C, no bias</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	336	47	0	
CY62137V-ZSIB	4852210	619903364	CSPI-R	1000	47	0	
CY62137V-ZSIB	4902501	619905577	CSPI-R	336	48	0	
<b>STRESS: TC CONDITION C, -65C TO 150C, PRE COND 192 HRS 30C/60% RH, MSL3</b>							
CY62137V-ZSIB	4852210	619903364	CSPI-R	300	48	0	
CY62137V-ZSIB	4852210	619903364	CSPI-R	1000	48	0	
CY62137V-ZSIB	4902501	619905577	CSPI-R	300	48	0	
CY62137V-ZSIB	4902501	619905577	CSPI-R	1000	48	0	





## Reliability Test Data

QTP #: 99075

<i>Device</i>	<i>Fab Lot #</i>	<i>Assy Lot #</i>	<i>Assy Loc</i>	<i>Duration</i>	<i>Samp</i>	<i>Rej</i>	<i>Failure Mechanism</i>
---------------	------------------	-------------------	-----------------	-----------------	-------------	------------	--------------------------

**STRESS: PRESSURE COOKER TEST (121C, 100%RH), PRE COND 192HRS 30C/60%RH, MSL3**

CY62137V-ZSIB	4852210	619903364	CSPI-R	168	48	0	
---------------	---------	-----------	--------	-----	----	---	--

**STRESS: HI-ACCEL SATURATION TEST, (140C, 3.63V), 85%RH, PRE COND 192 HR 30C/60%RH, MSL3**

CY62137V-ZSIB	4852210	619903364	CSPI-R	128	48	0	
---------------	---------	-----------	--------	-----	----	---	--

CY62137V-ZSIB	4852210	619903364	CSPI-R	256	48	0	
---------------	---------	-----------	--------	-----	----	---	--

CY62137V-ZSIB	4902501	619905577	CSPI-R	128	48	0	
---------------	---------	-----------	--------	-----	----	---	--

CY62137V-ZSIB	4902501	619905577	CSPI-R	256	48	0	
---------------	---------	-----------	--------	-----	----	---	--

CY62137V-ZSIB	4903568	619907944	CSPI-R	128	48	0	
---------------	---------	-----------	--------	-----	----	---	--



## Reliability Test Data

QTP #: 052103

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
<b>STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 150C, 3.45V, Vcc Max</b>							
CYDC256B16 (7C02628A)	4531145	610540035	TAIWN-G	48	330	0	
CYDC256B16 (7C02628A)	4531145	610540036	TAIWN-G	48	328	0	
CYDC256B16 (7C02628A)	4531145	610540037	TAIWN-G	48	332	0	
<b>STRESS: ESD-CHARGE DEVICE MODEL, 500V</b>							
CYDM256B16 (7C02628A)	4531145	610539449	TAIWN-G	COMP	9	0	
CYDC256B16 (7C02628A)	4531145	610540035/6/7	TAIWN-G	COMP	9	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-B, 2,200V</b>							
CYDM256B16 (7C02628A)	4531145	610539449	TAIWN-G	COMP	9	0	
CYDC256B16 (7C02628A)	4531145	610540035/6/7	TAIWN-G	COMP	9	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER MIL STD 883, METHOD 3015, 2,200V</b>							
CYDM256B16 (7C02628A)	4531145	610539449	TAIWN-G	COMP	3	0	
CYDC256B16 (7C02628A)	4531145	610540035/6/7	TAIWN-G	COMP	3	0	
<b>STRESS: STATIC LATCH-UP TESTING (125C, 7.0V, +/-300mA)</b>							
CYDM256B16 (7C02628A)	4531145	610539449	TAIWN-G	COMP	3	0	
<b>STRESS: PRESSURE COOKER TEST, 121C, 100%RH, PRE COND 192 HR 30C/60%RH, MSL3</b>							
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	168	50	0	
<b>STRESS: TC COND. C -65C TO 150C, PRE COND 192 HRS 30C/60%RH, MSL3</b>							
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	300	50	0	
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	500	50	0	
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	1000	50	0	



## Reliability Test Data

QTP #: 062201

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
<b>STRESS: ALPHA PARTICLE EMISSION</b>							
CYDC256B16 (7C02628A)	4522569	610543349	TAIWN-G	COMP	5	0	
<b>STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 150C, 3.45V, Vcc Max</b>							
CYDCX256A16 (7C02638A)	4622252	610647256	CML-R	48	485	0	
CYDCX256A16 (7C02638A)	4622252	610647257	CML-R	48	400	0	
<b>STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 125C, 3.45V, Vcc Max</b>							
CYDMX256A16 (7C02638A)	4622252	610646577	TAIWN-G	96	193	0	
<b>STRESS: ESD-CHARGE DEVICE MODEL, 500V</b>							
CYDMX256A16 (7C02638A)	4622252	610646577	TAIWN-G	COMP	9	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-B, 2,200V</b>							
CYDMX256A16 (7C02638A)	4622252	610646577	TAIWN-G	COMP	9	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER MIL STD 883, METHOD 3015, 2,200V</b>							
CYDMX256A16 (7C02638A)	4622252	610646577	TAIWN-G	COMP	3	0	
<b>STRESS: STATIC LATCH-UP TESTING (125C, 5.4V, +/-200mA)</b>							
CYDMX256A16 (7C02638A)	4622252	610646577	TAIWN-G	COMP	3	0	
<b>STRESS: PRESSURE COOKER TEST, 121C, 100%RH, PRE COND 192 HR 30C/60%RH, MSL3</b>							
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	168	50	0	
<b>STRESS: TC COND. C -65C TO 150C, PRE COND 192 HRS 30C/60%RH, MSL3</b>							
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	300	50	0	
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	500	50	0	
CYDM256A16 (7C02618A)	4503160	610510254	TAIWN-G	1000	50	0	



## Document History Page

Document Title: QTP # 062201 : MoBL ADM DUAL-PORT RAM, (CYDMX064/128/256xxx Product Family ),  
R52LD-3 TECHNOLOGY, FAB 4  
Document Number: 001-88008

Rev.	ECN No.	Orig. of Change	Description of Change
**	4033621	ILZ	Initial Spec Release Qualification report published on Cypress.com is documented on memo HGA-168 and not in spec format. Initiated spec for QTP 062201 and all data from memo# HGA-168 was transferred to qualification report spec template. Deleted package qualification details on package qualification history table. Deleted Cypress reference Spec and replaced with Industry Standards Updated package availability based on current qualified test & assembly site.
*A	4417735	JYF	Sunset review: Updated QTP title page and Reliability Tests Performed table (ESD-HBM, HAST, EFR/LFR, HTSSL, HTS, LLV, LTOL, PCT) for template alignment.

Distribution: WEB

Posting: None