

Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

Cypress Semiconductor Product Qualification Report

**QTP# 095301
May 2013**

32 Meg Asynchronous SRAM Family C9FD-3R Technology, Fab4	
CY7C1071DV33	32-Mbit (2M x 16) Static RAM
CY7C1079DV33	32-Mbit (4M x 8) Static RAM

CYPRESS TECHNICAL CONTACT FOR QUALIFICATION DATA:

Zhaomin Ji
Principal Reliability Engineer
(408) 432-7021

Mira Ben-Tzur
Quality Engineering Director
(408) 943-2675

PRODUCT QUALIFICATION HISTORY

Qual Report	Description of Qualification Purpose	Date Comp
052207	C9FD-3R, Fab 4 New Process using CY7C104*D (4Meg Fast Synchronous SRAM) Product Family	Mar 06
080602	Qualify 16 Meg Fast Async Rev.B Mask DDLIM Fix	Jun 08
095301	Qualify C9 32M - Stack Die of C9 16M device	Mar 10

PRODUCT DESCRIPTION (for qualification)	
Purpose: Qualify C932M - stack die of C916M device	
Marketing Part #:	CY7C1071DV33, CY7C1079DV33
Device Description:	32M Asynchronous SRAM
Cypress Division:	Cypress Semiconductor Corporation –Memory Image Division (MID)

TECHNOLOGY/FAB PROCESS DESCRIPTION – C9FD-3R			
Number of Metal Layers:	2	Metal Composition:	Metal 1: 100Å Ti / 3200Å Al / 300Å TiW Metal 2: 150Å Ti / 8000Å Al / 300Å TiW
Passivation Type and Materials:	Si ₂ N ₃ 7000Å & SiO ₂ 700Å (on metal2), Si ₂ N ₃ 9000Å & SiO ₂ 1000Å (on flat)		
Generic Process Technology/Design Rule (□-drawn):	C9FD-3R/0.90µm		
Gate Oxide Material/Thickness (MOS):	20.5Å (LV) & 58Å		
Name/Location of Die Fab (prime) Facility:	Cypress Semiconductor -- Bloomington, MN		
Die Fab Line ID/Wafer Process ID:	Fab4/C9FD-3R		

PACKAGE AVAILABILITY

PACKAGE	ASSEMBLY SITE FACILITY
54-Lead TSOPII	ASE-Taiwan (G)
119 BGA	ASE-Taiwan (G)
48 BGA	ASE-Taiwan (G)

Note: Package Qualification details upon request

MAJOR PACKAGE INFORMATION USED IN THIS QUALIFICATION	
Package Designation:	BK48J
Package Outline, Type, or Name:	48-Lead Ball Grid Array (BGA)
Mold Compound Name/Manufacturer:	KE-G-2270
Mold Compound Flammability Rating:	UL-94
Mold Compound Alpha Emission Rate:	0.001c/cm2-h
Oxygen Rating Index:	>28%
Lead Finish, Composition / Thickness:	SAC405
Substrate Material:	A10856
Die Backside Preparation Method/Metallization:	Backgrind
Die Separation Method:	100% Saw Through
Die Attach Supplier:	Ablestik /Hitachi
Die Attach Material:	Ablestik 2025D / Hitachi FH-900
Die Attach Method:	Tape Film
Bond Diagram Designation:	001-51846
Wire Bond Method:	Thermosonic
Wire Material/Size:	Au, 0.8mil
Thermal Resistance Theta JA °C/W:	59.06CW
Package Cross Section Yes/No:	Yes
Assembly Process Flow:	001-56462
Name/Location of Assembly (prime) facility:	ASE-Taiwan (G)
MSL Level	3
Reflow Profile	260C

ELECTRICAL TEST / FINISH DESCRIPTION	
Test Location:	CML-R

Note: Please contact a Cypress Representative for other packages availability

RELIABILITY TESTS PERFORMED PER SPECIFICATION REQUIREMENT

Stress/Test	Test Condition (Temp/Bias)	Result P/F
High Temperature Operating Life Early Failure Rate	Dynamic Operating Condition, Vcc Max = 3.77V, 150°C, JESD22-A108 Dynamic Operating Condition, Vcc Max = 3.77V, 125°C, JESD22-A108	P
High Temperature Operating Life Latent Failure Rate	Dynamic Operating Condition, Vcc Max = 3.77V, 150°C, JESD22-A108 Dynamic Operating Condition, Vcc Max = 3.77V, 125°C, JESD22-A108	P
Long Life Verification	Dynamic Operating Condition, Vcc = 3.77V, 150°C, JESD22-A108	P
High Temperature Steady State Life	Static Operating Condition, Vcc Max = 3.77V, 150°C, JESD22-A108 Static Operating Condition, Vcc Max = 3.77V, 150°C, JESD22-A108	P
High Accelerated Saturation Test (HAST)	JEDEC STD 22-A110: 130°C, 3.63V, 85%RH Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30°C/60%RH+3IR-Reflow, 260°C +0, -5°C 130°C, 3.65V, 85%RH Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30°C/60%RH+3IR-Reflow, 260°C +0, -5°C	P
Temperature Cycle	MIL-STD-883C, Method 1010, Condition C, -65°C to 150°C Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30°C/60%RH+3IR-Reflow, 260°C +0, -5°C	P
Pressure Cooker	JESD22-A102: 121°C, 100%RH, 15 Psig Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30°C/60%RH+3IR-Reflow, 260°C +0, -5°C	P
High Temperature Storage	JESD22-A103: 150°C, no bias	P
Electrostatic Discharge Human Body Model (ESD-HBM)	2,200V MIL-STD-883, Method 3015.7	P
Electrostatic Discharge Human Body Model (ESD-HBM)	2,200V JEDEC EIA/JESD22-A114	P
Electrostatic Discharge Charge Device Model (ESD-CDM)	500V JESD22-C101	P
Current Density	Meets the Technology Device Level Reliability Specifications	P
Age Bond Strength	200°C, 4HRS MIL-STD-883, Method 883-2011	P
Acoustic Microscopy	J-STD-020 Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30°C/60%RH+3IR-Reflow, 260°C +0, -5°C	P
Static Latch up	125C, \pm 200/200mA 125C, 5.4V \pm 140mA JESD78	P

RELIABILITY FAILURE RATE SUMMARY

Stress/Test	Device Tested/ Device Hours	# Fails	Activation Energy	Thermal AF ³	Failure Rate
High Temperature Operating Life Early Failure Rate	2994 Devices	0	N/A	N/A	0 PPM
High Temperature Operating Life ^{1,2} Long Term Failure Rate	2,683,300 DHRs	6*	0.7	170	18 FIT

¹ Assuming an ambient temperature of 55°C and a junction temperature rise of 15°C.

² Chi-squared 60% estimations used to calculate the failure rate..

³ Thermal Acceleration Factor is calculated from the Arrhenius equation

$$AF = \exp \left[\frac{E_A}{k} \left[\frac{1}{T_2} - \frac{1}{T_1} \right] \right]$$

where:

E_A =The Activation Energy of the defect mechanism.

k = Boltzmann's constant = 8.62x10⁻⁵ eV/Kelvin.

T₁ is the junction temperature of the device under stress and T₂ is the junction temperature of the device at use conditions.

* Failures are fixed with reference corrective action (CAR) # 200613035.

Reliability Test Data

QTP #: 052207

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
STRESS: ACOUSTIC-MSL3							
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	COMP	15	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	COMP	15	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	COMP	15	0	
STRESS: AGE BOND STRENGTH							
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	COMP	10	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	COMP	10	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	COMP	10	0	
STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 150C, 3.77V, Vcc Max							
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	48	1551	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	48	1518	1	LI DEFFECT
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	48	3314	1	NON-VISUAL
STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-LATENT FAILURE RATE, 150C, 3.77V, Vcc Max							
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	80	1544	0	
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	500	1542	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	80	1516	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	500	1514	3	SINGLE BIT & BLOCKED CONTACT
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	80	1517	1	LOST REJECT
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	500	1511	2	SINGLE BIT
STRESS: LONG LIFE VERIFICATION, 150C, 3.77V, Vcc Max							
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	1000	400	0	
STRESS: HIGH TEMPERATURE STEADY STATE LIFE, 150C, 3.77V, Vcc Max							
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	80	80	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	168	80	0	
STRESS: HIGH TEMPERATURE STORAGE							
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	500	50	0	
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	1000	50	0	

Reliability Test Data

QTP #: 052207

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
--------	-----------	------------	----------	----------	------	-----	-------------------

STRESS: ESD-CHARGE DEVICE MODEL, 500V

CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	COMP	9	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	COMP	9	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	COMP	9	0	
CY7C1041D (7C1541N)	4538630	610610603	CML-R	COMP	9	0	
CY7C1049D (7C1549N)	4538680	610611050	CML-R	COMP	9	0	
CY7C1046D (7C1346N)	4538680	610610606	CML-R	COMP	9	0	

STRESS: ESD-HUMAN BODY CIRCUIT PER JEDEC EIA/JESD22-A114-B, 2,200V

CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	COMP	9	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	COMP	9	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	COMP	9	0	
CY7C1041D (7C1541N)	4530733	610607231	CML-R	COMP	9	0	
CY7C1049D (7C1549N)	4538680	610611050	CML-R	COMP	9	0	
CY7C1046D (7C1346N)	4538680	610610606	CML-R	COMP	9	0	
CY7C1049DV33 (7C1349N)	4538680	610611051	CML-R	COMP	9	0	

STRESS: ESD-HUMAN BODY CIRCUIT PER MIL STD 883, METHOD 3015, 2,200V

CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	COMP	3	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	COMP	3	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	COMP	3	0	
CY7C1041D (7C1541N)	4530733	610607231	CML-R	COMP	3	0	
CY7C1049D (7C1549N)	4538680	610611050	CML-R	COMP	3	0	
CY7C1046D (7C1346N)	4538680	610610606	CML-R	COMP	3	0	
CY7C1049DV33 (7C1349N)	4538680	610611051	CML-R	COMP	3	0	

STRESS: STATIC LATCH-UP TESTING, 125C, 6.5V, +/-200mA

CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	COMP	3	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	COMP	3	0	
CY7C1046DV33 (7C1346N)	4538680	610610605	CML-R	COMP	3	0	
CY7C1049DV33 (7C1349N)	4538680	610611051	CML-R	COMP	3	0	

STRESS: STATIC LATCH-UP TESTING, 125C, 6.5V, +/-300mA

CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	COMP	3	0	
------------------------	---------	-----------	-------	------	---	---	--

Company Confidential

A printed copy of this document is considered uncontrolled. Refer to online copy for latest revision.

Reliability Test Data

QTP #: 052207

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
--------	-----------	------------	----------	----------	------	-----	-------------------

STRESS: STATIC LATCH-UP TESTING, 125C, 8.5V, +/-200mA

CY7C1049D (7C1549N)	4538680	610611050	CML-R	COMP	3	0	
CY7C1046D (7C1346N)	4538680	610610606	CML-R	COMP	3	0	
CY7C1041D (7C1541N)	4552229	610617290	CML-R	COMP	3	0	

STRESS: HI-ACCEL SATURATION TEST, 130C, 85%RH, 3.63V, PRE COND 192 HR 30C/60%RH, MSL3

CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	128	45	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	128	45	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	128	45	0	

STRESS: PRESSURE COOKER TEST, 121C, 100%RH, 15 Psig, PRE COND 192 HR 30C/60%RH, MSL3

CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	168	46	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	168	50	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	288	50	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	168	50	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	288	50	0	

STRESS: TC COND. C -65C TO 150C, PRE COND 192 HRS 30C/60%RH, MSL3

CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	300	45	0	
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	500	45	0	
CY7C1041DV33 (7C1341N)	4533793	610553668	CML-R	1000	45	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	300	50	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	500	50	0	
CY7C1041DV33 (7C1341N)	4536828	610558451	CML-R	1000	50	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	300	50	0	
CY7C1041DV33 (7C1341N)	4530733	610607229	CML-R	500	50	0	

Reliability Test Data

QTP #: 080602

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
--------	-----------	------------	----------	----------	------	-----	-------------------

STRESS: ACOUSTIC-MSL3

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	COMP	15	0	
CY7C1061DV33 (7C1061NC)	4646309	610706778	TAIWAN-G	COMP	15	0	
CY7C1062DV33 (7C1062NC)	4648234	610730021	TAIWAN-G	COMP	15	0	

STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 125C, 3.77V, Vcc Max

CY7C1061DV33 (7C1061NC)	4801414	610809978N	TAIWAN-G	96	1415	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485	TAIWAN-G	96	918	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485N	TAIWAN-G	96	217	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485N1	TAIWAN-G	96	444	0	

STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-LATENT FAILURE RATE, 125C, 3.77V, Vcc Max

CY7C1061DV33 (7C1061NC)	4801414	610809978N	TAIWAN-G	168	199	0	
CY7C1061DV33 (7C1061NC)	4801414	610809978N	TAIWAN-G	1000	199	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485R222	TAIWAN-G	168	200	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485R222	TAIWAN-G	1000	200	0	

STRESS: ESD-CHARGE DEVICE MODEL, 500V

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	COMP	9	0	
CY7C1062DV33 (7C1062NC)	4713292	0	TAIWAN-G	COMP	9	0	

STRESS: ESD-HUMAN BODY CIRCUIT PER JEDEC EIA/JESD22-A114-E, 2,200V

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	COMP	8	0	
CY7C1062DV33 (7C1062NC)	4713292	0	TAIWAN-G	COMP	8	0	

STRESS: HI-ACCEL SATURATION TEST, 130C, 85%RH, 3.65V, PRE COND 192 HR 30C/60%RH, MSL3

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	128	45	0	
-------------------------	---------	-----------	----------	-----	----	---	--

STRESS: HIGH TEMPERATURE STEADY STATE LIFE, 150C, 3.77V, Vcc Max

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	168	80	0	
-------------------------	---------	-----------	----------	-----	----	---	--

STRESS: PRESSURE COOKER TEST, 121C, 100%RH, 15 Psig, PRE COND 192 HR 30C/60%RH, MSL3

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	168	45	0	
-------------------------	---------	-----------	----------	-----	----	---	--

STRESS: STATIC LATCH-UP TESTING, 125C, 6.5V, +/-200mA

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	COMP	3	0	
-------------------------	---------	-----------	----------	------	---	---	--

Reliability Test Data

QTP #: 080602

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
---------------	------------------	-------------------	-----------------	-----------------	-------------	------------	--------------------------

STRESS: TC COND. C -65C TO 150C, PRE COND 192 HRS 30C/60%RH, MSL3

CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	300	45	0	
CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	500	44	0	
CY7C1061DV33 (7C1061NC)	4641622	610673799	TAIWAN-G	1000	44	0	
CY7C1061DV33 (7C1061NC)	4646309	610706778	TAIWAN-G	300	45	0	
CY7C1062DV33 (7C1062NC)	4648234	610730021	TAIWAN-G	300	50	0	
CY7C1062DV33 (7C1062NC)	4648234	610730021	TAIWAN-G	500	50	0	
CY7C1062DV33 (7C1062NC)	4648234	610730021	TAIWAN-G	1000	45	0	

Reliability Test Data

QTP #: 095301

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
--------	-----------	------------	----------	----------	------	-----	-------------------

STRESS: ACOUSTIC, MSL3

CY7C1071DV33 (7C1071NC)	4907587	610927400	TAIWAN-G	COMP	14	0	
CY7C1071DV33 (7C1071NC)	4908217	610927398	TAIWAN-G	COMP	15	0	
CY7C1071DV33 (7C1071NC)	4906129	610927399	TAIWAN-G	COMP	15	0	

STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 125C, 3.77V, Vcc Max

CY7C1061DV33 (7C1061NC)	4801414	610809978N	TAIWAN-G	96	1415	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485	TAIWAN-G	96	1579	0	

STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-LATENT FAILURE RATE, 125C, 3.77V, Vcc Max

CY7C1061DV33 (7C1061NC)	4801414	610809978N	TAIWAN-G	168	199	0	
CY7C1061DV33 (7C1061NC)	4801414	610809978N	TAIWAN-G	1000	199	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485	TAIWAN-G	168	200	0	
CY7C1061DV33 (7C1061NC)	4802871	610814485	TAIWAN-G	1000	200	0	

STRESS: ESD-CHARGE DEVICE MODEL, 500V

CY7C1071DV33 (7C1071NC)	4908217	610927398	TAIWAN-G	COMP	9	0	
-------------------------	---------	-----------	----------	------	---	---	--

STRESS: ESD-HUMAN BODY CIRCUIT PER JEDEC EIA/JESD22-A114-E, 2,200V

CY7C1071DV33 (7C1071NC)	4908217	610927398	TAIWAN-G	COMP	8	0	
-------------------------	---------	-----------	----------	------	---	---	--

STRESS: HI-ACCEL SATURATION TEST, 130C, 85%RH, 3.65V, PRE COND 192 HR 30C/60%RH, MSL3

CY7C1071DV33 (7C1071NC)	4908217	610927398	TAIWAN-G	264	77	0	
-------------------------	---------	-----------	----------	-----	----	---	--

STRESS: STATIC LATCH-UP TESTING, 125C, 5.4V, +/-140mA

CY7C1071DV33 (7C1071NC)	4908217	610927398	TAIWAN-G	COMP	6	0	
-------------------------	---------	-----------	----------	------	---	---	--

STRESS: TC COND. C -65C TO 150C, PRE COND 192 HRS 30C/60%RH, MSL3

CY7C1071DV33 (7C1071NC)	4907587	610927400	TAIWAN-G	500	76	0	
CY7C1071DV33 (7C1071NC)	4907587	610927400	TAIWAN-G	1000	76	0	
CY7C1071DV33 (7C1071NC)	4908217	610927398	TAIWAN-G	500	76	0	
CY7C1071DV33 (7C1071NC)	4908217	610927398	TAIWAN-G	1000	76	0	
CY7C1071DV33 (7C1071NC)	4906129	610927399	TAIWAN-G	500	77	0	
CY7C1071DV33 (7C1071NC)	4906129	610927399	TAIWAN-G	1000	77	0	

Document History Page

Document Title: 095301: 32 MEG ASYNCHRONOUS SRAM FAMILY C9FD-3R TECHNOLOGY, FAB4
Document Number: 001-61392

Rev.	ECN No.	Orig. of Change	Description of Change
**	2927519	HGA	Initial spec release
*A	4005013	NSR	Removed VERSION 1.0 in the title page. Removed reference Cypress specs in reliability tests performed table and added the reference industry standards.

Distribution: WEB

Posting: None