

Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

Cypress Semiconductor Package Qualification Report

**QTP# 104811 VERSION*B
March, 2014**

**28/32-Lead SOJ / 28-Lead SNC (300 mils)
NiPdAu, MSL3, 260°C Reflow
JCET-China (JT)**

FOR ANY QUESTIONS ON THIS REPORT, PLEASE CONTACT
reliability@cypress.com or via a CYLINK CRM CASE

Prepared By:
Josephine Pineda
Reliability Engineer

Reviewed By:
Rene Rodgers
Reliability Manager

Approved By:
Richard Oshiro
Reliability Director

PACKAGE QUALIFICATION HISTORY

QTP Number	Description of Qualification Purpose	Date
104811	Qualify New Assembly Site (JCET) Qual – for SOJ 28L/ 32L, SNC 28L (300 mils body) - Pb-Free (KEG6000, QMI509, 0.9 mil, NiPdAu)	Feb 2011

MAJOR PACKAGE INFORMATION USED IN THIS QUALIFICATION

Package Designation:	SY28 / VZ28 / VZ32
Package Outline, Type, or Name:	28L SNC / 28L/32L SOJ (300 mils)
Mold Compound Name/Manufacturer:	KEG6000 / Kyocera
Mold Compound Flammability Rating:	V-O per UL94
Mold Compound Alpha Emission Rate:	0.002 CPH/cm2
Oxygen Rating Index: >28%	N/A
Lead Frame Designation:	Reduced Metal Pad
Lead Frame Material:	Copper
Substrate Material:	N/A
Lead Finish, Composition / Thickness:	NiPdAu
Die Backside Preparation Method/Metallization:	Backgrind
Die Separation Method:	Wafersaw
Die Attach Supplier:	Henkel
Die Attach Material:	QMI 509
Bond Diagram Designation	001-37239, 10-06668, 001-07499
Wire Bond Method:	Thermosonic
Wire Material/Size:	0.9mil / Au
Thermal Resistance Theta JA °C/W:	11.3 °C/W
Package Cross Section Yes/No:	Yes
Assembly Process Flow:	001-64159
Name/Location of Assembly (prime) facility:	JT-JCET China
MSL LEVEL	3
REFLOW PROFILE	260C

ELECTRICAL TEST / FINISH DESCRIPTION

Test Location:	CML-R
----------------	-------

Note: Please contact a Cypress Representative for other package availability.

RELIABILITY TESTS PERFORMED PER SPECIFICATION REQUIREMENTS

Stress/Test	Test Condition (Temp/Bias)	Result P/F
High Accelerated Saturation Test (HAST)	JEDEC STD 22-A110: 130 °C, 85%RH, 5.5V Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30 °C /60%RH+Reflow, 260 °C +0, -5 °C	P
Pressure Cooker Test	JESD22-A102: 121 °C, 100%RH, 15 PSIG Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30 °C /60%RH+Reflow, 260 °C +0, -5 °C	P
Temperature Cycle	MIL-STD-883, Method 1010, Condition C, -65 °C to 150 °C Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30 °C /60%RH+Reflow, 260 °C +0, -5 °C	P
High Temp Storage	JESD22-A103: 150 °C, no bias	P
Electrostatic Discharge Human Body Model (ESD-HBM)	2200V JEDEC EIA/JESD22-A114	P
Electrostatic Discharge Charge Device Model (ESD-CDM)	500V JESD22-C101	P
Acoustic Microscopy	J-STD-020 Precondition: JESD22 Moisture Sensitivity MSL 3 192 Hrs, 30 °C /60%RH+Reflow, 260 °C +0, -5 °C	P
Ball Shear	JESD22-B116, Cpk : 1.33, Ppk : 1.66	P
Bond Pull	MIL-STD-883 – Method 2011, Cpk : 1.33, Ppk : 1.66	P
Constructional Analysis	Criteria: Meet external and internal characteristics of Cypress package	P
Dye Penetrant Test	Test to determine the existence and extent of cracks, Criteria: No Package Crack	P
Internal Visual	MIL-STD-883-2014	P
Final Visual Inspection	JESD22-B101	P
Lead Integrity	JESD22-B105, MIL STD 883	P
Physical Dimension	MIL-STD-1835, JESD22-B100	P
Thermal Shock	MIL-STD-883, Method 1011, Condition B, -55 °C to 125 °C and JESD22-A106, Condition C, -55 °C to 125 °C	P
Solderability, Steam Aged	J-STD-002, JESD22-B102 95% solder coverage minimum	P
X-Ray	MIL-STD-883 - 2012	P

Reliability Test Data

QTP #: 104811

<i>Device</i>	<i>Fab Lot #</i>	<i>Assy Lot #</i>	<i>Assy Loc</i>	<i>Duration</i>	<i>Samp</i>	<i>Rej</i>	<i>Failure Mechanism</i>
STRESS: ACOUSTIC, MSL3							
CY62256NLL(7C62256NFK)	4038465	611057353	JT-CHINA	COMP	15	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	15	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	15	0	
STRESS: BALL SHEAR							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	30	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	30	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	30	0	
STRESS: BOND PULL							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	30	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	30	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	30	0	
STRESS: CONSTRUCTIONAL ANALYSIS							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	5	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	5	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	5	0	
STRESS: DYE PENETRATION TEST							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	15	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	15	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	15	0	
STRESS: ESD-CHARGE DEVICE MODEL, (500V)							
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	9	0	
STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114, 2,200V							
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	8	0	
STRESS: HI-ACCEL SATURATION TEST, 130C, 5.50V, 85%RH, PRE COND 192 HR 30C/60%RH, MSL3							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	128	76	0	

Reliability Test Data

QTP #: 104811

<i>Device</i>	<i>Fab Lot #</i>	<i>Assy Lot #</i>	<i>Assy Loc</i>	<i>Duration</i>	<i>Samp</i>	<i>Rej</i>	<i>Failure Mechanism</i>
STRESS: HIGH TEMP STORAGE							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	500	80	0	
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	1000	80	0	
STRESS: INTERNAL VISUAL							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	5	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	5	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	5	0	
STRESS: LEAD INTEGRITY							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	5	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	5	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	5	0	
STRESS: PRESSURE COOKER TEST (121C, 100%RH), 15 Psig, PRE COND 192 HR 30C/60%RH (MSL3)							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	168	80	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	168	77	0	
STRESS: PHYSICAL DIMENSION							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	30	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	30	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	30	0	
STRESS: SOLDERABILITY							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	3	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	3	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	3	0	
STRESS: TC COND. C -65C TO 150C, PRE COND 192 HR 30C/60%RH, MSL3							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	500	79	0	
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	1000	79	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	500	77	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	1000	77	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	500	77	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	1000	77	0	

Reliability Test Data

QTP #: 104811

<i>Device</i>	<i>Fab Lot #</i>	<i>Assy Lot #</i>	<i>Assy Loc</i>	<i>Duration</i>	<i>Samp</i>	<i>Rej</i>	<i>Failure Mechanism</i>
STRESS: THERMAL SHOCK							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	200	80	0	
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	1000	80	0	
STRESS: X-RAY							
CY62256NLL (7C62256NFK)	4038465	611057353	JT-CHINA	COMP	15	0	
CY7C1399BN (7C1399SHC)	4027913	611057993	JT-CHINA	COMP	15	0	
CY7C1399BN (7C1399SHC)	4027913	611057351	JT-CHINA	COMP	15	0	

Document History Page

Document Title: QTP 104811: 28/32-Lead SOJ / 28-Lead SNC (300 mils) NiPdAu, MSL3 260C Reflow JCET-China (JT)
Document Number: 001-67408

Rev.	ECN No.	Orig. of Change	Description of Change
**	3157998	NRG	Initial spec release
*A	3186813	NRG	Updated the mold compound and die attach using complete material name.
*B	4310956	JYF	Alignment of QTP title page and Reliability Tests Performed table to standard template.

Distribution: WEB

Posting: None