

**Please note that Cypress is an Infineon Technologies Company.**

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

**Continuity of document content**

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

**Continuity of ordering part numbers**

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

# Cypress Semiconductor Automotive Package Qualification Report

QTP# 105209 VERSION \*A  
April 2014

**Automotive 28L SNC (300 mils)  
NiPdAu, MSL3, 235°C Reflow  
JCET-China (JT)**

**FOR ANY QUESTIONS ON THIS REPORT, PLEASE CONTACT  
[reliability@cypress.com](mailto:reliability@cypress.com) or via a CYLINK CRM CASE**

**Prepared By:**  
Lorena R. Zapanta (ILZ)  
Reliability Engineer

**Reviewed By:**  
Rene Rodgers (RT)  
Reliability Manager

**Approved By:**  
Richard Oshiro(RGO)  
Reliability Director

## PRODUCT QUALIFICATION HISTORY

QTP Number	Description of Qualification Purpose	Date
105208	New Assembly Site (JCET) Qual – Automotive SNC 28ld 300 mils body – <b>Pb-Free</b> (KEG6000, QMI 509, 1.0 mil Wire, NiPdAu)	Feb 2011
105209	New Assembly Site (JCET) Qual – Automotive SNC 28ld 300 mils body – <b>Standard</b> (KEG6000, QMI 509, 1.0 mil Wire, NiPdAu)	Feb 2011

<b>MAJOR PACKAGE INFORMATION USED IN THIS QUALIFICATION</b>	
Package Designation:	SY283
Package Outline, Type, or Name:	28L SNC
Mold Compound Name/Manufacturer:	KEG6000 / Kyocera
Mold Compound Flammability Rating:	V-O per UL94
Mold Compound Alpha Emission Rate:	0.002 CPH/cm2
Oxygen Rating Index: >28%	N/A
Lead Frame Designation:	Full Metal Pad
Lead Frame Material:	Copper
Substrate Material:	N/A
Lead Finish, Composition / Thickness:	NiPdAu
Die Backside Preparation Method/Metallization:	Backgrind
Die Separation Method:	Wafersaw
Die Attach Supplier:	Henkel
Die Attach Material:	QMI509
Bond Diagram Designation	10-06638, 10-06639
Wire Bond Method:	Thermosonic
Wire Material/Size:	1.0 mil / Au
Thermal Resistance Theta JA °C/W:	N/A
Package Cross Section Yes/No:	Yes
Assembly Process Flow:	001-67698
Name/Location of Assembly (prime) facility:	JT-JCET China
MSL LEVEL	3
REFLOW PROFILE	235C

<b>ELECTRICAL TEST / FINISH DESCRIPTION</b>	
Test Location:	CML-R

**Note:** Please contact a Cypress Representative for other package availability.

## RELIABILITY TESTS PERFORMED PER SPECIFICATION REQUIREMENTS

Stress/Test	Test Condition (Temp/Bias)	Result P/F
Electrostatic Discharge Human Body Model (ESD-HBM)	AEC-Q100-002	P
Electrostatic Discharge Charge Device Model (ESD-CDM)	AEC-Q100-011	P
Latch-up Sensitivity	AEC-Q100-004	P
High Temperature Operating Life Early Failure Rate	AEC-Q100-008 and JESD22-A108, 150 C Dynamic Operating Condition, Vcc = 5.75V	P
High Temperature Operating Life Latent Failure Rate	JESD22-A108, 150 C /125C Dynamic Operating Condition, Vcc = 5.75V, 150C	P
High Accelerated Saturation Test (HAST)	JESD22-A110, 130 C, 85%RH, 5.50V Precondition: JESD22-A113 Moisture Sensitivity Level (192 Hrs., 30 C°, 60% RH)	P
High Temperature Storage Life Test	JESD22-A103, 150 C	P
Temperature Cycle	JESD22-A104, -65 C to 150 C Precondition: JESD22-A113 Moisture Sensitivity Level (192 Hrs., 30 C°, 60% RH)	P
Post Temperature Cycle Wire Bond Pull	Mil-Std 883, Method 2011	P
Pressure Cooker Test	JESD22-A102, 121 C, 100%RH, 15 PSIG Precondition: JESD22-A113 Moisture Sensitivity Level (192 Hrs., 30 C°, 60% RH)	P
Wire Bond Shear	AEC Q100-001	P
Wire Bond Pull	Mil-Std 883, Method 2011	P
Solderability	JESD22-B102	P
Physical Dimensions	JESD22B100 and B108	P
Electrical Distributions	AEC Q100-009	P
Lead Integrity	JESD22-B105	P



## Reliability Test Data

**QTP #: 105208**

<b>Device</b>	<b>Fab Lot #</b>	<b>Assy Lot #</b>	<b>Assy Loc</b>	<b>Duration</b>	<b>Samp</b>	<b>Rej</b>	<b>Failure Mechanism</b>
<b>STRESS: ACOUSTIC, MSL3</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	22	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	22	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	22	0	
<b>STRESS: BOND SHEAR</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	30	0	
<b>STRESS: BOND PULL</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	30	0	
<b>STRESS: CONSTRUCTIONAL ANALYSIS</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	5	0	
<b>STRESS: DYE PENETRATION TEST</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	15	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	15	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	15	0	
<b>STRESS: ESD-CHARGE DEVICE MODEL, 250V</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	3	0	
<b>STRESS: ESD-CHARGE DEVICE MODEL, 500V</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	3	0	
<b>STRESS: ESD-CHARGE DEVICE MODEL, 750V</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	3	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (500V)</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	3	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (1000V)</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	3	0	
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (1500V)</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	3	0	

## Reliability Test Data

**QTP #: 105208**

<b>Device</b>	<b>Fab Lot #</b>	<b>Assy Lot #</b>	<b>Assy Loc</b>	<b>Duration</b>	<b>Samp</b>	<b>Rej</b>	<b>Failure Mechanism</b>
<b>STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (2000V)</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	3	0	
<b>STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 150C, 5.75V, Vcc Core</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	48	799	0	
CY62256VNL (7A622574NDC)	4037633	611057997	JT-CHINA	48	798	0	
CY62256VNL (7A622574NDC)	4037633	611058668	JT-CHINA	48	800	0	
<b>STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-LATENT FAILURE RATE, 150C, 5.75V, Vcc Core</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	408	77	0	
CY62256VNL (7A622574NDC)	4037633	611057997	JT-CHINA	408	80	0	
CY62256VNL (7A622574NDC)	4037633	611058668	JT-CHINA	408	80	0	
<b>STRESS: STATIC LATCH-UP TESTING, 125C, +/-140Ma</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	6	0	
<b>STRESS: HI-ACCEL SATURATION TEST, 130C, 5.50V, 85%RH, PRE COND 192 HR 30C/60%RH, MSL3</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	96	77	0	
CY62256VNL (7A622574NDC)	4037633	611057997	JT-CHINA	96	75	0	
CY62256VNL (7A622574NDC)	4037633	611058668	JT-CHINA	96	78	0	
<b>STRESS: HIGH TEMP STORAGE</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	1000	77	0	
<b>STRESS: LEAD INTEGRITY</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	5	0	
<b>STRESS: PRESSURE COOKER TEST (121C, 100%RH), 15 Psig, PRE COND 192 HR 30C/60%RH (MSL3)</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	96	77	0	
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	168	77	0	
CY62256VNL (7A622574NDC)	4037633	611057997	JT-CHINA	96	77	0	
CY62256VNL (7A622574NDC)	4037633	611057997	JT-CHINA	168	77	0	
CY62256VNL (7A622574NDC)	4037633	611058668	JT-CHINA	96	80	0	
CY62256VNL (7A622574NDC)	4037633	611058668	JT-CHINA	168	80	0	

## Reliability Test Data

### QTP #: 105208

<i>Device</i>	<i>Fab Lot #</i>	<i>Assy Lot #</i>	<i>Assy Loc</i>	<i>Duration</i>	<i>Samp</i>	<i>Rej</i>	<i>Failure Mechanism</i>
<b>STRESS: PHYSICAL DIMENSION</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	30	0	
<b>STRESS: DIE SHEAR</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	30	0	
<b>STRESS: SOLDERABILITY</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	15	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	15	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	15	0	
<b>STRESS: TC COND. C –65C TO 150C, PRE COND 192 HR 30C/60%RH, MSL3</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	500	87	0	
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	1000	85	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	500	90	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	1000	90	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	500	89	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	1000	89	0	
<b>STRESS: POST TCT BOND PULL</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	5	0	
<b>STRESS: ELECTRICAL DISTRIBUTIONS</b>							
CY62256NLL (7A62256ZEC)	4013150	611057996	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611057997	JT-CHINA	COMP	30	0	
CY62256VNLL (7A622574NDC)	4037633	611058668	JT-CHINA	COMP	30	0	



## Document History Page

Document Title: QTP 105209: Automotive 28L SNC (300 mils) NiPdAu, MSL3, 235C Reflow JCET-China (JT)  
Qualification Report  
Document Number: 001-68150

Rev.	ECN No.	Orig. of Change	Description of Change
**	3178043	NRG	Initial Spec Release
*A	4364883	ILZ	Sunset spec review Updated front page to reflect new qualification report template per Spec 001-57717 Page 3 – Major package information table – Replaced assembly process flow spec# 001-64159 with 001-67698

Distribution: WEB

Posting: None