


CYPRESS

S6BP203A, 3.3V, 2.4A OUTPUT BUCK-BOOST DC/DC CONVERTER

HIGH-STABILITY, EASY-TO-INTEGRATE POWER MANAGEMENT
SYSTEMS FOR INSTRUMENT CLUSTERS AND ADVANCED DRIVER
ASSISTANCE SYSTEMS



PRODUCT OVERVIEW

INTRODUCTION

Cypress S6BP203A is a one-channel, buck-boost DC/DC converter IC for automotive and industrial applications. S6BP203A is ideal for automotive instrument clusters and advanced driver assistance systems that consume high power. These PMICs have high output current capability and provide stable power output across a wide range of input voltages. The 3.3V stable power supply overcomes battery fluctuations, cold-cranking and load dumping. S6BP203A is also compatible with idle reduction systems.

SMALL AND COST-EFFECTIVE

Cypress's unique buck-boost technology enables a smaller PMIC system design by shrinking input electrolytic capacitors. This smaller design eliminates large, expensive components and enables you to create one small, affordable and efficient power management solution.

EASE OF DESIGN

S6BP203A is versatile and easy-to-integrate into new or existing automotive systems. Cypress's Easy DesignSim Software further simplifies automotive system design by ensuring connectivity among parts.

FEATURES

- 1-channel buck-boost converter
- Input voltage range: 2.5V–42V
- Maximum output current: 2.4A
- Switching Frequency: 200k–2.1MHz
- Synchronization with external clock from 200kHz–400kHz
- Maximum operating temperature: 125°C
- Compliant with AEC-Q100 Grade 1
- Quiescent current: 50uA

LOW BOM

- Built-in switching transistors, output voltage setting resistors, phase compensation circuits

PROTECT FUNCTION


- Power good function
- UVLO, TSD, OCP, OVP, UVP

PACKAGES

- 16-pin Thermally Enhanced TSSOP (5mm x 6.45mm x 1.1mm, 0.65mm pitch)

APPLICATIONS



- Advanced Driver Assistance System (ADAS)
- Instrument Cluster
- Automotive and Industrial



Block Diagram

COLD-CRANK TOLERANT/LINE REGULATION

Supplies uninterrupted power to electronic equipment.



1-CHANNEL BUCK-BOOST DC/DC CONVERTER SERIES SELECTOR GUIDE

Part Number	Input Voltage	Output Voltage	Output Voltage Accuracy	Frequency	Current Capability	Package	Main Application
S6BP201A	2.5V–42V	5V, 5.05V, 5.075V, 5.1V, 5.125V, 5.15V, 5.2V (factory preset)	+/- 1.5%	200kHz - 2.1MHz (synchronization from 200kHz to 400kHz with external clock)	1000 mA	16-HTSSOP	Body Control Module (BCM) and Gateway module
S6BP202A	2.5V–42V	5V, 5.05V, 5.075V, 5.1V, 5.125V, 5.15V, 5.2V (factory preset)	+/- 1.5%	200kHz - 2.1MHz (synchronization from 200kHz to 400kHz with external clock)	2400 mA	16-HTSSOP	Instrument Cluster, Advanced Driver Assistance Systems (ADAS), and Gateway module
S6BP203A	2.5V–42V	3.3V	+/- 1.5%	200kHz - 2.1MHz (synchronization from 200kHz to 400kHz with external clock)	2400 mA	16-HTSSOP	Instrument Cluster, Advanced Driver Assistance Systems (ADAS)

GET STARTED NOW

For more information on our S6BP203A buck-boost DC/DC Converter for Automotive ECUs, visit:

www.cypress.com/automotive-pmic

Access Easy DesignSim, Cypress's online web simulator software. Just register on www.cypress.com/easy-design-sim and access the tool.

Contact your local reseller or Cypress Sales Representative to order the S6BP203A Evaluation Kit S6SBP203A8FVA1001.

Cypress Semiconductor Corporation

198 Champion Court, San Jose CA 95134
 phone +1 408.943.2600 fax +1 408.943.6848
 toll free +1 800.858.1810 (U.S. only) Press "1" to reach your local sales representative

© 2015-2017 Cypress Semiconductor Corporation. All rights reserved. All other trademarks are the property of their respective owners.
 002-03793 Rev*B

