


All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.467
A1	0.122	-	-
D	4.1068 BSC		
E	3.9025 BSC		
Øb	0.188	0.218	0.248
eD	0.21 BSC		
eE	0.28 BSC		
eS	0.35 BSC		
SD	0 BSC		
SE	0.14 BSC		