



Bottom view



$\varnothing b$	$\varnothing 0.05$	(M)	C	A	B
$\varnothing b$	$\varnothing 0.015$	(M)	C		

SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.467
A1	0.122	-	-
D	2.8819 BSC		
E	3.1024 BSC		
$\varnothing b$	0.188	0.218	0.248
eD	0.42 BSC		
eE1s	0.56 BSC		
eE2s	0.621 BSC		
eE3s	0.682 BSC		
eS1	0.35 BSC		
eS2	0.40 BSC		
SD	0.21 BSC		
SE	0.00 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []