


NPN Silicon RF Transistor

- For broadband amplifiers up to 1 GHz at collector currents from 1 mA to 20 mA
- Pb-free (RoHS compliant) package





ESD (Electrostatic discharge) sensitive device, observe handling precaution!

Туре	Marking	Pin Configuration			Package
BFS17W	MCs	1 = B	2 = E	3 = C	SOT323

Maximum Ratings at T_A = 25 °C, unless otherwise specified

Parameter	Symbol	Value	Unit
Collector-emitter voltage	$V_{\sf CEO}$	15	V
Collector-base voltage	V_{CBO}	25	
Emitter-base voltage	V _{EBO}	2.5	
Collector current	I _C	25	mA
Peak collector current, <i>f</i> = 10 MHz	I _{CM}	50	
Total power dissipation ¹⁾	P _{tot}	280	mW
<i>T</i> _S ≤ 93 °C			
Junction temperature	T_{J}	150	°C
Ambient temperature	T_{A}	-65 150	
Storage temperature	T _{Stg}	-65 150	

Thermal Resistance

Parameter	Symbol	Value	Unit
Junction - soldering point ²⁾	R _{thJS}	≤ 205	K/W

1

 $^{^{1}}T_{
m S}$ is measured on the collector lead at the soldering point to the pcb

 $^{^2}$ For calculation of R_{thJA} please refer to Application Note AN077 (Thermal Resistance Calculation)



Electrical Characteristics at $T_A = 25$ °C, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
DC Characteristics					•
Collector-emitter breakdown voltage	V _{(BR)CEO}	15	-	-	V
$I_{\rm C}$ = 1 mA, $I_{\rm B}$ = 0					
Collector-base cutoff current	I _{CBO}				μΑ
$V_{\rm CB} = 10 \text{ V}, I_{\rm E} = 0$		-	-	0.05	
$V_{\rm CB} = 25 \text{V}, I_{\rm E} = 0$		ı	-	10	
Emitter-base cutoff current	I _{EBO}	ı	-	100	
$V_{\rm EB}$ = 2.5 V, $I_{\rm C}$ = 0					
DC current gain	h _{FE}				-
$I_{\rm C}$ = 2 mA, $V_{\rm CE}$ = 1 V, pulse measured		40	-	150	
$I_{\rm C}$ = 25 mA, $V_{\rm CE}$ = 1 V, pulse measured		20	70	-	
Collector-emitter saturation voltage	V _{CEsat}	-	0.1	0.4	V
$I_{\rm C}$ = 10 mA, $I_{\rm B}$ = 1 mA					




Electrical Characteristics at T_{Δ} = 25°C, unless otherwise specified


Parameter	Symbol		Values	1	Unit
		min.	typ.	max.	
AC Characteristics (verified by random sampling	ıg)				
Transition frequency	f_{T}				GHz
$I_{\rm C}$ = 2 mA, $V_{\rm CE}$ = 5 V, f = 200 MHz		1	1.4	-	
$I_{\rm C}$ = 25 mA, $V_{\rm CE}$ = 5 V, f = 200 MHz		1.3	2.5	-	
Collector-base capacitance	C _{cb}	-	0.55	0.8	pF
$V_{\text{CB}} = 5 \text{ V}, f = 1 \text{ MHz}, V_{\text{BE}} = 0$,					
emitter grounded					
Collector emitter capacitance	C _{ce}	-	0.3	-	
$V_{CE} = 5 \text{ V}, f = 1 \text{ MHz}, V_{BE} = 0$,					
base grounded					
Emitter-base capacitance	C _{eb}	-	0.9	1.45	
$V_{\text{EB}} = 0.5 \text{ V}, f = 1 \text{ MHz}, V_{\text{CB}} = 0$,					
collector grounded					
Minimum noise figure	NF _{min}	-	3.5	5	dB
$I_{\rm C}$ = 2 mA, $V_{\rm CE}$ = 5 V, $Z_{\rm S}$ = 50 Ω ,					
f = 800 MHz					
Transducer gain	S _{21e} ²	-	14	-	dB
$I_{\rm C}$ = 20 mA, $V_{\rm CE}$ = 5 V, $Z_{\rm S}$ = $Z_{\rm L}$ = 50 Ω ,					
f = 500 MHz					
Third order intercept point at output	IP ₃	-	22.5	-	dBm
V_{CE} = 5 V, I_{C} = 20 mA, f = 800 MHz,					
$Z_{\rm S} = Z_{\rm Sopt}, Z_{\rm L} = Z_{\rm Lopt}$					
1dB compression point	P _{-1dB}	-	11	-	-
$I_{\rm C}$ = 20 mA, $V_{\rm CE}$ = 5 V, $Z_{\rm S}$ = $Z_{\rm L}$ = 50 Ω ,					
f = 800 MHz					



Total power dissipation $P_{tot} = f(T_S)$


Permissible Pulse Load $R_{thJS} = f(t_p)$






Permissible Pulse Load

 $P_{\text{totmax}}/P_{\text{totDC}} = f(t_{\text{p}})$




Collector-base capacitance $C_{cb} = f(V_{CB})$ Emitter-base capacitance $C_{eb} = f(V_{EB})$





Transition frequency $f_T = f(I_C)$

 V_{CE} = parameter





5 2011-07-20




Package Outline








Foot Print




Marking Layout (Example)



Standard Packing

Reel ø180 mm = 3.000 Pieces/Reel Reel ø330 mm = 10.000 Pieces/Reel



6



Edition 2009-11-16

Published by Infineon Technologies AG 81726 Munich, Germany

© 2009 Infineon Technologies AG All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (<www.infineon.com>).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

7