



# Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

**Adobe Reader version 7.0.5 is required to complete this declaration.**

1752-1 1.1	IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>	<b>Form Type *</b> Distribute	<b>Declaration Class *</b> Class 4 - RoHS Yes/No, JIG Format Substances, Mfg Info
------------	--	----------------------------------	--

## Supplier Information

<b>Company Name *</b> CHiL Semiconductor	Company Unique ID	Unique ID Authority	<b>Response Date *</b> 2010-10-25	Response Document ID				
<b>Contact Name *</b> Manu Jain	Title - Contact	<b>Phone - Contact *</b> 978-640-0011	<b>Email - Contact *</b> quality@chilsemi.com					
<b>Authorized Representative *</b> Manu Jain	Title - Representative	<b>Phone - Representative *</b> 978-640-0011	<b>Email - Representative *</b> quality@chilsemi.com		Supplier Comments or URL for Additional Information			
Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	<b>Weight *</b>	UOM	Unit Type
	<b>CHL8314</b>	<b>CHL8314</b>	<b>2010-10-25</b>			<b>145</b>	<b>mg</b>	<b>Each</b>
Alternate Recommendation			Alternate Item Comments					

## Manufacturing Process Information

Terminal Plating / Grid Array Material <b>Matte Tin (Sn)</b>	Terminal Base Alloy <b>CU Alloy</b>	J-STD-020 MSL Rating <b>1</b>	Peak Process Body Temperature <b>257 C</b>	Max Time at Peak Temperature <b>25 seconds</b>	Number of Reflow Cycles <b>1</b>
Comments <b>Does not contain PFOS</b>					

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Locked

## RoHS Material Composition Declaration

Declaration Type \*

Custom

**RoHS Directive 2002/95/EC** **RoHS Definition:** Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Subject to the limitations below, CHiL Semiconductor Corporation certifies the following information as of the document date.

1. CHiL products designated "ROHS Compliant" comply with the European Unions Directive on the Restriction of the Use of Hazardous Substances 2002/95/EC ("RoHS").
2. CHiL products do not contain and are not manufactured with ozone depleting compounds.
3. CHiL products do not contain substances identified by the European Chemical Agency ("ECHA") as substances of very high concern ("SVHC") per REACH Regulation (EC) No 1907/2006. CHiL also complies with use restrictions as stipulated in Annex XVII of REACH.
4. CHiL's list of banned and reportable substances and management system is based on the current version of the Joint Industrial Guide, JIG-101.

CHiL has taken commercially reasonable steps to provide representative and accurate information but may not have independently verified information provided or conducted chemical analysis of incoming materials. Equivalent compliant materials may have been substituted for those stated herein. Material concentrations are the maximum expected concentration of the substance in the device and may not represent the actual concentration. CHiL and its suppliers consider certain limited information to be confidential and thus CAS numbers and other limited information may not be available for release.

CHiL ACCEPTS NO DUTY TO NOTIFY USERS OF THIS DECLARATION OF UPDATES OR CHANGES TO THIS DECLARATION

RoHS Declaration \*

1 - Item(s) does not contain RoHS restricted substances per the definition above

Supplier Acceptance \*

Accepted

**Exemptions:** If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

## Declaration Signature

**Instructions:** Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

## Joint Industry Guide (JIG) Material Composition Declaration for Electronic Products

Instructions: Declare whether the item substances exceed the threshold levels shown in the table and report accordingly. Where threshold levels include the words "intentionally added", substances must be declared if they are added intentionally, regardless of threshold level. For each RoHS substance, identified with dual asterisks (\*\*), report the worst case PPM at the homogeneous material level and optionally the total weight of the substance in the item. For all remaining (non-RoHS) JIG A & B substances, and any additional substances, report the total weight and optionally the PPM at the part level for each item.

				JIG A autofill - No	JIG B autofill - No	All autofill - No	
JIG	Category Name	Threshold Level	Above Threshold Level?	If yes, enter total weight and worse case PPM			Description of Use
Level	As defined in the Joint Industry Guide	Intentionally added or PPM	Yes/No	Weight	UoM	PPM	
A	Asbestos	Intentionally Added	No				
A	Certain Azo colorants	Intentionally Added	No				
A	Cadmium/Cadmium Compounds **	75 PPM or Intentionally Added	No				
A	Hexavalent Chromium/Hexavalent Chromium Compounds **	1000 PPM or Intentionally Added	No				
A	Lead/Lead Compounds **	1000 PPM or Intentionally Added	No				
A	Lead/Lead Compounds - PVC Cables and Wires Only **	300 PPM	No				
A	Mercury/Mercury Compounds **	1000 PPM or Intentionally Added	No				
A	Ozone Depleting Substances - Class I (CFCs, HBFCs, etc.)	Intentionally Added	No				
A	Ozone Depleting Substances - Class II (HCFCs)	1000 PPM	No				
A	Polybrominated Biphenyls (PBBs) **	1000 PPM or Intentionally Added	No				
A	Polybrominated Diphenylethers (PBDEs) **	1000 PPM or Intentionally Added	No				
A	Polychlorinated Biphenyls (PCBs)	Intentionally Added	No				
A	Polychlorinated Naphthalenes ( > 3 chlorine atoms)	Intentionally Added	No				
A	Radioactive Substances	Intentionally Added	No				
A	Certain Shortchain Chlorinated Paraffins	Intentionally Added	No				
A	Tributyl Tin (TBT) and Triphenyl Tin (TPT)	Intentionally Added	No				
A	Tributyl Tin Oxide (TBTO)	Intentionally Added	No				
B	Antimony/Antimony Compounds	1000 PPM	No				
B	Arsenic/Arsenic Compounds	1000 PPM	No				
B	Beryllium/Beryllium Compounds	1000 PPM	No				
B	Bismuth/Bismuth Compounds	1000 PPM	No				
B	Brominated Flame Retardants (other than PBBs or PBDEs)	1000 PPM	No				
B	Nickel (external applications only)	1000 PPM	No				
B	Certain Phthalates	1000 PPM	No				
B	Selenium/Selenium Compounds	1000 PPM	No				
B	Polyvinyl Chloride (PVC)	1000 PPM	No				

**OTHER Material Composition Declaration**

**Requester Instructions:** The requester can optionally include additional substances that must be declared for the item on this form. This is in addition to JIG Level A and JIG Level B substances. The requester should enter additional substances as well as the threshold levels that specify the substance at the item level.

**Supplier Instructions:** Explicitly declare whether the item exceed the threshold level by selecting Yes or No. If the maximum concentration of any substance exceeds the threshold levels defined by the requester, then the substance content must be reported in total weight and/or worst case PPM, along with a description of material use.

JIG	Category Name	Threshold Level
Other	As defined by the Supplier	Defined by the Supplier
+ -		
Add Other Material Composition to JIG Tab		Clear Other Material Composition in JIG Tab