

## Solution brief

# XENSIV™ connected sensor kit

## Fast IoT experience enabled by XENSIV™ sensors

The connected sensor kit solves the four biggest challenges of any IoT device development and deployment: sensing the world around us (sense), making sense of the raw data (compute), and connecting devices to the cloud (connect).

It is a feather compatible development kit for rapid prototyping and deployment of IoT devices. It consists of Infineon's highly accurate and precise XENSIV™ sensors (60 GHz radar sensor, PAS CO2 and DPS368 pressure sensor), low power dual core microcontroller (PSoC™ 6-2M), Bluetooth® and Wi-Fi as connectivity options within a software ecosystem provided through ModusToolbox™.


### Key features

- > Small form factor: 22.5 x 63 x 30 mm – feather compatible
- > Flexibility – Interchangeable sensor wing boards-stacked individually or combined
- > Sensors: XENSIV™ 60 GHz radar, PAS CO2 and DPS368 pressure sensor
- > PSoC™ 6-2M microcontroller
- > Connectivity – dual-band (2.4 and 5.0 GHz) Wi-Fi and Bluetooth 5.0-compliant combo radio module
- > Security – OPTIGA™ Trust M for secure authentication of IoT devices


### Key benefits

- > Rapid prototyping – a connected sensor kit for fast development and deployment
- > One-stop-shop for any IoT device development based on XENSIV™ 60 GHz radar, PAS CO2 and DPS368 pressure sensor
- > Seamless integration to ModusToolbox™ with application code examples and sensor drivers for faster go-to-market

### XENSIV™ connected sensor kit



Software stack in ModusToolbox™



1) Coming soon

**Sensors**

- > XENSIV™ PAS CO2, BGT60TR13C radar and DPS368 pressure sensor

**Microcontroller and connectivity**

- > CYSBSYS-RP01 – Rapid IoT module (FCC and CE certified module) (PSoC™ 62M MCU (Cortex M4F/M0+) + Wi-Fi-Bluetooth® Combo)

**Security**

- > OPTIGA™ Trust M

**Kit certification**

- > CE

**Target applications**

- > Smart home devices, smart appliances, building management and control



[www.infineon.com](http://www.infineon.com)

Published by  
Infineon Technologies AG  
Am Campeon 1-15, 85579 Neubiberg  
Germany

© 2022 Infineon Technologies AG  
All rights reserved.

Date: 04 / 2022

**Please note!**

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

**Additional information**

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

**Warnings**

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.