International
IOR Rectifier

PD- 95286

SMPS MOSFET

IRF7469PbF

HEXFET® Power MOSFET

Applications

- High Frequency Isolated DC-DC Converters with Synchronous Rectification for Telecom and Industrial Use
- High Frequency Buck Converters for Computer Processor Power
- Lead-Free

V_{DSS}	$R_{DS(on)}$ max(mΩ)	I_D
40V	17@V_{GS} = 10V	9.0A



Top View


SO-8

Benefits

- Ultra-Low Gate Impedance
- Very Low $R_{DS(on)}$
- Fully Characterized Avalanche Voltage and Current

Absolute Maximum Ratings

Symbol	Parameter	Max.	Units
V_{DS}	Drain-Source Voltage	40	V
V_{GS}	Gate-to-Source Voltage	± 20	V
I_D @ T_A = 25°C	Continuous Drain Current, V_{GS} @ 10V	9.0	A
I_D @ T_A = 70°C	Continuous Drain Current, V_{GS} @ 10V	7.3	
I_{DM}	Pulsed Drain Current①	73	
P_D @T_A = 25°C	Maximum Power Dissipation③	2.5	W
P_D @T_A = 70°C	Maximum Power Dissipation③	1.6	W
	Linear Derating Factor	0.02	mW/°C
T_J , T_{STG}	Junction and Storage Temperature Range	-55 to + 150	°C

Thermal Resistance

Symbol	Parameter	Typ.	Max.	Units
$R_{\theta JL}$	Junction-to-Drain Lead	——	20	°C/W
$R_{\theta JA}$	Junction-to-Ambient ④	——	50	

Notes ① through ④ are on page 8

08/17/04

Static @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	40	——	——	V	V_{GS} = 0V, I_D = 250µA
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	——	0.04	——	V/°C	Reference to 25°C, I_D = 1mA
$R_{DS(on)}$	Static Drain-to-Source On-Resistance	——	12	17	mΩ	V_{GS} = 10V, I_D = 9.0A ③
		——	15.5	21		V_{GS} = 4.5V, I_D = 7.2A ③
$V_{GS(th)}$	Gate Threshold Voltage	1.0	——	3.0	V	V_{DS} = V_{GS}, I_D = 250µA
I_{DSS}	Drain-to-Source Leakage Current	——	——	20	µA	V_{DS} = 32V, V_{GS} = 0V
		——	——	100		V_{DS} = 32V, V_{GS} = 0V, T_J = 125°C
I_{GSS}	Gate-to-Source Forward Leakage	——	——	200	nA	V_{GS} = 16V
	Gate-to-Source Reverse Leakage	——	——	-200		V_{GS} = -16V

Dynamic @ T_J = 25°C (unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
g_{fs}	Forward Transconductance	17	——	——	S	V_{DS} = 20V, I_D = 7.2A
Q_g	Total Gate Charge	——	15	23	nC	I_D = 7.2A
Q_{gs}	Gate-to-Source Charge	——	7.0	11		V_{DS} = 20V
Q_{gd}	Gate-to-Drain ("Miller") Charge	——	5.0	8.0		V_{GS} = 4.5V ③
Q_{oss}	Output Gate Charge	——	16	24		V_{GS} = 0V, V_{DS} = 16V
$t_{d(on)}$	Turn-On Delay Time	——	11	——	ns	V_{DD} = 20V
t_r	Rise Time	——	2.2	——		I_D = 7.2A
$t_{d(off)}$	Turn-Off Delay Time	——	14	——		R_G = 1.8Ω
t_f	Fall Time	——	3.5	——		V_{GS} = 4.5V ③
C_{iss}	Input Capacitance	——	2000	——	pF	V_{GS} = 0V
C_{oss}	Output Capacitance	——	480	——		V_{DS} = 20V
C_{rss}	Reverse Transfer Capacitance	——	28	——		ƒ = 1.0MHz

Avalanche Characteristics

Symbol	Parameter	Typ.	Max.	Units
E_{AS}	Single Pulse Avalanche Energy②	——	210	mJ
I_{AR}	Avalanche Current①	——	7.2	A

Diode Characteristics

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	——	——	2.3	A	MOSFET symbol showing the integral reverse p-n junction diode. 
I_{SM}	Pulsed Source Current (Body Diode) ①	——	——	73		
V_{SD}	Diode Forward Voltage	——	0.80	1.3	V	T_J = 25°C, I_S = 7.2A, V_{GS} = 0V ③
		——	0.65	——		T_J = 125°C, I_S = 7.2A, V_{GS} = 0V ③
t_{rr}	Reverse Recovery Time	——	47	71	ns	T_J = 25°C, I_F = 7.2A, V_R=15V
Q_{rr}	Reverse Recovery Charge	——	91	140	nC	di/dt = 100A/µs ③
t_{rr}	Reverse Recovery Time	——	77	120	ns	T_J = 125°C, I_F = 7.2A, V_R=20V
Q_{rr}	Reverse Recovery Charge	——	150	230	nC	di/dt = 100A/µs ③



Fig 1. Typical Output Characteristics



Fig 2. Typical Output Characteristics



Fig 3. Typical Transfer Characteristics



Fig 4. Normalized On-Resistance
Vs. Temperature



Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage



Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage



Fig 7. Typical Source-Drain Diode Forward Voltage



Fig 8. Maximum Safe Operating Area





Fig 10a. Switching Time Test Circuit



Fig 10b. Switching Time Waveforms



Fig 10. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient



Fig 12. On-Resistance Vs. Drain Current



Fig 13. On-Resistance Vs. Gate Voltage



Fig 13a&b. Basic Gate Charge Test Circuit and Waveform





Fig 14a&b. Unclamped Inductive Test circuit and Waveforms

Fig 14c. Maximum Avalanche Energy Vs. Drain Current

SO-8 Package Outline

Dimensions are shown in millimeters (inches)



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.0532	.0688	1.35	1.75
A1	.0040	.0098	0.10	0.25
b	.013	.020	0.33	0.51
c	.0075	.0098	0.19	0.25
D	.189	.1968	4.80	5.00
E	.1497	.1574	3.80	4.00
e	.050 BASIC		1.27 BASIC	
e 1	.025 BASIC		0.635 BASIC	
H	.2284	.2440	5.80	6.20
K	.0099	.0196	0.25	0.50
L	.016	.050	0.40	1.27
y	0°	8°	0°	8°





NOTES:

1. DIMENSIONING & TOLERANCING PER ASME Y14.5M-1994.
2. CONTROLLING DIMENSION: MILLIMETER
3. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
4. OUTLINE CONFORMS TO JEDEC OUTLINE MS-012AA.
5. DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.15 [.006].
6. DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.25 [.010].
7. DIMENSION IS THE LENGTH OF LEAD FOR SOLDERING TO A SUBSTRATE.

FOOTPRINT



SO-8 Part Marking

EXAMPLE: THIS IS AN IRF7101 (MOSFET)



SO-8 Tape and Reel



NOTES:
1. CONTROLLING DIMENSION : MILLIMETER.
2. ALL DIMENSIONS ARE SHOWN IN MILLIMETERS(INCHES).
3. OUTLINE CONFORMS TO EIA-481 & EIA-541.



NOTES :
1. CONTROLLING DIMENSION : MILLIMETER.
2. OUTLINE CONFORMS TO EIA-481 & EIA-541.

Notes:

① Repetitive rating; pulse width limited by max. junction temperature.

② Starting T_J = 25°C, L = 8.1mH R_G = 25Ω, I_{AS} = 7.2A.

③ Pulse width ≤ 400µs; duty cycle ≤ 2%.

④ When mounted on 1 inch square copper board.

Data and specifications subject to change without notice.
This product has been designed and qualified for the Consumer market.
Qualifications Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7903
Visit us at www.irf.com for sales contact information.08/04

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie") .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (**www.infineon.com**).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.