

## Fast switching diode chip in Emitter Controlled Technology

### Features:

- 1200V technology 120 µm chip
- soft, fast switching
- low reverse recovery charge
- small temperature coefficient
- qualified according to JEDEC for target applications

### **Recommended for:**

power modules and discrete devices



#### **Applications:**

• SMPS, resonant applications, drives

Chip Type	V <sub>R</sub>	<b>I</b> Fn	Die Size	Package
SIDC23D120F6	1200V	25A	3.5 x 6.5 mm <sup>2</sup>	sawn on foil

## **Mechanical Parameters**

	513			
Die size		3.5 x 6.5		
Area total		22.75	mm <sup>2</sup>	
Anode pad size		2.78 x 5.78		
Thickness		120	μm	
Wafer size		150	mm	
Max. possible chips pe	er wafer	644		
Passivation frontside		Photoimide		
Pad metal		3200 nm AlSiCu		
Backside metal		Ni Ag –system		
Die bond		Electrically conductive epoxy glue and soft solder		
Wire bond		Al, ≤500µm		
Reject ink dot size		Ø 0.65mm; max 1.2mm		
Storage environment	for original and sealed MBB bags	Ambient atmosphere air, Temperature 17°C – 25°C, < 6 month		
	for open MBB bags	Acc. to IEC62258-3: Atmosphere >99% Nitrogen or ine Humidity <25%RH, Temperature 17°C – 25°C, < 6 m		



### **Maximum Ratings**

Parameter	Symbol	Condition	Value	Unit
Repetitive peak reverse voltage	V <sub>RRM</sub>	<i>T</i> <sub>vj</sub> = 25 °C	1200	V
Continuous forward current	I <sub>F</sub>	<i>T</i> <sub>vj</sub> < 150°C	1)	Α
Maximum repetitive forward current <sup>2)</sup>	I <sub>FRM</sub>	<i>T</i> <sub>vj</sub> < 150°C	50	
Operating junction and storage temperature	$T_{\rm vj,} T_{\rm stg}$		-55+150	°C

<sup>1)</sup> depending on thermal properties of assembly

<sup>2</sup>) not subject to production test - verified by design/characterisation

## Static Characteristics (tested on wafer), T<sub>vi</sub> = 25 °C

Parameter	Symbol Conditions	Conditions	Value			Unit
Falameter		min.	typ.	max.	Onit	
Reverse leakage current	I <sub>R</sub>	V <sub>R</sub> =1200V			20	μA
Cathode-Anode breakdown Voltage	V <sub>BR</sub>	I <sub>R</sub> =0.25mA	1200			V
Forward voltage drop	V <sub>F</sub>	<i>I</i> <sub>F</sub> =25A	1.68	2.1	2.42	

## Electrical Characteristics (not subject to production test - verified by design/characterization)

Parameter		Symbol	bol Conditions	Value			Unit
		Symbol		min.	typ.	max.	Unit
Forward voltage drop	<i>T</i> <sub>vj</sub> = 125°C	V <sub>F</sub>	/ <sub>F</sub> =25A		1.8		V


## **Further Electrical Characteristics**

Switching characteristics and thermal properties are depending strongly on module design and mounting technology and can therefore not be specified for a bare die.

This chip data sheet refers to the device data sheet		
--	--	--



## **Chip Drawing**



A: Anode pad



### Description

AQL 0,65 for visual inspection according to failure catalogue

Electrostatic Discharge Sensitive Device according to MIL-STD 883

### **Revision History**

Version	Subjects (major changes since last revision)	Date
2.0	Final data sheet	11.12.2012
2.1	Operating junction and storage temperature	14.05.2013

Published by Infineon Technologies AG 81726 Munich, Germany © 2013 Infineon Technologies AG All Rights Reserved.

#### Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

#### Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

#### Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office. The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace devices or systems or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.