


IRG4BC30UDPbF

INSULATED GATE BIPOLAR TRANSISTOR WITH
 ULTRAFast SOFT RECOVERY DIODE

UltraFast CoPack IGBT

Features


- UltraFast: Optimized for high operating frequencies 8-40 kHz in hard switching, >200 kHz in resonant mode
- Generation 4 IGBT design provides tighter parameter distribution and higher efficiency than Generation 3
- IGBT co-packaged with HEXFRED™ ultrafast, ultra-soft-recovery anti-parallel diodes for use in bridge configurations
- Industry standard TO-220AB package
- Lead-Free



| |
|-----------------------------|
| $V_{CES} = 600V$ |
| $V_{CE(on) typ.} = 1.95V$ |
| @ $V_{GE} = 15V, I_C = 12A$ |

Benefits

- Generation -4 IGBT's offer highest efficiencies available
- IGBTs optimized for specific application conditions
- HEXFRED diodes optimized for performance with IGBTs . Minimized recovery characteristics require less/no snubbing
- Designed to be a "drop-in" replacement for equivalent industry-standard Generation 3 IR IGBTs



Absolute Maximum Ratings

| | Parameter | Max. | Units |
|---------------------------|--|---------------------|-------|
| V_{CES} | Collector-to-Emitter Voltage | 600 | V |
| $I_C @ T_C = 25^\circ C$ | Continuous Collector Current | 23 | A |
| $I_C @ T_C = 100^\circ C$ | Continuous Collector Current | 12 | |
| I_{CM} | Pulsed Collector Current ① | 92 | |
| I_{LM} | Clamped Inductive Load Current ② | 92 | |
| $I_F @ T_C = 100^\circ C$ | Diode Continuous Forward Current | 12 | |
| I_{FM} | Diode Maximum Forward Current | 92 | |
| V_{GE} | Gate-to-Emitter Voltage | ± 20 | V |
| $P_D @ T_C = 25^\circ C$ | Maximum Power Dissipation | 100 | W |
| $P_D @ T_C = 100^\circ C$ | Maximum Power Dissipation | 42 | |
| T_J | Operating Junction and Storage Temperature Range | -55 to +150 | °C |
| T_{STG} | | | |
| | | | |
| | Mounting Torque, 6-32 or M3 Screw. | 10 lbf•in (1.1 N•m) | |

Thermal Resistance

| | Parameter | Min. | Typ. | Max. | Units |
|-----------------|---|-------|----------|-------|-------|
| $R_{\theta JC}$ | Junction-to-Case - IGBT | ----- | ----- | 1.2 | °C/W |
| $R_{\theta JC}$ | Junction-to-Case - Diode | ----- | ----- | 2.5 | |
| $R_{\theta CS}$ | Case-to-Sink, flat, greased surface | ----- | 0.50 | ----- | |
| $R_{\theta JA}$ | Junction-to-Ambient, typical socket mount | ----- | ----- | 80 | |
| Wt | Weight | ----- | 2 (0.07) | ----- | |

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

| | Parameter | Min. | Typ. | Max. | Units | Conditions |
|--|---|------|------|------|-------|--|
| V _{(BR)CES} | Collector-to-Emitter Breakdown Voltage ^③ | 600 | ---- | ---- | V | V _{GE} = 0V, I _C = 250μA |
| ΔV _{(BR)CES} /ΔT _J | Temperature Coeff. of Breakdown Voltage | ---- | 0.63 | ---- | V/°C | V _{GE} = 0V, I _C = 1.0mA |
| V _{CE(on)} | Collector-to-Emitter Saturation Voltage | ---- | 1.95 | 2.1 | V | I _C = 12A |
| | | ---- | 2.52 | ---- | | I _C = 23A |
| | | ---- | 2.09 | ---- | | I _C = 12A, T _J = 150°C |
| V _{GE(th)} | Gate Threshold Voltage | 3.0 | ---- | 6.0 | | V _{CE} = V _{GE} , I _C = 250μA |
| ΔV _{GE(th)} /ΔT _J | Temperature Coeff. of Threshold Voltage | ---- | -11 | ---- | mV/°C | V _{CE} = V _{GE} , I _C = 250μA |
| g _{fe} | Forward Transconductance ^④ | 3.1 | 8.6 | ---- | S | V _{CE} = 100V, I _C = 12A |
| I _{CES} | Zero Gate Voltage Collector Current | ---- | ---- | 250 | μA | V _{GE} = 0V, V _{CE} = 600V |
| | | ---- | ---- | 2500 | | V _{GE} = 0V, V _{CE} = 600V, T _J = 150°C |
| V _{FM} | Diode Forward Voltage Drop | ---- | 1.4 | 1.7 | V | I _C = 12A |
| | | ---- | 1.3 | 1.6 | | I _C = 12A, T _J = 150°C |
| I _{GES} | Gate-to-Emitter Leakage Current | ---- | ---- | ±100 | nA | V _{GE} = ±20V |

Switching Characteristics @ T_J = 25°C (unless otherwise specified)

| | Parameter | Min. | Typ. | Max. | Units | Conditions | | |
|--------------------------|---|------|------|------|--------------------------------|--|--|-----------------------|
| Q _g | Total Gate Charge (turn-on) | ---- | 50 | 75 | | I _C = 12A | | |
| Q _{ge} | Gate - Emitter Charge (turn-on) | ---- | 8.1 | 12 | nC | V _{CC} = 400V | | |
| Q _{gc} | Gate - Collector Charge (turn-on) | ---- | 18 | 27 | | V _{GE} = 15V | | |
| t _{d(on)} | Turn-On Delay Time | ---- | 40 | ---- | | T _J = 25°C | | |
| t _r | Rise Time | ---- | 21 | ---- | ns | I _C = 12A, V _{CC} = 480V | | |
| t _{d(off)} | Turn-Off Delay Time | ---- | 91 | 140 | | V _{GE} = 15V, R _G = 23Ω | | |
| t _f | Fall Time | ---- | 80 | 130 | | Energy losses include "tail" and diode reverse recovery. | | |
| E _{on} | Turn-On Switching Loss | ---- | 0.38 | ---- | | mJ | See Fig. 9, 10, 11, 18 | |
| E _{off} | Turn-Off Switching Loss | ---- | 0.16 | ---- | | | | |
| E _{ts} | Total Switching Loss | ---- | 0.54 | 0.9 | | | | |
| t _{d(on)} | Turn-On Delay Time | ---- | 40 | ---- | | ns | T _J = 150°C, See Fig. 9, 10, 11, 18 | |
| t _r | Rise Time | ---- | 22 | ---- | | | I _C = 12A, V _{CC} = 480V | |
| t _{d(off)} | Turn-Off Delay Time | ---- | 120 | ---- | | | V _{GE} = 15V, R _G = 23Ω | |
| t _f | Fall Time | ---- | 180 | ---- | | | Energy losses include "tail" and diode reverse recovery. | |
| E _{ts} | Total Switching Loss | ---- | 0.89 | ---- | mJ | | Measured 5mm from package | |
| L _E | Internal Emitter Inductance | ---- | 7.5 | ---- | | | nH | |
| C _{ies} | Input Capacitance | ---- | 1100 | ---- | pF | | V _{GE} = 0V | |
| C _{oes} | Output Capacitance | ---- | 73 | ---- | | | V _{CC} = 30V | |
| C _{res} | Reverse Transfer Capacitance | ---- | 14 | ---- | | | f = 1.0MHz | |
| t _{rr} | Diode Reverse Recovery Time | ---- | 42 | 60 | ns | | T _J = 25°C See Fig. | |
| I _{rr} | Diode Peak Reverse Recovery Current | ---- | 80 | 120 | | T _J = 125°C 14 | I _F = 12A | |
| | | ---- | 3.5 | 6.0 | | T _J = 25°C See Fig. | | |
| Q _{rr} | Diode Reverse Recovery Charge | ---- | 5.6 | 10 | | T _J = 125°C 15 | | V _R = 200V |
| | | ---- | 80 | 180 | | T _J = 25°C See Fig. | | |
| di _{(rec)M} /dt | Diode Peak Rate of Fall of Recovery During t _b | ---- | 220 | 600 | T _J = 125°C 16 | di/dt 200A/μs | | |
| | | ---- | 180 | ---- | T _J = 25°C See Fig. | | | |
| | | ---- | 120 | ---- | T _J = 125°C 17 | | | |




Fig. 1 - Typical Load Current vs. Frequency
(Load Current = I_{RMS} of fundamental)




Fig. 2 - Typical Output Characteristics




Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Maximum Collector Current vs. Case Temperature




Fig. 5 - Typical Collector-to-Emitter Voltage vs. Junction Temperature




Fig. 6 - Maximum IGBT Effective Transient Thermal Impedance, Junction-to-Case




Fig. 7 - Typical Capacitance vs. Collector-to-Emitter Voltage




Fig. 8 - Typical Gate Charge vs. Gate-to-Emitter Voltage




Fig. 9 - Typical Switching Losses vs. Gate Resistance




Fig. 10 - Typical Switching Losses vs. Junction Temperature




Fig. 11 - Typical Switching Losses vs. Collector-to-Emitter Current




Fig. 12 - Turn-Off SOA




Fig. 13 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current




Fig. 14 - Typical Reverse Recovery vs. di_f/dt




Fig. 15 - Typical Recovery Current vs. di_f/dt




Fig. 16 - Typical Stored Charge vs. di_f/dt




Fig. 17 - Typical $di_{(rec)M}/dt$ vs. di_f/dt




Fig. 18a - Test Circuit for Measurement of I_{LM} , E_{on} , $E_{off}(\text{diode})$, t_{rr} , Q_{rr} , I_{rr} , $t_{d(on)}$, t_r , $t_{d(off)}$, t_f




Fig. 18b - Test Waveforms for Circuit of Fig. 18a, Defining E_{off} , $t_{d(off)}$, t_f




Fig. 18c - Test Waveforms for Circuit of Fig. 18a, Defining E_{on} , $t_{d(on)}$, t_r




Fig. 18d - Test Waveforms for Circuit of Fig. 18a, Defining E_{rec} , t_{rr} , Q_{rr} , I_{rr}




Figure 18e. Macro Waveforms for Figure 18a's Test Circuit





Figure 19. Clamped Inductive Load Test Circuit



Pulsed Collector Current Test Circuit
 Figure 20. Pulsed Collector Current Test Circuit


IRG4BC30UDPbF

International
IR Rectifier

Notes:

- ① Repetitive rating: $V_{GE}=20V$; pulse width limited by maximum junction temperature (figure 20)
- ② $V_{CC}=80\%(V_{CES})$, $V_{GE}=20V$, $L=10\mu H$, $R_G = 23\Omega$ (figure 19)
- ③ Pulse width $\leq 80\mu s$; duty factor $\leq 0.1\%$.
- ④ Pulse width $5.0\mu s$, single shot.

TO-220AB Package Outline (Dimensions are shown in millimeters (inches))



- NOTES:
- 1- DIMENSIONING AND TOLERANCING AS PER ASME Y14.5 M-1994.
 - 2- DIMENSIONS ARE SHOWN IN INCHES (MILLIMETERS).
 - 3- LEAD DIMENSION AND FINISH UNCONTROLLED IN 1:1.
 - 4- DIMENSION D, DI & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005" (0.127) PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
 - 5- DIMENSION b1, b3 & c1 APPLY TO BASE METAL ONLY.
 - 6- CONTROLLING DIMENSION - INCHES.
 - 7- THERMAL PAD CONTOURS OPTIONAL WITHIN DIMENSIONS E1, D2 & E1.
 - 8- DIMENSION E2 x H1 DEFINE A ZONE WHERE STAMPING AND SINGULATION IRREGULARITIES ARE ALLOWED.
 - 9- OUTLINE CONFORMS TO JEDEC TO-220, EXCEPT A2 (max.) AND D2 (min.) WHERE DIMENSIONS ARE DERIVED FROM THE ACTUAL PACKAGE OUTLINE.

| SYMBOL | DIMENSIONS | | | | NOTES |
|--------|-------------|-------|----------|------|-------|
| | MILLIMETERS | | INCHES | | |
| | MIN. | MAX. | MIN. | MAX. | |
| A | 3.56 | 4.83 | .140 | .190 | |
| A1 | 0.51 | 1.40 | .020 | .055 | |
| A2 | 2.03 | 2.92 | .080 | .115 | |
| b | 0.38 | 1.01 | .015 | .040 | 5 |
| b1 | 0.38 | 0.91 | .015 | .036 | |
| b2 | 1.14 | 1.78 | .045 | .070 | |
| b3 | 1.14 | 1.73 | .045 | .068 | 5 |
| c | 0.36 | 0.61 | .014 | .024 | |
| c1 | 0.26 | 0.56 | .014 | .022 | 5 |
| D | 14.22 | 16.51 | .560 | .650 | 4 |
| D1 | 8.38 | 9.02 | .330 | .355 | 7 |
| D2 | 11.68 | 12.88 | .460 | .507 | 7 |
| E | 9.65 | 10.67 | .380 | .420 | 4, 7 |
| E1 | 6.86 | 8.89 | .270 | .350 | 7 |
| E2 | - | 0.76 | - | 0.30 | 8 |
| e | 2.54 BSC | - | .100 BSC | - | |
| e1 | 2.54 BSC | - | .100 BSC | - | |
| H1 | 5.84 | 6.86 | .230 | .270 | 7, 8 |
| L | 12.70 | 14.73 | .500 | .580 | |
| L1 | 3.56 | 4.06 | .140 | .160 | 3 |
| MP | 3.54 | 4.08 | .139 | .161 | |
| Q | 2.54 | 3.42 | .100 | .135 | |

LEAD ASSIGNMENTS

- 1- GATE
- 2- DRN
- 3- SOURCE


SEMI CONDUCTOR

- 1- GATE
- 2- COLLECTOR
- 3- GATE

- 1- ANODE
- 2- CATHODE
- 3- ANODE

TO-220AB Part Marking Information

EXAMPLE: THIS IS AN IRF1010
 LOT CODE 1789
 ASSEMBLED ON WW 19, 1997
 IN THE ASSEMBLY LINE 'C'
Note: "P" in assembly line position indicates "Lead-Free"



Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>

Data and specifications subject to change without notice.

International
IR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
 TAC Fax: (310) 252-7903

Visit us at www.irf.com for sales contact information.02/2010