Series PVG612APbF

Microelectronic Power IC

HEXFET® Power MOSFET Photovoltaic Relay Single-Pole, Normally-Open, 0-60V, 2.0A AC / 4.0A DC

General Description

The PVG612A Series Photovoltaic Relay is a single-pole, normally open solid-state relay that can replace electromechanical relays in many applications. It utilizes International Rectifier's proprietary HEXFET power MOSFET as the output switch, driven by an integrated circuit photovoltaic generator of novel construction. The output switch is controlled by radiation from a GaAlAs light emitting diode (LED) which is optically isolated from the photovoltaic generator.


These units exceed the performance capabilities of electromechanical relays in operating life, sensitivity, stability of on-resistance, miniaturization, insensitivity to magnetic fields and ruggedess. The compact PVG612A is particularly suited for isolated switching of high currents from 12 to 48 Volt AC or DC power sources.

Series PVG612A Relays are packaged in a 6-pin, molded DIP package with either thru-hole or surface mount (gull-wing) terminals. It is available in standard plastic shipping tubes or on tape-and-reel. Please refer to Part Identification information opposite.

Features

- Bounce-free operation
- High load current capacity
- High off-state resistance
- Linear AC/DC operation
- 4,000 V_{BMS} I/O Isolation
- Solid-State reliability
- UL recognized
- ESD Tolerance:

4000V Human Body Model 500V Machine Model



Applications

- Programmable Logic Controllers
- Computers and Peripheral Devices
- Audio Equipment
- Power Supplies and Power Distribution
- Control of Displays and Indicators
- Industrial Automation

Part Identification

PVG612APbF thru-hole
PVG612ASPbF surface-mount

PVG612AS-TPbF surface-mount, tape

and reel

(HEXFET is the registered trademark for International Rectifier Power MOSFETs)



Electrical Specifications (-40°C \leq T_A \leq +85°C unless otherwise specified)

INPUT CHARACTERISTICS	Limits	Units
Minimum Control Current (see figure 1)	5.0	mA
Maximum Control Current for Off-State Resistance @ T _A = +25°C	0.4	mA
Control Current Range (Caution: current limit input LED, see figure 6)	5.0 - 25	mA
Maximum Reverse Voltage (1mA max.)	6.0	V

OUTPUT CHARACTERISTICS		Limits	Units
Operating Voltage Range		0 to ±60	V(DC or AC peak)
Maximum Continuous Load Current @ T _A = +40°C, 10mA Control			
(see figure 1)	A Connection	2.0	A (AC or DC)
	B Connection	2.5	A (DC)
	C Connection	4.0	A (DC)
Maximum Pulsed Load Current @ TA =+25°C (100 ms @ 10% Duty Cycle)		
	A Connection	7.5	A (AC or DC)
	B Connection	8.5	A (DC)
	C Connection	15.5	A (DC)
Typical Thermal Resistance (Rthja, Junction-to	o-Ambient)		
	A Connection	79.1	(°C/W)
	B Connection	112.2	(°C/W)
	C Connection	81.0	(°C/W)
Maximum On-State Resistance @TA =+25°C			
For 1A pulsed load, 10mA Control (see figure 4)	A Connection	100	mΩ
	B Connection	50	mΩ
	C Connection	35	mΩ
Maximum Off-State Leakage @ 60V, TA =+25°C		1.0	μΑ
Maximum Turn-On Time @TA =+25°C (see figures 7 & 8) For 500mA, 50V _{DC} load, 10mA Control, 10mS pulse width		3.5	ms
Maximum Turn-Off Time @TA =+25°C (see figures 7 & 8) For 500mA, 50V _{DC} load, 10mA Control, 10mS pulse width		0.5	ms
Typical Output Capacitance @ Vdd=50V, f=1MHz (see figure 2)		105	pF


GENERAL CHARACTERISTICS		Limits	Units
Minimum Dielectric Strength, Input-Output		4000	V _{RMS}
Minimum Insulation Resistance, Input-Output, @Ta=+25°C, 50%RH, 100VDC		1012	Ω
Maximum Capacitance, Input-Output		1.0	pF
Maximum Pin Soldering Temperature (10 seconds maximum)		+260	
Ambient Temperature Range:	Operating	-40 to +85	°C
	Storage	-40 to +100	


International Rectifier does not recommend the use of this product in aerospace, avionics, military or life support applications. Users of this International Rectifier product in such applications assume all risks of such use and indemnify International Rectifier against all damages resulting from such use.




Connection Diagrams "A" Connection

AC or DC











Figure 1. Current Derating Curves

Figure 2. Typical Output Capacitance






Figure 3. Typical Linearity Characteristics

Figure 4. Typical Normalized On-Resistance






Figure 5. Typical Normalized Off-State Leakage




Figure 6. Input Characteristics (Current Controlled)




Figure 7. Typical Delay Times






Figure 8. Delay Time Definitions



Case Outlines





Note: For the most current drawing please refer to IR website at: http://www.irf.com/package/



Qualification information[†]

Qualification level	Industrial		
Qualification level	(per JEDEC JESD47I ^{††} guidelines)		
Moisture Sensitivity Level	PVG612APbF	N/A	
	PVG612ASPbF	MSL4	
	PVG612AS-TPbF	(per JEDEC J-STD-020E & JEDEC J-STD-033C ^{††})	
RoHS compliant		Yes	

qualification standards can be found at International Rectifier's web site: http://www.irf.com/product-info/reliability

Revision History

Date	Comments
5/4/2015	Added Qualification Information Table on page 6
	Updated data sheet with new IR corporate template



IR WORLD HEADQUARTERS: 101 N. Sepulveda Blvd., El Segundo, California 90245, USA

Data and specifications subject to change without notice

To contact International Rectifier, please visit http://www.irf.com/whoto-call/

^{††} Applicable version of JEDEC standard at the time of product release