

Technical drawing of a 3.5-inch floppy diskette, showing dimensions in millimeters [inches].

Top View:

- Overall diameter: $\varnothing 360.00$ [14.173] MAX.
- Inner diameter (hole): $\varnothing 13.52$ [.532]
- Inner diameter (hole): $\varnothing 12.80$ [.504]
- Distance from center to outer edge (top): 4.10 [.161]
- Distance from center to outer edge (bottom): 3.90 [.153]
- Distance from center to outer edge (left): 1.85 [.073]
- Distance from center to outer edge (right): 1.65 [.065]
- Distance from center to outer edge (bottom-left): 10.90 [.429]
- Distance from center to outer edge (bottom-right): 10.70 [.421]
- Distance from center to outer edge (right): 16.10 [.634]
- Distance from center to outer edge (top-right): 11.60 [.457]
- Distance from center to outer edge (bottom-right): 11.40 [.449]
- Distance from center to outer edge (right): $\varnothing 1.75$ [.069]
- Distance from center to outer edge (right): $\varnothing 1.25$ [.049]

Side View:

- Overall thickness: 15.42 [.609]
- Overall thickness: 15.22 [.601]
- Overall thickness: 24.30 [.957]
- Overall thickness: 23.90 [.941]
- Overall thickness: 4.72 [.186]
- Overall thickness: 4.52 [.178]
- Overall thickness: 0.368 [.0145]
- Overall thickness: 0.342 [.0135]

Detail View:

- Overall diameter: $\varnothing 60.00$ [3.362] MIN.
- Overall diameter: 26.40 [1.039]
- Overall diameter: 24.40 [.961]

Notes:

- OUTLINE CONFORMS TO EIA-481 & EIA-541.
- DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].

1. OUTLINE CONFORMS TO EIA-481 & EIA-541.
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].