

BGA824N6

BGA824N6 with improved rejection of
LTE Band-13 (777-787MHz) for GNSS
Applications, 0201 components

Application Note AN334

Revision: Rev.1.1
2017-05-26

Edition 2017-05-26

**Published by
Infineon Technologies AG
81726 Munich, Germany**

**© 2017 Infineon Technologies AG
All Rights Reserved.**

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Application Note AN334
Revision History: 2017-05-26
Previous Revision: Rev 1.0 (2013-07-01)

Page	Subjects (major changes since last revision)
6	Inserted description of LTE band 13 second harmonic ((B13 H2)) measurement setup
10,11	Updated Table 3, Table 4 titles
10,11	Updated measurement conditions for LTE band 13 second harmonic and results
10,11	Inserted measurement results of B13 H2 Output-referred, OIP3oob into performance summary
12	Inserted results of B13 H2 Output-referred
22	Inserted figure for B13 H2 Output-referred

Trademarks of Infineon Technologies AG

AURIX™, C166™, CanPAK™, CIPOS™, CIPURSE™, EconoPACK™, CoolMOS™, CoolSET™, CORECONTROL™, CROSSAVE™, DAVE™, DI-POL™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPIM™, EconoPACK™, EiceDRIVER™, eupec™, FCOS™, HITFET™, HybridPACK™, I²RF™, ISOFACE™, IsoPACK™, MIPAQ™, ModSTACK™, my-d™, NovalithIC™, OptiMOS™, ORIGA™, POWERCODE™, PRIMARION™, PrimePACK™, PrimeSTACK™, PRO-SIL™, PROFET™, RASIC™, ReverSave™, SatRIC™, SIEGET™, SINDRION™, SIPMOS™, SmartLEWIS™, SOLID FLASH™, TEMPFET™, thinQ!™, TRENCHSTOP™, TriCore™.

Other Trademarks

Advance Design System™ (ADS) of Agilent Technologies, AMBA™, ARM™, MULTI-ICE™, KEIL™, PRIMECELL™, REALVIEW™, THUMB™, µVision™ of ARM Limited, UK. AUTOSAR™ is licensed by AUTOSAR development partnership. Bluetooth™ of Bluetooth SIG Inc. CAT-iq™ of DECT Forum. COLOSSUS™, FirstGPS™ of Trimble Navigation Ltd. EMV™ of EMVCo, LLC (Visa Holdings Inc.). EPCOS™ of Epcos AG. FLEXGO™ of Microsoft Corporation. FlexRay™ is licensed by FlexRay Consortium. HYPERTERMINAL™ of Hilgraeve Incorporated. IEC™ of Commission Electrotechnique Internationale. IrDA™ of Infrared Data Association Corporation. ISO™ of INTERNATIONAL ORGANIZATION FOR STANDARDIZATION. MATLAB™ of MathWorks, Inc. MAXIM™ of Maxim Integrated Products, Inc. MICROTEC™, NUCLEUS™ of Mentor Graphics Corporation. MIPI™ of MIPI Alliance, Inc. MIPS™ of MIPS Technologies, Inc., USA. muRata™ of MURATA MANUFACTURING CO., MICROWAVE OFFICE™ (MWO) of Applied Wave Research Inc., OmniVision™ of OmniVision Technologies, Inc. Openwave™ Openwave Systems Inc. RED HAT™ Red Hat, Inc. RFMD™ RF Micro Devices, Inc. SIRIUS™ of Sirius Satellite Radio Inc. SOLARIS™ of Sun Microsystems, Inc. SPANSION™ of Spansion LLC Ltd. Symbian™ of Symbian Software Limited. TAIYO YUDEN™ of Taiyo Yuden Co. TEAKLITE™ of CEVA, Inc. TEKTRONIX™ of Tektronix Inc. TOKO™ of TOKO KABUSHIKI KAISHA TA. UNIX™ of X/Open Company Limited. VERILOG™, PALLADIUM™ of Cadence Design Systems, Inc. VLYNQ™ of Texas Instruments Incorporated. VXWORKS™, WIND RIVER™ of WIND RIVER SYSTEMS, INC. ZETEX™ of Diodes Zetex Limited.

Last Trademarks Update 2011-11-11

Table of Content

1	Introduction of Global Navigation Satellite Systems (GNSS)	5
2	BGA824N6 Overview	8
2.1	Features	8
2.2	Key Applications of BGA824N6	8
2.3	Description	8
3	Application Circuit and Performance Overview	10
3.1	Summary of Measurement Results.....	10
3.2	Summary BGA824N6 as 1550-1615 MHz LNA for GNSS.....	12
3.3	Schematics and Bill-of-Materials.....	13
4	Measurement Graphs	14
5	Evaluation Board and Layout Information	23
6	Authors	25
7	Remark	25

List of Figures

Figure 1	BGA824N6 TSNP-6-2 leadless Package size	7
Figure 2	BGA824N6 in TSNP-6-2	8
Figure 3	Equivalent Circuit Block diagram of BGA824N6	9
Figure 4	Package and pin connections of BGA824N6	9
Figure 5	Schematic of the BGA824N6 Application Circuit	13
Figure 6	Power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands	14
Figure 7	Narrowband power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands	14
Figure 8	Noise figure of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands	15
Figure 9	Input matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands.....	15
Figure 10	Input matching smith chart for COMPASS, Galileo, GPS and GLONASS bands	16
Figure 11	Output matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands.....	16
Figure 12	Output matching smith chart for COMPASS, Galileo, GPS and GLONASS bands	17
Figure 13	Reverse isolation of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands.....	17
Figure 14	Stability factor k of BGA824N6 upto 10 GHz	18
Figure 15	Stability factor μ_1 of BGA824N6 upto 10 GHz	18
Figure 16	Stability factor μ_2 of BGA824N6 upto 10 GHz	19
Figure 17	Input 1 dB compression point of BGA824N6 at supply voltage of 1.8 V for COMPASS, Galileo, GPS and GLONASS bands	19
Figure 18	Input 1 dB compression point of BGA824N6 at supply voltage of 2.8 V for COMPASS, Galileo, GPS and GLONASS bands	20
Figure 19	Carrier and intermodulation products of BGA824N6 for GPS band at $V_{cc}=1.8$ V	20
Figure 20	Carrier and intermodulation products of BGA824N6 for GPS band at $V_{cc}=2.8$ V	21
Figure 21	Carrier and intermodulation products of BGA824N6 for GLONASS band at $V_{cc}=2.8$ V	21
Figure 22	Picture of Evaluation Board (overview)	23
Figure 23	Picture of Evaluation Board (detailed view)	23
Figure 24	PCB Layer Information.....	24

List of Tables

Table 1	Pin Assignment of BGA824N6	9
Table 2	Pin Assignment of BGA824N6	9
Table 3	Electrical Characteristics for COMPASS/Galileo at $V_{cc} = V_{pon} = 1.8$ V	10
Table 4	Electrical Characteristics for COMPASS/Galileo at $V_{cc} = V_{pon} = 2.8$ V	11
Table 5	Bill-of-Materials.....	13

1 Introduction of Global Navigation Satellite Systems (GNSS)

The BGA824N6 is a front-end Low Noise Amplifier (LNA) for Global Navigation Satellite Systems (GNSS) application. It is based on Infineon Technologies' B7HF Silicon-Germanium (SiGe) technology, enabling a cost-effective solution in a TSNP-6-2 leadless package with ultra low noise figure, high linearity, low current consumption and high gain, over a wide range of supply voltages from 1.5 V up to 3.6 V. All these features make BGA824N6 an excellent choice for GNSS LNA as it improves sensitivity, provide better immunity against out-of-band jammer signals, reduces filtering requirement and hence the overall cost of the GNSS receiver.

The GNSS satellites are at an orbit altitude of more than 20,000 km away from earth's surface and transmit power in the range of +47 dBm. After taking losses (atmospheric, antenna etc.) into account, the received signal strength at the GNSS device input is very low in the range of -130 dBm. The ability of the GNSS device to receive such low signal strength and provide meaningful information to the end-user depends strongly on the noise figure of the GNSS receives chain. This ability which is called receiver sensitivity can be improved by using a low-noise amplifier with low noise figure and high gain at the input of the receiver chain. The improved sensitivity results in a shorter Time-To-First-Fix (TTFF), which is the time required for a GNSS receiver to acquire satellite signals and navigation data, and calculate a position. Noise figure of the LNA defines the overall noise figure of the GNSS receiver system. This is where BGA824N6 excels by providing noise figure as low as 0.55 dB and high gain of 17 dB, thereby improving the receiver sensitivity significantly.

The ever growing demand to integrate more and more functionality into one device leads to many challenges when transmitter/receiver has to work simultaneously without degrading the performance of each other. In today's smart-phones a GNSS receiver simultaneously co-exists with transceivers in the GSM/EDGE/UMTS/LTE bands. These 3G/4G transceivers transmit high power in the range of +24 dBm which due to insufficient isolation couple to the GNSS receiver. The cellular signals can mix to produce Intermodulation products exactly in the GNSS receiver frequency band. For example, GSM 1712.7 MHz mixes with UMTS 1850 MHz to produce third-order-product exactly at GPS band. To quantify the effect, BGA824N6

shows out-of-band input IP3 at GPS band of +7 dBm, as a result of frequency mixing between GSM 1712.7 MHz and UMTS 1850 MHz with power levels of -20 dBm. Due to this high out-of-band input 3rd order intercept point (IIP3), BGA824N6 is especially suitable for the GPS function in mobile phones.

Another major interference signal at the GNSS frequency band is the presence of LTE band 13 second harmonics. For example, a jammer signal from 787 MHz will generate a second harmonic signal at 1574 MHz, and thus add interference to the wanted GNSS signal. In this application note, we measure the influence of LTE band 13 second harmonic with below setup. The bandpass filter before the Device-under-test (DUT) is intended to let through the Band 13 signal, and to filter out the second harmonic generated by the signal generator. The attenuator is used to improve the mismatch at the B13 frequency. The bandpass filter after the Device-under-test is intended to let through the GNSS signal while filtering out the B13 frequency from the DUT output. The attenuator is used to improve the mismatch at the B13 frequency. In below application note, the losses from BPF2 and Attenuator 2 after DUT have been compensated, when measuring the B13 H2out for Table 3 and Table 4.




Figure 1 Measurement setup for LTE Band 13 second harmonic

As the industry inclines toward assembly miniaturization and also surface mount technology matures, there is a desire to have smaller and thinner components. This is especially the case with portable electronics where higher circuit density allows device design flexibility and also optimum use of the limited space available. BGA824N6 has a small package with dimensions of 0.70mm x 1.1mm x 0.375mm and it requires only one external component at

its input, the inductor providing the input matching. The DC block at input is optional as it is usually provided by the pre-filter before the LNA in many GPS applications. All the device/phone manufacturers implement very good power supply filtering on their boards so that the RF bypass capacitor mentioned in this application circuit may not be needed in the end. The minimal number of external SMD components reduces the application bill of materials, assembly complexity and the PCB area thus making it an ideal solution for compact and cost-effective GNSS LNA. The output of the BGA824N6 is internally matched to 50 Ω, and a DC blocking capacitor is integrated on-chip, thus no external component is required at the output.




Figure 2 BGA824N6 TSNP-6-2 leadless package size

The device also integrates an on-chip ESD protection which can resist until 2 kV (referenced to human body model) in all pins. The integrated power on/off feature provides for low power consumption and increased stand-by time for GNSS handsets. Moreover, the low current consumption (3.8 mA) makes the device suitable for portable technology like GNSS receivers and mobiles phones.

The Internal circuit block diagram of the BGA824N6 is presented in Figure 4. Table 1 shows the pin assignment of BGA824N6. Table 2 shows the truth table to turn on/off BGA824N6 by applying different voltage to the PON pin.

2 BGA824N6 Overview

2.1 Features

- High insertion power gain: 17.0 dB
- Out-of-band input 3rd order intercept point: +7 dBm
- Input 1 dB compression point: -6 dBm
- Low noise figure: 0.55 dB
- Low current consumption: 3.8 mA
- Operating frequencies: 1550 - 1615 MHz
- Supply voltage: 1.5 V to 3.6 V
- Digital on/off switch (1 V logic high level)
- Ultra small TSNP-6-2 leadless package (footprint: 0.7 x 1.1 mm²)
- B7HF Silicon Germanium technology
- RF output internally matched to 50 Ω
- Only 1 external SMD component necessary
- 2 kV HBM ESD protection (including AI-pin)
- Pb-free (RoHS compliant) package




Figure 3 BGA824N6 in TSNP-6-2



2.2 Key Applications of BGA824N6

- Ideal for all Global Navigation Satellite Systems (GNSS) like
 - GPS (Global Positioning System) working in the L1 band at 1575.42 MHz
 - GLONASS (Russian GNSS) working in the L1 band from 1598.06 MHz to 1605.38 MHz
 - Galileo (European GNSS) working in the E2-L1-E1 band from 1559 MHz to 1592 MHz
 - COMPASS (Chinese Beidou Navigation System) working in E2 band at 1561.10 MHz and E1 band at 1589.74 MHz

2.3 Description

The BGA824N6 is a front-end low noise amplifier for Global Navigation Satellite Systems (GNSS) from 1550 MHz to 1615 MHz like GPS, GLONASS, Beidou, Galileo and others. The LNA provides 17.0 dB gain and 0.55 dB noise figure at a current consumption of 3.8 mA in the application configuration described in **Chapter 3**. The BGA824N6 is based upon Infineon Technologies B7HF Silicon Germanium technology. It operates from 1.5 V to 3.6 V supply voltage.




Figure 4 Equivalent Circuit Block diagram of BGA824N6




Figure 5 Package and pin connections of BGA824N6

Table 1 Pin Assignment of BGA824N6

Pin No.	Symbol	Function
1	GND	Ground
2	VCC	DC supply
3	AO	LNA output
4	GND	Ground
5	AI	LNA input
6	PON	Power on control

Table 2 Pin Assignment of BGA824N6

LNA Mode	Symbol	ON/OFF Control Voltage at PON pin	
		Min	Max
ON	PON, on	1.0 V	VCC
OFF	PON, off	0 V	0.4 V

3 Application Circuit and Performance Overview

Device: BGA824N6

Application: BGA824N6 with improved rejection of LTE Band-13 (777-787 MHz) for GNSS Applications, 0201 components

PCB Marking: BGA824N6

3.1 Summary of Measurement Results

Table 3 Electrical Characteristics for GNSS Applications at $V_{cc} = V_{pon} = 1.8\text{ V}$

Parameter	Symbol	Value			Unit	Comment/Test Condition
DC Voltage	Vcc	1.8			V	
DC Current	Icc	3.9			mA	
Navigation System	Sys	COMPASS/ Galileo	GPS	GLONASS		
Frequency Range	Freq	1559-1593	1575.42	1598-1606	MHz	
Gain	G	16.4	16.3	16.2	dB	
Noise Figure	NF	0.89	0.88	0.86	dB	PCB and SMA losses 0.08 dB are subtracted
Input Return Loss	RLin	11.1	11	11.1	dB	
Output Return Loss	RLout	31	29.8	22.8	dB	
Reverse Isolation	IRev	23	23	23	dB	
Input P1dB	IP1dB	-10.1	-10.1	-9.8	dBm	$f_{gal} = 1559\text{ MHz}$
Output P1dB	OP1dB	5.3	5.2	5.4	dBm	$f_{gps} = 1575.42\text{ MHz}$ $f_{GLONASS} = 1605\text{ MHz}$
Input IP3 In-band	IIP3	-7.4	-7.2	-6.7	dBm	$f_{1gal} = 1559\text{ MHz}$, $f_{2gal} = 1560\text{ MHz}$ $f_{1gps} = 1575.42\text{ MHz}$,
Output IP3 In-band	OIP3	9	9.1	9.5	dBm	$f_{2gps} = 1576.42\text{ MHz}$ $f_{1GLONASS} = 1602\text{ MHz}$, $f_{2GLONASS} = 1603\text{ MHz}$ $P_{IN} = -35\text{ dBm}$
LTE Band-13 2 nd Harmonic input referred	B13 H2in	-111.5			dBm	Calculated based on B13 H2out and Gain@ f_{H2}
LTE Band-13 2 nd Harmonic output referred	B13 H2out	-95.2			dBm	$f_{IN} = 787\text{ MHz}$, $P_{IN} = -25\text{ dBm}$; $f_{H2} = 1574\text{ MHz}$
Input IP3 Out-of-band	IIP3 _{OOB}	7.3			dBm	$f_1 = 1712.7\text{ MHz}$, $P_{1IN} = -25\text{ dBm}$; $f_2 = 1850\text{ MHz}$, $P_{2IN} = -65\text{ dBm}$; $f_{IIP3} = 1575.4\text{ MHz}$

Table 3 Electrical Characteristics for GNSS Applications at Vcc = Vpon = 1.8 V

Parameter	Symbol	Value	Unit	Comment/Test Condition
Output IP3 Out-of-band	OIP3 _{OOB}	23.6	dBm	
Stability	k	>1	--	Unconditionnally Stable from 0 to 10GHz

Table 4 Electrical Characteristics for GNSS Applications at Vcc = Vpon = 2.8 V

Parameter	Symbol	Value			Unit	Comment/Test Condition
DC Voltage	Vcc	2.8			V	
DC Current	Icc	4.0			mA	
Navigation System	Sys	COMPASS/ Galileo	GPS	GLONASS		
Frequency Range	Freq	1559-1593	1575.42	1598-1606	MHz	
Gain	G	16.5	16.4	16.3	dB	
Noise Figure	NF	0.89	0.88	0.86	dB	PCB and SMA losses 0.08dB are subtracted
Input Return Loss	RLin	11.2	11.2	11.2	dB	
Output Return Loss	RLout	34.3	27.2	20.9	dB	
Reverse Isolation	IRev	24	24	24	dB	
Input P1dB	IP1dB	-8.9	-8.7	-8	dBm	f _{gal} = 1559 MHz
Output P1dB	OP1dB	6.6	6.7	7.7	dBm	f _{gps} = 1575.42 MHz f _{GLONASS} = 1605 MHz
Input IP3 In-band	IIP3	-7.3	-7.1	-6.7	dBm	f _{1gal} = 1559 MHz, f _{2gal} = 1560 MHz f _{1gps} = 1575.42 MHz,
Output IP3 In-band	OIP3	7.6	9.3	9.6	dBm	f _{2gps} = 1576.42 MHz f _{1GLO} = 1602MHz, f _{2GLO} = 1603MHz P _{IN} = -35 dBm
LTE Band-13 2 nd Harmonic input referred	B13 H2in	-111.7			dBm	Calculated based on B13 H2out and Gain@f _{H2}
LTE Band-13 2 nd Harmonic output referred	B13 H2out	-95.3			dBm	f _{IN} = 787 MHz, P _{IN} = -25 dBm; f _{H2} = 1574 MHz
Input IP3 Out-of-band	IIP3 _{OOB}	7.4			dBm	f ₁ = 1712.7 MHz, P _{1IN} = -25 dBm; f ₂ = 1850 MHz, P _{2IN} = -65 dBm;
Output IP3 Out-of-band	OIP3 _{OOB}	23.8			dBm	f _{IIP3} = 1575.4 MHz
Stability	k	>1			--	Unconditionnally Stable from 0 to 10GHz

3.2 Summary BGA824N6 as 1550-1615 MHz LNA for GNSS

This application note addresses the issue of out-of-band jammers and improving the immunity of BGA824N6 against LTE Band-13 jammers.

The jamming resistance of BGA824N6 against B13 jammer is improved by increasing the attenuation of the circuit at Band-13 (777-787 MHz). This is achieved by placing a notch filter using external SMDs before BGA824N6. The component values are fine tuned so as to have optimal noise figure, jammer rejection, gain and input matching. The circuit requires only three 0201 passive components including the notch filters.

At 2.8 V, the circuit provides inband gain of 16.5 dB. It achieves input return loss better than 11 dB, as well as output return loss better than 20 dB. At room temperature the noise figure is 0.88 dB (SMA and PCB losses are subtracted) for the GPS frequency. Furthermore, the circuit is unconditionally stable till 10 GHz.

At 2.8 V, using two tones spacing of 1 MHz, the output third order intercept point OIP3 at GPS frequency band is 9.3 dBm. And for the GLONASS frequency band, the OIP3 reaches 9.6 dBm. Input P1dB of the GNSS LNA is about -8.7 dBm for the GPS frequency and -8 dBm for GLONASS frequency band. In presence of the jammer signal from LTE Band-13 frequency, this circuit shows very low level of second harmonic (H2) of -95.3 dBm (LNA output referred) at the GPS frequency.

3.3 Schematics and Bill-of-Materials




Figure 6 Schematic of the BGA824N6 Application Circuit

Table 5 Bill-of-Materials

Symbol	Value	Unit	Size	Manufacturer	Comment
C1	1.8	pF	0201	Various	DC block/Input matching
L1	6.8	nH	0201	Murata LQP type	Input matching and 787.76 MHz Notch
C2	5.6	pF	0201	Various	Input matching and 787.76 MHz Notch
C3 (optional)	10	nF	0201	Various	RF bypass
N1	BGA824N6		TSNP-6-2	Infineon	SiGe LNA

4 Measurement Graphs




Figure 7 Power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




Figure 8 Narrowband power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




Figure 9 Noise figure of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




Figure 10 Input matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




Figure 11 Input matching smith chart for COMPASS, Galileo, GPS and GLONASS bands




Figure 12 Output matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




Figure 13 Output matching smith chart for COMPASS, Galileo, GPS and GLONASS bands




Figure 14 Reverse isolation of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




Figure 15 Stability factor k of BGA824N6 upto 10 GHz




Figure 16 Stability factor μ_1 of BGA824N6 upto 10 GHz




Figure 17 Stability factor μ_2 of BGA824N6 upto 10 GHz




Figure 18 Input 1 dB compression point of BGA824N6 at supply voltage of 1.8 V for COMPASS, Galileo, GPS and GLONASS bands




Figure 19 Input 1 dB compression point of BGA824N6 at supply voltage of 2.8 V for COMPASS, Galileo, GPS and GLONASS bands




Figure 20 Carrier and intermodulation products of BGA824N6 for GPS band at Vcc=1.8 V




Figure 21 Carrier and intermodulation products of BGA824N6 for GPS band at Vcc=2.8 V




Figure 22 Carrier and intermodulation products of BGA824N6 for GLONASS band at Vcc=2.8 V




Figure 23 LTE Band 13 second harmonic at Vcc=2.8 V, 1574 MHz (LNA output referred)

5 Evaluation Board and Layout Information

In this application note, the following PCB is used:

PCB material: FR4

ϵ_r of PCB material: 4.3




Figure 24 Picture of Evaluation Board (overview)




Figure 25 Picture of Evaluation Board (detailed view)




Figure 26 PCB Layer Information

6 Authors

Moakhkhrul Islam, Application Engineer of Business Unit “RF and Protection Devices”.
Jagjit Singh Bal, Application Engineer of Business Unit “RF and Protection Devices”
Xiang Li, Application Engineer of Business Unit “RF and Protection Devices”

7 Remark

The graphs are generated with the simulation program AWR Microwave Office®.

www.infineon.com