

Automotive MOSFET

OptiMOS™ 7 Power-Transistor

PG-HSOF-8

Features

- OptiMOS™ power MOSFET for automotive applications
- N-channel - Enhancement mode - Normal Level
- Extended qualification beyond AEC-Q101
- Enhanced electrical testing
- Robust design
- MSL1 up to 260°C peak reflow
- 175°C operating temperature
- RoHS compliant
- 100% Avalanche tested

Potential applications

General automotive applications.



Product validation

Qualified for Automotive applications.

Product validation according to AEC-Q101.

Table 1 Key performance parameters

Parameter	Value	Unit
V_{DS}	80	V
$R_{DS(on)}$	1.14	mΩ
I_D (chip limited)	330	A



Part number	Package	Marking	Related links
IAUTN08S7N011	PG-HSOF-8	7N08N011	see Appendix A

Table of contents

Description	1
Maximum ratings	3
Thermal characteristics	4
Electrical characteristics	4
Electrical characteristics diagrams	6
Test circuits	10
Package outlines	11
Appendix A	14
Revision history	15
Trademarks	16
Disclaimer	16

1 Maximum ratings

at $T_j=25\text{ °C}$, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Continuous drain current	I_D	-	-	330	A	Chip limitation, $V_{GS} = 10\text{ V}$ ^{1) 2)}
				330		DC current, $V_{GS} = 10\text{ V}$
				45		R_{thJA} on 2s2p, $V_{GS} = 10\text{ V}$, $T_a = 100\text{ °C}$ ^{1) 3)}
Pulsed drain current ¹⁾	$I_{D,pulse}$	-	-	1154	A	$T_C = 25\text{ °C}$, $t_p = 100\text{ }\mu\text{s}$
Avalanche energy, single pulse ¹⁾	E_{AS}	-	-	324	mJ	$I_D = 97\text{ A}$
Avalanche current, single pulse	I_{AS}	-	-	194	A	-
Gate source voltage	V_{GS}	-20	-	20	V	
Power dissipation	P_{tot}	-	-	268	W	$T_C = 25\text{ °C}$
Operating temperature	T_j	-55	-	175	°C	-

¹⁾ The parameter is not subject to production testing - specified by design.

²⁾ The current is limited by the overall system design, including the customer-specific PCB.

³⁾ Device on 2s2p FR4 PCB defined in accordance with JEDEC standards (JESD51-5, -7). PCB is vertical in still air.

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case 4)	R_{thJC}	-	-	0.56	K/W	-
Thermal resistance, junction - ambient 5) 4)	R_{thJA}		15	-		

4) The parameter is not subject to production testing - specified by design.

5) Device on 2s2p FR4 PCB defined in accordance with JEDEC standards (JESD51-5, -7). PCB is vertical in still air.

3 Electrical characteristics

at $T_j = 25^\circ\text{C}$, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	80	-	-	V	$I_D = 1\text{ mA}$, $V_{GS} = 0\text{ V}$
Gate threshold voltage	$V_{GS(th)}$	2.3	2.8	3.2	V	$V_{DS} = V_{GS}$, $I_D = 175\text{ }\mu\text{A}$
Zero gate voltage drain current	I_{DSS}	-	-	1	μA	$V_{DS} = 80\text{ V}$, $T_j = 25^\circ\text{C}$, $V_{GS} = 0\text{ V}$
				44		$V_{DS} = 80\text{ V}$, $T_j = 100^\circ\text{C}$, $V_{GS} = 0\text{ V}$ ⁶⁾
Gate-source leakage current	I_{GSS}	-	-	100	nA	$V_{DS} = 0\text{ V}$, $V_{GS} = 20\text{ V}$
Drain-source on-state resistance	$R_{DS(on)}$	-	1.18	1.32	m Ω	$I_D = 50\text{ A}$, $V_{GS} = 7\text{ V}$
			1.06	1.14		$I_D = 100\text{ A}$, $V_{GS} = 10\text{ V}$
Gate resistance ⁶⁾	R_G	-	1.2	-	Ω	-

6) The parameter is not subject to production testing - specified by design.

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Input capacitance ⁷⁾	C_{iss}	-	8690	11290	pF	$V_{DS} = 40\text{ V}$, $V_{GS} = 0\text{ V}$, $f = 1\text{ MHz}$
Output capacitance ⁷⁾	C_{oss}		3510	4560		
Reverse transfer capacitance ⁷⁾	C_{rss}		36	55		
Turn-on delay time ⁷⁾	$t_{d(on)}$	-	30	-	ns	$I_D = 100\text{ A}$, $V_{GS} = 10\text{ V}$, $V_{DD} = 40\text{ V}$, $R_G = 3.5\ \Omega$
Rise time ⁷⁾	t_r		27			
Turn-off delay time ⁷⁾	$t_{d(off)}$		68			
Fall time ⁷⁾	t_f		35			

⁷⁾ The parameter is not subject to production testing - specified by design.

Table 6 Gate Charge Characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Gate to source charge ⁸⁾	Q_{gs}	-	40	52	nC	$I_D = 100\text{ A}$, $V_{DS} = 40\text{ V}$, $V_{GS} = 0\text{ V to } 10\text{ V}$
Gate to drain charge ⁸⁾	Q_{gd}		23	35	nC	
Gate charge total ⁸⁾	Q_g		126	163	nC	
Gate plateau voltage ⁸⁾	$V_{plateau}$		4.6	-	V	

⁸⁾ The parameter is not subject to production testing - specified by design.


Table 7 Reverse Diode

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Diode continuous forward current ⁹⁾	I_S	-	-	330	A	$T_C = 25\text{ °C}$
Diode pulse current ⁹⁾	$I_{S,pulse}$	-	-	1154	A	$T_C = 25\text{ °C}$, $t_p = 100\ \mu\text{s}$
Diode forward voltage	V_{SD}	-	0.85	0.95	V	$T_j = 25\text{ °C}$, $V_{GS} = 0\text{ V}$, $I_F = 100\text{ A}$
Reverse recovery time ⁹⁾	t_{rr}	-	52	78	ns	$di_F/dt = 100\text{ A}/\mu\text{s}$, $V_R = 40\text{ V}$, $I_F = 50\text{ A}$
Reverse recovery charge ⁹⁾	Q_{rr}		46	92	nC	

⁹⁾ The parameter is not subject to production testing - specified by design.


4 Electrical characteristics diagrams

Diagram 1: Power dissipation




$$P_{tot}=f(T_c); V_{GS} \geq 6 \text{ V}$$

Diagram 2: Drain Current




$$I_D=f(T_c); V_{GS} \geq 6 \text{ V}$$

Diagram 3: Safe operating area




$$I_D=f(V_{DS}); T_c=25^\circ\text{C}; D=0; \text{parameter: } t_p$$

Diagram 4: Max. transient thermal impedance




$$Z_{thjC}=f(t_p); \text{parameter: } D=t_p/T$$

Diagram 5: Typ. output characteristics




$I_D = f(V_{DS})$; $T_j = 25^\circ\text{C}$; parameter: V_{GS}

Diagram 6: Typ. drain-source on-state resistance




$R_{DS(on)} = f(I_D)$; $T_j = 25^\circ\text{C}$; parameter: V_{GS}

Diagram 7: Typ. transfer characteristics




$I_D = f(V_{GS})$; $V_{DS} = 6\text{ V}$; parameter: T_j

Diagram 8: Typ. drain-source on-state resistance




$R_{DS(on)} = f(T_j)$; parameter: I_D , V_{GS}

Diagram 9: Typ. gate threshold voltage




$$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}; \text{parameter: } I_D$$

Diagram 10: Typ. capacitances




$$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 1 \text{ MHz}$$

Diagram 11: Typ. forward diode characteristics




$$I_F = f(V_{SD}); \text{parameter: } T_j$$

Diagram 12: Typ. avalanche characteristics




$$I_{AS} = f(t_{AV}); \text{parameter: } T_{j(\text{start})}$$

Diagram 13: Typical avalanche Energy




$E_{AS}=f(T_j)$; parameter: I_D

Diagram 14: Drain-source breakdown voltage



$V_{(Br)DSS}=f(T_j)$; $I_D=1\text{ mA}$

Diagram 15: Typ. gate charge



$V_{GS}=f(Q_{gate})$; $I_D=100\text{ A}$ pulsed; parameter: V_{DD}

5 Test circuits

Table 8 Diode characteristics




Table 9 Unclamped inductive load test circuit






Table 10 Switching times test circuit for resistive load



6 Package outlines



1) Lead length up to anti flash profile; mold flashes excluded.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0,1$; $\pm 1^\circ 30'$

Figure 1 Outline PG-HSOF-8, dimensions in mm





Figure 2 Footprint drawing PG-HSOF-8, dimensions in mm



All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Figure 3 Packaging variant PG-HSOF-8, dimensions in mm

7 Appendix A

Table 11 **Related links**

- IFX Optimos™ Power-Transistor Webpage

Revision history

IAUTN08S7N011

Revision 2026-09-28, Rev. 1.0

Previous revisions

Revision	Date	Subjects (major changes since last revision)
1.0	2026-09-28	final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Published by Infineon Technologies AG, Am Campeon 1-15, 85579 Neubiberg, Germany
Copyright (c) 2026 Infineon Technologies AG and its affiliates. All Rights Reserved.

Important notice

Products which may also include samples and may be comprised of hardware or software or both ("Product(s)") are sold or provided and delivered by Infineon Technologies AG and its affiliates ("Infineon") subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

For the avoidance of doubt, Infineon disclaims all warranties of non-infringement of third-party rights and implied warranties such as warranties of fitness for a specific use/purpose or merchantability.

Infineon shall not be responsible for any information with respect to samples, the application or customer's specific use of any Product or for any examples or typical values given in this document.

The data contained in this document is exclusively intended for technically qualified and skilled customer representatives. It is the responsibility of the customer to evaluate the suitability of the Product for the intended application and the customer's specific use and to verify all relevant technical data contained in this document in the intended application and the customer's specific use. The customer is responsible for properly designing, programming, and testing the functionality and safety of the intended application, as well as complying with any legal requirements related to its use.

Unless otherwise explicitly approved by Infineon, Products may not be used in any application where a failure of the Products or any consequences of the use thereof can reasonably be expected to result in personal injury. However, the foregoing shall not prevent the customer from using any Product in such fields of use that Infineon has explicitly designed and sold it for, provided that the overall responsibility for the application lies with the customer.

Infineon expressly reserves the right to use its content for commercial text and data mining (TDM) according to applicable laws, e.g. Section 44b of the German Copyright Act (UrhG).

If the Product includes security features: Because no computing device can be absolutely secure, and despite security measures implemented in the Product, Infineon does not guarantee that the Product will be free from intrusion, data theft or loss, or other breaches ("Security Breaches"), and Infineon shall have no liability arising out of any Security Breaches.

If this document includes or references software:

The software is owned by Infineon under the intellectual property laws and treaties of the United States, Germany, and other countries worldwide. All rights reserved. Therefore, you may use the software only as provided in the software license agreement accompanying the software. If no software license agreement applies, Infineon hereby grants you a personal, non-exclusive, non-transferable license (without the right to sublicense) under its intellectual property rights in the software (a) for software provided in source code form, to modify and reproduce the software solely for use with Infineon hardware products, only internally within your organization, and (b) to distribute the software in binary code form externally to end users, solely for use on Infineon hardware products. Any other use, reproduction, modification, translation, or compilation of the software is prohibited.

For further information on the Product, technology, delivery terms and conditions, and prices, please contact your nearest Infineon office or visit <https://www.infineon.com>.