

Eval-iSSI20B11F user guide

Infineon coreless-transformer advanced solid-state isolator

About this document

Scope and purpose

This user guide describes the functionalities and key features of Infineon's coreless-transformer advanced solid-state isolator.

Infineon SSI evaluation board EVAL-iSSI20B11F features the coreless-transformer advanced solid-state isolator, iSSI20B11F. This user guide covers the design revision 1.0 of this evaluation board.

iSSI20B11F is certified as per UL 1577.

Intended audience

- Engineers who want to learn how to use Infineon's SSI advanced iSSI20B11F
- Experienced design engineers who design circuits with photovoltaic isolators (PVI), IGBTs, and MOSFETs
- Design engineers who develop solid-state relays

About this product group

Target applications

- [Solid-state relay \(SSR\) modules](#)
- [Low voltage building automation](#)
- [Laboratory power supplies](#)
- [Telecom infrastructure](#)
- [Industrial automation - PLC I/O](#)
- Test and measurement systems
- Photovoltaic isolator Replacement

Product family

Infineon's iSSI20B03F belongs to the advanced solid-state isolator (SSI) family, using coreless-transformer technology. The Infineon SSI family provides powerful energy transmission over a galvanic isolation barrier to drive the gates of MOS-controlled power transistors, such as CoolMOS™, OptiMOS™, or TRENCHSTOP™ IGBT. The output side of the Infineon SSI family does not require a dedicated voltage supply to drive the power transistor's gate. The output side offers advanced control functions such as fast turn-on, fast turn-off, overcurrent protection and over-temperature protection to easily and safely build up solid-state relays for various applications.

Evaluation board

EVAL-iSSI20B11F is designed based on environmental conditions described in this document. It has been tested as described in this document, but not qualified regarding manufacturing, lifetime, or over the full range of ambient operating conditions. The boards provided by Infineon are not subject to full production tests.

Eval-iSSI20B11F user guide

Infineon coreless-transformer advanced solid-state isolator

About this product group

Evaluation boards are not subject to the same procedures as regular products regarding returned material analysis (RMA), process change notification (PCN), and product discontinuation (PD). Evaluation boards are intended to be used under laboratory conditions and by trained specialists only.

Note: The PCB and auxiliary circuits are NOT optimized for final customer design.

Safety precautions

Safety precautions

Note: The following warnings regarding the hazards associated with development systems

Table 1 Safety precautions

	Warning: The DC link potential of this board is up to 1000 VDC. When measuring voltage waveforms by oscilloscope, high voltage differential probes must be used. Failure to do so may result in personal injury or death.
	Warning: The evaluation or reference board contains DC bus capacitors which take time to discharge after removal of the main supply. Before working on the drive system, wait five minutes for capacitors to discharge to safe voltage levels. Failure to do so may result in personal injury or death. Darkened display LEDs are not an indication that capacitors have discharged to safe voltage levels.
	Warning: The evaluation or reference board is connected to the grid input during testing. Hence, high-voltage differential probes must be used when measuring voltage waveforms by oscilloscope. Failure to do so may result in personal injury or death. Darkened display LEDs are not an indication that capacitors have discharged to safe voltage levels.
	Warning: Remove or disconnect power from the drive before you disconnect or reconnect wires, or perform maintenance work. Wait five minutes after removing power to discharge the bus capacitors. Do not attempt to service the drive until the bus capacitors have discharged to zero. Failure to do so may result in personal injury or death.
	Caution: The heat sink and device surfaces of the evaluation or reference board may become hot during testing. Hence, necessary precautions are required while handling the board. Failure to comply may cause injury.
	Caution: Only personnel familiar with the drive, power electronics and associated machinery should plan, install, commission and subsequently service the system. Failure to comply may result in personal injury and/or equipment damage.
	Caution: The evaluation or reference board contains parts and assemblies sensitive to electrostatic discharge (ESD). Electrostatic control precautions are required when installing, testing, servicing or repairing the assembly. Component damage may result if ESD control procedures are not followed. If you are not familiar with electrostatic control procedures, refer to the applicable ESD protection handbooks and guidelines.
	Caution: A drive that is incorrectly applied or installed can lead to component damage or reduction in product lifetime. Wiring or application errors such as undersizing the motor, supplying an incorrect or inadequate AC supply, or excessive ambient temperatures may result in system malfunction.
	Caution: The evaluation or reference board is shipped with packing materials that need to be removed prior to installation. Failure to remove all packing materials that are unnecessary for system installation may result in overheating or abnormal operating conditions.

Table of contents

Table of contents

About this document.....	1
About this product group.....	1
Safety precautions.....	3
Table of contents.....	4
1 Overview and key features	5
2 Absolute maximum ratings, operating conditions, and supply voltages	6
3 Getting started with EVAL-iSSI20B11F	7
3.1 Overcurrent protection	8
3.2 Over-temperature protection (optional)	8
3.3 Connectors and pin assignment	8
3.4 Board options	9
3.5 EMI options	9
4 Schematic diagram.....	10
5 Layout	11
6 Bill of materials.....	12
7 Related resources	14
References.....	15
Revision history.....	16
Disclaimer.....	17

1 Overview and key features

1 Overview and key features

EVAL-iSSI20B11F is intended for evaluating the product features of Infineon's SSI iSSI20B11F, in an application circuit. The key features of the board and the iSSI20B11F are as follows:

- Evaluation board with **iSSI20B11F** and two **CoolMOS™ IPT60R065S7** MOSFETs in an AC switch configuration
- Ultra-fast overcurrent detection that is triggered at the typical peak current of 9 A
- Over-temperature protection with PTC resistor (optional)
- Fast turn-on
- Fast turn-off after overcurrent and over-temperature protection




Figure 1 EVAL-iSSI20B11F evaluation board

This board is best suited for testing the switching performance of Infineon SSI and **CoolMOS™ S7** as described in section 3. It requires additional considerations about thermal and power balance for continuous operation.

The control interface can be connected to a pulse generator, a microcontroller, or other digital circuits with appropriate driving capability of at least 25 mA.

2 Absolute maximum ratings, operating conditions, and supply voltages

2 Absolute maximum ratings, operating conditions, and supply voltages

Some components on the evaluation boards as well as Infineon's SSI have defined operating conditions and maximum ratings to avoid damage to individual parts and the overall evaluation board.

Table 2 Absolute maximum ratings

Pin name / parameter	Connector / symbol	Minimum	Maximum	Unit	Note
VSUP	X2.1	-10	5.3	V	Input, Infineon SSI voltage supply
INP	X4.2	-10	15	V	Input, digital signal
HV-AC1 HV-AC2	X1 X5	-320	320	V	Input, high-voltage power supply. For 42 V and above, special high-voltage lab environment is strongly recommended
RMS current	X1/X5	–	2	A	–
DC current	X1/X5	–	2	A	–
AC1 peak current AC2 peak current	X1 X5	–	9	A	Phase peak current for overcurrent protection test (tpulse < 20 µs)
Switching frequency	f _{sw}	–	1	Hz	Maximum switching frequency for continuous operation. Power dissipation required for power transistor and Infineon SSI has been carefully considered
Ambient temperature	T _a	–	30	°C	–

The PCB assembly is optimized for a VSUP voltage supply of 5 V. Higher supply voltages may require adjustments to the current limiting resistor, R1.

Table 3 Operating conditions and supply voltages

Pin name / parameter	Min.	Typ.	Max.	Unit	Note
VSUP	4.8	5	5.2	V	Input voltage supply
INP	0	–	5.2	V	Input, digital signal, can be shorted to VSUP
HV-AC1	-320	–	320	V	Input, high-voltage power supply, referenced to HV-AC2. For 42 V and above, special high-voltage lab environment is strongly recommended
Inductive load	–	–	200	µH	–
Ambient temperature	–	25	30	°C	–

3 Getting started with EVAL-iSSI20B11F

3 Getting started with EVAL-iSSI20B11F

Follow the steps given in this chapter to set up and power up the board, and to perform initial evaluations.

Prerequisites

- Have a low voltage supply ready for the input supply voltage (V_{SUP}), with a current capability of at least 25 mA for V_{SUP}
- Have a power supply, V_{HV} , in series with a suitable load (Z_{Load}), ready to connect X1 and X5
- Have a function generator ready for control signal input INP

To adapt the circuit to application requirements, resistor or capacitor values can be changed to optimize performance.

Steps to power up the board

1. Connect the V_{SUP} , to connector X2.1 with +5 V and the GND , to connector X2.2
2. Connect the digital pulse-width modulation (PWM) generator to input signal connector X4.2 and GND to connector X4.1. Make sure that the outputs of the PWM generator are disabled, or the signals are set to low
3. Connect the power supply, V_{HV} , to connector X1
4. Connect the ground of power supply, V_{HV} , to one end of the load, Z_{Load} , and the other end to connector X5.

The board is now ready to evaluate switching.

Steps to safely power down the board

1. Turn off the power supply, V_{HV} .
2. Discharge the DC-link capacitor (if available) and check the DC-link voltage with, for example, a digital multimeter or an oscilloscope (for DC operation)
3. Turn off the low-voltage supply




Figure 2 Connection of load Z_{Load} , for tests

3 Getting started with EVAL-iSSI20B11F

3.1 Overcurrent protection

The detection circuit monitors the voltage across shunt resistor, R_{sh} . This signal passes a noise RC filter, consisting of R3 and C6. The integrated comparator of the SSI compares it to a fixed threshold voltage $V_{CS,th}$ at terminal CS of iSSI20B11F. The maximum peak current can be adapted to application requirements by changing the R_{sh} , using the following equation:

$$R_{sh} = \frac{V_{CS,th}}{I_{pk,max}}$$

Equation 1 Shunt resistor calculation

Once triggered, the protection reacts quickly and can turn off, for example, CoolMOS™ IPT60R065S7 in a very short time. The triggering of the over-temperature protection leads to the latched turn-off of the power switch with a sinking current of $I_{off, fast,sat}$. To return to normal operation, applying either 0 V to $VSUP$ or a low signal at the logic control input, INP , is required.

The triggering of the over-temperature protection can be forced by externally heating of the temperature sensor, as well.

3.2 Over-temperature protection (optional)

The over-temperature feature is not given by default. iSSI20B11F provides a constant bias current, $I_{TS,bias}$, biasing a positive temperature coefficient (PTC) resistor. The constant current generates a voltage at the PTC that is connected to terminal TS, and the terminal voltage is compared to the threshold voltage $V_{TS,th}$. The integrated comparator includes a noise filter of duration $t_{TS,filter}$ for safely detecting the sensor signal. This noise filter is complemented by an external RC filter (R3, C6).

3.3 Connectors and pin assignment

Table 4 Connectors and pin assignment

Connector	Pin	Marking/ function	Note
X2	1	<i>VSUP</i>	Infineon SSI voltage supply
	2	<i>GND1</i>	Infineon SSI voltage supply reference
X4	1	<i>GND1</i>	Infineon SSI voltage supply reference
	2	<i>INP</i>	Infineon SSI input signal /INF
X3	1,2	<i>GND2</i>	Infineon SSI output reference
X1	1, 2	<i>HV-AC1</i>	High-voltage power supply
X5	1, 2	<i>HV-AC2</i>	High-voltage power supply

3 Getting started with EVAL-iSSI20B11F

3.4 Board options

The evaluation board offers functional options implemented by parts that are not populated. These options are:

- Realization of a snubber circuit (C11, C12, R7)
- Drive switches (T1A and T2A) with another package TO-247
- Implement an over-temperature protection using PTC resistor R14. This option requires the following actions:
 - Short shunt resistor Rsh
 - Depopulate resistor R9
 - Populate PTC resistor R14

3.5 EMI options

Different EMI mitigation schemes can be applied to the evaluation board to meet the EMC standards under test. Standalone or a combination of mitigation techniques usually work together to meet EMI.

- **Capacitive return paths:** Use a discrete Y capacitor between the primary ground and secondary ground. The board offers options for surface-mount components C8 and C9 (default assembly) and for through-hole components C10 and C13 (not assembled). Sometimes the system design requires a Y capacitor for safety purposes as a capacitive return path. For functional isolation a normal capacitor with sufficient voltage rating can be used
- **Inductive components:** A pair of ferrite beads with a high frequency impedance is assembled on the input side. Alternatively, a CM choke may be placed on the same footprint for the supply or ground system

4 Schematic diagram

4 Schematic diagram




Figure 3 Schematics of Eval-iSSI20B11F (assembled components only)

5 Layout

5 Layout




Figure 4 Top (a) and bottom (b) layers of Eval-iSSI20B11F

6 Bill of materials
6 Bill of materials
Table 5 Eval-iSSI20B11F bill of materials

Component	Value	Description	Manufacturer	Part number
C1	4.7 nF	CAP / CERA / 4.7nF / 25V / 10% / X7R (EIA) / -55°C to 125°C / 0603(1608) / SMD / -	MuRata	GRM188R71E472KA01
C2	1 nF	CAP / CERA / 1nF / 50V / 10% / X7R (EIA) / -55°C to 125°C / 0603(1608) / SMD / -	Würth Elektronik	885012206083
C3	10 µF	Multilayer ceramic capacitors MLCC - SMD/SMT 10 uF 6.3 VDC 20% 0402 X5R	MuRata	GRJ155R60J106ME11D
C4	1 µF	Multilayer ceramic capacitors MLCC - SMD/SMT 0402 10VDC 1µF 10% X5R	MuRata	GXT155R61A105KE01D
C5	68 nF	CAP / CERA / 68nF / 50V / 10% / X7R (EIA) / -55 °C to 125 °C / 1206(3216) / SMD / -	MuRata	GRM319R71H683KA01
C6	1 nF	CAP / CERA / 1nF / 50V / 10% / X7R (EIA) / -55°C to 125°C / 1206(3216) / SMD / -	MuRata	GRM319R71H102KA01
C7	10 nF	CAP / CERA / 10nF / 25V / 10% / X7R (EIA) / -55°C to 125°C / 0402(1005) / SMD / -	MuRata	GRM155R71E103KA01
C8, C9	4.7 nF	Multilayer ceramic capacitors MLCC - SMD/SMT 4700PF 250V 10% 1812	Knowles Syfer	1812YA250472KJTSYX
D1	SMCJ440CA	Surface mount TVS diode, 440V, 2kW	Littelfuse	SMCJ440CA
FB1, FB2	2k	2 kΩ at 100 MHz 1 signal line ferrite bead 1206 (3216 Metric) 200mA 600mΩ	Max Echo	EBMS321611DB202
R1, R3	100R	RES / STD / 100R / 125mW / 1% / 100ppm/K / -55°C to 155°C / 0805(2012) / SMD / -	Vishay	CRCW0805100RFK
R9	0R	RES / STD / 0R / - / 0% / - / -55jǎC to 155jǎC / 1206(3216) / SMD / -	Vishay	CRCW12060000Z0EA
R14	DNI	RES / STD / 680R / 125mW / 1% / 100ppm/K / -55°C to 155°C / 0805(2012) / SMD / -	Vishay	CRCW0805680RFK
Rsh	22mR	RES / STD / 22mR / 1W / 1% / 35ppm/K / -55jǎC to 155jǎC / 1206(3216) / SMD / -	Susumu	KRL3216T4A-M-R022-F-T1

6 Bill of materials

Component	Value	Description	Manufacturer	Part number
T1, T2	IPT60R065S7	600V CoolMOS™ SJ S7 power device	Infineon Technologies	IPT60R065S7
U1	iSSI20B11F	Coreless-transformer advanced solid-state isolators	Infineon Technologies	iSSI20B11F
X1, X2, X3, X4, X5	MKDSN 2,5/ 2-5,08	PCB terminal block, nominal current 16A, nominal voltage 400V ,5.08mm pitch	Phoenix Contact	MKDSN 2,5/ 2-5,08
X6	22-28-4033	2.54mm pitch KK header, breakaway, vertical, 3 circuits, 0.38µm gold selective plating, mating pin length 6.09 mm	Molex	22-28-4033

7 Related resources

7 Related resources

- [Solid-state isolators](#)
- [Evaluation board](#)
- [Developer Community](#)

References

References

- [1] Infineon Technologies AG: *iSSI20B02F, iSSI20B03F and iSSI20B11F datasheet*; [Available online](#)
- [2] Infineon Technologies AG: *ISC035N10NM5LF2 datasheet*; [Available online](#)

Revision history

Revision history

Document revision	Date	Description of changes
V 1.0	2026-09-22	Initial release

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition: 2026-09-22

Published by
Infineon Technologies AG
Am Campeon 1-15
85579 Neubiberg, Germany

© 2026 Infineon Technologies AG.
All rights reserved

Do you have a question about this document?
Email: erratum@infineon.com

Document reference:
UG110421

Important Notice

This evaluation board, demonstration board, reference board or kit and any related documentation ("Evaluation Board") is sold or provided and delivered by Infineon Technologies AG and its affiliates ("Infineon"). Evaluation Boards are part of Infineon's non-serial products.

This Evaluation Board is delivered to customer "AS IS", without any warranty (whether express or implied) or liability of Infineon of any kind, including but without limitation any warranty of merchantability, fitness for a particular purpose or non-infringement. These limitations and exclusions shall not apply in case of Infineon's willful misconduct or in any other case where liability is mandatory at law.

This Evaluation Board shall only be used by customer for test purposes and not for series production. However, the Evaluation Board shall not to be used for reliability testing. The Evaluation Board is exclusively intended for technically qualified and skilled customer representatives. The Evaluation Board shall not be used in any way where a failure of the Evaluation Board, or any consequences of the use thereof, can reasonably be expected to result in personal injury. Evaluation Boards may not comply with CE or similar standards (including without limitation the EMC Directive 2004/EC/108 and the EMC Act) and may not fulfill other requirements of the country in which they are operated by the customer. The customer shall ensure that each Evaluation Board will be handled in a way which is compliant with all relevant requirements and standards in the country in which it is operated. Software and associated documentation and materials included or referenced in the Evaluation Board ("Software") is owned by Infineon and is protected by and subject to worldwide patent protection, worldwide copyright laws, and international treaty provisions. Therefore, you may use this Software only as provided in the license agreement accompanying the software package from which you obtained this Software.

If no license agreement applies, then any use, reproduction, modification, translation, or compilation of this Software is prohibited without the express written permission of Infineon. Unless otherwise expressly agreed with Infineon, this Software is provided to customer "AS IS", without any warranty (whether express or implied) or liability of Infineon of any kind, including but without limitation any warranty of merchantability, fitness for a particular purpose or non-infringement.

These limitations and exclusions shall not apply in case of Infineon's willful misconduct or in any other case where liability is mandatory at law. Infineon reserves the right to make changes to the Software without notice. You are responsible for properly designing, programming, and testing the functionality and safety of your intended application of the Software, as well as complying with any legal requirements related to its use. Infineon does not guarantee that the Software will be free from intrusion, data theft or loss, or other breaches ("Security Breaches"), and Infineon shall have no liability arising out of any Security Breaches. The Software shall not be used in any way where a failure of the Evaluation Board or any consequences of the use thereof, can reasonably be expected to result in personal injury.

Safety & Operating Instructions:

Customer shall check the Evaluation Board for any physical damage which may have occurred during transport. If customer detects any damages or defects in the Evaluation Board, customer shall not connect the Evaluation Board to a power source. Customer shall contact Infineon for further support. If customer observes unusual operating behavior during the evaluation process, customer shall immediately shut off the power supply to the Evaluation Board and consult Infineon for support.

Customer shall not touch the Evaluation Board during operation and keep a safe distance.

Customer shall not touch the Evaluation Board after disconnecting the power supply, several components may still store electrical voltage and can discharge through physical contact. Several parts, like heat sinks and transformers, may still be very hot. Allow the components to cool before touching or servicing. The electrical installation must be completed in accordance with the appropriate safety requirements.