

EconoPIM™2 module with TRENCHSTOP™ IGBT7 and emitter controlled 7 diode and NTC

Features

- Electrical features
 - $V_{CES} = 1200\text{ V}$
 - $I_{C\text{ nom}} = 25\text{ A} / I_{CRM} = 50\text{ A}$
 - TRENCHSTOP™ IGBT7
 - Overload operation up to 175°C
 - Low $V_{CE,sat}$
- Mechanical features
 - High power density
 - Compact design
 - Al_2O_3 substrate with low thermal resistance
 - 2.5 kV AC 1 minute insulation



Typical appearance

Potential applications

- Auxiliary inverters
- Air conditioning
- Motor drives

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	3
3	Diode, Inverter	5
4	Diode, Rectifier	6
5	IGBT, Brake-Chopper	7
6	Diode, Brake-Chopper	9
7	NTC-Thermistor	10
8	Characteristics diagrams	11
9	Circuit diagram	17
10	Package outlines	18
11	Module label code	19
	Revision history	20
	Disclaimer	21

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	2.5	kV
Material of module baseplate			Cu	
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	d_{Creep}	terminal to heatsink	10.0	mm
Clearance	d_{Clear}	terminal to heatsink	7.5	mm
Comparative tracking index	CTI		> 200	
Relative thermal index (electrical)	RTI	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{sCE}			35		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_C = 25 \text{ °C}$, per switch		6.9		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_C = 25 \text{ °C}$, per switch		5.9		mΩ
Storage temperature	T_{stg}		-40		125	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	3		5	Nm
Weight	G			180		g

Note: $T_{vj \text{ op}} > 150 \text{ °C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

The current under continuous operation is limited to 50 A rms per connector pin

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Collector-emitter voltage	V_{CES}	$T_{vj} = 25 \text{ °C}$	1200	V
Continuous DC collector current	I_{CDC}	$T_{vj \text{ max}} = 175 \text{ °C}$ $T_C = 120 \text{ °C}$	25	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj \text{ op}}$	50	A

(table continues...)

Table 3 (continued) Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Gate-emitter peak voltage	V_{GES}		± 20	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 25\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$	1.60	1.85	V
			$T_{vj} = 125\ ^\circ C$	1.74		
			$T_{vj} = 175\ ^\circ C$	1.82		
Gate threshold voltage	V_{GEth}	$I_C = 0.525\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$	5.15	5.80	6.45	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CC} = 600\ V$		0.395		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\ ^\circ C$		0		Ω
Input capacitance	C_{ies}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		4.77		nF
Reverse transfer capacitance	C_{res}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		0.017		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1200\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$		0.0056	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$			100	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 25\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Gon} = 9.1\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.040		μs
			$T_{vj} = 125\ ^\circ C$	0.042		
			$T_{vj} = 175\ ^\circ C$	0.043		
Rise time (inductive load)	t_r	$I_C = 25\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Gon} = 9.1\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.045		μs
			$T_{vj} = 125\ ^\circ C$	0.048		
			$T_{vj} = 175\ ^\circ C$	0.050		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 25\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Goff} = 9.1\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.209		μs
			$T_{vj} = 125\ ^\circ C$	0.325		
			$T_{vj} = 175\ ^\circ C$	0.376		
Fall time (inductive load)	t_f	$I_C = 25\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Goff} = 9.1\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.164		μs
			$T_{vj} = 125\ ^\circ C$	0.233		
			$T_{vj} = 175\ ^\circ C$	0.300		
Turn-on energy loss per pulse	E_{on}	$I_C = 25\ A, V_{CC} = 600\ V, L_\sigma = 35\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 9.1\ \Omega, di/dt = 640\ A/\mu s (T_{vj} = 175\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$	2.29		mJ
			$T_{vj} = 125\ ^\circ C$	3.01		
			$T_{vj} = 175\ ^\circ C$	3.52		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-off energy loss per pulse	E_{off}	$I_C = 25\text{ A}$, $V_{CC} = 600\text{ V}$, $L_\sigma = 35\text{ nH}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 9.1\ \Omega$, $dv/dt = 2900\text{ V}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	1.57		mJ
			$T_{vj} = 125\text{ °C}$	2.58		
			$T_{vj} = 175\text{ °C}$	3.15		
SC data	I_{SC}	$V_{GE} \leq 15\text{ V}$, $V_{CC} = 800\text{ V}$, $V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$	$t_p \leq 8\ \mu\text{s}$, $T_{vj} = 150\text{ °C}$	80		A
			$t_p \leq 7\ \mu\text{s}$, $T_{vj} = 175\text{ °C}$	75		
Thermal resistance, junction to case	R_{thJC}	per IGBT			0.967	K/W
Thermal resistance, case to heat sink	R_{thCH}	per IGBT, $\lambda_{grease} = 1\text{ W}/(\text{m} \cdot \text{K})$		0.170		K/W
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	°C

Note: $T_{vj\text{ op}} > 150\text{ °C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25\text{ °C}$	1200	V
Continuous DC forward current	I_F		25	A
Repetitive peak forward current	I_{FRM}	$t_p = 1\text{ ms}$	50	A
I^2t - value	I^2t	$t_p = 10\text{ ms}$, $V_R = 0\text{ V}$	$T_{vj} = 125\text{ °C}$	A^2s
			$T_{vj} = 175\text{ °C}$	

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 25\text{ A}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$	1.83	2.30	V
			$T_{vj} = 125\text{ °C}$	1.70		
			$T_{vj} = 175\text{ °C}$	1.63		

(table continues...)

Table 6 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Peak reverse recovery current	I_{RM}	$V_{CC} = 600\text{ V}$, $I_F = 25\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 640\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	17.3		A
			$T_{vj} = 125\text{ °C}$	22.1		
			$T_{vj} = 175\text{ °C}$	25.1		
Recovered charge	Q_r	$V_{CC} = 600\text{ V}$, $I_F = 25\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 640\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	2.01		μC
			$T_{vj} = 125\text{ °C}$	3.57		
			$T_{vj} = 175\text{ °C}$	4.72		
Reverse recovery energy	E_{rec}	$V_{CC} = 600\text{ V}$, $I_F = 25\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 640\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	0.74		mJ
			$T_{vj} = 125\text{ °C}$	1.36		
			$T_{vj} = 175\text{ °C}$	1.79		
Thermal resistance, junction to case	R_{thJC}	per diode			1.43	K/W
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot\text{K})$		0.182		K/W
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	°C

Note: $T_{vj\text{ op}} > 150\text{ °C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

4 Diode, Rectifier

Table 7 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = 25\text{ °C}$	1600	V
Maximum RMS forward current per chip	I_{FRMSM}	$T_C = 80\text{ °C}$		70	A
Maximum RMS current at rectifier output	I_{RMSM}	$T_C = 80\text{ °C}$		100	A
Surge forward current	I_{FSM}	$t_P = 10\text{ ms}$	$T_{vj} = 25\text{ °C}$	560	A
			$T_{vj} = 150\text{ °C}$	435	
I^2t - value	I^2t	$t_P = 10\text{ ms}$	$T_{vj} = 25\text{ °C}$	1570	A^2s
			$T_{vj} = 150\text{ °C}$	945	

Table 8 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 25 \text{ A}$	$T_{vj} = 150 \text{ °C}$		0.88		V
Reverse current	I_r	$T_{vj} = 150 \text{ °C}, V_R = 1600 \text{ V}$			1		mA
Thermal resistance, junction to case	R_{thJC}	per diode				0.870	K/W
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1 \text{ W/(m·K)}$			0.166		K/W
Temperature under switching conditions	$T_{vj, op}$			-40		150	°C

5 IGBT, Brake-Chopper

Table 9 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = 25 \text{ °C}$	1200	V
Continuous DC collector current	I_{CDC}	$T_{vj \text{ max}} = 175 \text{ °C}$	$T_C = 125 \text{ °C}$	15	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj \text{ op}}$		30	A
Gate-emitter peak voltage	V_{GES}			±20	V

Table 10 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE \text{ sat}}$	$I_C = 15 \text{ A}, V_{GE} = 15 \text{ V}$	$T_{vj} = 25 \text{ °C}$		1.60	1.85	V
			$T_{vj} = 125 \text{ °C}$		1.74		
			$T_{vj} = 175 \text{ °C}$		1.82		
Gate threshold voltage	V_{GEth}	$I_C = 0.553 \text{ mA}, V_{CE} = V_{GE}, T_{vj} = 25 \text{ °C}$		5.15	5.80	6.45	V
Gate charge	Q_G	$V_{GE} = \pm 15 \text{ V}, V_{CC} = 600 \text{ V}$			0.234		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25 \text{ °C}$			0		Ω
Input capacitance	C_{ies}	$f = 100 \text{ kHz}, T_{vj} = 25 \text{ °C}, V_{CE} = 25 \text{ V}, V_{GE} = 0 \text{ V}$			2.82		nF
Reverse transfer capacitance	C_{res}	$f = 100 \text{ kHz}, T_{vj} = 25 \text{ °C}, V_{CE} = 25 \text{ V}, V_{GE} = 0 \text{ V}$			0.01		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1200 \text{ V}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$			0.003	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0 \text{ V}, V_{GE} = 20 \text{ V}, T_{vj} = 25 \text{ °C}$				100	nA

(table continues...)

Table 10 (continued) **Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-on delay time (inductive load)	t_{don}	$I_C = 15\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 10\ \Omega$	$T_{vj} = 25\text{ °C}$	0.034		μs
			$T_{vj} = 125\text{ °C}$	0.035		
			$T_{vj} = 175\text{ °C}$	0.036		
Rise time (inductive load)	t_r	$I_C = 15\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 10\ \Omega$	$T_{vj} = 25\text{ °C}$	0.053		μs
			$T_{vj} = 125\text{ °C}$	0.054		
			$T_{vj} = 175\text{ °C}$	0.055		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 15\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 10\ \Omega$	$T_{vj} = 25\text{ °C}$	0.336		μs
			$T_{vj} = 125\text{ °C}$	0.534		
			$T_{vj} = 175\text{ °C}$	0.632		
Fall time (inductive load)	t_f	$I_C = 15\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 10\ \Omega$	$T_{vj} = 25\text{ °C}$	0.272		μs
			$T_{vj} = 125\text{ °C}$	0.313		
			$T_{vj} = 175\text{ °C}$	0.333		
Turn-on energy loss per pulse	E_{on}	$I_C = 15\text{ A}$, $V_{CC} = 600\text{ V}$, $L_\sigma = 35\text{ nH}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 10\ \Omega$, $di/dt = 520\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	4.57		mJ
			$T_{vj} = 125\text{ °C}$	5.55		
			$T_{vj} = 175\text{ °C}$	6.07		
Turn-off energy loss per pulse	E_{off}	$I_C = 15\text{ A}$, $V_{CC} = 600\text{ V}$, $L_\sigma = 35\text{ nH}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 10\ \Omega$, $dv/dt = 2100\text{ V}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	0.927		mJ
			$T_{vj} = 125\text{ °C}$	1.49		
			$T_{vj} = 175\text{ °C}$	1.77		
SC data	I_{SC}	$V_{GE} \leq 15\text{ V}$, $V_{CC} = 800\text{ V}$, $V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$	$t_p \leq 8\ \mu\text{s}$, $T_{vj} = 150\text{ °C}$	48		A
			$t_p \leq 7\ \mu\text{s}$, $T_{vj} = 175\text{ °C}$	45		
Thermal resistance, junction to case	R_{thJC}	per IGBT			1.29	K/W
Thermal resistance, case to heat sink	R_{thCH}	per IGBT, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot\text{K})$		0.180		K/W
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	°C

Note: $T_{vj\text{ op}} > 150\text{ °C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

6 Diode, Brake-Chopper

Table 11 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = 25\text{ °C}$	1200	V
Continuous DC forward current	I_F			10	A
Repetitive peak forward current	I_{FRM}	$t_P = 1\text{ ms}$		20	A
I^2t - value	I^2t	$t_P = 10\text{ ms}, V_R = 0\text{ V}$	$T_{vj} = 125\text{ °C}$	30	A^2s
			$T_{vj} = 175\text{ °C}$	25	

Table 12 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 10\text{ A}, V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$	1.72	2.10	V
			$T_{vj} = 125\text{ °C}$	1.59		
			$T_{vj} = 175\text{ °C}$	1.52		
Peak reverse recovery current	I_{RM}	$V_{CC} = 600\text{ V}, I_F = 10\text{ A}, V_{GE} = -15\text{ V}, -di_F/dt = 450\text{ A}/\mu s (T_{vj} = 175\text{ °C})$	$T_{vj} = 25\text{ °C}$	11.2		A
			$T_{vj} = 125\text{ °C}$	13.4		
			$T_{vj} = 175\text{ °C}$	14.5		
Recovered charge	Q_r	$V_{CC} = 600\text{ V}, I_F = 10\text{ A}, V_{GE} = -15\text{ V}, -di_F/dt = 450\text{ A}/\mu s (T_{vj} = 175\text{ °C})$	$T_{vj} = 25\text{ °C}$	0.95		μC
			$T_{vj} = 125\text{ °C}$	1.68		
			$T_{vj} = 175\text{ °C}$	2.05		
Reverse recovery energy	E_{rec}	$V_{CC} = 600\text{ V}, I_F = 10\text{ A}, V_{GE} = -15\text{ V}, -di_F/dt = 450\text{ A}/\mu s (T_{vj} = 175\text{ °C})$	$T_{vj} = 25\text{ °C}$	0.37		mJ
			$T_{vj} = 125\text{ °C}$	0.66		
			$T_{vj} = 175\text{ °C}$	0.83		
Thermal resistance, junction to case	R_{thJC}	per diode			1.81	K/W
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1\text{ W}/(m \cdot K)$		0.181		K/W
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	°C

Note: $T_{vj\text{ op}} > 150\text{ °C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

7 NTC-Thermistor

Table 13 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25\text{ °C}$		5		kΩ
Deviation of R_{100}	$\Delta R/R$	$T_{NTC} = 100\text{ °C}, R_{100} = 493\text{ Ω}$	-5		5	%
Power dissipation	P_{25}	$T_{NTC} = 25\text{ °C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15\text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15\text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15\text{ K}))]$		3433		K


Note: Specification according to the valid application note.

8 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 175\text{ °C}$



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


$V_{CE} = 20\text{ V}$



Switching losses (typical), IGBT, Inverter

$E = f(I_C)$


$R_{Goff} = 9.1\text{ }\Omega$, $R_{Gon} = 9.1\text{ }\Omega$, $V_{GE} = \pm 15\text{ V}$, $V_{CC} = 600\text{ V}$



8 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $V_{GE} = \pm 15\text{ V}$, $I_C = 25\text{ A}$, $V_{CC} = 600\text{ V}$




Switching times (typical), IGBT, Inverter

$t = f(I_C)$
 $R_{Goff} = 9.1\ \Omega$, $R_{Gon} = 9.1\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $V_{CC} = 600\text{ V}$, $T_{vj} = 175\text{ °C}$




Switching times (typical), IGBT, Inverter

$t = f(R_G)$
 $V_{GE} = \pm 15\text{ V}$, $I_C = 25\text{ A}$, $V_{CC} = 600\text{ V}$, $T_{vj} = 175\text{ °C}$



Transient thermal impedance , IGBT, Inverter


$Z_{th} = f(t)$



Voltage slope (typical), IGBT, Inverter

$$dv/dt = f(R_G)$$


$I_C = 25 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $T_{vj} = 25 \text{ }^\circ\text{C}$



Reverse bias safe operating area (RBSOA), IGBT, Inverter

$$I_C = f(V_{CE})$$


$R_{Goff} = 9.1 \text{ } \Omega$, $V_{GE} = \pm 15 \text{ V}$, $T_{vj} = 175 \text{ }^\circ\text{C}$



Capacity characteristic (typical), IGBT, Inverter

$$C = f(V_{CE})$$


$f = 100 \text{ kHz}$, $V_{GE} = 0 \text{ V}$, $T_{vj} = 25 \text{ }^\circ\text{C}$



Gate charge characteristic (typical), IGBT, Inverter


$$V_{GE} = f(Q_G)$$

$I_C = 25 \text{ A}$, $T_{vj} = 25 \text{ }^\circ\text{C}$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$
 $R_{Gon} = 9.1, V_{CC} = 600\text{ V}$




Forward characteristic (typical), Diode, Inverter

$I_F = f(V_F)$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$
 $I_F = 25\text{ A}, V_{CC} = 600\text{ V}$




Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$




Transient thermal impedance, Diode, Rectifier

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, Rectifier


$I_F = f(V_F)$



Output characteristic (typical), IGBT, Brake-Chopper


$I_C = f(V_{CE})$

$V_{GE} = 15\text{ V}$




Forward characteristic (typical), Diode, Brake-Chopper

$I_F = f(V_F)$



Temperature characteristic (typical), NTC-Thermistor

$$R = f(T_{NTC})$$



9 **Circuit diagram**





Figure 1



Revision 1.00
2022-11-28

11 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
			
71549142846550549911530		71549142846550549911530	

Figure 3

Revision history

Document revision	Date of release	Description of changes
V1.0	2019-11-14	Target datasheet
n/a	2020-09-01	Datasheet migrated to a new system with a new layout and new revision number schema: target or preliminary datasheet = 0.xy; final datasheet = 1.xy
1.00	2022-11-28	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-11-28

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2022 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAY212-002

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.