Preliminary datasheet
EasyPACK™ module with CoolSiC™ Trench MOSFET and PressFIT / NTC

Features



Typical appearance

- Electrical features
  - V_{DSS} = 1200 V
  - I_{DN} = 30 A / I_{DRM} = 60 A
  - Low inductive design
  - Low switching losses
- Mechanical features
  - Rugged mounting due to integrated mounting clamps
  - PressFIT contact technology
  - Integrated NTC temperature sensor
  - AlN substrate with low thermal resistance

Potential applications

- High-frequency switching application
- DC/DC converter
- Motor drives
- UPS systems

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

Description . . . 1
Features . . . 1
Potential applications . . . 1
Product validation . . . 1
Table of contents . . . 2
1 Package . . . 3
2 MOSFET . . . 3
3 Body diode (MOSFET) . . . 5
4 NTC-Thermistor . . . 5
5 Characteristics diagrams . . . 7
6 Circuit diagram . . . 12
7 Package outlines . . . 13
8 Module label code . . . 14
Revision history . . . 15
Disclaimer . . . 16

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, f = 50 Hz, *t* = 1 min	3.0	kV
Internal isolation		basic insulation (class 1, IEC 61140)	AlN	
Comparative tracking index	*CTI*		> 200	
Relative thermal index (electrical)	*RTI*	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{sCE}			19		nH
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	T_H = 25 °C, per switch		5.3		mΩ
Storage temperature	T_{stg}		-40		125	°C
Mounting force per clamp	*F*		20		50	N
Weight	*G*			24		g

Note: The current under continuous operation is limited to 25 A rms per connector pin.

2 MOSFET

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage	V_{DSS}		T_{vj} = 25 °C	1200	V
Continuous DC drain current	I_{DDC}	T_{vj} = 175 °C, V_{GS} = 18 V	T_H = 125 °C	30	A
Repetitive peak drain current	I_{DRM}	verified by design, t_p limited by T_{vjmax}		60	A
Gate-source voltage, max. transient voltage	V_{GS}	*D* < 0.01		-10/23	V
Gate-source voltage, max. static voltage	V_{GS}			-7/20	V

Table 4 Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
On-state gate voltage	$V_{GS(on)}$		15...18	V
Off-state gate voltage	$V_{GS(off)}$		-5...0	V

Table 5 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on-resistance	$R_{DS(on)}$	I_D = 30 A	V_{GS} = 18 V, T_{vj} = 25 °C		26.4		mΩ
			V_{GS} = 18 V, T_{vj} = 125 °C		42.8		
			V_{GS} = 18 V, T_{vj} = 150 °C		49.3		
			V_{GS} = 15 V, T_{vj} = 25 °C		31.8		
Gate threshold voltage	$V_{GS(th)}$	I_D = 12 mA, V_{DS} = V_{GS}, T_{vj} = 25 °C, (tested after 1ms pulse at V_{GS} = +20 V)		3.45	4.3	5.15	V
Total gate charge	Q_G	V_{DD} = 800 V, V_{GS} = -3/18 V			0.09		µC
Internal gate resistor	R_{Gint}	T_{vj} = 25 °C			3.8		Ω
Input capacitance	C_{ISS}	f = 100 kHz, V_{DS} = 800 V, V_{GS} = 0 V	T_{vj} = 25 °C		2.7		nF
Output capacitance	C_{OSS}	f = 100 kHz, V_{DS} = 800 V, V_{GS} = 0 V	T_{vj} = 25 °C		0.128		nF
Reverse transfer capacitance	C_{rss}	f = 100 kHz, V_{DS} = 800 V, V_{GS} = 0 V	T_{vj} = 25 °C		0.009		nF
C_{OSS} stored energy	E_{OSS}	V_{DS} = 800 V, V_{GS} = -3/18 V, T_{vj} = 25 °C			52.4		µJ
Drain-source leakage current	I_{DSS}	V_{DS} = 1200 V, V_{GS} = -3 V	T_{vj} = 25 °C		0.02	208	µA
Gate-source leakage current	I_{GSS}	V_{DS} = 0 V, T_{vj} = 25 °C	V_{GS} = 20 V			400	nA
Turn-on delay time (inductive load)	$t_{d\,on}$	I_D = 30 A, R_{Gon} = 6.2 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V	T_{vj} = 25 °C		16		ns
			T_{vj} = 125 °C		16		
			T_{vj} = 150 °C		16		
Rise time (inductive load)	t_r	I_D = 30 A, R_{Gon} = 6.2 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V	T_{vj} = 25 °C		30		ns
			T_{vj} = 125 °C		30		
			T_{vj} = 150 °C		30		
Turn-off delay time (inductive load)	$t_{d\,off}$	I_D = 30 A, R_{Goff} = 5.1 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V	T_{vj} = 25 °C		47		ns
			T_{vj} = 125 °C		52		
			T_{vj} = 150 °C		54		
Fall time (inductive load)	t_f	I_D = 30 A, R_{Goff} = 5.1 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V	T_{vj} = 25 °C		19		ns
			T_{vj} = 125 °C		19		
			T_{vj} = 150 °C		19		

(table continues...)

Table 5 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Turn-on energy loss per pulse	E_{on}	I_D = 30 A, V_{DD} = 600 V, L_σ = 35 nH, V_{GS} = -3/18 V, R_{Gon} = 6.2 Ω, di/dt = 2.7 kA/µs (T_{vj} = 150 °C)	T_{vj} = 25 °C		0.47		mJ
			T_{vj} = 125 °C		0.589		
			T_{vj} = 150 °C		0.625		
Turn-off energy loss per pulse	E_{off}	I_D = 30 A, V_{DD} = 600 V, L_σ = 35 nH, V_{GS} = -3/18 V, R_{Goff} = 5.1 Ω, dv/dt = 25 kV/µs (T_{vj} = 150 °C)	T_{vj} = 25 °C		0.112		mJ
			T_{vj} = 125 °C		0.121		
			T_{vj} = 150 °C		0.122		
Thermal resistance, junction to heat sink	R_{thJH}	per MOSFET, λ_{grease} = 1 W/(m·K)			0.654		K/W
Temperature under switching conditions	$T_{vj\,op}$			-40		150	°C

Note: The selection of positive and negative gate-source voltages impacts losses and the long-term behavior of the MOSFET and body diode. The design guidelines described in Application Notes AN 2018-09 and AN 2021-13 must be considered to ensure sound operation of the device over the planned lifetime.

3 Body diode (MOSFET)

Table 6 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
DC body diode forward current	I_{SD}	T_{vj} = 175 °C, V_{GS} = -3 V	T_H = 125 °C	15	A

Table 7 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Forward voltage	V_{SD}	I_{SD} = 30 A, V_{GS} = -3 V	T_{vj} = 25 °C		4.2	5.35	V
			T_{vj} = 125 °C		3.9		
			T_{vj} = 150 °C		3.85		

4 NTC-Thermistor

Table 8 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	T_{NTC} = 25 °C		5		kΩ
Deviation of R_{100}	$\Delta R/R$	T_{NTC} = 100 °C, R_{100} = 493 Ω	-5		5	%

(table continues...)


Table 8 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Power dissipation	P_{25}	T_{NTC} = 25 °C			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2\text{-}1/(298{,}15\ K))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2\text{-}1/(298{,}15\ K))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2\text{-}1/(298{,}15\ K))]$		3433		K


Note: Specification according to the valid application note.

5 Characteristics diagrams


Output characteristic (typical), MOSFET
$I_D = f(V_{DS})$
V_{GS} = 18 V




Output characteristic (typical), MOSFET
$I_D = f(V_{DS})$
V_{GS} = 15 V



Drain source on-resistance (typical), MOSFET
$R_{DS(on)} = f(I_D)$
V_{GS} = 18 V




Drain source on-resistance (typical), MOSFET
$R_{DS(on)} = f(T_{vj})$
I_D = 30 A




Output characteristic field (typical), MOSFET

$I_D = f(V_{DS})$
$T_{vj} = 150\ °C$




Transfer characteristic (typical), MOSFET

$I_D = f(V_{GS})$
$V_{DS} = 20\ V$




Gate-source threshold voltage (typical), MOSFET

$V_{GS(th)} = f(T_{vj})$
$V_{GS} = V_{DS}$



Gate charge characteristic (typical), MOSFET


$V_{GS} = f(Q_G)$
$I_D = 30\ A$, $T_{vj} = 25\ °C$



Capacity characteristic (typical), MOSFET

$C = f(V_{DS})$


$f = 100\ kHz$, $T_{vj} = 25\ °C$, $V_{GS} = 0\ V$



Forward characteristic body diode (typical), MOSFET

$I_{SD} = f(V_{SD})$


$T_{vj} = 25\ °C$



Forward voltage of body diode (typical), MOSFET

$V_{SD} = f(T_{vj})$


$I_{SD} = 30\ A$



Switching losses (typical), MOSFET

$E = f(I_D)$


$R_{Goff} = 5.1\ \Omega$, $R_{Gon} = 6.2\ \Omega$, $V_{DD} = 600\ V$, $V_{GS} = -3/18\ V$



Switching losses (typical), MOSFET

$E = f(R_G)$


V_{DD} = 600 V, I_D = 30 A, V_{GS} = -3/18 V



Switching times (typical), MOSFET

$t = f(I_D)$


R_{Goff} = 5.1 Ω, R_{Gon} = 6.2 Ω, V_{DD} = 600 V, T_{vj} = 150 °C, V_{GS} = -3/18 V



Switching times (typical), MOSFET

$t = f(R_G)$


V_{DD} = 600 V, I_D = 30 A, T_{vj} = 150 °C, V_{GS} = -3/18 V



Current slope (typical), MOSFET

$di/dt = f(R_G)$


V_{DD} = 600 V, I_D = 30 A, V_{GS} = -3/18 V



Voltage slope (typical), MOSFET

$dv/dt = f(R_G)$


V_{DD} = 600 V, I_D = 30 A, V_{GS} = -3/18 V



Reverse bias safe operating area (RBSOA), MOSFET


$I_D = f(V_{DS})$

R_{Goff} = 5.1 Ω, T_{vj} = 150 °C, V_{GS} = -3/18 V




Transient thermal impedance , MOSFET

$Z_{th} = f(t)$



Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



6 Circuit diagram




Figure 1

7 Package outlines




Figure 2

8 Module label code


Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	*Content* Module serial number Module material number Production order number Date code (production year) Date code (production week)	*Digit* 1 – 5 6 - 11 12 - 19 20 – 21 22 – 23	*Example* 71549 142846 55054991 15 30
Example	 7154914284655054991530	 7154914284655054991530	

Figure 3

Revision history

Document revision	Date of release	Description of changes
0.10	2022-08-02	Initial version
0.20	2023-02-28	Preliminary datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-02-28

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2023 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABB872-002

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.