


CoolGaN™
CoolGaN™ BDS 40 V

SG-UFWLB-22


Features

- E-mode bidirectional transistor - normally OFF switch
- Drain-to-Drain configuration
- Bidirectional blocking capability
- Low on-resistance, low gate charge, low output charge
- Qualified according to JEDEC for target applications
- Space saving chip scale packaging with topside protective coating



Potential applications

- High side load switch
- OVP protection in smart phone USB port
- Switch circuits in multiple power supply system




Product validation

Qualified according to relevant JEDEC tests.

Table 1 Key performance parameters

Parameter	Value	Unit
V_{DD}	40	V
$R_{DD(on)}$	4.2	mΩ
I_D	53	A
Q_{oss}	7.1	nC
Q_G	9.1	nC



Part number	Package	Marking	Related links
IGK048B041S	SG-UFWLB-22	48BF1	see Appendix A

Table of contents

Description	1
Maximum ratings	3
Recommended operating conditions	4
Thermal characteristics	5
Electrical Characteristics	6
Electrical characteristics diagrams	7
Package outlines	12
Appendix A	15
Revision history	16
Trademarks	17
Disclaimer	17

1 Maximum ratings

at $T_j = 25\text{ °C}$, unless otherwise specified. Stresses beyond max ratings may cause permanent damage to the device. For optimum lifetime and reliability, Infineon recommends operating conditions that do not continuously exceed 80 % of the maximum ratings stated (unless otherwise explicitly stated). For further information, contact your local Infineon sales office.

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Continuous drain-drain voltage	V_{DD}	-	-	40	V	$V_{GD}=0\text{ V}$
Pulsed drain-drain voltage ¹⁾	$V_{DD,pulse}$	-	-	48	V	$V_{GD}=0\text{ V}$, 1 h total time
Continuous drain current	I_D	-	-	53	A	$V_{GD}=5\text{ V}$, $T_C=25\text{ °C}$
Pulsed drain current ²⁾	$I_{D,pulse}$	-	-	120	A	$T_j=125\text{ °C}$
Gate-drain voltage ¹⁾	V_{GD}	-40	-	6.0	V	-
Power dissipation	P_{tot}	-	-	25	W	$T_C=25\text{ °C}$
				1.7		$T_A=25\text{ °C}$, $R_{thJA}=59\text{ °C/W}$ ³⁾
Storage temperature	T_{stg}	-40	-	150	°C	-
Junction temperature	T_j			125		

¹⁾ Provided as measure of robustness under abnormal operating conditions and not recommended for normal operation.

²⁾ Pulse current limited by transfer characteristic.

³⁾ Device on 1-layer FR4 PCB, vertical in still air.

2 Recommended operating conditions

Table 3 Recommended operating conditions

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Gate-drain voltage	V_{GD}	-32	5.0	5.5	V	-

3 Thermal characteristics

Table 4 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case, top	R_{thJC}	-	17	20	°C/W	-
Thermal resistance, junction - case, bottom		-	3.3	4.0		
Thermal resistance, junction - ambient 1s0p	R_{thJA}	-	59	-	°C/W	On 1 layer PCB, vertical in still air.

4 Electrical Characteristics

at $T_j=25\text{ °C}$, unless otherwise specified

Table 5 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Gate threshold voltage	$V_{GD(th)}$	1.2	2.0	2.9	V	$V_{DD}=V_{GD}$, $I_D=3.0\text{ mA}$
Drain-drain leakage current	I_{DDs}	-	0.05	3.0	μA	$V_{DD}=40\text{ V}$, $V_{GD}=0\text{ V}$, $T_j=25\text{ °C}$
Gate-drain leakage current	I_{GDS}	-	3.2	10.6	μA	$V_{GD}=5\text{ V}$, $T_j=25\text{ °C}$
			0.01	0.1		$V_{GD}=-4\text{ V}$, $T_j=25\text{ °C}$
			9.4	32		$V_{GD}=5\text{ V}$, $T_j=85\text{ °C}$
			0.01	0.1		$V_{GD}=-4\text{ V}$, $T_j=85\text{ °C}$
Drain-drain on-state resistance	$R_{DD(on)}$	-	4.2	4.8	$\text{m}\Omega$	$V_{GD}=5\text{ V}$, $I_D=5\text{ A}$
Gate resistance ⁴⁾	R_G	-	0.5	-	Ω	-

⁴⁾ Defined by design. Not subject to production test.

Table 6 Capacitance characteristics ⁵⁾

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Input capacitance	C_{ISS}	-	600	-	pF	$V_{GD}=0\text{ V}$, $V_{DD}=20\text{ V}$, $f=1\text{ MHz}$
Output capacitance	C_{OSS}		212			
Reverse transfer capacitance	C_{RSS}		127			

⁵⁾ Defined by design. Not subject to production test.

Table 7 Gate charge characteristics ⁶⁾

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Gate charge at threshold	$Q_{g(th)}$	-	1.5	-	nC	$V_{DD}=20\text{ V}$, $I_D=5\text{ A}$, $V_{GD}=0\text{ to }5\text{ V}$
Gate to drain charge	Q_{gd}		5.0		nC	
Gate charge total	Q_g		9.1		nC	
Gate plateau voltage	$V_{plateau}$		2.7		V	
Output charge	Q_{OSS}		7.1		nC	

⁶⁾ Defined by design. Not subject to production test.

5 Electrical characteristics diagrams







Diagram 5: Typ. output characteristics




$I_D = f(V_{DS}); T_j = 25\text{ °C};$ parameter: V_{GS}

Diagram 6: Typ. transfer characteristics




$I_D = f(V_{GS}); |V_{DS}| > 2|I_D|R_{DS(on)max};$ parameter: T_j

Diagram 7: Typ. channel reverse characteristics



$I_S = f(V_{SD}); T_j = 25\text{ °C};$ parameter: V_{GS}

Diagram 8: Typ. channel reverse characteristics



$I_S = f(V_{SD}); T_j = 125\text{ °C};$ parameter: V_{GS}









Diagram 13: Typ. capacitances




$C=f(V_{DS}); V_{GS}=0\text{ V}$

Diagram 14 Typ. gate charge




$V_{GS}=f(Q_{gate}); I_D=5\text{ A pulsed}; \text{parameter: } V_{DS}$

Diagram 15: Typ. output charge




$Q_{oss}=f(V_{DS}), V_{GS}=0\text{ V}$

Diagram 16: Typ. Coss stored Energy




$E_{oss}=f(V_{DS}), V_{GS}=0\text{ V}$

Diagram 17: Typ. gate characteristics forward




$I_{GS}=f(V_{GS}); V_{DS}=0$ V; parameter: T_j

6 Package outlines




PACKAGE - GROUP NUMBER: SG-UFWLB-22-U01		
DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
A	0.531	0.597
A1	0.175	0.235
A2	0.346	0.374
A3	0.022	0.028
b	0.241	0.295
D	2.10	
E	2.10	
e	0.40	
e1	0.40	
e2	1.60	
e3	1.60	
L	0.25	
L1	0.25	

Figure 1 Outline SG-UFWLB-22, dimensions in mm



All dimensions are in units mm
All pads are non-solder mask defined

Figure 2 Footprint drawing SG-UFWLB-22, dimensions in mm



All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 []

Figure 3 Packaging variant SG-UFWLB-22, dimensions in mm

7 Appendix A

Table 8 Related links

- [IFX CoolGaN™ GaN webpage](#)
- [IFX CoolGaN™ reliability white paper](#)
- [IFX Packages Description-SG-UFWLB-22-1](#)



Revision history

IGK048B041S

Revision 2026-01-07, Rev. 1.0

Previous revisions

Revision	Date	Subjects (major changes since last revision)
1.0	2026-01-07	Release of final version

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Published by Infineon Technologies AG, Am Campeon 1-15, 85579 Neubiberg, Germany
Copyright (c) 2026 Infineon Technologies AG and its affiliates. All Rights Reserved.

Important notice

Products which may also include samples and may be comprised of hardware or software or both (“Product(s)”) are sold or provided and delivered by Infineon Technologies AG and its affiliates (“Infineon”) subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

For the avoidance of doubt, Infineon disclaims all warranties of non-infringement of third-party rights and implied warranties such as warranties of fitness for a specific use/purpose or merchantability.

Infineon shall not be responsible for any information with respect to samples, the application or customer’s specific use of any Product or for any examples or typical values given in this document.

The data contained in this document is exclusively intended for technically qualified and skilled customer representatives. It is the responsibility of the customer to evaluate the suitability of the Product for the intended application and the customer’s specific use and to verify all relevant technical data contained in this document in the intended application and the customer’s specific use. The customer is responsible for properly designing, programming, and testing the functionality and safety of the intended application, as well as complying with any legal requirements related to its use.

Unless otherwise explicitly approved by Infineon, Products may not be used in any application where a failure of the Products or any consequences of the use thereof can reasonably be expected to result in personal injury. However, the foregoing shall not prevent the customer from using any Product in such fields of use that Infineon has explicitly designed and sold it for, provided that the overall responsibility for the application lies with the customer.

Infineon expressly reserves the right to use its content for commercial text and data mining (TDM) according to applicable laws, e.g. Section 44b of the German Copyright Act (UrhG).

If the Product includes security features: Because no computing device can be absolutely secure, and despite security measures implemented in the Product, Infineon does not guarantee that the Product will be free from intrusion, data theft or loss, or other breaches (“Security Breaches”), and Infineon shall have no liability arising out of any Security Breaches.

If this document includes or references software:

The software is owned by Infineon under the intellectual property laws and treaties of the United States, Germany, and other countries worldwide. All rights reserved. Therefore, you may use the software only as provided in the software license agreement accompanying the software. If no software license agreement applies, Infineon hereby grants you a personal, non-exclusive, non-transferable license (without the right to sublicense) under its intellectual property rights in the software (a) for software provided in source code form, to modify and reproduce the software solely for use with Infineon hardware products, only internally within your organization, and (b) to distribute the software in binary code form externally to end users, solely for use on Infineon hardware products. Any other use, reproduction, modification, translation, or compilation of the software is prohibited.

For further information on the Product, technology, delivery terms and conditions, and prices, please contact your nearest Infineon office or visit <https://www.infineon.com>.