Final datasheet

High speed DuoPack: IGBT in Trench and Fieldstop technology with soft, fast recovery antiparallel diode

Features

- V_{CE} = 1200 V
- I_C = 40 A
- Very low V_{CEsat}
- Low EMI
- Very soft, fast recovery antiparallel diode
- Maximum junction temperature T_{vjmax} = 175°C
- Qualified according to JEDEC for target applications
- Pb-free lead plating; RoHS compliant
- Complete product spectrum and PSpice Models: http://www.infineon.com/igbt/

Halogen-free

Lead-free

Green

RoHS

Potential applications

- Uninterruptible power supplies
- Welding converters
- Converters with high switching frequency

Description

Package pin definition:

- Pin G – Gate
- Pin C & backside – Collector
- Pin E – Emitter



Type	Package	Marking
IKW40N120H3	PG-TO247-3	K40H1203

Table of contents

	Description	1
	Features	1
	Potential applications	1
	Table of contents	2
1	**Package**	3
2	**IGBT**	3
3	**Diode**	5
4	**Characteristics diagrams**	7
5	**Package outlines**	14
6	**Testing conditions**	15
	Revision history	16
	Disclaimer	17

1 Package

Table 1 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Internal emitter inductance measured 5 mm (0.197 in.) from case	L_E			13		nH
Storage temperature	T_{stg}		-55		150	°C
Soldering temperature	T_{sold}	wave soldering 1.6 mm (0.063 in.) from case for 10 s			260	°C
Mounting torque	M	M3 screw, Maximum of mounting processes: 3			0.6	Nm
Thermal resistance, junction-ambient	$R_{th(j-a)}$				40	K/W
IGBT thermal resistance, junction-case	$R_{th(j-c)}$				0.31	K/W
Diode thermal resistance, junction-case	$R_{th(j-c)}$				1.11	K/W

2 IGBT

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CE}	$T_{vj} \geq 25$ °C		1200	V
DC collector current, limited by T_{vjmax}	I_C		$T_c = 25$ °C	80	A
			$T_c = 100$ °C	40	
Pulsed collector current, t_p limited by T_{vjmax}	I_{Cpulse}			160	A
Turn-off safe operating area		$V_{CE} \leq 1200$ V, $T_{vj} \leq 175$ °C		160	A
Gate-emitter voltage	V_{GE}			±20	V
Transient gate-emitter voltage	V_{GE}	$t_p \leq 10$ µs, $D < 0.01$		±30	V
Short-circuit withstand time	t_{SC}	$V_{CC} \leq 600$ V, $V_{GE} = 15$ V, Allowed number of short circuits < 1000, Time between short circuits ≥ 1.0 s, $T_{vj} = 175$ °C		10	µs
Power dissipation	P_{tot}		$T_c = 25$ °C	483	W
			$T_c = 100$ °C	220	

Table 3 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter breakdown voltage	V_{BRCES}	I_C = 0.5 mA, V_{GE} = 0 V		1200			V
Collector-emitter saturation voltage	V_{CEsat}	I_C = 40 A, V_{GE} = 15 V	T_{vj} = 25 °C		2.05	2.4	V
			T_{vj} = 125 °C		2.5		
			T_{vj} = 175 °C		2.7		
Gate-emitter threshold voltage	V_{GEth}	I_C = 1 mA, V_{CE} = V_{GE}		5	5.8	6.5	V
Zero gate-voltage collector current	I_{CES}	V_{CE} = 1200 V, V_{GE} = 0 V	T_{vj} = 25 °C			250	µA
			T_{vj} = 175 °C			2500	
Gate-emitter leakage current	I_{GES}	V_{CE} = 0 V, V_{GE} = 20 V				600	nA
Transconductance	g_{fs}	I_C = 40 A, V_{CE} = 20 V			20		S
Short-circuit collector current	I_{SC}	$V_{CC} \le$ 600 V, V_{GE} = 15 V, $t_{SC} \le$ 10 µs, Allowed number of short circuits < 1000, Time between short circuits ≥ 1.0 s, T_{vj} = 175 °C			139		A
Input capacitance	C_{ies}	V_{CE} = 25 V, V_{GE} = 0 V, f = 1000 kHz			2330		pF
Output capacitance	C_{oes}	V_{CE} = 25 V, V_{GE} = 0 V, f = 1000 kHz			185		pF
Reverse transfer capacitance	C_{res}	V_{CE} = 25 V, V_{GE} = 0 V, f = 1000 kHz			130		pF
Gate charge	Q_G	V_{CC} = 960 V, I_C = 40 A, V_{GE} = 15 V			185		nC
Turn-on delay time	$t_{d(on)}$	V_{CC} = 600 V, V_{GE} = 0/15 V, $R_{G(on)}$ = 12 Ω, $R_{G(off)}$ = 12 Ω	T_{vj} = 25 °C, I_C = 40 A		30		ns
			T_{vj} = 175 °C, I_C = 40 A		29		
Rise time (inductive load)	t_r	V_{CC} = 600 V, V_{GE} = 0/15 V, $R_{G(on)}$ = 12 Ω, $R_{G(off)}$ = 12 Ω	T_{vj} = 25 °C, I_C = 40 A		57		ns
			T_{vj} = 175 °C, I_C = 40 A		49		
Turn-off delay time	$t_{d(off)}$	V_{CC} = 600 V, V_{GE} = 0/15 V, $R_{G(on)}$ = 12 Ω, $R_{G(off)}$ = 12 Ω	T_{vj} = 25 °C, I_C = 40 A		290		ns
			T_{vj} = 175 °C, I_C = 40 A		366		
Fall time (inductive load)	t_f	V_{CC} = 600 V, V_{GE} = 0/15 V, $R_{G(on)}$ = 12 Ω, $R_{G(off)}$ = 12 Ω	T_{vj} = 25 °C, I_C = 40 A		16		ns
			T_{vj} = 175 °C, I_C = 40 A		48		

(table continues...)

Table 3 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Turn-on energy	E_{on}	V_{CC} = 600 V, V_{GE} = 0/15 V, $R_{G(on)}$ = 12 Ω, $R_{G(off)}$ = 12 Ω	T_{vj} = 25 °C, I_C = 40 A		3.2		mJ
			T_{vj} = 175 °C, I_C = 40 A		4.4		
Turn-off energy	E_{off}	V_{CC} = 600 V, V_{GE} = 0/15 V, $R_{G(on)}$ = 12 Ω, $R_{G(off)}$ = 12 Ω	T_{vj} = 25 °C, I_C = 40 A		1.2		mJ
			T_{vj} = 175 °C, I_C = 40 A		2.6		
Total switching energy	E_{ts}	V_{CC} = 600 V, V_{GE} = 0/15 V, $R_{G(on)}$ = 12 Ω, $R_{G(off)}$ = 12 Ω	T_{vj} = 25 °C, I_C = 40 A		4.4		mJ
			T_{vj} = 175 °C, I_C = 40 A		7		
Operating junction temperature	T_{vj}			-40		175	°C

3 Diode

Table 4 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}	T_{vj} ≥ 25 °C		1200	V
Diode forward current, limited by T_{vjmax}	I_F		T_c = 25 °C	40	A
			T_c = 100 °C	20	
Diode pulsed current, t_p limited by T_{vjmax}	I_{Fpulse}			160	A

Table 5 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Diode forward voltage	V_F	I_F = 20 A	T_{vj} = 25 °C		1.8	2.35	V
			T_{vj} = 175 °C		1.85		
Diode forward voltage	V_F	I_F = 40 A	T_{vj} = 25 °C		2.4	3.05	V
			T_{vj} = 125 °C		2.6		
			T_{vj} = 175 °C		2.6		
Reverse leakage current	I_R	V_R = 1200 V	T_{vj} = 25 °C			250	µA
			T_{vj} = 175 °C			2500	

(table continues...)

Table 5 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Diode reverse recovery time	t_{rr}	V_R = 600 V, $R_{G(on)}$ = 12 Ω	T_{vj} = 25 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		355		ns
			T_{vj} = 175 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		639		
Diode reverse recovery charge	Q_{rr}	V_R = 600 V, $R_{G(on)}$ = 12 Ω	T_{vj} = 25 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		1.9		µC
			T_{vj} = 175 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		4.3		
Diode peak reverse recovery current	I_{rrm}	V_R = 600 V, $R_{G(on)}$ = 12 Ω	T_{vj} = 25 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		12.8		A
			T_{vj} = 175 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		16		
Diode peak rate of fall of reverse recovery current	di_{rr}/dt	V_R = 600 V, $R_{G(on)}$ = 12 Ω	T_{vj} = 25 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		-105		A/µs
			T_{vj} = 175 °C, I_F = 40 A, $-di_F/dt$ = 500 A/µs		-84		
Operating junction temperature	T_{vj}			-40		175	°C

***Note**: Maximum rated values: For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.*

Characteristic values at T_{vj} = 25°C, unless otherwise specified.

Dynamic test circuit: L_σ = 70 nH , C_σ = 67 pF from Figure E. Energy losses include “tail” and diode reverse recovery.

4 Characteristics diagrams

Collector current as a function of switching frequency

$I_C = f(f)$

D = 0.5 , V_{CE} = 20 V, $T_{vj} \leq 175$ °C, V_{GE} = 0/15 V, R_G = 12 Ω



Forward bias safe operating area

$I_C = f(V_{CE})$

D = 0 , $T_{vj} \leq 175$ °C, V_{GE} = 15 V, T_c = 25 °C



Power dissipation as a function of heatsink temperature

$P_{tot} = f(T_c)$

$T_{vj} \leq 175$ °C



Collector current as a function of heatsink temperature

$I_C = f(T_c)$

$T_{vj} \leq 175$ °C, $V_{GE} \geq 15$ V



Typical output characteristic

$I_C = f(V_{CE})$
$T_{vj} = 25\ °C$



Typical output characteristic

$I_C = f(V_{CE})$
$T_{vj} = 175\ °C$



Typical transfer characteristic

$I_C = f(V_{GE})$
$V_{CE} = 20\ V$



Typical collector-emitter saturation voltage as a function of junction temperature

$V_{CEsat} = f(T_{vj})$
$V_{GE} = 15\ V$



Gate-emitter threshold voltage as a function of junction temperature

$V_{GEth} = f(T_{vj})$

$I_C = 1$ mA



Typical switching times as a function of collector current

$t = f(I_C)$

$V_{CC} = 600$ V, $T_{vj} = 175$ °C, $V_{GE} = 0/15$ V, $R_G = 12\ \Omega$



Typical switching times as a function of gate resistor

$t = f(R_G)$

$I_C = 40$ A, $V_{CC} = 600$ V, $T_{vj} = 175$ °C, $V_{GE} = 0/15$ V



Typical switching times as a function of junction temperature

$t = f(T_{vj})$

$I_C = 40$ A, $V_{CC} = 600$ V, $V_{GE} = 0/15$ V, $R_G = 12\ \Omega$



Typical switching energy losses as a function of collector current

$E = f(I_C)$

V_{CC} = 600 V, T_{vj} = 175 °C, V_{GE} = 0/15 V, R_G = 12 Ω



Typical switching energy losses as a function of gate resistor

$E = f(R_G)$

I_C = 40 A, V_{CC} = 600 V, T_{vj} = 175 °C, V_{GE} = 0/15 V



Typical switching energy losses as a function of junction temperature

$E = f(T_{vj})$

I_C = 40 A, V_{CC} = 600 V, V_{GE} = 0/15 V, R_G = 12 Ω



Typical switching energy losses as a function of collector emitter voltage

$E = f(V_{CE})$

I_C = 40 A, T_{vj} = 175 °C, V_{GE} = 0/15 V, R_G = 12 Ω



Typical gate charge

$V_{GE} = f(Q_G)$

$I_C = 40$ A



Typical capacitance as a function of collector-emitter voltage

$C = f(V_{CE})$

$f = 1000$ kHz, $V_{GE} = 0$ V



Typical short circuit collector current as a function of gate-emitter voltage

$I_{C(SC)} = f(V_{GE})$

$T_{vj,\,start} = 25$ °C, $V_{CC} \leq 600$ V



Short circuit withstand time as a function of gate-emitter voltage

$t_{SC} = f(V_{GE})$

$T_{vj,\,start} \leq 150$ °C, $V_{CC} \leq 600$ V



IGBT transient thermal impedance as a function of pulse width

$Z_{th(j-c)} = f(t_p)$
$D = t_p/T$



Diode transient thermal impedance as a function of pulse width

$Z_{th(j-c)} = f(t_p)$
$D = t_p/T$



Typical diode forward current as a function of forward voltage

$I_F = f(V_F)$



Typical diode forward voltage as a function of junction temperature

$V_F = f(T_{vj})$



Typical reverse recovery time as a function of diode current slope

$t_{rr} = f(di_F/dt)$

$V_R = 600\ V,\ I_F = 40\ A$



Typical reverse recovery charge as a function of diode current slope

$Q_{rr} = f(di_F/dt)$

$V_R = 600\ V,\ I_F = 40\ A$



Typical reverse recovery current as a function of diode current slope

$I_{rrm} = f(di_F/dt)$

$V_R = 600\ V,\ I_F = 40\ A$



Typical diode peak rate of fall of reverse recovery current as a function of diode current slope

$di_{rr}/dt = f(di_F/dt)$

$V_R = 600\ V,\ I_F = 40\ A$



5 Package outlines

Package Drawing PG-TO247-3



DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
A	4.70	5.30
A1	2.20	2.60
A2	1.50	2.50
b	1.00	1.40
b1	1.60	2.41
b2	2.57	3.43
c	0.38	0.89
D	20.70	21.50
D1	13.08	17.65
D2	0.51	1.35
E	15.50	16.30
E1	12.38	14.15
E2	3.40	5.10
E3	1.00	2.60
e	5.44	
L	19.80	20.40
L1	3.85	4.50
P	3.50	3.70
Q	5.35	6.25
S	6.04	6.30

DOCUMENT NO.
Z8B00003327

REVISION
06

SCALE 3:1
0 1 2 3 4 5mm

EUROPEAN PROJECTION

ISSUE DATE
25.07.2018

Figure 1

6 Testing conditions



Figure A. **Definition of switching times**



Figure B. **Definition of switching losses**



Figure C. **Definition of diode switching characteristics**



Figure D. **Thermal equivalent circuit**



Figure E. **Dynamic test circuit**
Parasitic inductance L_σ,
parasitic capacitor C_σ,
relief capacitor C_r,
(only for ZVT switching)

Figure 2

Revision history

Document revision	Date of release	Description of changes
V1.1	2009-12-03	
V1.2	2010-02-10	
V2.1	2014-11-26	Final data sheet
V2.2	2015-09-30	Minor change figure 28
n/a	2020-11-30	Datasheet migrated to a new system with a new layout and new revision number schema: target or preliminary datasheet = 0.xy; final datasheet = 1.xy
1.10	2021-09-08	Update of legend at the diagram $V_F = f(T_{vj})$
1.20	2025-06-12	Added transient Gate-emitter voltage Editorial changes

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-06-12

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2025 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAK488-006

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.