Final datasheet

CoolSiC™ 1200 V SiC MOSFET G2 : Silicon Carbide MOSFET with .XT interconnection technology

Features



- V_{DSS} = 1200 V at T_{vj} = 25°C
- I_{DDC} = 69 A at T_C = 100°C
- $R_{DS(on)}$ = 17 mΩ at V_{GS} = 18 V, T_{vj} = 25°C
- Very low switching losses
- Overload operation up to T_{vj} = 200°C
- Short circuit withstand time 2 µs
- Benchmark gate threshold voltage, $V_{GS(th)}$ = 4.2 V
- Robust against parasitic turn on, 0 V turn-off gate voltage can be applied
- Robust body diode for hard commutation
- .XT interconnection technology for best-in-class thermal performance
- Suitable Infineon gate drivers can be found under https://www.infineon.com/gdfinder

Halogen-free
Green
Lead-free
RoHS

Potential applications

- General purpose drives (GPD)
- EV Charging
- Online UPS / Industrial UPS
- String inverter
- Energy storage systems (ESS)
- Welding

Product validation

- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22

Description

Pin definition:


• Pin 1 – Drain

• Pin 2 – Source

• Pin 3 – Kelvin sense contact

• Pin 4 – Gate

Note: the source and sense pins are not exchangeable, their exchange might lead to malfunction



Type	Package	Marking
IMZC120R017M2H	PG-TO247-4-U07	12M2H017

Table of contents

Description 1
Features 1
Potential applications 1
Product validation 1
Table of contents 2
1 Package 3
2 MOSFET 3
3 Body diode (MOSFET) 6
4 Characteristics diagrams 8
5 Package outlines 15
6 Testing conditions 16
Revision history 17
Disclaimer 18

1 Package

Table 1 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Storage temperature	T_{stg}		-55		150	°C
Soldering temperature	T_{sold}	Wave soldering only allowed at leads 1.6 mm (0.063 in.) from case for 10 s			260	°C
Mounting torque	M	M3 screw, Maximum of mounting processes: 3			0.6	Nm
Thermal resistance, junction-ambient	$R_{th(j-a)}$				62	K/W
MOSFET/body diode thermal resistance, junction-case	$R_{th(j-c)}$			0.3	0.39	K/W

2 MOSFET

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage	V_{DSS}	$T_{vj} \geq 25$ °C		1200	V
Continuous DC drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$	I_{DDC}	$V_{GS} = 18$ V	$T_c = 25$ °C	97	A
			$T_c = 100$ °C	69	
Peak drain current, t_p limited by $T_{vj(max)}$ [1)]	I_{DM}	$V_{GS} = 18$ V		345	A
Gate-source voltage, max. transient voltage	V_{GS}	$t_p \leq 0.5$ µs, $D < 0.01$		-10...25	V
Gate-source voltage, max. static voltage [2)]	V_{GS}			-7...23	V
Avalanche energy, single pulse	E_{AS}	$I_D = 40$ A, $V_{DD} = 50$ V, $L = 0.6$ mH, $T_{vj(start)} = 25$ °C		508	mJ
Avalanche energy, repetitive	E_{AR}	$I_D = 40$ A, $V_{DD} = 50$ V, $L = 3.2$ µH, $T_{vj(start)} = 25$ °C		2.54	mJ
Short-circuit withstand time	t_{SC}	$V_{DD} \leq 800$ V, $V_{DS,peak} < 1200$ V, $V_{GS(on)} = 15$ V, $T_{vj(start)} = 25$ °C		2	µs
Power dissipation, limited by $T_{vj(max)}$	P_{tot}		$T_c = 25$ °C	382	W
			$T_c = 100$ °C	191	

1) Verified by design.
2) The maximum gate-source voltage in the application design should be in accordance to IPC-9592B.

Table 3 Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
Recommended turn-on gate voltage	$V_{GS(on)}$		15...18	V
Recommended turn-off gate voltage	$V_{GS(off)}$		-5...0	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on-state resistance	$R_{DS(on)}$	I_D = 40 A	T_{vj} = 25 °C, $V_{GS(on)}$ = 18 V		17		mΩ
			T_{vj} = 150 °C, $V_{GS(on)}$ = 18 V		35	45	
			T_{vj} = 175 °C, $V_{GS(on)}$ = 18 V		41		
			T_{vj} = 25 °C, $V_{GS(on)}$ = 15 V		21		
Gate-source threshold voltage	$V_{GS(th)}$	I_D = 12.7 mA, V_{DS} = V_{GS} (tested after 1 ms pulse at V_{GS} = 20 V)	T_{vj} = 25 °C	3.5	4.2	5.1	V
			T_{vj} = 175 °C		3.2		
Zero gate-voltage drain current	I_{DSS}	V_{DS} = 1200 V, V_{GS} = 0 V	T_{vj} = 25 °C			350	µA
			T_{vj} = 175 °C		6		
Gate leakage current	I_{GSS}	V_{DS} = 0 V	V_{GS} = 23 V			120	nA
			V_{GS} = -10 V			-120	
Forward transconductance	g_{fs}	I_D = 40 A, V_{DS} = 20 V			27		S
Internal gate resistance	$R_{G,int}$	f = 1 MHz, V_{AC} = 25 mV			3		Ω
Input capacitance	C_{iss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			2910		pF
Output capacitance	C_{oss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			126		pF
Reverse transfer capacitance	C_{rss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			11		pF
C_{oss} stored energy	E_{oss}	Calculated based on C_{oss} = f(V_{DD})			53		µJ
Output charge	Q_{oss}	Calculated based on C_{oss} = f(V_{DD})			196		nC
Effective output capacitance, energy related	$C_{o(er)}$	V_{DS} = 0...800 V, V_{GS} = 0 V, Calculated based on E_{oss}			166		pF
Effective output capacitance, time related	$C_{o(tr)}$	I_D = constant, V_{DS} = 0...800 V, V_{GS} = 0 V, Calculated based on Q_{oss}			245		pF
Total gate charge	Q_G	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, turn-on pulse			89		nC

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Plateau gate charge	$Q_{GS(pl)}$	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, turn-on pulse			19		nC
Gate-drain charge	Q_{GD}	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, turn-on pulse			24		nC
Turn-on delay time	$t_{d(on)}$	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		10		ns
			T_{vj} = 175 °C		7.5		
Rise time	t_r	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		6.1		ns
			T_{vj} = 175 °C		5.4		
Turn-off delay time	$t_{d(off)}$	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		21.2		ns
			T_{vj} = 175 °C		24.8		
Fall time	t_f	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		9.1		ns
			T_{vj} = 175 °C		10.7		
Turn-on energy	E_{on}	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		310		µJ
			T_{vj} = 175 °C		550		
Turn-off energy	E_{off}	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		120		µJ
			T_{vj} = 175 °C		180		
Total switching energy[1)]	E_{tot}	V_{DD} = 800 V, I_D = 40 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		590		µJ
			T_{vj} = 175 °C		1200		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Turn-on energy at -5 V	E_{on}	V_{DD} = 800 V, I_D = 40 A, V_{GS} = -5/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = -5 V	T_{vj} = 25 °C		288		µJ
			T_{vj} = 175 °C		513		
Turn-off energy at -5 V	E_{off}	V_{DD} = 800 V, I_D = 40 A, V_{GS} = -5/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = -5 V	T_{vj} = 25 °C		53		µJ
			T_{vj} = 175 °C		53		
Total switching energy at -5 V[1)]	E_{tot}	V_{DD} = 800 V, I_D = 40 A, V_{GS} = -5/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 12 nH, diode: body diode at V_{GS} = -5 V	T_{vj} = 25 °C		506		µJ
			T_{vj} = 175 °C		1122		
Virtual junction temperature	T_{vj}			-55		175	°C
Virtual junction temperature	$T_{vj(over)}$	overload, cumulative max. 100 h[2)]				200	°C

1) including E_{fr}
2) up to 5000 cycles. Maximum ΔT limited to 100 K.

***Note**: The chip technology was characterized up to 200 kV/µs. The measured dV/dt was limited by measurement test setup and package.*
Characteristics at T_{vj} = 25°C, unless otherwise specified.

3 Body diode (MOSFET)

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage	V_{DSS}	T_{vj} ≥ 25 °C		1200	V
Continuous reverse drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$	I_{SDC}	V_{GS} = 0 V	T_c = 25 °C	72	A
			T_c = 100 °C	40	
Peak reverse drain current, t_p limited by $T_{vj(max)}$	I_{SM}	V_{GS} = 0 V		207	A

Table 6 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source reverse voltage	V_{SD}	I_{SD} = 40 A, V_{GS} = 0 V	T_{vj} = 25 °C		4.2	5.5	V
			T_{vj} = 100 °C		4.11		
			T_{vj} = 175 °C		4.05		
MOSFET forward recovery charge	Q_{fr}	V_{DD} = 800 V, I_{SD} = 40 A, V_{GS} = 0 V, $R_{GS(on)}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		0.34		µC
			T_{vj} = 175 °C		0.97		
MOSFET peak forward recovery current	I_{frm}	V_{DD} = 800 V, I_{SD} = 40 A, V_{GS} = 0 V, $R_{GS(on)}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		41.7		A
			T_{vj} = 175 °C		71.2		
MOSFET forward recovery energy	E_{fr}	V_{DD} = 800 V, I_{SD} = 40 A, V_{GS} = 0 V, $R_{GS(on)}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		160		µJ
			T_{vj} = 175 °C		470		
MOSFET forward recovery energy at -5 V	E_{fr}	V_{DD} = 800 V, I_{SD} = 40 A, V_{GS} = -5 V, $R_{GS(on)}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		165		µJ
			T_{vj} = 175 °C		556		
Virtual junction temperature	T_{vj}			-55		175	°C
Virtual junction temperature	$T_{vj(over)}$	overload, cumulative max. 100 h[1)]				200	°C


1) up to 5000 cycles. Maximum ΔT limited to 100 K.

4 Characteristics diagrams

Safe operating area (SOA)


$I_D = f(V_{DS})$

$T_c = 25\ °C$, $T_{vj} \leq 175\ °C$




Power dissipation as a function of case temperature

$P_{tot} = f(T_c)$



Maximum DC drain to source current as a function of case temperature limited by bond wire


$I_D = f(T_c)$



Maximum source to drain current as a function of case temperature limited by bond wire

$I_{SD} = f(T_c)$


$V_{GS} = 0\ V$



Typical transfer characteristic

$I_D = f(V_{GS})$


V_{DS} = 20 V, t_p = 20 µs



Typical gate-source threshold voltage as a function of junction temperature

$V_{GS(th)} = f(T_{vj})$


I_D = 12.7 mA



Typical output characteristic, V_{GS} as a parameter

$I_D = f(V_{DS})$


T_{vj} = 25 °C, t_p = 20 µs



Typical output characteristic, V_{GS} as a parameter


$I_D = f(V_{DS})$

T_{vj} = 175 °C, t_p = 20 µs




Typical on-state resistance as a function of junction temperature

$R_{DS(on)} = f(T_{vj})$
$I_D = 40$ A




Typical gate charge

$V_{GS} = f(Q_G)$
$I_D = 40$ A, $V_{DS} = 800$ V




Typical capacitance as a function of drain-source voltage

$C = f(V_{DS})$
$f = 100$ kHz, $V_{GS} = 0$ V



Typical reverse drain voltage as a function of junction temperature


$V_{SD} = f(T_{vj})$
$I_{SD} = 40$ A, $V_{GS} = 0$ V



Typical reverse drain current as a function of reverse drain voltage, V_{GS} as a parameter

$I_{SD} = f(V_{SD})$


$T_{vj} = 25\ °C$, $t_p = 20\ µs$



Typical reverse drain current as a function of reverse drain voltage, V_{GS} as a parameter

$I_{SD} = f(V_{SD})$


$T_{vj} = 175\ °C$, $t_p = 20\ µs$



Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\ V$

$E = f(T_{vj})$


$V_{GS} = 0/18\ V$, $I_D = 40\ A$, $R_{G,ext} = 2.3\ Ω$, $V_{DD} = 800\ V$



Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = -5\ V$

$E = f(T_{vj})$


$V_{GS} = -5/18\ V$, $I_D = 40\ A$, $R_{G,ext} = 2.3\ Ω$, $V_{DD} = 800\ V$



Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(I_D)$


V_{GS} = 0/18 V, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω, V_{DD} = 800 V



Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

$E = f(I_D)$


V_{GS} = -5/18 V, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω, V_{DD} = 800 V



Typical switching energy as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(R_{G,ext})$


V_{GS} = 0/18 V, I_D = 40 A, T_{vj} = 175 °C, V_{DD} = 800 V



Typical switching energy as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

$E = f(R_{G,ext})$


V_{GS} = -5/18 V, I_D = 40 A, T_{vj} = 175 °C, V_{DD} = 800 V



Typical switching energy as a function of DC link voltage, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(V_{DD})$


V_{GS} = 0/18 V, I_D = 40 A, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω



Typical switching energy as a function of DC link voltage, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

$E = f(V_{DD})$


V_{GS} = -5/18 V, I_D = 40 A, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω



Typical switching times as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$t = f(R_{G,ext})$


V_{GS} = 0/18 V, I_D = 40 A, T_{vj} = 175 °C, V_{DD} = 800 V



Typical reverse recovery charge as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$Q_{fr} = f(-di_{SD}/dt)$


V_{GS} = 0/18 V, I_{SD} = 40 A, V_{DD} = 800 V



Typical reverse recovery current as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$I_{frm} = f(-di_{SD}/dt)$

V_{GS} = 0/18 V, I_{SD} = 40 A, V_{DD} = 800 V




Typical switching energy as a function of dead time / blanking time, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(t_{dead})$

I_D = 40 A, V_{GS} = 0/18 V, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω


V_{DD} = 800 V




Max. transient thermal impedance (MOSFET/diode)

$Z_{th(j-c),max} = f(t_p)$

$D = t_p/T$



5 Package outlines



PACKAGE - GROUP NUMBER:	PG-TO247-4-U07				
DIMENSIONS	**MILLIMETERS**		**DIMENSIONS**	**MILLIMETERS**	
	MIN.	MAX.		MIN.	MAX.
A	4.90	5.10	**E**	15.60	16.00
A1	1.90	2.10	**E1**	13.10	13.50
A2	1.50	1.70	**E2**	0.60	1.20
A3	2.16	2.36	**E3**	2.48	2.68
A4	2.31	2.51	**E4**	9.05	9.25
b	0.60	0.80	**E5**	3.97	4.17
b1	1.10	1.30	**E6**	1.80	2.20
b2	---	0.15	**e**	5.08	
b3	1.10	1.30	**e1**	2.79	
b4	1.90	2.10	**e2**	2.54	
c	0.50	0.70	**K**	3.50	---
D	23.10	23.50	**L**	17.50	17.80
D1	16.25	16.85	**L1**	2.61	2.91
D2	0.97	1.37	**N**	4	
D3	6.00	6.30	**ØP1**	7.00	7.40
D4	2.50	2.70	**ØP**	3.50	3.70
D5	2.30	2.70	**ØU**	1.40	1.80

NOTES: DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURRS
N IS THE NUMBER OF LEADS

Figure 1

6 Testing conditions




Figure A. **Definition of switching times**




Figure B. **Definition of body diode switching characteristics**




Figure C. **Definition of switching losses**




Figure D. **Definition of QGD**




Figure E. **Thermal equivalent circuit**




Figure F. **Dynamic test circuit**
Parasitic inductance L_σ,
Parasitic capacitor C_σ,

Figure 2

Revision history

Document revision	Date of release	Description of changes
0.10	2024-09-06	Preliminary datasheet
1.00	2024-09-27	Final datasheet
1.10	2025-02-04	Updated “Potential Applications” on Page 1 Correction of switching parameters in Table 4 and corresponding graphs Correction of body diode characteristic values in Table 6 and corresponding graphs Editorial changes
1.20	2025-07-04	Increased I_{DM} in Table 2 Added switching information for V_{GS} = -5/18 V in Table 5 and 6 and corresponding diagrams Added I_{SDC} in Table 5 Added SOA diagram on page 8 Added diagram E = f(V_{DD}) @ V_{GS} = 0/18 V Added diagram E = f(V_{DD}) @ V_{GS} = -5/18 V Editorial changes

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-07-04

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2025 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABL380-004

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.