


CIPOS™ Prime

AMM12S62LB1Z

Features

- 1200 V SiC MOSFET 6-pack
- 62 mΩ of typical $R_{DS(on)}$ at $V_{GS} = 18\text{ V}$, $T_J = 25^\circ\text{C}$
- Maximum operating $T_J = 175^\circ\text{C}$
- Very low switching losses
- Robust against parasitic turn on, 0 V turn-off gate voltage can be applied
- Robust body diode for hard commutation
- High performance AlN DCB substrate
- Integrated NTC thermistor



Potential applications

- On-board charger
- DC-DC converter
- EV charging
- Power conversion AC-DC, DC-AC

Product validation

Qualified for automotive applications

Product validation according to AEC-Q101 / 200 and AQG 324

Description

The CIPOS™ Prime product offers an integrated solution for high frequency power conversion applications. The power module includes six SiC MOSFETs and a NTC and enables high power density. Infineon's SiC technology provides excellent switching performance, wide range of gate-source voltage, and benchmark gate threshold voltage. The DCB substrate enables optimal thermal performance and package is designed to ensure a high creepage distance.

Table 1 Product Information

Base Part Number	Package Type	Standard Pack		Sales Product Number
		Form	MOQ	
AMM12S62LB1Z	DIP 44x28DA	11 pcs / Tube	176 pcs	SP006043533



Table of contents

Features 1

Potential applications 1

Product validation 1

Description 1

Table of contents 2

1 MOSFET 3

2 MOSFET body diode 5

3 Package 6

4 Thermistor 7

5 Characteristics diagrams 8

6 Pin description 13

7 Package outline 14

Revision history 15

1 MOSFET

Table 2 Maximum ratings

Description	Symbol	Condition	Values	Unit
Drain-source voltage	V_{DS}	$T_J \geq 25^\circ\text{C}$	1200	V
Continuous drain current for $R_{th(j-c)}$, limited by $T_{J,max}$	I_D	$V_{GS} = 18\text{ V}, T_C = 25^\circ\text{C}$	29	A
		$V_{GS} = 18\text{ V}, T_C = 100^\circ\text{C}$	20	
Peak drain current, t_p limited by $T_{J,max}$	I_{DM}	$V_{GS} = 18\text{ V}$	60	A
Gate-source voltage, max. transient voltage	V_{GS}	$t_p \leq 0.5\ \mu\text{s}, D < 0.01$	-10 ~ 23	V
Gate-source voltage, max. static voltage	V_{GS}		-5 ~ 20	V
Power dissipation per switch	P_D		128	W
Operating junction temperature	T_J		-40 ~ 175	$^\circ\text{C}$

Table 3 Recommended values

Description	Symbol	Condition	Values	Unit
Turn-on gate-source voltage	$V_{GS(on)}$		15 ~ 18	V
Turn-off gate-source voltage	$V_{GS(off)}$		-3 ~ 0	V

Table 4 Electrical characteristics

($T_J = 25^\circ\text{C}$ if not stated otherwise)

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Drain-source on-state resistance	$R_{DS(on)}$	$I_D = 11.3\text{ A}, V_{GS} = 18\text{ V}$		62	88.3	m Ω
		$I_D = 11.3\text{ A}, V_{GS} = 18\text{ V}, T_J = 175^\circ\text{C}$		147		
		$I_D = 11.3\text{ A}, V_{GS} = 15\text{ V}$		75		
Gate-source threshold voltage	$V_{GS(th)}$	$I_D = 3.6\text{ mA}, V_{DS} = V_{GS}$	3.5	4.2	5.1	V
		$I_D = 3.6\text{ mA}, V_{DS} = V_{GS}, T_J = 175^\circ\text{C}$		3.2		
Zero gate-voltage drain current	I_{DSS}	$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}$			100	μA
		$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}, T_J = 175^\circ\text{C}$		1.5		
Gate leakage current	I_{GSS}	$V_{DS} = 0\text{ V}, V_{GS} = 23\text{ V}$			120	nA
		$V_{DS} = 0\text{ V}, V_{GS} = -10\text{ V}$			-120	
Forward transconductance	g_{fs}	$I_D = 11.3\text{ A}, V_{DS} = 20\text{ V}$		5.0		S

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Internal gate resistance	$R_{G,int}$	$f = 1 \text{ MHz}, V_{AC} = 25 \text{ mV}$		13		Ω
Input capacitance	C_{iss}	$V_{DS} = 800 \text{ V}, V_{GS} = 0 \text{ V}, f = 100 \text{ kHz}, V_{AC} = 25 \text{ mV}$		804		pF
Output capacitance	C_{oss}			49		
Reverse transfer capacitance	C_{rss}			4.8		
C_{oss} stored energy	E_{oss}			20		
Total gate charge	Q_G	$V_{DS} = 800 \text{ V}, I_D = 11.3 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}$		29		nC
Plateau gate charge	$Q_{GS(pl)}$			12		
Gate-to-drain charge	Q_{GD}			6.5		
Turn-on energy	E_{on}	$V_{DS} = 800 \text{ V}, I_D = 11.3 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega$		70		μJ
		$V_{DS} = 800 \text{ V}, I_D = 11.3 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega, T_J = 175^\circ\text{C}$		75		
Turn-off energy	E_{off}	$V_{DS} = 800 \text{ V}, I_D = 11.3 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega$		60		μJ
		$V_{DS} = 800 \text{ V}, I_D = 11.3 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega, T_J = 175^\circ\text{C}$		60		

2 MOSFET body diode

Table 5 Maximum ratings

Description	Symbol	Condition	Values	Unit
Drain-source voltage	V_{DSS}	$T_J \geq 25^\circ\text{C}$	1200	V
Peak reverse drain current, t_p limited by $T_{J,max}$	I_{SM}	$V_{GS} = 0\text{ V}$	26	A

Table 6 Electrical characteristics

($T_J = 25^\circ\text{C}$ if not stated otherwise)

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Drain-source reverse voltage	V_{SD}	$I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}$		4.2	5.5	V
		$I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}, T_J = 175^\circ\text{C}$		4.05		
MOSFET reverse recovery charge	Q_{rr}	$V_{DS} = 800\text{ V}, I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes Q_C		0.22		μC
		$V_{DS} = 800\text{ V}, I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C, T_J = 175^\circ\text{C}$		0.29		
MOSFET peak reverse recovery current	I_{rrm}	$V_{DS} = 800\text{ V}, I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes Q_C		17.6		A
		$V_{DS} = 800\text{ V}, I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C, T_J = 175^\circ\text{C}$		21.8		
MOSFET reverse recovery energy	E_{rr}	$V_{DS} = 800\text{ V}, I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes Q_C		90		μJ
		$V_{DS} = 800\text{ V}, I_{SD} = 11.3\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C, T_J = 175^\circ\text{C}$		120		

Package

3 Package

Table 7 Characteristics and ratings

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Storage temperature	T_{stg}		-40		125	°C
Thermal resistance, junction-case per switch	$R_{th(j-c)}$				1.17	K/W
Isolation voltage	V_{ISO}	1 min., RMS, f = 50 Hz	3.5			kV
Clearance distance		Pin to pin	2.4			mm
		Pin to flat heatsink	3.3			
Creepage distance		Pin to pin	5.5			
		Pin to DCB	12.12			
Comparative tracking index	CTI		600			V
Mounting torque		M3 SEMS screw	0.39	0.68	0.98	Nm
DCB flatness			0		120	μm
Weight				13.8		g

4 Thermistor


Table 8 Characteristic values

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Resistance	R_{25}	$T = 25^{\circ}\text{C}$		10		$\text{k}\Omega$
Tolerance			-2		2	%
Resistance	R_{100}	$T = 100^{\circ}\text{C}$		674.4		Ω
Tolerance			-4.75		4.75	%
B-constant	B(25/50)	$T = 25^{\circ}\text{C}$ to 50°C		3946		K
	B(25/85)	$T = 25^{\circ}\text{C}$ to 85°C		3988		
	B(25/100)	$T = 25^{\circ}\text{C}$ to 100°C		4000		
Operating temperature range	T_{NTC}		-40		150	$^{\circ}\text{C}$

5 Characteristics diagrams


Forward bias safe operating area (FBSOA)

$I_D = f(V_{DS}), T_C = 25^\circ\text{C}, D = 0$, parameter: t_p




Reverse bias safe operating area (RBSOA)

$I_D = f(V_{DS}), V_{GS} = 0/18\text{ V}, T_J \leq 175^\circ\text{C}, T_C = 25^\circ\text{C}$




Power dissipation

$P_{tot} = f(T_C)$



Max. transient thermal impedance


$Z_{th(j-c),max} = f(t_p), D = t_p/T$



Characteristics diagrams


Typical transfer characteristics

$I_{DS} = f(V_{GS}), V_{DS} = 20\text{ V}$




Typical gate-source threshold voltage vs junction temperature

$V_{GS(th)} = f(T_J), I_D = 3.6\text{ mA}$




Typical output characteristics

$I_D = f(V_{DS}), T_J = 25^\circ\text{C}$




Typical output characteristics

$I_D = f(V_{DS}), T_J = 175^\circ\text{C}$




Typical on-state resistance vs junction temperature

$R_{DS(on)} = f(T_J), I_D = 11.3 \text{ A}$




Typical gate charge

$V_{GS} = f(Q_G), I_D = 11.3 \text{ A}, V_{DS} = 800 \text{ V}$




Typical capacitance vs drain-source voltage

$C = f(V_{DS}), f = 100 \text{ kHz}, V_{GS} = 0 \text{ V}$



Typical Coss stored energy


$E = f(V_{DS})$



Characteristics diagrams


Typical Coss stored charge

$Q = f(V_{DS})$




Typical reverse drain voltage characteristics

$V_{SD} = f(T_J), I_{SD} = 11.3 \text{ A}, V_{GS} = 0 \text{ V}$




Typical reverse drain current characteristics

$I_{SD} = f(V_{SD}), T_J = 25^\circ\text{C}$




Typical reverse drain current characteristics

$I_{SD} = f(V_{SD}), T_J = 175^\circ\text{C}$




Typical switching losses vs junction temperature

$E = f(T_J), V_{GS} = 0/18\text{ V}, I_D = 11.3\text{ A}, R_{G,ext} = 5\ \Omega, V_{DS} = 800\text{ V}$




Typical switching losses vs drain current

$E = f(I_D), V_{GS} = 0/18\text{ V}, T_J = 175^\circ\text{C}, R_{G,ext} = 5\ \Omega, V_{DS} = 800\text{ V}$




Typical switching losses vs gate resistance

$E = f(R_{G,ext}), V_{GS} = 0/18\text{ V}, T_J = 175^\circ\text{C}, I_D = 11.3\text{ A}, V_{DS} = 800\text{ V}$



NTC thermistor characteristics

$R = f(T_{NTC})$



6 Pin description




Figure 1 Pin-out (bottom view)

Table 9 Pin description

Pin number	Description	Pin number	Description
1	N	17	P
2	N	18	P
3	NC	19	G1
4	NC	20	S1
5	PH3	21	G2
6	PH3	22	S2
7	NC	23	G3
8	NC	24	S3
9	PH2	25	G4
10	PH2	26	S4
11	NC	27	G5
12	NC	28	S5
13	PH1	29	G6
14	PH1	30	S6
15	T2	31	NC
16	T1	32	NC

7 Package outline




Figure 2 AMM12S62LB1Z

Revision history

Document version	Date of release	Description of changes
2.0	2026-01-30	Initial release

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2026-01-30

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2026 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

Document reference

ifx1

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.