

TLE4922-XAN-F

Product Description



The TLE4922 is an active mono cell Hall sensor suited to detect motion and position of ferromagnetic and permanent magnet structures. An additional self-calibration module has been implemented to achieve optimum accuracy during normal running operation.

Target Application

The TLE4922 is a speed sensor especially optimized for small engine (2- and 3 wheeler) applications.

- Crankshaft speed and position sensing
- Transmission speed on output shaft
- Speedometer application

Excellent sensitivity and accuracy combined with its wide operational temperature range makes the sensor ideally suited for harsh environments.

Key Features and Benefits

- Twist independent mounting (TIM) “enables one sensor fits all”
- Small thin package (PG-SSO-4-1)
- Protected against harsh environment due to
 - Short-circuit current protection at the output
 - Over temperature shutdown at the output and
 - Reverse voltage protection
- Supreme performance due to adaptive symmetrical hysteresis / threshold
- Independent of back bias magnet polarity due to $\pm 400\text{mT}$ full scale range
- Enhanced EMC & ESD robustness - ESD: $\pm 3\text{kV}$ HBM
- Wide operating temperature range - T_j : -40°C - 155°C
- True zero speed up to 8kHz signal frequency
- Enabling Low Power Application: $I_{dd} = 5\text{mA}$ at $V_{dd} = 9\text{V}$
- Large operating voltage range of 4.5V up to 18V
- Robustness against wheel run outs enables to sense broad range of wheels

Product Description




Figure 1 Application circuit TLE4922

Product Type	Marking	Ordering Code	Package
TLE4922-XAN-F	22BAA1	SP001106758	PG-SSO-4-1

Table of contents

Table of contents

	Table of contents	3
1	Specification	4
1.1	Absolute Maximum Ratings	4
1.2	Operating Range	4
1.3	Electrical Characteristics	5
1.4	Magnetic Characteristics and Self-Calibration Characteristics	6
1.5	Electromagnetic Compatibility (EMC)	8
1.6	Block Diagram TLE4922	8
1.7	Reference Target Wheel	9
1.8	Performance Graphs	10
1.9	Application	11
2	Package Information	12
2.1	Package Information PG-SSO-4-1	13
	Revision history	15
	Disclaimer	16

1 Specification

1 Specification

The listed characteristics are ensured over the operating range and lifetime of the integrated circuit.

1.1 Absolute Maximum Ratings

Table 1 Absolute Maximum Ratings

Parameter	Symbol	Values			Unit	Note or Test Condition
		Min.	Typ.	Max.		
Supply voltage	V_S	-18	-	-	V	
		-	-	18	V	
		-	-	24	V	max. 1 hour
	V_{SAC}	-	-	30	V	max. 1 min with $R_{SERIES} = 200\Omega$
Output OFF voltage	V_Q	-1	-	-	V	max. 60 min @ $T_A = 25^\circ\text{C}$
		-0.3	-	18	V	
Output ON voltage	V_Q	-	-	18	V	
Junction temperature	$T_J^{1)}$			195	$^\circ\text{C}$	3h
Overall lifetime	$T_{Pol}^{2)}$	-40	-	150	$^\circ\text{C}$	0.5 years
		-40	-	50	$^\circ\text{C}$	15 years
ESD compliance	ESD_{HBM}	-3	-	3	kV	HBM according ANSI/ESDA/JEDEC JS-001

Note: Stresses above the max. values listed here may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the integrated circuit.

1.2 Operating Range

The following operating conditions must not be exceeded in order to ensure correct operation of the IC. All parameters specified in the following sections refer to these operating conditions unless otherwise mentioned.

Table 2 Operating Range

Parameter	Symbol	Values			Unit	Note or Test Condition
		Min.	Typ.	Max.		
Supply voltage	V_S	4.5	-	18	V	
Continuous output ON current	I_Q	-	-	8.8	mA	

(table continues...)

¹ In temperature range between operating temperature and absolute maximum temperature no functionality is guaranteed.

² Maximum exposure time at other junction temperatures shall be calculated based on the values specified using the Arrhenius-model.

1 Specification

Table 2 (continued) Operating Range

Parameter	Symbol	Values			Unit	Note or Test Condition
		Min.	Typ.	Max.		
Operating junction temperature	$T_J^{3)}$	-40	-	155	°C	5000h
Frequency range of magnetic input signal	f	0 ⁴⁾	-	8000	Hz	

1.3 Electrical Characteristics

Table 3 Electrical Parameters

Parameter	Symbol	Values			Unit	Note or Test Condition
		Min.	Typ.	Max.		
Supply current	I_S	3.5	5.3	7.0	mA	
Output saturation voltage	V_{QSAT}	-	0.15	0.4	V	$I_Q = 8.8 \text{ mA}$
Output leakage current	I_{QLEAK}	-	-	10	μA	
Current limit for short-circuit protection	$I_{QSHORT}^{5)}$	37	44	52	mA	
Junction temperature for output protection	$T_{PROT}^{5)}$	175	195	215	°C	Output will shut down (high impedance) when exceeded
Power on time	$t_{ON}^{5)}$	-	0.7	0.9	ms	
Output fall time	$t_f^{6)}$	2.2	2.8	3.8	μs	$V_{LOAD} = 5 \text{ V}, C_{LOAD} = 4.7 \text{ nF}, R_{LOAD} = 1.2 \text{ k}\Omega$
Output rise time	$t_r^{5)6)}$	1	-	20	μs	$V_{LOAD} = 5 \text{ V}, C_{LOAD} = 4.7 \text{ nF}, R_{LOAD} = 1.2 \text{ k}\Omega$
Delay time	$t_d^{5)7)}$	12.5	18	23.5	μs	$V_{LOAD} = 5 \text{ V}, C_{LOAD} = 4.7 \text{ nF}, R_{LOAD} = 1.2 \text{ k}\Omega, f = 5 \text{ kHz}$, see Figure 2

³⁾ Typical R_{thJA} is 170K/W. As soon as back bias magnet is attached or customer mold covers the TLE4922 this value will decrease due to larger surface and mass of the module. Maximum exposure time at other junction temperatures shall be calculated based on the values specified using the Arrhenius-model.

⁴⁾ Maximum one additional pulse may occur due to temperature variation during stand still.

⁵⁾ Parameter is characterized by simulation/verification.

⁶⁾ Time between 20% and 80% value of V_{LOAD} .

⁷⁾ Only valid for the falling edge.

1 Specification

1.4 Magnetic Characteristics and Self-Calibration Characteristics

Table 4 Magnetic Characteristics and Self-Calibration Characteristics: 10 Gauss = 1mT

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Linear Region	$B_{LR}^{8)}$	-400	-	400	mT	
Peak to peak magnetic hysteresis	$B_{MIN}^{8)}$	2.0	3.0	5.3	mT	Full frequency range
		2.0	3.0	3.8	mT	Up to 3kHz signal frequency
Temperature compensation of magnetic hysteresis	TC_{Bmin}	-	-650	-	ppm	Temperature range from 25°C to 150°C
Back Bias Magnet Range	B_{BIAS}	-400	-	400	mT	At $T_a=25^\circ\text{C}$, please notice relation between back bias magnet and linear region as described in user manual
Duty Cycle	$DC^{9)}$	40	50	60	%	
		30	50	70	%	Including EMC (magnetic distortion)
Number of falling output edges required to be calibrated	$n_{Calib}^{9)/10)}$	-	-	3	-	At 4 th falling edge full accuracy reached.
Relative phase error in calibrated mode	$\phi_{rel}^{9)/11)}$	-	± 0.3	± 1.5	°crank	Forward and backward rotational direction. Temperature and airgap included.
Output falling edge repeatability (phase jitter) in calibrated mode	$\phi_{jitter}^{9)/11)}$	-	0.05	0.2	°crank	99.7 %, 3 pulses out of 1000 above limit. Equivalent to $\pm 3\sigma$ of a Gaussian distribution.

⁸ Is calculated out of measured sensitivity.

⁹ Parameter is characterized by simulation/verification.

¹⁰ Maximum one additional pulse may occur due to temperature variation during stand still.

¹¹ Performance measured on wheel described in [Chapter 1.7](#) within air gap range 0.5mm to 3.2mm.

1 Specification




Figure 2 Phase error and delay time definition




Figure 3 Phase jitter definition

1 Specification

1.5 Electromagnetic Compatibility (EMC)

The TLE4922 is characterized according to the IC level EMC requirements described in the “Generic IC EMC Test Specification” Version 1.2 from 2007¹²⁾. Additionally, component level EMC characterizations according to ISO 7637-2:2011, ISO 7637-3:2007 and ISO 16750-2:2010 regarding pulse immunity and CISPR 25 (2009-01) Ed. 3.0 regarding conducted emissions are performed.

Figure 1 outlines all needed external components to operate the DUT under application conditions. They are treated as inherent part of the DUT during component level EMC characterizations.

Note: Characterisation of Electro Magnetic Compatibility (EMC) are carried out on sample base of one qualification lot. Not all specification parameters are monitored during EMC exposure. Only key parameters e.g. switching current and duty cycle are monitored.

Parameter	Symbol	Level	Class
Testpulse 1	V_{EMC}	-100 V	C
Testpulse 2a ¹³⁾		100 V	A
Testpulse 2b		10 V	C
Testpulse 3a		-150 V	A
Testpulse 3b		100 V	A
Testpulse 4 ¹⁴⁾		-7 V	C
Testpulse 5b ¹⁵⁾		86.5 V	A

1.6 Block Diagram TLE4922




Figure 4 Block Diagram TLE4922

¹²⁾ The document is available online at <http://www.zvei.org/Verband/Publikationen/Seiten/Generic-IC-EMCTest-Specification-english.aspx>

¹³⁾ ISO 7637-2 (2004) describes internal resistance = 2Ω

¹⁴⁾ According to 7637-2 for test pulse 4 the test voltage shall be $12\text{ V} \pm 0.2\text{ V}$.

¹⁵⁾ A central load dump protection of 35V is used.

1 Specification

1.7 Reference Target Wheel

Table 5 Toothed wheel performance

Parameter	Symbol	Values			Unit	Note or Test Condition
		Min.	Typ.	Max		
Operational IC air-gap	AG ^{16/17)}	-	-	3.2	mm	Field strength of 300mT at 0.7mm above surface of back-bias magnet (is sensitive area of TLE4922)
Air-gap variation over one complete target revolution. Global run-out.	AG _{GLRO} ¹⁶⁾	-	-	0.5	mm	Difference between min. and max. air-gap over one complete target revolution.




Figure 5 Infineon reference toothed wheel: dimension in mm

Table 6 Reference target wheel geometry

Parameter	Typ value	Unit	Remarks
Material	ST37	-	
Tooth notch ratio	1.00	-	

¹⁶ Parameter is characterized by verification

¹⁷ Measured from surface of package to toothed wheel, explained in [Figure 5](#).

1 Specification

1.8 Performance Graphs

Following graphs of typical sensor behavior will help to optimize application performance:




Figure 6 Typical Performance

1 Specification

1.9 Application

Basic functionality

The TLE4922 is a mono-cell Hall sensor with analog to digital converter and full digital signal processing for detecting the magnetic field crossing of the threshold levels. A chopped Hall probe is used to mimic the offset and has advantages for 0-Hz feature. [Figure 2](#) in [Chapter 1.4](#) shows the basic functionality of TLE4922.

Unique Feature: Polarity of Pre Induction

The back bias magnet can be mounted in both directions to TLE4922 without any difference in performance. One polarity results in switching the output to “LOW” when passing a tooth and to “HIGH” when passing a notch, whereas the other polarity of back-bias magnet will switch the output to “HIGH” when passing a tooth and to “LOW” when passing a notch.




Figure 7 Changing polarity of back bias magnet will change the polarity of TLE4922 output

Start-Up and Running Mode

In Start-Up-Mode the TLE4922 starts with output at “HIGH” and stays there until a first minimum in magnetic field is detected after start-up time. Calibrated mode is reached after a maximum of four output transitions (The offset compensation algorithm is considering 4 teeth for averaging). At the 4th falling edge full accuracy on output signal is reached. These first transitions are determined by the detection of magnetic signal maxima and minima. Output transitions in running phase are determined by the hidden adaptive hysteresis algorithm.

Application circuit

[Figure 1](#) shows an option of an application circuit. The resistor R_S is recommended due to reason of EMC. The resistor R_L has to be at a value to match the applied V_{ECU} to keep I_Q limited to the operating range of maximal 8.8mA.e.g.: $V_{LOAD} = 9V$; $I_Q = 9V/1200\ \Omega = 7.5mA$

Consideration on R_{thJA}

The R_{th} is modified by attaching a back-bias magnet or doing molding at the customer. There is dependency on the attached wires: The thicker the attached wire the smaller the value of R_{th} . It depends on ambient condition: When one end of the module is cooled in oil or through air-flow the R_{thJA} will decrease.

Global run out

Due to averaging, global run out is depending on the number of teeth. The wheel in [Chapter 1.7](#) allows a global run out of 0.8mm. Wheels with equal or more than 8 teeth are capable of up to 0.5mm global run out.

2 Package Information

2 Package Information

Green Product (RoHS compliant)

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e. Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).




Figure 8 Pinning, Sensitive Area

2 Package Information

2.1 Package Information PG-SSO-4-1

Pure tin covering (green lead plating) is used. The product is RoHS (Restriction of Hazardous Substances) compliant and marked with letter G in front of the data code marking and may contain a data matrix code on the rear side of the package. Please refer to your key account team or regional sales if your need further information.




Figure 9 Marking pattern




Figure 10 PG-SSO-4-1 package dimensions, dimensions in mm

2 Package Information




Figure 11 **PG-SSO-4-1 packaging, dimensions in mm**

Revision history**Revision history**

Document version	Date of release	Description of changes
1.0	2016-11-21	Initial release
2.0	2025-02-28	- Table 1: Supply voltage extended to max. 24V, max. 1hour - Table 1: Overall lifetime -40°C ... 150°C extended to 0.5 years - Table 2: Supply voltage extended to max. 18V - Table 2: Operating junction temperature -40°C ... 155°C extended to 5000h - Editorial changes, new template

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-02-28

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2025 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-hrc1739531393376

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.