


## CIPOS™ Prime

### AMM12S36LB1Z

#### Features

- 1200 V SiC MOSFET 6-pack
- 36 mΩ of typical  $R_{DS(on)}$  at  $V_{GS} = 18\text{ V}$ ,  $T_J = 25^\circ\text{C}$
- Maximum operating  $T_J = 175^\circ\text{C}$
- Very low switching losses
- Robust against parasitic turn on, 0 V turn-off gate voltage can be applied
- Robust body diode for hard commutation
- High performance AlN DCB substrate
- Integrated NTC thermistor



#### Potential applications

- On-board charger
- DC-DC converter
- EV charging
- Power conversion AC-DC, DC-AC

#### Product validation

Qualified for automotive applications

Product validation according to AEC-Q101 / 200 and AQG 324

#### Description

The CIPOS™ Prime product offers an integrated solution for high frequency power conversion applications. The power module includes six SiC MOSFETs and a NTC and enables high power density. Infineon's SiC technology provides excellent switching performance, wide range of gate-source voltage, and benchmark gate threshold voltage. The DCB substrate enables optimal thermal performance and package is designed to ensure a high creepage distance.

**Table 1** Product Information

Base Part Number	Package Type	Standard Pack		Sales Product Number
		Form	MOQ	
AMM12S36LB1Z	DIP 44x28DA	11 pcs / Tube	176 pcs	SP006043512



**Table of contents**

Features ..... 1

Potential applications ..... 1

Product validation ..... 1

Description ..... 1

Table of contents ..... 2

1 MOSFET ..... 3

2 MOSFET body diode ..... 5

3 Package ..... 6

4 Thermistor ..... 7

5 Characteristics diagrams ..... 8

6 Pin description ..... 13

7 Package outline ..... 14

Revision history ..... 15

# 1 MOSFET

**Table 2 Maximum ratings**

Description	Symbol	Condition	Values	Unit
Drain-source voltage	$V_{DS}$	$T_J \geq 25^\circ\text{C}$	1200	V
Continuous drain current for $R_{th(j-c)}$ , limited by $T_{J,max}$	$I_D$	$V_{GS} = 18\text{ V}, T_C = 25^\circ\text{C}$	46	A
		$V_{GS} = 18\text{ V}, T_C = 100^\circ\text{C}$	33	
Peak drain current, $t_p$ limited by $T_{J,max}$	$I_{DM}$	$V_{GS} = 18\text{ V}$	99	A
Gate-source voltage, max. transient voltage	$V_{GS}$	$t_p \leq 0.5\ \mu\text{s}, D < 0.01$	-10 ~ 23	V
Gate-source voltage, max. static voltage	$V_{GS}$		-5 ~ 20	V
Power dissipation per switch	$P_D$		189	W
Operating junction temperature	$T_J$		-40 ~ 175	$^\circ\text{C}$

**Table 3 Recommended values**

Description	Symbol	Condition	Values	Unit
Turn-on gate-source voltage	$V_{GS(on)}$		15 ~ 18	V
Turn-off gate-source voltage	$V_{GS(off)}$		-3 ~ 0	V

**Table 4 Electrical characteristics**

( $T_J = 25^\circ\text{C}$  if not stated otherwise)

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Drain-source on-state resistance	$R_{DS(on)}$	$I_D = 18.2\text{ A}, V_{GS} = 18\text{ V}$		36	50.8	m $\Omega$
		$I_D = 18.2\text{ A}, V_{GS} = 18\text{ V}, T_J = 175^\circ\text{C}$		86		
		$I_D = 18.2\text{ A}, V_{GS} = 15\text{ V}$		44		
Gate-source threshold voltage	$V_{GS(th)}$	$I_D = 5.7\text{ mA}, V_{DS} = V_{GS}$	3.5	4.2	5.1	V
		$I_D = 5.7\text{ mA}, V_{DS} = V_{GS}, T_J = 175^\circ\text{C}$		3.2		
Zero gate-voltage drain current	$I_{DSS}$	$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}$			180	$\mu\text{A}$
		$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}, T_J = 175^\circ\text{C}$		3		
Gate leakage current	$I_{GSS}$	$V_{DS} = 0\text{ V}, V_{GS} = 23\text{ V}$			120	nA
		$V_{DS} = 0\text{ V}, V_{GS} = -10\text{ V}$			-120	
Forward transconductance	$g_{fs}$	$I_D = 18.2\text{ A}, V_{DS} = 00\text{ V}$		9.0		S

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Internal gate resistance	$R_{G,int}$	$f = 1 \text{ MHz}, V_{AC} = 25 \text{ mV}$		7.5		$\Omega$
Input capacitance	$C_{iss}$	$V_{DS} = 800 \text{ V}, V_{GS} = 0 \text{ V}, f = 100 \text{ kHz}, V_{AC} = 25 \text{ mV}$		1415		$\text{pF}$
Output capacitance	$C_{oss}$			68		
Reverse transfer capacitance	$C_{rss}$			6.2		
$C_{oss}$ stored energy	$E_{oss}$			27		
Total gate charge	$Q_G$	$V_{DS} = 800 \text{ V}, I_D = 18.2 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}$		44		$\text{nC}$
Plateau gate charge	$Q_{GS(pl)}$			20		
Gate-to-drain charge	$Q_{GD}$			7.6		
Turn-on energy	$E_{on}$	$V_{DS} = 800 \text{ V}, I_D = 18.2 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega$		120		$\mu\text{J}$
		$V_{DS} = 800 \text{ V}, I_D = 18.2 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega, T_J = 175^\circ\text{C}$		135		
Turn-off energy	$E_{off}$	$V_{DS} = 800 \text{ V}, I_D = 18.2 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega$		80		$\mu\text{J}$
		$V_{DS} = 800 \text{ V}, I_D = 18.2 \text{ A}, V_{GS} = 0 \text{ to } 18 \text{ V}, R_G = 5 \Omega, T_J = 175^\circ\text{C}$		85		

## 2 MOSFET body diode

**Table 5** Maximum ratings

Description	Symbol	Condition	Values	Unit
Drain-source voltage	$V_{DSS}$	$T_J \geq 25^\circ\text{C}$	1200	V
Peak reverse drain current, $t_p$ limited by $T_{J,max}$	$I_{SM}$	$V_{GS} = 0\text{ V}$	42	A

**Table 6** Electrical characteristics

( $T_J = 25^\circ\text{C}$  if not stated otherwise)

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Drain-source reverse voltage	$V_{SD}$	$I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}$		4.2	5.5	V
		$I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}, T_J = 175^\circ\text{C}$		4.05		
MOSFET reverse recovery charge	$Q_{rr}$	$V_{DS} = 800\text{ V}, I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C$		0.29		$\mu\text{C}$
		$V_{DS} = 800\text{ V}, I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C, T_J = 175^\circ\text{C}$		0.4		
MOSFET peak reverse recovery current	$I_{rrm}$	$V_{DS} = 800\text{ V}, I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C$		20.8		A
		$V_{DS} = 800\text{ V}, I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C, T_J = 175^\circ\text{C}$		27.3		
MOSFET reverse recovery energy	$E_{rr}$	$V_{DS} = 800\text{ V}, I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C$		120		$\mu\text{J}$
		$V_{DS} = 800\text{ V}, I_{SD} = 18.2\text{ A}, V_{GS} = 0\text{ V}, di/dt = 1000\text{ A}/\mu\text{s}, Q_{rr}$ includes $Q_C, T_J = 175^\circ\text{C}$		160		

Package

### 3 Package

**Table 7 Characteristics and ratings**

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Storage temperature	$T_{stg}$		-40		125	°C
Thermal resistance, junction-case per switch	$R_{th(j-c)}$				0.79	K/W
Isolation voltage	$V_{ISO}$	1 min., RMS, f = 50 Hz	3.5			kV
Clearance distance		Pin to pin	2.4			mm
		Pin to flat heatsink	3.3			
Creepage distance		Pin to pin	5.5			
		Pin to DCB	12.12			
Comparative tracking index	CTI		600			V
Mounting torque		M3 SEMS screw	0.39	0.68	0.98	Nm
DCB flatness			0		120	μm
Weight				13.8		g

## 4 Thermistor


**Table 8 Characteristic values**

Description	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Resistance	$R_{25}$	$T = 25^{\circ}\text{C}$		10		$\text{k}\Omega$
Tolerance			-2		2	%
Resistance	$R_{100}$	$T = 100^{\circ}\text{C}$		674.4		$\Omega$
Tolerance			-4.75		4.75	%
B-constant	B(25/50)	$T = 25^{\circ}\text{C}$ to $50^{\circ}\text{C}$		3946		K
	B(25/85)	$T = 25^{\circ}\text{C}$ to $85^{\circ}\text{C}$		3988		
	B(25/100)	$T = 25^{\circ}\text{C}$ to $100^{\circ}\text{C}$		4000		
Operating temperature range	$T_{\text{NTC}}$		-40		150	$^{\circ}\text{C}$

## 5 Characteristics diagrams


### Forward bias safe operating area (FBSOA)

$I_D = f(V_{DS})$ ,  $T_C = 25^\circ\text{C}$ ,  $D = 0$ , parameter:  $t_p$




### Reverse bias safe operating area (RBSOA)

$I_D = f(V_{DS})$ ,  $V_{GS} = 0/18\text{ V}$ ,  $T_J \leq 175^\circ\text{C}$ ,  $T_C = 25^\circ\text{C}$




### Power dissipation

$P_{tot} = f(T_C)$



### Max. transient thermal impedance


$Z_{th(j-c),max} = f(t_p)$ ,  $D = t_p/T$



Characteristics diagrams


**Typical transfer characteristics**

$I_{DS} = f(V_{GS}), V_{DS} = 20\text{ V}$




**Typical gate-source threshold voltage vs junction temperature**

$V_{GS(th)} = f(T_J), I_D = 5.7\text{ mA}$




**Typical output characteristics**

$I_D = f(V_{DS}), T_J = 25^\circ\text{C}$



**Typical output characteristics**


$I_D = f(V_{DS}), T_J = 175^\circ\text{C}$



Characteristics diagrams


**Typical on-state resistance vs junction temperature**

$R_{DS(on)} = f(T_J), I_D = 18.2 A$




**Typical gate charge**

$V_{GS} = f(Q_G), I_D = 18.2 A, V_{DS} = 800 V$




**Typical capacitance vs drain-source voltage**

$C = f(V_{DS}), f = 100 kHz, V_{GS} = 0 V$



**Typical Coss stored energy**


$E = f(V_{DS})$



Characteristics diagrams


Typical Coss stored charge

$Q = f(V_{DS})$




Typical reverse drain voltage characteristics

$V_{SD} = f(T_J), I_{SD} = 18.2 \text{ A}, V_{GS} = 0 \text{ V}$




Typical reverse drain current characteristics

$I_{SD} = f(V_{SD}), T_J = 25^\circ\text{C}$



Typical reverse drain current characteristics


$I_{SD} = f(V_{SD}), T_J = 175^\circ\text{C}$



Characteristics diagrams


**Typical switching losses vs junction temperature**

$E = f(T_J), V_{GS} = 0/18\text{ V}, I_D = 18.2\text{ A}, R_{G,ext} = 5\ \Omega, V_{DS} = 800\text{ V}$




**Typical switching losses vs drain current**

$E = f(I_D), V_{GS} = 0/18\text{ V}, T_J = 175^\circ\text{C}, R_{G,ext} = 5\ \Omega, V_{DS} = 800\text{ V}$




**Typical switching losses vs gate resistance**

$E = f(R_{G,ext}), V_{GS} = 0/18\text{ V}, T_J = 175^\circ\text{C}, I_D = 18.2\text{ A}, V_{DS} = 800\text{ V}$



**NTC thermistor characteristics**

$R = f(T_{NTC})$



## 6 Pin description




Figure 1 Pin-out (bottom view)

Table 9 Pin description

Pin number	Description	Pin number	Description
1	N	17	P
2	N	18	P
3	NC	19	G1
4	NC	20	S1
5	PH3	21	G2
6	PH3	22	S2
7	NC	23	G3
8	NC	24	S3
9	PH2	25	G4
10	PH2	26	S4
11	NC	27	G5
12	NC	28	S5
13	PH1	29	G6
14	PH1	30	S6
15	T2	31	NC
16	T1	32	NC

## 7 Package outline




Figure 2 AMM12S36LB1Z



**Revision history**

<b>Document version</b>	<b>Date of release</b>	<b>Description of changes</b>
2.0	2026-01-30	Initial release

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2026-01-30**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2026 Infineon Technologies AG.**

**All Rights Reserved.**

**Do you have a question about this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

**ifx1**

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

## WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.