

Final datasheet

CoolSiC™ 1400 V SiC MOSFET G2 : Silicon Carbide MOSFET with .XT interconnection technology

特徴

- $V_{DSS} = 1400\text{ V}$ at $T_{vj} = 25^\circ\text{C}$
- $I_{DC} = 104\text{ A}$ at $T_C = 100^\circ\text{C}$
- $R_{DS(on)} = 11.5\text{ m}\Omega$ at $V_{GS} = 18\text{ V}$, $T_{vj} = 25^\circ\text{C}$
- Very low switching losses
- Short circuit withstand time $2\text{ }\mu\text{s}$
- Benchmark gate threshold voltage, $V_{GS(th)} = 4.2\text{ V}$
- Robust against parasitic turn on, 0 V turn-off gate voltage can be applied
- Robust body diode for hard commutation
- .XT interconnection technology for best-in-class thermal performance
- 最適なインフィニオン製ゲートドライバーは以下でご覧になれます。
<https://www.infineon.com/gdfinder>



- Halogen-free
- Green
- Lead-free
- RoHS

可能性のある用途

- General purpose drives (GPD)
- EV Charging
- Online UPS / Industrial UPS
- String inverter
- Energy storage systems (ESS)
- Welding

製品検証


- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22

詳細

Pin definition:

- Pin 1 – Drain
- Pin 2 – Source
- Pin 3 – Kelvin sense contact
- Pin 4 – Gate

Note: the source and sense pins are not exchangeable, their exchange might lead to malfunction



| Type | Package | Marking |
|----------------|----------------|----------|
| IMZC140R011M2H | PG-TO247-4-U07 | 14M2H011 |

目次

| | | |
|----------|----------------------------------|-----------|
| | 詳細..... | 1 |
| | 特徴..... | 1 |
| | 可能性のある用途..... | 1 |
| | 製品検証..... | 1 |
| | 目次..... | 2 |
| 1 | ハウジング | 3 |
| 2 | MOSFET | 3 |
| 3 | Body diode (MOSFET) | 6 |
| 4 | 特性図 | 8 |
| 5 | パッケージ外形図 | 15 |
| 6 | Testing conditions | 16 |
| | 改訂履歴..... | 17 |
| | 免責事項..... | 18 |

1 ハウジング

1 ハウジング

表 1 電気的特性

| 項目 | 記号 | 条件及び注記 | 規格値 | | | 単位 |
|---|---------------|--|-----|-----|------|-----|
| | | | 最小 | 標準 | 最大 | |
| Storage temperature | T_{stg} | | -55 | | 150 | °C |
| Soldering temperature | T_{sold} | Wave soldering only allowed at leads 1.6 mm (0.063 in.) from case for 10 s | | | 260 | °C |
| Mounting torque | M | M3 screw, Maximum of mounting processes: 3 | | | 0.6 | Nm |
| Thermal resistance, junction-ambient | $R_{th(j-a)}$ | | | | 62 | K/W |
| MOSFET/body diode thermal resistance, junction-case | $R_{th(j-c)}$ | | | 0.2 | 0.26 | K/W |

2 MOSFET

表 2 最大定格

| 項目 | 記号 | 条件及び注記 | 定格値 | 単位 | |
|--|-----------|---|-----------------------|---------------|---|
| ドレイン・ソース間電圧 | V_{DSS} | $T_{vj} \geq 25\text{ °C}$ | 1400 | V | |
| Continuous DC drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$ | I_{DDC} | $V_{GS} = 18\text{ V}$ | $T_c = 25\text{ °C}$ | 147 | A |
| | | | $T_c = 100\text{ °C}$ | 104 | |
| Peak drain current, t_p limited by $T_{vj(max)}$ ¹⁾ | I_{DM} | $V_{GS} = 18\text{ V}$ | 520 | A | |
| Gate-source voltage, max. transient voltage | V_{GS} | $t_p \leq 0.5\ \mu\text{s}, D < 0.01$ | -10...25 | V | |
| Gate-source voltage, max. static voltage ²⁾ | V_{GS} | | -7...23 | V | |
| Avalanche energy, single pulse | E_{AS} | $I_D = 69.1\text{ A}, V_{DD} = 50\text{ V}, L = 0.4\text{ mH}, T_{vj(start)} = 25\text{ °C}$ | 865 | mJ | |
| Avalanche energy, repetitive | E_{AR} | $I_D = 69.1\text{ A}, V_{DD} = 50\text{ V}, L = 1.8\ \mu\text{H}, T_{vj(start)} = 25\text{ °C}$ | 4.3 | mJ | |
| Short-circuit withstand time | t_{SC} | $V_{DD} \leq 800\text{ V}, V_{DS,peak} < 1400\text{ V}, V_{GS(on)} = 15\text{ V}, T_{vj(start)} = 25\text{ °C}$ | 2 | μs | |
| Power dissipation, limited by $T_{vj(max)}$ | P_{tot} | | $T_c = 25\text{ °C}$ | 568 | W |
| | | | $T_c = 100\text{ °C}$ | 284 | |

1) Verified by design.

2) The maximum gate-source voltage in the application design should be in accordance to IPC-9592B.

表 3 推奨値

| 項目 | 記号 | 条件及び注記 | [JA]Values | 単位 |
|-----------------------------------|---------------|--------|------------|----|
| Recommended turn-on gate voltage | $V_{GS(on)}$ | | 15...18 | V |
| Recommended turn-off gate voltage | $V_{GS(off)}$ | | -5...0 | V |

表 4 電気的特性

| 項目 | 記号 | 条件及び注記 | 規格値 | | | 単位 | |
|--|--------------|--|--|------|------|------|----|
| | | | 最小 | 標準 | 最大 | | |
| Drain-source on-state resistance | $R_{DS(on)}$ | $I_D = 69.1 \text{ A}$ | $T_{vj} = 25 \text{ }^\circ\text{C}, V_{GS(on)} = 18 \text{ V}$ | | 11.5 | | mΩ |
| | | | $T_{vj} = 150 \text{ }^\circ\text{C}, V_{GS(on)} = 18 \text{ V}$ | | 23.9 | 31.3 | |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}, V_{GS(on)} = 18 \text{ V}$ | | 28 | | |
| | | | $T_{vj} = 25 \text{ }^\circ\text{C}, V_{GS(on)} = 15 \text{ V}$ | | 14 | | |
| Gate-source threshold voltage | $V_{GS(th)}$ | $I_D = 21.7 \text{ mA}, V_{DS} = V_{GS}$ (tested after 1 ms pulse at $V_{GS} = 20 \text{ V}$) | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 3.5 | 4.2 | 5.1 | V |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 3.2 | | |
| Zero gate-voltage drain current | I_{DSS} | $V_{DS} = 1400 \text{ V}, V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | | | 520 | μA |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 8.8 | | |
| Gate leakage current | I_{GSS} | $V_{DS} = 0 \text{ V}$ | $V_{GS} = 23 \text{ V}$ | | | 120 | nA |
| | | | $V_{GS} = -10 \text{ V}$ | | | -120 | |
| Forward transconductance | g_{fs} | $I_D = 69.1 \text{ A}, V_{DS} = 20 \text{ V}$ | | 45 | | S | |
| Internal gate resistance | $R_{G,int}$ | $f = 1 \text{ MHz}, V_{AC} = 25 \text{ mV}$ | | 4.5 | | Ω | |
| Input capacitance | C_{iss} | $V_{DS} = 1000 \text{ V}, V_{GS} = 0 \text{ V}, f = 100 \text{ kHz}, V_{AC} = 25 \text{ mV}$ | | 4830 | | pF | |
| Output capacitance | C_{oss} | $V_{DS} = 1000 \text{ V}, V_{GS} = 0 \text{ V}, f = 100 \text{ kHz}, V_{AC} = 25 \text{ mV}$ | | 168 | | pF | |
| Reverse transfer capacitance | C_{rss} | $V_{DS} = 1000 \text{ V}, V_{GS} = 0 \text{ V}, f = 100 \text{ kHz}, V_{AC} = 25 \text{ mV}$ | | 15 | | pF | |
| C_{oss} stored energy | E_{oss} | Calculated based on $C_{oss} = f(V_{DD})$ | | 107 | | μJ | |
| Output charge | Q_{oss} | Calculated based on $C_{oss} = f(V_{DD})$ | | 294 | | nC | |
| Effective output capacitance, energy related | $C_{o(er)}$ | $V_{DS} = 0...1000 \text{ V}, V_{GS} = 0 \text{ V},$ Calculated based on E_{oss} | | 334 | | pF | |
| Effective output capacitance, time related | $C_{o(tr)}$ | $I_D = \text{constant}, V_{DS} = 0...1000 \text{ V}, V_{GS} = 0 \text{ V},$ Calculated based on Q_{oss} | | 368 | | pF | |

(続く)

表 4 (続き) 電気的特性

| 項目 | 記号 | 条件及び注記 | 規格値 | | | 単位 |
|--------------------------------------|--------------|--|---------------------------------------|------|------|---------------|
| | | | 最小 | 標準 | 最大 | |
| Total gate charge | Q_G | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, turn-on pulse | | 130 | | nC |
| Plateau gate charge | $Q_{GS(pl)}$ | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, turn-on pulse | | 36 | | nC |
| Gate-drain charge | Q_{GD} | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, turn-on pulse | | 34 | | nC |
| Turn-on delay time | $t_{d(on)}$ | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{G,ext} = 2.3 \Omega$, $L_\sigma = 12 \text{ nH}$, diode: body diode at $V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 23 | | ns |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 20 | |
| Rise time | t_r | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{G,ext} = 2.3 \Omega$, $L_\sigma = 12 \text{ nH}$, diode: body diode at $V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 14 | | ns |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 13 | |
| Turn-off delay time | $t_{d(off)}$ | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{G,ext} = 2.3 \Omega$, $L_\sigma = 12 \text{ nH}$, diode: body diode at $V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 56 | | ns |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 62 | |
| Fall time | t_f | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{G,ext} = 2.3 \Omega$, $L_\sigma = 12 \text{ nH}$, diode: body diode at $V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 23 | | ns |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 25 | |
| Turn-on energy | E_{on} | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{G,ext} = 2.3 \Omega$, $L_\sigma = 12 \text{ nH}$, diode: body diode at $V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 1078 | | μJ |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 2456 | |
| Turn-off energy | E_{off} | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{G,ext} = 2.3 \Omega$, $L_\sigma = 12 \text{ nH}$, diode: body diode at $V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 1084 | | μJ |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 1207 | |
| Total switching energy ¹⁾ | E_{tot} | $V_{DD} = 1000 \text{ V}$, $I_D = 69.1 \text{ A}$, $V_{GS} = 0/18 \text{ V}$, $R_{G,ext} = 2.3 \Omega$, $L_\sigma = 12 \text{ nH}$, diode: body diode at $V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 2040 | | μJ |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | | 4020 | |

(続く)

3 Body diode (MOSFET)

表 4 (続き) 電気的特性

| 項目 | 記号 | 条件及び注記 | 規格値 | | | 単位 |
|--|-----------|--|--------------------------------------|----|------|------------------|
| | | | 最小 | 標準 | 最大 | |
| Turn-on energy at -5 V | E_{on} | $V_{DD} = 1000\text{ V}$, $I_D = 69.1\text{ A}$, $V_{GS} = -5/18\text{ V}$, $R_{G,ext} = 2.3\ \Omega$, $L_\sigma = 12\text{ nH}$, diode: body diode at $V_{GS} = -5\text{ V}$ | $T_{vj} = 25\text{ }^\circ\text{C}$ | | 1078 | μJ |
| | | | $T_{vj} = 175\text{ }^\circ\text{C}$ | | 2513 | |
| Turn-off energy at -5 V | E_{off} | $V_{DD} = 1000\text{ V}$, $I_D = 69.1\text{ A}$, $V_{GS} = -5/18\text{ V}$, $R_{G,ext} = 2.3\ \Omega$, $L_\sigma = 12\text{ nH}$, diode: body diode at $V_{GS} = -5\text{ V}$ | $T_{vj} = 25\text{ }^\circ\text{C}$ | | 652 | μJ |
| | | | $T_{vj} = 175\text{ }^\circ\text{C}$ | | 714 | |
| Total switching energy at -5 V ¹⁾ | E_{tot} | $V_{DD} = 1000\text{ V}$, $I_D = 69.1\text{ A}$, $V_{GS} = -5/18\text{ V}$, $R_{G,ext} = 2.3\ \Omega$, $L_\sigma = 12\text{ nH}$, diode: body diode at $V_{GS} = -5\text{ V}$ | $T_{vj} = 25\text{ }^\circ\text{C}$ | | 1822 | μJ |
| | | | $T_{vj} = 175\text{ }^\circ\text{C}$ | | 3605 | |
| Virtual junction temperature | T_{vj} | | -55 | | 175 | $^\circ\text{C}$ |

1) including E_{fr}

注: The chip technology was characterized up to 200 kV/ μs . The measured dV/dt was limited by measurement test setup and package.

Characteristics at $T_{vj} = 25\text{ }^\circ\text{C}$, unless otherwise specified.

3 Body diode (MOSFET)

表 5 最大定格

| 項目 | 記号 | 条件及び注記 | 定格値 | 単位 | |
|---|-----------|--|-----------------------------------|-----|---|
| Drain-source voltage | V_{DSS} | $T_{vj} \geq 25\text{ }^\circ\text{C}$ | 1400 | V | |
| Continuous reverse drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$ | I_{SDC} | $V_{GS} = 0\text{ V}$ | $T_c = 25\text{ }^\circ\text{C}$ | 108 | A |
| | | | $T_c = 100\text{ }^\circ\text{C}$ | 59 | |
| Peak reverse drain current, t_p limited by $T_{vj(max)}$ | I_{SM} | $V_{GS} = 0\text{ V}$ | 312 | A | |


表 6 電気的特性

| 項目 | 記号 | 条件及び注記 | 規格値 | | | 単位 |
|--|-----------|---|---------------------------------------|------|-----|------------------|
| | | | 最小 | 標準 | 最大 | |
| Drain-source reverse voltage | V_{SD} | $I_{SD} = 69.1 \text{ A}, V_{GS} = 0 \text{ V}$ | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 4.2 | 5.5 | V |
| | | | $T_{vj} = 100 \text{ }^\circ\text{C}$ | 4.11 | | |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | 4.05 | | |
| MOSFET forward recovery charge | Q_{fr} | $V_{DD} = 1000 \text{ V}, I_{SD} = 69.1 \text{ A}, V_{GS} = 0 \text{ V}, R_{GS(on)} = 2.3 \text{ } \Omega, Q_{fr}$ includes also Q_C | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 0.58 | | μC |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | 2.11 | | |
| MOSFET peak forward recovery current | I_{frm} | $V_{DD} = 1000 \text{ V}, I_{SD} = 69.1 \text{ A}, V_{GS} = 0 \text{ V}, R_{GS(on)} = 2.3 \text{ } \Omega, Q_{fr}$ includes also Q_C | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 63 | | A |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | 109 | | |
| MOSFET forward recovery energy | E_{fr} | $V_{DD} = 1000 \text{ V}, I_{SD} = 69.1 \text{ A}, V_{GS} = 0 \text{ V}, R_{GS(on)} = 2.3 \text{ } \Omega, Q_{fr}$ includes also Q_C | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 82 | | μJ |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | 357 | | |
| MOSFET forward recovery energy at -5 V | E_{fr} | $V_{DD} = 1000 \text{ V}, I_{SD} = 69.1 \text{ A}, V_{GS} = -5 \text{ V}, R_{GS(on)} = 2.3 \text{ } \Omega, Q_{fr}$ includes also Q_C | $T_{vj} = 25 \text{ }^\circ\text{C}$ | 92 | | μJ |
| | | | $T_{vj} = 175 \text{ }^\circ\text{C}$ | 378 | | |
| Virtual junction temperature | T_{vj} | | -55 | | 175 | $^\circ\text{C}$ |

4 特性図


Safe operating area (SOA)

$I_D = f(V_{DS})$
 $T_{vj} \leq 175\text{ }^\circ\text{C}, T_c = 25\text{ }^\circ\text{C}$




Power dissipation as a function of case temperature

$P_{tot} = f(T_c)$




Maximum DC drain to source current as a function of case temperature limited by bond wire

$I_D = f(T_c)$



Maximum source to drain current as a function of case temperature limited by bond wire


$I_{SD} = f(T_c)$
 $V_{GS} = 0\text{ V}$



4 特性图


Typical transfer characteristic

$I_D = f(V_{GS})$
 $V_{DS} = 20\text{ V}, t_p = 20\ \mu\text{s}$




Typical gate-source threshold voltage as a function of junction temperature

$V_{GS(th)} = f(T_{vj})$
 $I_D = 21.7\text{ mA}$




Typical output characteristic, V_{GS} as a parameter

$I_D = f(V_{DS})$
 $T_{vj} = 25\ ^\circ\text{C}, t_p = 20\ \mu\text{s}$



Typical output characteristic, V_{GS} as a parameter


$I_D = f(V_{DS})$
 $T_{vj} = 175\ ^\circ\text{C}, t_p = 20\ \mu\text{s}$



4 特性図


Typical on-state resistance as a function of junction temperature

$R_{DS(on)} = f(T_{vj})$
 $I_D = 69.1 \text{ A}$




Typical gate charge

$V_{GS} = f(Q_G)$
 $I_D = 69.1 \text{ A}, V_{DS} = 1000 \text{ V}$




Typical capacitance as a function of drain-source voltage

$C = f(V_{DS})$
 $f = 100 \text{ kHz}, V_{GS} = 0 \text{ V}$



Typical reverse drain voltage as a function of junction temperature


$V_{SD} = f(T_{vj})$
 $I_{SD} = 69.1 \text{ A}, V_{GS} = 0 \text{ V}$



4 特性图


Typical reverse drain current as a function of reverse drain voltage, V_{GS} as a parameter

$I_{SD} = f(V_{SD})$
 $T_{vj} = 25\text{ }^{\circ}\text{C}$, $t_p = 20\text{ }\mu\text{s}$




Typical reverse drain current as a function of reverse drain voltage, V_{GS} as a parameter

$I_{SD} = f(V_{SD})$
 $T_{vj} = 175\text{ }^{\circ}\text{C}$, $t_p = 20\text{ }\mu\text{s}$




Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$E = f(T_{vj})$
 $V_{GS} = 0/18\text{ V}$, $I_D = 69.1\text{ A}$, $R_{G,ext} = 2.3\text{ }\Omega$, $V_{DD} = 1000\text{ V}$



Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = -5\text{ V}$

$E = f(T_{vj})$
 $V_{GS} = -5/18\text{ V}$, $I_D = 69.1\text{ A}$, $R_{G,ext} = 2.3\text{ }\Omega$, $V_{DD} = 1000\text{ V}$




4 特性图

Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$E = f(I_D)$


$V_{GS} = 0/18\text{ V}$, $T_{vj} = 175\text{ °C}$, $R_{G,ext} = 2.3\ \Omega$, $V_{DD} = 1000\text{ V}$



Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = -5\text{ V}$

$E = f(I_D)$


$V_{GS} = -5/18\text{ V}$, $T_{vj} = 175\text{ °C}$, $R_{G,ext} = 2.3\ \Omega$, $V_{DD} = 1000\text{ V}$



Typical switching energy as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$E = f(R_{G,ext})$


$V_{GS} = 0/18\text{ V}$, $I_D = 69.1\text{ A}$, $T_{vj} = 175\text{ °C}$, $V_{DD} = 1000\text{ V}$



Typical switching energy as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = -5\text{ V}$

$E = f(R_{G,ext})$

$V_{GS} = -5/18\text{ V}$, $I_D = 69.1\text{ A}$, $T_{vj} = 175\text{ °C}$, $V_{DD} = 1000\text{ V}$




4 特性图

Typical switching energy as a function of DC link voltage, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$E = f(V_{DD})$


$V_{GS} = 0/18\text{ V}$, $I_D = 69.1\text{ A}$, $T_{vj} = 175\text{ °C}$, $R_{G,ext} = 2.3\text{ }\Omega$



Typical switching energy as a function of DC link voltage, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = -5\text{ V}$

$E = f(V_{DD})$


$V_{GS} = -5/18\text{ V}$, $I_D = 69.1\text{ A}$, $T_{vj} = 175\text{ °C}$, $R_{G,ext} = 2.3\text{ }\Omega$



Typical switching times as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$t = f(R_{G,ext})$


$V_{GS} = 0/18\text{ V}$, $I_D = 69.1\text{ A}$, $T_{vj} = 175\text{ °C}$, $V_{DD} = 1000\text{ V}$



Typical reverse recovery charge as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$Q_{fr} = f(-di_{SD}/dt)$

$V_{GS} = 0/18\text{ V}$, $I_{SD} = 69.1\text{ A}$, $V_{DD} = 1000\text{ V}$




4 特性図

Typical reverse recovery current as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$$I_{frm} = f(-di_{SD}/dt)$$


$I_{SD} = 69.1\text{ A}$, $V_{DD} = 1000\text{ V}$, $V_{GS} = 0/18\text{ V}$



Typical switching energy as a function of dead time / blanking time, test circuit in Fig. F, 2nd device own body diode: $V_{GS} = 0\text{ V}$

$$E = f(t_{dead})$$


$V_{GS} = 0/18\text{ V}$, $I_D = 69.1\text{ A}$, $T_{vj} = 175^\circ\text{C}$, $R_{G,ext} = 2.3\ \Omega$
 $V_{DD} = 1000\text{ V}$




Max. transient thermal impedance (MOSFET/diode)

$$Z_{th(j-c),max} = f(t_p)$$

$$D = t_p/T$$



5 パッケージ外形図



| PACKAGE - GROUP NUMBER: | | PG-T0247-4-U07 | | | |
|-------------------------|-------------|----------------|------------|-------------|-------|
| DIMENSIONS | MILLIMETERS | | DIMENSIONS | MILLIMETERS | |
| | MIN. | MAX. | | MIN. | MAX. |
| A | 4.90 | 5.10 | E | 15.60 | 16.00 |
| A1 | 1.90 | 2.10 | E1 | 13.10 | 13.50 |
| A2 | 1.50 | 1.70 | E2 | 0.60 | 1.20 |
| A3 | 2.16 | 2.36 | E3 | 2.48 | 2.68 |
| A4 | 2.31 | 2.51 | E4 | 9.05 | 9.25 |
| b | 0.60 | 0.80 | E5 | 3.97 | 4.17 |
| b1 | 1.10 | 1.30 | E6 | 1.80 | 2.20 |
| b2 | --- | 0.15 | e | 5.08 | |
| b3 | 1.10 | 1.30 | e1 | 2.79 | |
| b4 | 1.90 | 2.10 | e2 | 2.54 | |
| c | 0.50 | 0.70 | K | 3.50 | --- |
| D | 23.10 | 23.50 | L | 17.50 | 17.80 |
| D1 | 16.25 | 16.85 | L1 | 2.61 | 2.91 |
| D2 | 0.97 | 1.37 | N | 4 | |
| D3 | 6.00 | 6.30 | ØP1 | 7.00 | 7.40 |
| D4 | 2.50 | 2.70 | ØP | 3.50 | 3.70 |
| D5 | 2.30 | 2.70 | ØU | 1.40 | 1.80 |

NOTES: DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURRS
N IS THE NUMBER OF LEADS

図 1

6 Testing conditions




Figure A. Definition of switching times




Figure B. Definition of body diode switching characteristics




Figure C. Definition of switching losses




Figure D. Definition of QGD




Figure E. Thermal equivalent circuit




Figure F. Dynamic test circuit

Parasitic inductance L_σ ,
Parasitic capacitor C_σ ,

改訂履歷

改訂履歷

| 文書改訂 | 発行日 | 変更内容 |
|------|------------|-----------------------|
| 0.10 | 2025-05-28 | Preliminary datasheet |
| 1.00 | 2025-06-12 | Final datasheet |

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-06-12

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2025 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference

IFX-ABM844-002

重要事項

本文書に記載された情報は、いかなる場合も、条件または特性の保証とみなされるものではありません（「品質の保証」）。

本文に記された一切の事例、手引き、もしくは一般的価値、および／または本製品の用途に関する一切の情報に関し、インフィニオンテクノロジーズ（以下、「インフィニオン」）はここに、第三者の知的所有権の不侵害の保証を含むがこれに限らず、あらゆる種類の一切の保証および責任を否定いたします。

さらに、本文書に記載された一切の情報は、お客様の用途におけるお客様の製品およびインフィニオン製品の一切の使用に関し、本文書に記載された義務ならびに一切の関連する法的要件、規範、および基準をお客様が遵守することを条件としています。

本文書に含まれるデータは、技術的訓練を受けた従業員のみを対象としています。本製品の対象用途への適合性、およびこれら用途に関連して本文書に記載された製品情報の完全性についての評価は、お客様の技術部門の責任にて実施してください。

本製品は、Automotive Electronics Council の AECQ100 または AECQ101 の文書に準拠していない点にご注意ください。

警告事項

技術的要件に伴い、製品には危険物質が含まれる可能性があります。当該種別の詳細については、インフィニオンの最寄りの営業所までお問い合わせください。

インフィニオンの正式代表者が署名した書面を通じ、インフィニオンによる明示の承認が存在する場合を除き、インフィニオンの製品は、当該製品の障害またはその使用に関する一切の結果が、合理的に人的傷害を招く恐れのある一切の用途に使用することはできないこと予めご了承ください。