

**BFR843EL3**

**BFR843EL3 SiGe:C Ultra Low Noise  
RF Transistor in Dual-Band 2.4 - 2.5  
GHz & 5 - 6 GHz WiFi / WLAN  
Application**

(For 802.11a / b / g / n / ac Wireless LAN Applications)

**Application Note AN307**

Revision: Rev. 1.0  
2013-02-28

**Edition 2013-02-28**

**Published by  
Infineon Technologies AG  
81726 Munich, Germany**

**© 2013 Infineon Technologies AG  
All Rights Reserved.**

#### **Legal Disclaimer**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

#### **Information**

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

#### **Warnings**

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

**Application Note AN307**

**Revision History: 2013-02-28**

**Previous Revision: No previous revision**

Page	Subjects (major changes since last revision)

**Trademarks of Infineon Technologies AG**

AURIX™, C166™, CanPAK™, CIPOS™, CIPURSE™, EconoPACK™, CoolMOS™, CoolSET™, CORECONTROL™, CROSSAVE™, DAVE™, DI-POL™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPIM™, EconoPACK™, EiceDRIVER™, eupec™, FCOS™, HITFET™, HybridPACK™, I<sup>2</sup>RF™, ISOFACE™, IsoPACK™, MIPAQ™, ModSTACK™, my-d™, NovalithIC™, OptiMOS™, ORIGA™, POWERCODE™, PRIMARION™, PrimePACK™, PrimeSTACK™, PRO-SIL™, PROFET™, RASIC™, ReverSave™, SatRIC™, SIEGET™, SINDRION™, SIPMOS™, SmartLEWIS™, SOLID FLASH™, TEMPFET™, thinQ!™, TRENCHSTOP™, TriCore™.

**Other Trademarks**

Advance Design System™ (ADS) of Agilent Technologies, AMBA™, ARM™, MULTI-ICE™, KEIL™, PRIMECELL™, REALVIEW™, THUMB™, µVision™ of ARM Limited, UK. AUTOSAR™ is licensed by AUTOSAR development partnership. Bluetooth™ of Bluetooth SIG Inc. CAT-iq™ of DECT Forum. COLOSSUS™, FirstGPS™ of Trimble Navigation Ltd. EMV™ of EMVCo, LLC (Visa Holdings Inc.). EPCOS™ of Epcos AG. FLEXGO™ of Microsoft Corporation. FlexRay™ is licensed by FlexRay Consortium. HYPERTERMINAL™ of Hilgraeve Incorporated. IEC™ of Commission Electrotechnique Internationale. IrDA™ of Infrared Data Association Corporation. ISO™ of INTERNATIONAL ORGANIZATION FOR STANDARDIZATION. MATLAB™ of MathWorks, Inc. MAXIM™ of Maxim Integrated Products, Inc. MICROTEC™, NUCLEUS™ of Mentor Graphics Corporation. MIPI™ of MIPI Alliance, Inc. MIPS™ of MIPS Technologies, Inc., USA. muRata™ of MURATA MANUFACTURING CO., MICROWAVE OFFICE™ (MWO) of Applied Wave Research Inc., OmniVision™ of OmniVision Technologies, Inc. Openwave™ Openwave Systems Inc. RED HAT™ Red Hat, Inc. RFMD™ RF Micro Devices, Inc. SIRIUS™ of Sirius Satellite Radio Inc. SOLARIS™ of Sun Microsystems, Inc. SPANSION™ of Spansion LLC Ltd. Symbian™ of Symbian Software Limited. TAIYO YUDEN™ of Taiyo Yuden Co. TEAKLITE™ of CEVA, Inc. TEKTRONIX™ of Tektronix Inc. TOKO™ of TOKO KABUSHIKI KAISHA TA. UNIX™ of X/Open Company Limited. VERILOG™, PALLADIUM™ of Cadence Design Systems, Inc. VLYNQ™ of Texas Instruments Incorporated. VXWORKS™, WIND RIVER™ of WIND RIVER SYSTEMS, INC. ZETEX™ of Diodes Zetex Limited.

Last Trademarks Update 2011-11-11

## Table of Content

<b>1</b>	<b>Introduction .....</b>	<b>5</b>
1.1	About Wi-Fi® / Wireless LAN (WLAN) .....	5
<b>2</b>	<b>BFR843EL3 Overview .....</b>	<b>7</b>
2.1	Features .....	7
2.2	Key Applications of BFR843EL3 .....	7
<b>3</b>	<b>BFR843EL3 as Dual-Band LNA for 2.4 – 2.5 GHz and 5.0 – 6.0 GHz Wireless LAN Applications</b>	<b>8</b>
3.1	Description .....	8
3.2	Performance Overview .....	9
3.3	Schematics and Bill-of-Materials .....	10
<b>4</b>	<b>Measurement Graphs .....</b>	<b>11</b>
<b>5</b>	<b>Evaluation Board and Layout Information .....</b>	<b>19</b>
<b>6</b>	<b>Authors .....</b>	<b>21</b>

## List of Figures

Figure 1	Dual-Band Wi-Fi® Wireless LAN at 2.4 - 2.5 GHz and 5 - 6 GHz .....	6
Figure 2	BFR843EL3 in TSLP-3-9 .....	7
Figure 3	Package and pin connections of BFR843EL3 in Topview .....	8
Figure 4	Schematic Diagram of the Application Circuit .....	10
Figure 5	Wideband Insertion Power Gain of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 .....	11
Figure 6	Reverse Isolation of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 .....	11
Figure 7	Noise Figure of 2.4 – 2.5 GHz WLAN LNA with BFR843EL3 .....	12
Figure 8	Noise Figure of 5 – 6 GHz WLAN LNA with BFR843EL3 .....	12
Figure 9	Input Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 .....	13
Figure 10	Input Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 (Smith Chart) .....	13
Figure 11	Output Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 .....	14
Figure 12	Output Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 (Smith Chart) .....	14
Figure 13	Wideband Stability k Factor of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 .....	15
Figure 14	Wideband Stability $\mu$ Factor of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 .....	15
Figure 15	Input 1dB Compression Point of the BFR843EL3 Circuit at 2400 MHz .....	16
Figure 16	Input 1dB Compression Point of the BFR843EL3 Circuit at 5500 MHz .....	16
Figure 17	Output 3 <sup>rd</sup> Order Intercept Point of 2.4 GHz WLAN LNA with BFR843EL3 .....	17
Figure 18	Output 3 <sup>rd</sup> Order Intercept Point of 5 – 6 GHz WLAN LNA with BFR843EL3 (Measured @ 5.5 GHz) .....	17
Figure 19	OFF-Mode (Vcc = 0V, Icc = 0mA) S21 of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 .....	18
Figure 20	Photo Picture of Evaluation Board for LNA with BFR843EL3 .....	19
Figure 21	Zoom-In of Photo Picture .....	19
Figure 22	Layout Proposal for RF Grounding of the 2.4 – 6 GHz WLAN LNA with BFR843EL3 .....	20
Figure 23	PCB Layer Information .....	20

## List of Tables

Table 1	Summary of Measurement Results .....	9
Table 2	Bill-of-Materials .....	10

## 1 Introduction


### 1.1 About Wi-Fi® /Wireless LAN (WLAN)

The Wi-Fi® function is one of the most important connectivity functions in notebooks, smart phones and tablet PCs. Wi-Fi is a registered trademark made of the Wi-Fi Alliance created to certify devices for Wireless LAN (WLAN) applications based on the IEEE 802.11 standard. The WLAN standard has evolved over the years from its legacy systems known as 802.11-1997, through 802.11a, b, g, and n, to the newest 802.11ac. Today the trend is rapidly changing where Wi-Fi is not only used for high data rate access to internet but also for content consumption such as streaming music and High Definition (HD) video on TVs, smart phones, tablets, game consoles etc.

With the requirements on high speed, high quality wireless data transfer wireless data quality becoming more stringent than ever, the new Wireless LAN standards are being developed by using higher order modulation schemes, wider channels and multiple data streams.

Wi-Fi according to IEEE802.11b/g/n at 2.4 GHz widely implemented over years suffers from the interference from other devices such as cordless phones, microwave ovens, Bluetooth devices etc. in the 2.4 GHz spectrum. 802.11a/n operating at 5 GHz has less interference and can transmit data at greater speeds (54 Mbps) but at the cost of reduced range. 802.11n provides enhanced performance and range over prior 802.11 technologies by operating in both the 2.4 GHz and 5 GHz. It introduces the advanced technique, Multiple Input-Multiple Output (MIMO) and operates with a channel bandwidth of 40 MHz. With this, data rates up to 600Mbps (for 4 streams) can be achieved in the 5 GHz band. To cater to these high throughput requirements, major performance criteria have to be fulfilled: sensitivity, strong signal capability and interference immunity.

The **Figure 1** shows one example of general block diagram of a dual band WLAN system.



**Figure 1** Dual-Band Wi-Fi® Wireless LAN at 2.4 - 2.5 GHz and 5 - 6 GHz

A Wi-Fi router has to receive relatively weak signals from Wi-Fi enabled devices such as mobile phones. Therefore, it should have high sensitivity to detect a weak signal in the presence of strong interfering signals. We can improve the sensitivity of the receiver by using a low noise amplifier (LNA) as a first block of the receiver front end to improve the Signal-to-Noise Ratio (SNR) of the overall system. As an example, an increase in the sensitivity by 5 dB corresponds to nearly double link distance.


WLAN systems are subject to co-channel interference and also interference from strong co-existing cellular signals. High linearity characteristics such as 3<sup>rd</sup>-order intercept point (IP3) and 1dB compression point (P1dB) are required to improve an application's ability to distinguish between desired signals and spurious signals received close together. This avoids saturation, degradation of the gain and increased noise figure.

This application note is focusing on the LNA block, but Infineon does also support with [RF-switches](#), [TVS-diodes](#) for ESD protection and [RF Schottky diodes](#) for power detection for WLAN.

## 2 BFR843EL3 Overview

### 2.1 Features

- Low noise broadband NPN RF transistor based on Infineon's reliable, high volume SiGe:C bipolar technology
- High maximum RF input power and ESD robustness
- Unique combination of high RF performance, robustness and ease of use
- Low noise figure:  $NF_{min} = 0.95$  dB at 2.4 GHz and 1.1 dB at 5.5 GHz, 1.8 V, 8 mA
- High gain  $|S_{21}|^2 = 21.5$  dB at 2.4 GHz and 16.5 dB at 5.5 GHz, 1.8 V, 15 mA
- $OIP3 = 22$  dBm at 2.4 GHz and 20 dBm at 5.5 GHz, 1.8 V, 15 mA
- Ideal for low voltage applications e.g.  $V_{CC} = 1.2$  V and 1.8 V (2.85 V, 3.3 V, 3.6 V requires corresponding collector resistor)
- Low power consumption, ideal for mobile applications
- Thin small flat Pb-free (RoHS compliant) and halogen-free package
- Qualification report according to AEC-Q101 available



**Figure 2 BFR843EL3 in TSLP-3-9**



### 2.2 Key Applications of BFR843EL3

As Low Noise Amplifier (LNA) in:

- Wireless Communications: 2.4 GHz Wireless LAN IEEE802.11b/g/n, 5 - 6 GHz Wireless LAN IEEE802.11a/n/ac, WiMAX
- Satellite navigation systems (e.g. GPS, GLONASS, COMPASS...) and satellite C-band LNB (1st and 2nd stage LNA)
- Broadband amplifiers: Dualband WLAN, multiband mobile phone, UWB up to 10 GHz
- ISM bands up to 10 GHz

### 3 BFR843EL3 as Dual-Band LNA for 2.4 – 2.5 GHz and 5.0 – 6.0 GHz Wireless LAN Applications


#### 3.1 Description

BFR843EL3 is a discrete SiGe:C hetero-junction bipolar transistor (HBT) specifically designed for high performance dual band 2- 6 GHz band low noise amplifier (LNA) solutions for Wi-Fi connectivity applications. This has been developed using Infineon’s latest B9HFM technology. The key features of this technology are very high transition frequency ( $f_T = 80$  GHz) and low parasitics, which enable to achieve higher gain and lower noise figure compared to the previous generation RF transistor BFR740L3RH. BFR843EL3 features an integrated on-chip R-C feedback network. The negative feedback reduces the effects of performance variations of the amplifier. The design is therefore less sensitive to variations in PCB layout resulting in an amplifier with broader bandwidth, easier impedance matching and improved stability margin. However the price paid for using negative feedback is slight degradation of noise figure and decrease in gain.

The BFR843EL3 is housed in low-height 0.31mm TSLP-3-9 package specially fitting into modules. It is also available in other packages, e.g. BFP843 in SOT343 and BFP843F in TSFP-4-1 package.

The BFR843EL3 has an integrated 1.5 kV HBM ESD protection which makes the device robust against electrostatic discharge and extreme RF input power. The device offers its high performance at low current and voltage and is especially well-suited for portable battery powered applications in which energy efficiency is a key requirement.

**Figure 2** shows the pin assignment of package of BFR843EL3 in the top view:



**Figure 3** Package and pin connections of BFR843EL3 in Topview



### 3.2 Performance Overview

**Device:** BFR843EL3

**Application:** Dual-Band LNA for 2.4 - 6.0 GHz WLAN Applications

**PCB Marking:** BFR843EL3 **M130129**

(designed for 0201 SMD)

**Table 1 Summary of Measurement Results**

Parameter	Symbol	Value					Unit	Note/Test Condition
DC Voltage	$V_{CC}$	3.0					V	
DC Current	$I_{CC}$	12.2					mA	
Frequency Range	Freq	2400	2500	5100	5500	5900	MHz	
Gain (On Mode)	$G_{ON}$	18.5	18.2	13.7	13.3	13	dB	
Gain (Off Mode)	$G_{OFF}$	-20.3	-20.5	-26.0	-29.2	-36.2	dB	$V_{CC} = 0V, I_{CC} = 0mA$
Noise Figure	NF	1.0	1.0	1.25	1.35	1.3	dB	SMA and PCB losses (0.07 dB @ 2.4 GHz, 0.12 dB @ 5 GHz) are subtracted
Input Return Loss	$RL_{in}$	12.4	12.6	17.5	20.8	24.9	dB	
Output Return Loss	$RL_{out}$	20.0	18.6	12.9	14.3	16.4	dB	
Reverse Isolation	IR <sub>rev</sub>	25.8	25.8	22.6	21.8	20.9	dB	
Input P1dB (On Mode)	IP1dB <sub>ON</sub>	-12	-12.1	-7.8	-7.5	-6.2	dBm	
Output P1dB (On Mode)	OP1dB <sub>ON</sub>	5.5	5.5	4.9	4.9	4.8	dBm	
Input IP3	IIP3	-1.1	-1.9	1.2	2.8	3.3	dBm	
Output IP3	OIP3	17.4	16.2	14.9	16.1	16.2	dBm	Power @ Input: -25 dBm
Stability	k	> 1					--	Stability measured from 10MHz to 10GHz

### 3.3 Schematics and Bill-of-Materials





Figure 4 Schematic Diagram of the Application Circuit


Table 2 Bill-of-Materials

Symbol	Value	Unit	Size	Manufacturer	Comment
C1	6.8	pF	0201	Various	Input DC block & input matching
C2	2.2	pF	0201	Various	Output DC block
C3	33	pF	0201	Various	RF decoupling /DC blocking cap
L1	4.3	nH	0201	LQP03T	RF decoupling / Output matching
R1	100	Ω	0201	Various	DC biasing
R2	18	kΩ	0201	Various	DC biasing
R3	0	Ω	0201	Various	Jumper
Q1			TSLP-3-9	Infineon Technologies	BFR843EL3 SiGe:C Heterojunction Bipolar RF Transistor


## 4 Measurement Graphs




**Figure 5 Wideband Insertion Power Gain of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3**




**Figure 6 Reverse Isolation of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3**




**Figure 7** Noise Figure of 2.4 – 2.5 GHz WLAN LNA with BFR843EL3




**Figure 8** Noise Figure of 5 – 6 GHz WLAN LNA with BFR843EL3




**Figure 9** Input Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3




**Figure 10** Input Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 (Smith Chart)




**Figure 11 Output Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3**




**Figure 12 Output Matching of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3 (Smith Chart)**




**Figure 13 Wideband Stability k Factor of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3**



**Figure 14 Wideband Stability  $\mu$  Factor of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3**




**Figure 15** Input 1dB Compression Point of the BFR843EL3 Circuit at 2400 MHz




**Figure 16** Input 1dB Compression Point of the BFR843EL3 Circuit at 5500 MHz






**Figure 17** Output 3<sup>rd</sup> Order Intercept Point of 2.4 GHz WLAN LNA with BFR843EL3



**Figure 18** Output 3<sup>rd</sup> Order Intercept Point of 5 – 6 GHz WLAN LNA with BFR843EL3 (Measured @ 5.5 GHz)



**Figure 19 OFF-Mode ( $V_{cc} = 0V$ ,  $I_{cc} = 0mA$ ) S21 of the Dual-Band (2.4 – 2.5 GHz & 5 – 6 GHz) WLAN LNA with BFR843EL3**

## 5 Evaluation Board and Layout Information




Figure 20 Photo Picture of Evaluation Board for LNA with BFR843EL3






Figure 21 Zoom-In of Photo Picture



**Figure 22** Layout Proposal for RF Grounding of the 2.4 – 6 GHz WLAN LNA with BFR843EL3



**Figure 23** PCB Layer Information

## **6 Authors**

Xi Chen, Internship Student of Application Engineering of Business Unit "RF and Protection Devices"

Ahmed Shamsuddin, Application Engineer of Business Unit "RF and Protection Devices"

[www.infineon.com](http://www.infineon.com)