

Features

- Density
 - 1 Gbit (128 Mbytes)
- Serial peripheral interface (SPI)
 - SPI clock polarity and phase modes 0 and 3
 - Double data rate (DDR) option
 - Extended addressing: 32-bit address
- READ commands
 - Dual-Quad SPI Quad Read: 104 MHz clock rate (104 MB/s)
 - Dual-Quad SPI Quad DDR Read: 80 MHz clock rate (160 MB/s)
 - Normal, Fast, Quad, Quad DDR
 - AutoBoot power up or reset and execute a Normal or Quad read command automatically at a preselected address
 - Common flash interface (CFI) data for configuration information.
- Programming (3 Mbytes/s)
 - 1024-byte page programming buffer
 - Quad-input page programming (QPP) for slow clock systems
 - Automatic error checking and correction (ECC) internal hardware ECC with single bit error correction
- Erase (1 Mbyte/s)
 - Uniform 512-kbyte sectors
 - Extended addressing: 24- or 32-bit address options
- Cycling endurance
 - 100,000 program-erase cycles, minimum
- · Data retention
 - 20 year data retention, minimum
- Security features
 - Separate one time program (OTP) array of 2048 bytes
 - Block protection:
 - Status register bits to control protection against program or erase of a contiguous range of sectors
 - Hardware and software control options
 - Advanced sector protection (ASP)
 - Individual sector protection controlled by boot code or password
- 65 nm MIRRORBIT[™] technology with Eclipse architecture
- Core supply voltage: 2.7 V to 3.6 V
- Temperature range:
 - Industrial (-40°C to +85°C)
 - Industrial Plus (-40°C to +105°C)
 - Automotive, AEC-Q100 grade 3 (-40°C to +85°C)
 - Automotive, AEC-Q100 grade 2 (-40°C to +105°C)



Features

- Packages (all Pb-free)
 - BGA-24 6 × 8 mm
 - 5 × 5 ball (ZSA024) footprint
- · Software features
 - Program suspend and resume
 - Erase suspend and resume
 - Status register provides status of embedded erase or programming operation
 - CFI-compliant allows the host system to identify the flash device and determine its capabilities
 - JEDEC JESD216 serial flash discoverable parameter (SFDP) support
 - User-configurable Configuration Register
- · Hardware features
 - Hardware reset input (RESET#) resets device to standby state



Performance summary

Performance summary

Maximum read rates SDR dual-quad SPI ($V_{CC} = 2.7 \text{ V to } 3.6 \text{ V}$)

| Command | Clock rate (MHz) MBps | | |
|-----------|-----------------------|------|--|
| Read | 50 | 12.5 | |
| Fast read | 133 | 33 | |
| Quad read | 104 | 104 | |

Maximum read rates DDR dual-quad SPI ($V_{CC} = 3 V \text{ to } 3.6 V$)

| Command | Clock rate (MHz) | MBps |
|---------------|------------------|------|
| DDR Quad read | 80 | 160 |

Typical program and erase rates dual-quad SPI

| Operation | |
|--|--|
| Page programming (1024-byte page buffer) | |
| 512-kbyte logical sector erase | |

Typical current consumption, dual-quad SPI

| Operation | Current (mA) | | |
|--------------------------|--------------|--|--|
| Serial read 50 MHz | 32 (max) | | |
| Serial fast read 133 MHz | 66 (max) | | |
| Quad read 104 MHz | 122 (max) | | |
| Program | 200 (max) | | |
| Erase | 200 (max) | | |
| Standby | 0.14 (typ) | | |



Table of contents

Table of contents

| Features | |
|---|----|
| Performance summary | 3 |
| Table of contents | 4 |
| 1 Overview | |
| 1.1 General description | |
| 2 SPI with multiple input / output (SPI-MIO) dual-quad | 9 |
| 3 Signal descriptions | 10 |
| 3.1 Input/output summary | 10 |
| 3.2 Multiple Input / Output (Dual-Quad SPI) | 11 |
| 3.3 RESET# | 11 |
| 3.4 Serial Clock (SCK1, SCK2) | 11 |
| 3.5 Chip Select (CS1#, CS2#) | 11 |
| 3.6 Input Output IO0–IO7 | 11 |
| 3.7 Core Voltage Supply (V _{CC}) | 11 |
| 3.8 Versatile I/O Power Supply (V _{IO}) | 12 |
| 3.9 Supply and Signal Ground (V _{SS}) | |
| 3.10 Not Connected (NC) | |
| 3.11 Reserved for Future Use (RFU) | 12 |
| 3.12 Do Not Use (DNU) | 12 |
| 3.13 Block diagram | |
| 4 Signal protocols | |
| 4.1 SPI clock modes | |
| 4.1.1 Single data rate (SDR) | 14 |
| 4.1.2 Double data rate (DDR) | |
| 4.2 Command protocol | |
| 4.2.1 Command sequence examples | |
| 4.3 Interface states | |
| 4.3.1 Power-off | 21 |
| 4.3.2 Low power hardware data protection | 21 |
| 4.3.3 Power-on (cold) reset | |
| 4.3.4 Hardware (warm) reset | 21 |
| 4.3.5 Interface Standby | |
| 4.3.6 Instruction cycle | |
| 4.3.7 Single input cycle — Host to Memory transfer | |
| 4.3.8 Single latency (dummy) cycle | |
| 4.3.9 Dual-Quad single output cycle — Memory to Host transfer | |
| 4.3.10 QPP or QOR address input cycle | |
| 4.3.11 Quad input cycle — Host to Memory transfer | |
| 4.3.12 Quad latency (dummy) cycle | |
| 4.3.13 Quad output cycle — Memory to Host transfer | 23 |
| 4.3.14 DDR quad input cycle — Host to Memory transfer | |
| 4.3.15 DDR latency cycle | |
| 4.3.16 DDR quad output cycle — Memory to Host transfer | |
| 4.4 Configuration Register effects on the interface | |
| 4.5 Data protection | |
| 4.5.1 Power-up | |
| 4.5.2 Low power | |
| 4.5.3 Clock pulse count | |
| 5 Electrical specifications | |
| 5.1 Absolute maximum ratings | |
| 5.2 Thermal resistance | |
| | |

2023-11-24



Table of contents

| 5.3 Operating ranges | 26 |
|---|----|
| 5.3.1 Temperature ranges | 26 |
| 5.3.2 Input signal overshoot | 26 |
| 5.4 Power-up and power-down | 27 |
| 5.5 DC characteristics | |
| 5.5.1 Active power and standby power modes | 29 |
| 6 Timing specifications | |
| 6.1 Key to switching waveforms | 30 |
| 6.2 AC test conditions | 31 |
| 6.2.1 Capacitance characteristics | 31 |
| 6.3 Reset | |
| 6.3.1 Power-on (cold) reset | 32 |
| 6.3.2 Hardware (warm) reset | |
| 6.4 SDR AC characteristics | |
| 6.4.1 Clock timing | |
| 6.4.2 Input / output timing | 35 |
| 6.5 DDR AC characteristics | 36 |
| 6.5.1 DDR input timing | 37 |
| 6.5.2 DDR output timing | 37 |
| 7 Physical interface | 39 |
| 7.1 Dual-Quad 24-ball BGA package (ZSA024) | 39 |
| 7.1.1 Connection diagram | 39 |
| 7.1.2 Physical diagram | 40 |
| 7.1.3 Special handling instructions for FBGA packages | 40 |
| 8 Address space maps | 41 |
| 8.1 Overview | 41 |
| 8.1.1 Extended address | 41 |
| 8.1.2 Multiple address spaces | 41 |
| 8.2 Flash memory array | 41 |
| 8.3 ID-CFI address space | |
| 8.4 JEDEC JESD216 serial flash discoverable parameters (SFDP) space | 42 |
| 8.5 OTP address space | 42 |
| 8.6 Registers | 44 |
| 8.6.1 Status Register 1 (SR1) | |
| 8.6.2 Configuration Register 1 (CR1) | 47 |
| 8.6.3 Status Register 2 (SR2) | 50 |
| 8.6.4 AutoBoot Register | 50 |
| 8.6.5 Bank Address Register | 51 |
| 8.6.6 ECC Status Register (ECCSR) | 52 |
| 8.6.7 ASP Register (ASPR) | 53 |
| 8.6.8 Password Register (PASS) | 54 |
| 8.6.9 PPB Lock Register (PPBL) | 54 |
| 8.6.10 PPB Access Register (PPBAR) | 54 |
| 8.6.11 DYB Access Register (DYBAR) | 55 |
| 8.6.12 SPI DDR Data Learning Registers | 55 |
| 9 Data protection | 56 |
| 9.1 Secure silicon region (OTP) | 56 |
| 9.1.1 Reading OTP memory space | 56 |
| 9.1.2 Programming OTP memory space | |
| 9.1.3 Infineon programmed random number | |
| 9.1.4 Lock bytes | |
| 9.2 Write Enable command | 56 |
| 9.3 Block protection | 57 |
| | |



Table of contents

| 9.3.1 Freeze bit | |
|--|----|
| 9.4 Advanced sector protection | 58 |
| 9.4.1 ASP register | |
| 9.4.2 Persistent protection bits | 59 |
| 9.4.3 Dynamic protection bits | 59 |
| 9.4.4 PPB Lock Bit (PPBL[0]) | 60 |
| 9.4.5 Sector protection states summary | 60 |
| 9.4.6 Persistent Protection mode | |
| 9.4.7 Password Protection mode | 61 |
| 10 Commands | |
| 10.1 Command set summary | |
| 10.1.1 Extended addressing | |
| 10.1.2 Read Device identification | |
| 10.1.3 Register read or write | |
| 10.1.4 Read flash array | |
| 10.1.5 Program flash array | |
| 10.1.6 Erase flash array | |
| 10.1.7 OTP, block protection, and advanced sector protection | |
| 10.1.8 Reset | |
| 10.1.9 Reserved | |
| 10.2 Identification commands | |
| 10.2.1 Read Identification — REMS (Read_ID or REMS 90h) | |
| 10.2.2 Read Identification (RDID 9Fh) | |
| 10.2.3 Read Electronic Signature (RES) (ABh) | |
| 10.2.4 Read serial flash discoverable parameters (RSFDP 5Ah) | |
| 10.3 Register Access commands | |
| 10.3.1 Read Status Register 1 (RDSR1 05h) | |
| 10.3.2 Read Status Register 2 (RDSR2 07h) | |
| 10.3.3 Read Configuration Register (RDCR 35h) | |
| 10.3.4 Bank Register Read (BRRD 16h) | 73 |
| 10.3.5 Bank Register Write (BRWR 17h) | |
| 10.3.6 Bank Register Access (BRAC B9h) | |
| 10.3.7 Write Registers (WRR 01h) | |
| 10.3.8 Write Enable (WREN 06h) | |
| 10.3.9 Write Disable (WRDI 04h) | |
| 10.3.10 Clear Status Register (CLSR 30h) | |
| 10.3.11 ECC Status Register Read (ECCRD 18h) | |
| 10.3.12 AutoBoot Pagistar Bood (ABBD 14h) | |
| 10.3.13 AutoBoot Register Read (ABRD 14h) | |
| 10.3.15 Program NVDLR (PNVDLR 43h) | |
| 10.3.16 Write VDLR (WVDLR 4Ah) | |
| 10.3.17 Data Learning Pattern Read (DLPRD 41h) | |
| 10.3.17 Data Learning Fattern Read (DEFRD 4111) | |
| 10.4.1 Read (Read 03h or 4READ 13h) | |
| 10.4.2 Fast Read (FAST_READ 0Bh or 4FAST_READ 0Ch) | |
| 10.4.3 Quad Output Read (QOR 6Bh or 4QOR 6Ch) | |
| 10.4.4 Quad I/O Read (QOR EBh or 4QIOR ECh) | |
| 10.4.5 DDR Quad I/O Read (EDh, EEh) | ۱۵ |
| 10.5 Program Flash Array commands | |
| 10.5.1 Program granularity | |
| 10.5.2 Page Program (PP 02h or 4PP 12h) | |
| 10.5.2 Page Program (PP 0211 01 4PP 1211) | |
| 10.0.0 Quad rage rrogiani (Qrr 021101 0011, 01 4Qrr 0411) | |

1 Gb (128 MB) Dual-Quad FL-S Flash SPI Multi-I/O, $3.0\,\mathrm{V}$



Table of contents

| 10.5.4 Program Suspend (PGSP 85h) and Resume (PGRS 8Ah) | 95 |
|--|-----|
| 10.6 Erase Flash Array commands | |
| 10.6.1 Sector Erase (SE D8h or 4SE DCh) | 96 |
| 10.6.2 Bulk Erase (BE 60h or C7h) | |
| 10.6.3 Erase Suspend and Resume commands (ERSP 75h or ERRS 7Ah) | 98 |
| 10.7 One Time Program Array commands | 100 |
| 10.7.1 OTP Program (OTPP 42h) | 100 |
| 10.7.2 OTP Read (OTPR 4Bh) | |
| 10.8 Advanced Sector Protection commands | 102 |
| 10.8.1 ASP Read (ASPRD 2Bh) | 102 |
| 10.8.2 ASP Program (ASPP 2Fh) | 102 |
| 10.8.3 DYB Read (DYBRD E0h) | 103 |
| 10.8.4 DYB Write (DYBWR E1h) | 103 |
| 10.8.5 PPB Read (PPBRD E2h) | 104 |
| 10.8.6 PPB Program (PPBP E3h) | 104 |
| 10.8.7 PPB Erase (PPBE E4h) | 105 |
| 10.8.8 PPB Lock Bit Read (PLBRD A7h) | 105 |
| 10.8.9 PPB Lock Bit Write (PLBWR A6h) | 106 |
| 10.8.10 Password Read (PASSRD E7h) | 106 |
| 10.8.11 Password Program (PASSP E8h) | 107 |
| 10.8.12 Password Unlock (PASSU E9h) | 108 |
| 10.9 Reset commands | |
| 10.9.1 Software Reset command (RESET F0h) | 109 |
| 10.9.2 Mode Bit Reset (MBR FFh) | 109 |
| 10.10 Embedded algorithm performance tables | 110 |
| 11 Data integrity | 111 |
| 11.1 Erase endurance | 111 |
| 11.2 Data retention | 111 |
| 12 Software interface reference | 112 |
| 12.1 Serial flash discoverable parameters (SFDP) address map | 112 |
| 12.1.1 Field definitions | |
| 12.2 Device ID and Common Flash Interface (ID-CFI) address map | |
| 12.2.1 Field definitions | |
| 12.3 Device ID and Common Flash Interface (ID-CFI) ASO map — automotive only | 137 |
| 12.4 Initial delivery state | |
| 13 Ordering information | |
| 13.1 Valid combinations — standard | |
| 13.2 Valid combinations — automotive grade / AEC-Q100 | 140 |
| Revision history | 141 |

infineon

Overview

1 Overview

1.1 General description

The S79FL01GS device is a flash non-volatile memory product using:

- MIRRORBIT™ technology that stores two data bits in each memory array transistor
- Eclipse architecture that dramatically improves program and erase performance
- 65-nm process lithography

The S79FL01GS device connects two Quad I/O SPI devices with a single CS# resulting in an eight bit I/O data path. This Byte I/O interface is called Dual-Quad I/O.

This device connects to a host system via a serial peripheral interface (SPI). Traditional SPI single bit serial input and output (IO1 and IO5) is supported as well as four-bit (Quad I/O or QIO) serial commands. This multiple width interface is called SPI multi-I/O or MIO. In addition, the S79FL01GS device adds support for double data rate (DDR) read commands for QIO that transfers address and read data on both edges of the clock.

The Eclipse architecture features a page programming buffer that allows up to 512 words (1024 bytes) to be programmed in one operation, resulting in significantly faster effective programming (up to 3 MB/s) and erase (up to 1 MB/s) than prior generation SPI program or erase algorithms.

Executing code directly from flash memory is often called eXecute-in-Place (XIP). By using the S79FL01GS device at the higher clock rates supported, with QIO or DDR-QIO commands, the instruction read transfer rate can match or exceed traditional parallel interface, asynchronous, NOR flash memories while reducing signal count dramatically.

The S79FL01GS product offers high density coupled with the fastest read and write performance required by a variety of embedded applications. It is ideal for code shadowing, XIP, and data storage.



SPI with multiple input / output (SPI-MIO) dual-quad

2 SPI with multiple input / output (SPI-MIO) dual-quad

Many memory devices connect to their host system with separate parallel control, address, and data signals that require a large number of signal connections and larger package size. The large number of connections increase power consumption due to so many signals switching and the larger package increases cost.

The S79FL01GS device reduces the number of signals for connection to the host system by serially transferring all control, address, and data information over 10 signals. This reduces the cost of the memory package, reduces signal switching power, and either reduces the host connection count or frees host connectors for use in providing other features.

The S79FL01GS Dual-Quad SPI device uses the industry standard single bit serial peripheral interface (SPI) using two Quad SPI devices in each package (Quad SPI-1 and Quad SPI-2). This interface is called Dual-Quad and enables support of Byte wide (8 bit) serial transfers. There is one package option available for S79FL01GS:

24-ball BGA package with separate balls for CS1#, SCK1 (Quad SPI-1) and CS2#, SCK1 (Quad SPI-2).

For documentation simplicity, all AC timings and waveforms and DC specification are defined using single CS# (Chip Select) and SCK (Serial Clock) signals. For S79FL01GS, the CS# signal for Quad SPI-1 and Quad SPI-2 are externally tied together, and the SCK signal for Quad SPI-1 and Quad SPI-2 are externally tied together.



Signal descriptions

3 Signal descriptions

3.1 Input/output summary

Table 1 Dual-quad input/output descriptions

| Signal name | Type | Description |
|--------------------|----------|---|
| RESET# | Input | Hardware Reset . LOW = device resets and returns to standby state, ready to receive a command. The signal has an internal pull-up resistor and may be left unconnected in the host system if not used. |
| SCK1 | Input | Serial Clock for Quad SPI-1 |
| SCK2 | Input | Serial Clock for Quad SPI-2 |
| CS1# | Input | Chip Select for Quad SPI-1 |
| CS2# | Input | Chip Select for Quad SPI-2 |
| 100 | I/O | I/O o for Quad SPI-1 |
| IO1 | I/O | I/O 1 for Quad SPI-1 |
| 102 | I/O | I/O 2 for Quad SPI-1 |
| 103 | I/O | I/O 3 for Quad SPI-1 |
| 104 | I/O | I/O o for Quad SPI-2 |
| 105 | I/O | I/O 1 for Quad SPI-2 |
| 106 | I/O | I/O 2 for Quad SPI-2 |
| 107 | I/O | I/O 3 for Quad SPI-2 |
| V _{CC} | Supply | Core Power Supply |
| V _{SS} | Supply | Ground |
| NC | Unused | Not Connected . No device internal signal is connected to the package connector nor is there any future plan to use the connector for a signal. The connection may safely be used for routing space for a signal on a printed circuit board (PCB). However, any signal connected to a NC pin must not have voltage levels higher than the V _{CC} absolute maximum shown on Features page (core supply voltage). |
| RFU | Reserved | Reserved for Future Use . No device internal signal is currently connected to the package connector but there is potential future use for the connector for a signal. It is recommended to not use RFU connectors for PCB routing channels so that the PCB may take advantage of future enhanced features in compatible footprint devices. |
| DNU | Reserved | Do Not Use . A device internal signal may be connected to the package connector. The connection may be used by Infineon for test or other purposes and is not intended for connection to any host system signal. Any DNU signal related function will be inactive when the signal is at $V_{\rm IL}$. The signal has an internal pull-down resistor and may be left unconnected in the host system or may be tied to VSS. Do not use these connections for PCB signal routing channels. Do not connect any host system signal to this connection. |

Note

1. For the BGA package, there are two CS# and two SCK balls.

infineon

Signal descriptions

3.2 Multiple Input / Output (Dual-Quad SPI)

Quad input / output (I/O) commands send instructions to the memory only on the IOO (Quad SPI-1) and IO4 (Quad SPI-2) signals. Address is sent from the host to the memory as four bit (nibble) on IOO, IO1, IO2, IO3 (Quad SPI-1) and repeated on IO4, IO5, IO6, IO7 (Quad SPI-2). Data is sent and returned to the host as bytes on IOO-IO7.

3.3 RESET#

The RESET# input provides a hardware method of resetting the device to standby state, ready for receiving a command. When RESET# is driven to logic LOW (V_{II}) for at least a period of t_{RP} , the device:

- terminates any operation in progress,
- tristates all outputs,
- resets the volatile bits in the Configuration Register,
- resets the volatile bits in the Status Registers,
- resets the Bank Address Register to zero,
- · loads the Program Buffer with all ones,
- reloads all internal configuration information necessary to bring the device to standby mode,
- and resets the internal control unit to standby state.

RESET# causes the same initialization process as is performed when power comes up and requires t_{PLI} time.

RESET# may be asserted LOW at any time. To ensure data integrity any operation that was interrupted by a hardware reset should be reinitiated once the device is ready to accept a command sequence.

When RESET# is first asserted LOW, the device draws I_{CC1} (50 MHz value) during t_{PU} . If RESET# continues to be held at V_{SS} the device draws CMOS standby current (I_{SB}).

RESET# has an internal pull-up resistor and may be left unconnected in the host system if not used.

The RESET# input is not available on all packages options. When not available the RESET# input of the device is tied to the inactive state, inside the package.

3.4 Serial Clock (SCK1, SCK2)

This input signal provides the synchronization reference for the SPI interface. Instructions, addresses, or data input are latched on the rising edge of the SCK signal. Data output changes after the falling edge of SCK, in SDR commands, and after every edge in DDR commands.

3.5 Chip Select (CS1#, CS2#)

The chip select signal indicates when a command for the device is in process and the other signals are relevant for the memory device. When the CS# signal is at the logic HIGH state, the device is not selected and all input signals are ignored and all output signals are high impedance. Unless an internal program, erase or write registers (WRR) embedded operation is in progress, the device will be in the Standby Power mode. Driving the CS# input to logic LOW state enables the device, placing it in the Active Power mode. After power-up, a falling edge on CS# is required prior to the start of any command.

3.6 Input Output IO0-IO7

These signals are input and outputs for receiving instructions, addresses, and data to be programmed (values latched on rising edge of serial SCK clock signal) as well as shifting out data (on the falling edge of SCK, in SDR commands, and on every edge of SCK, in DDR commands).

3.7 Core Voltage Supply (V_{CC})

V_{CC} is the voltage source for all device internal logic. It is the single voltage used for all device internal functions including read, program, and erase. The voltage may vary from 2.7 V to 3.6 V.

infineon

Signal descriptions

3.8 Versatile I/O Power Supply (V_{IO})

 V_{IO} functionality is not supported on the standard configuration of the S79FL01GS device. However, this V_{IO} signal (ball E4) is bonded out on the package and must be tied to V_{CC} on the PCB.

3.9 Supply and Signal Ground (V_{SS})

V_{SS} is the common voltage drain and ground reference for the device core, input signal receivers, and output drivers.

3.10 Not Connected (NC)

No device internal signal is connected to the package connector nor is there any future plan to use the connector for a signal. The connection may safely be used for routing space for a signal on a printed circuit board (PCB). However, any signal connected to an NC must not have voltage levels higher than $V_{\rm IO}$.

3.11 Reserved for Future Use (RFU)

No device internal signal is currently connected to the package connector but is there potential future use of the connector. It is recommended to not use RFU connectors for PCB routing channels so that the PCB may take advantage of future enhanced features in compatible footprint devices.

3.12 Do Not Use (DNU)

A device internal signal may be connected to the package connector. The connection may be used by Infineon for test or other purposes and is not intended for connection to any host system signal. Any DNU signal related function will be inactive when the signal is at V_{IL} . The signal has an internal pull-down resistor and may be left unconnected in the host system or may be tied to V_{SS} . Do not use these connections for PCB signal routing channels. Do not connect any host system signal to these connections.



Signal descriptions

3.13 Block diagram




Figure 1 SPI host and S79FL01GS dual-quad SPI device with dual CS# and SCK balls in the 24-ball BGA package (5x5 ball configuration)

Notes

- 2. The SPI host outputs one Chip Select (CS#) signal, that is routed to CS1# and CS2# balls on the S79FL01GS device
- 3. The SPI host outputs one Clock (SCK) signal, that is routed to SCK1 and SCK2 balls on the S79FL01GS device.



Signal protocols

4 Signal protocols

4.1 SPI clock modes

4.1.1 Single data rate (SDR)

The S79FL01GS device can be driven by an embedded microcontroller (bus master) in either of the two following clocking modes.

- Mode 0 with Clock Polarity (CPOL) = 0 and, Clock Phase (CPHA) = 0
- Mode 3 with CPOL = 1 and, CPHA = 1

For these two modes, input data into the device is always latched in on the rising edge of the SCK signal and the output data is always available from the falling edge of the SCK clock signal.

The difference between the two modes is the clock polarity when the bus master is in standby mode and not transferring any data.

- SCK will stay at logic LOW state with CPOL = 0, CPHA = 0
- SCK will stay at logic HIGH state with CPOL = 1, CPHA = 1




Figure 2 Dual-quad SPI SDR modes supported

Timing diagrams throughout the remainder of the document are generally shown as both Mode 0 and 3 by showing SCK as both HIGH and LOW at the fall of CS#. In some cases a timing diagram may show only Mode 0 with SCK LOW at the fall of CS#. In this case, Mode 3 timing simply means clock is HIGH at the fall of CS# so no SCK rising edge set up or hold time to the falling edge of CS# is needed for Mode 3.

SCK cycles are measured (counted) from one falling edge of SCK to the next falling edge of SCK. In Mode 0, the beginning of the first SCK cycle in a command is measured from the falling edge of CS# to the first falling edge of SCK because SCK is already LOW at the beginning of a command.



Signal protocols

4.1.2 Double data rate (DDR)

Mode 0 and Mode 3 are also supported for DDR commands. In DDR commands, the instruction bits are always latched on the rising edge of clock, the same as in SDR commands. However, the address and input data that follow the instruction are latched on both the rising and falling edges of SCK. The first address bit is latched on the first rising edge of SCK following the falling edge at the end of the last instruction bit. The first bit of output data is driven on the falling edge at the end of the last access latency (dummy) cycle.

SCK cycles are measured (counted) in the same way as in SDR commands, from one falling edge of SCK to the next falling edge of SCK. In Mode 0, the beginning of the first SCK cycle in a command is measured from the falling edge of CS# to the first falling edge of SCK because SCK is already LOW at the beginning of a command.




Figure 3 Dual-quad SPI DDR modes supported

infineon

Signal protocols

4.2 Command protocol

All communication between the host system and S79FL01GS memory device is in the form of units called commands.

All commands begin with an instruction that selects the type of information transfer or device operation to be performed. Commands may also have an address, instruction modifier, latency period, data transfer to the memory, or data transfer from the memory. All instruction, address, and data information is transferred serially between the host system and memory device.

Quad input / output (I/O) commands provide an address sent from the host as four bit (nibble) groups on IO0, IO1, IO2, IO3 and repeated on IO4, IO5, IO6, IO7, then followed by dummy cycles. Data is returned to the host as byte on IO0–IO7. This is referenced as 2-8-8 for Quad I/O command protocols.

Commands are structured as follows:

- Each command begins with CS# going LOW and ends with CS# returning HIGH. The memory device is selected by the host driving the Chip Select (CS#) signal LOW throughout a command.
- The serial clock (SCK) marks the transfer of each bit or group of bits between the host and memory.
- Each command begins with an 8-bit (byte) instruction. The instruction is always presented only as a single bit serial sequence on the Serial Input (SI) signal with one bit transferred to the memory device on each SCK rising edge. The instruction selects the type of information transfer or device operation to be performed.
- The instruction may be stand alone or may be followed by address bits to select a location within one of several address spaces in the device. The instruction determines the address space used. The address may be either a 24-bit or a 32-bit byte boundary, address. The address transfers occur on SCK rising edge, in SDR commands, or on every SCK edge, in DDR commands.
- Quad I/O read instructions send an instruction modifier called Continuous Read mode bits, following the address, to indicate whether the next command will be of the same type with an implied, rather than an explicit, instruction. These mode bits initiate or end the continuous read mode. In continuous read mode, the next command thus does not provide an instruction byte, only a new address and mode bits. This reduces the time needed to send each command when the same command type is repeated in a sequence of commands. The mode bit transfers occur on SCK rising edge, in SDR commands, or on every SCK edge, in DDR commands. The width of all transfers following the instruction are determined by the instruction sent. Following transfers may continue to be single bit serial on only the SI or Serial Output (SO) signals, they may be done in 4-bit groups per (quad) transfer on the IOO–IO3 signals. Within the quad groups the least significant bit is on IOO. More significant bits are placed in significance order on each higher numbered IO signal. Single bits or parallel bit groups are transferred in most to least significant bit order.
- Some instructions send an instruction modifier called mode bits, following the address, to indicate that the next command will be of the same type with an implied, rather than an explicit, instruction. The next command thus does not provide an instruction byte, only a new address and mode bits. This reduces the time needed to send each command when the same command type is repeated in a sequence of commands. The mode bit transfers occur on SCK rising edge, in SDR commands, or on every SCK edge, in DDR commands.
- The address or mode bits may be followed by write data to be stored in the memory device or by a read latency period before read data is returned to the host.
- Write data bit transfers occur on SCK rising edge, in SDR commands, or on every SCK edge, in DDR commands.
- SCK continues to toggle during any read access latency period. The latency may be zero to several SCK cycles (also referred to as dummy cycles). At the end of the read latency cycles, the first read data bits are driven from the outputs on SCK falling edge at the end of the last read latency cycle. The first read data bits are considered transferred to the host on the following SCK rising edge. Each following transfer occurs on the next SCK rising edge, in SDR commands, or on every SCK edge, in DDR commands.
- If the command returns read data to the host, the device continues sending data transfers until the host takes
 the CS# signal HIGH. The CS# signal can be driven HIGH after any transfer in the read data sequence. This will
 terminate the command.



Signal protocols

- At the end of a command that does not return data, the host drives the CS# input HIGH. The CS# signal must go HIGH after the eighth bit, of a standalone instruction or, of the last write data byte that is transferred. That is, the CS# signal must be driven HIGH when the number of clock cycles after CS# signal was driven LOW is an exact multiple of eight cycles. If the CS# signal does not go HIGH exactly at the eight SCK cycle boundary of the instruction or write data, the command is rejected and not executed.
- All instruction, address, and mode bits are shifted into the device with the Most Significant bits (MSB) first. The data bits are shifted in and out of the device MSB first. All data is transferred in byte units with the lowest address byte sent first. Following bytes of data are sent in lowest to highest byte address order i.e. the byte address increments.
- All attempts to read the flash memory array during a program, erase, or a write cycle (embedded operations)
 are ignored. The embedded operation will continue to execute without any affect. A very limited set of
 commands are accepted during an embedded operation. These are discussed in the individual command
 descriptions.
- Depending on the command, the time for execution varies. A command to read status information from an executing command is available to determine when the command completes execution and whether the command was successful.

4.2.1 Command sequence examples




Figure 4 Dual-Quad Standalone Instruction command




Figure 5 Dual-Quad Single bit Wide Input command

Note

4. Instruction needs to be the same for both IO0 (Quad SPI-1) and IO4 (Quad SPI-2).



Signal protocols




Figure 6 Dual-Quad Single bit Wide I/O command without latency




Figure 7 Dual-Quad Single bit Wide I/O command with latency




Figure 8 Dual-Quad, Quad Output Read command

Notes

5. Instruction needs to be the same for both IO0 (Quad SPI-1) and IO4 (Quad SPI-2).

6. A = MSB of address = 23 for 3-byte address, or 31 for 4-byte address.



Signal protocols




Figure 9 Dual-Quad, Quad I/O command




Figure 10 Dual-Quad DDR Quad I/O Read command

Additional sequence diagrams, specific to each command, are provided in "Commands" on page 62.

Notes

8. The gray bits are optional, the host does not have to drive bits during that cycle.

^{7.} Instruction, Address and Mode bits needs to be the same for both IO0–IO3 (Quad SPI-1) and IO4–IO7 (Quad SPI-2).

infineon

Signal protocols

4.3 Interface states

This section describes the input and output signal levels as related to the SPI interface behavior.

Table 2 Dual-Quad interface states summary

| Interface state | VDD | SCK | CS# | RESET# | 100-107 |
|--|------------------------------|-----|-----|--------|---------|
| Power-Off | < V _{CC} (low) | Х | Х | Х | Х |
| Low Power | _ | - | - | - | _ |
| Hardware Data Protection | < V _{CC} (cut-off) | Х | Х | Х | Х |
| Power-On (Cold) Reset | ≥V _{CC} (min) | Х | НН | Х | Х |
| Hardware (Warm) Reset Non-Quad Mode | ≥ V _{CC} (min) | Х | Х | HL | Х |
| Hardware (Warm) Reset Quad Mode | \geq V _{CC} (min) | Х | НН | HL | Х |
| Interface Standby | ≥ V _{CC} (min) | Х | НН | НН | Х |
| Instruction Cycle (Legacy SPI) | ≥ V _{CC} (min) | HT | HL | НН | Х |
| Single Input Cycle Host to Memory Transfer | ≥ V _{CC} (min) | HT | HL | НН | X |
| Single Latency (Dummy) Cycle | ≥V _{CC} (min) | HT | HL | НН | Х |
| Single Output Cycle Memory to Host Transfer | ≥ V _{CC} (min) | HT | HL | НН | Х |
| Quad Input Cycle Host to Memory Transfer | ≥ V _{CC} (min) | HT | HL | НН | Х |
| Quad Latency (Dummy) Cycle | ≥V _{CC} (min) | HT | HL | НН | Х |
| Quad Output Cycle Memory to Host Transfer | ≥ V _{CC} (min) | HT | HL | НН | Х |
| DDR Quad Input Cycle Host to Memory Transfer | ≥ V _{CC} (min) | HT | HL | НН | Х |
| DDR Latency (Dummy) Cycle | ≥V _{CC} (min) | HT | HL | НН | Х |
| DDR Quad Output Cycle Memory to Host Transfer | ≥ V _{CC} (min) | HT | HL | НН | Х |

Legend:

Z = No driver - floating signal

HL = Host driving V_{IL}

HH = Host driving V_{IH}

HV = Either HL or HH

X = HL or HH or Z

HT = Toggling between HL and HH

 $ML = Memory driving V_{IL}$

 $MH = Memory driving V_{IH}$

MV = Either ML or MH

infineon

Signal protocols

4.3.1 Power-off

When the core supply voltage is at or below the V_{CC} (low) voltage, the device is considered to be powered off. The device does not react to external signals, and is prevented from performing any program or erase operation.

4.3.2 Low power hardware data protection

When V_{CC} is less than V_{CC} (cut-off), the memory device will ignore commands to ensure that program and erase operations can not start when the core supply voltage is out of the operating range.

4.3.3 Power-on (cold) reset

When the core voltage supply remains at or below the V_{CC} (low) voltage for \geq t_{PD} time, then rises to \geq V_{CC} (Minimum) the device will begin its power-on reset (POR) process. POR continues until the end of t_{PU} . During t_{PU} , the device does not react to external input signals nor drive any outputs. Following the end of t_{PU} , the device transitions to the Interface Standby state and can accept commands. For additional information on POR see "Power-on (cold) reset" on page 32.

4.3.4 Hardware (warm) reset

Some of the device package options provide a RESET# input. When RESET# is driven LOW for t_{RP} time the device starts the hardware reset process. The process continues for t_{RPH} time. Following the end of both t_{RPH} and the reset hold time following the rise of RESET# (t_{RH}) the device transitions to the Interface Standby state and can accept commands. For additional information on hardware reset see **"POR followed by hardware reset"** on page 32.

4.3.5 Interface Standby

When CS# is HIGH, the SPI interface is in Standby state. Inputs other than RESET# are ignored. The interface waits for the beginning of a new command. The next interface state is Instruction Cycle when CS# goes LOW to begin a new command.

While in Interface Standby state the memory device draws standby current (I_{SB}) if no embedded algorithm is in progress. If an embedded algorithm is in progress, the related current is drawn until the end of the algorithm when the entire device returns to standby current draw.

4.3.6 Instruction cycle

When the host drives the MSB of an instruction and CS# goes LOW, on the next rising edge of SCK the device captures the MSB of the instruction that begins the new command. On each following rising edge of SCK, the device captures the next lower significance bit of the 8-bit instruction. The host keeps RESET# HIGH, CS# LOW.

Each instruction selects the address space that is operated on and the transfer format used during the remainder of the command. The transfer format may be Single, Quad output, Quad I/O, DDR Single I/O, or DDR Quad I/O. The expected next interface state depends on the instruction received.

Some commands are standalone, needing no address or data transfer to or from the memory. The host returns CS# HIGH after the rising edge of SCK for the eighth bit of the instruction in such commands. The next interface state in this case is Interface Standby.

4.3.7 Single input cycle — Host to Memory transfer

Several commands transfer information after the instruction on the single serial input (SI) signal from host to the memory device. The Quad Output commands send address to the memory using only SI but return read data using the I/O signals. The host keeps RESET# HIGH, CS# LOW, HOLD# HIGH, and drives SI as needed for the command. The memory does not drive the Serial Output (IO1 and IO5) signals.

The expected next interface state depends on the instruction. Some instructions continue sending address or data to the memory using additional single input cycles. Others may transition to single latency, or directly to Single, or Quad Output.

infineon

Signal protocols

4.3.8 Single latency (dummy) cycle

Read commands may have zero to several latency cycles during which read data is read from the main flash memory array before transfer to the host. The number of latency cycles are determined by the latency code in the Configuration Register (CR[7:6]). During the latency cycles, the host keeps RESET# HIGH, CS# LOW, and SCK toggles. The host may drive the IOO and IO4 signals during these cycles or the host may leave IOO and IO4 floating. The memory does not use any data driven on IOO and IO4 or other I/O signals during the latency cycles. In Quad Read commands, the host must stop driving the I/O signals on the falling edge at the end of the last latency cycle. It is recommended that the host stop driving I/O signals during latency cycles so that there is sufficient time for the host drivers to turn off before the memory begins to drive at the end of the latency cycles. This prevents driver conflict between host and memory when the signal direction changes. The memory does not drive the Serial Output (IOO and IO4) or I/O signals during the latency cycles.

The next interface state depends on the command structure i.e. the number of latency cycles, and whether the read is single, or quad width.

4.3.9 Dual-Quad single output cycle — Memory to Host transfer

Several commands transfer information back to the host on the Serial Outputs (IO1 and IO5) signals. The host keeps RESET# HIGH, CS# LOW. The memory ignores the Serial Input (IO0 and IO4) signals. The memory drives IO1 and IO5 with data.

The next interface state continues to be dual output cycle until the host returns CS# to HIGH ending the command.

4.3.10 QPP or QOR address input cycle

The Quad Page Program and Quad Output Read commands send address to the memory only on IO0 and IO4. The other IO signals are ignored because the device must be in Quad mode for these commands thus the Hold and Write Protect features are not active. The host keeps RESET# HIGH, CS# LOW, and drives IO0.

For QPP the next interface state following the delivery of address is the quad input cycle.

For QOR the next interface state following address is a quad latency cycle if there are latency cycles needed or quad output cycle if no latency is required.

4.3.11 Quad input cycle — Host to Memory transfer

The Quad I/O Read command transfers four address or mode bits to the memory in each cycle. The Quad Page Program command transfers four data bits to the memory in each cycle. The host keeps RESET# HIGH, CS# LOW, and drives the IO signals.

For Quad I/O Read, the next interface state following the delivery of address and mode bits is a quad latency cycle if there are latency cycles needed or quad output cycle if no latency is required. For Quad Page Program the host returns CS# HIGH following the delivery of data to be programmed and the interface returns to Standby state.

4.3.12 Quad latency (dummy) cycle

Read commands may have zero to several latency cycles during which read data is read from the main flash memory array before transfer to the host. The number of latency cycles are determined by the latency code in the Configuration Register (CR[7:6]). During the latency cycles, the host keeps RESET# HIGH, CS# LOW. The host may drive the IO signals during these cycles or the host may leave the IO floating. The memory does not use any data driven on IO during the latency cycles. The host must stop driving the IO signals on the falling edge at the end of the last latency cycle. It is recommended that the host stop driving them during all latency cycles so that there is sufficient time for the host drivers to turn off before the memory begins to drive at the end of the latency cycles. This prevents driver conflict between host and memory when the signal direction changes. The memory does not drive the IO signals during the latency cycles.

The next interface state following the last latency cycle is a guad output cycle.

infineon

Signal protocols

4.3.13 Quad output cycle — Memory to Host transfer

The Quad Output Read and Quad I/O Read return data to the host eight bits in each cycle. The host keeps RESET# HIGH, and CS# LOW. The memory drives data on IOO–IO3 signals during the quad output cycles.

The next interface state continues to be quad output cycle until the host returns CS# to HIGH ending the command.

4.3.14 DDR quad input cycle — Host to Memory transfer

The DDR Quad I/O Read command sends address, and mode bits to the memory on all the IO signals. Eight bits are transferred on the rising edge of SCK and four bits on the falling edge in each cycle. The host keeps RESET# HIGH, and CS# LOW.

The next interface state following the delivery of address and mode bits is a DDR latency cycle.

4.3.15 DDR latency cycle

DDR Read commands may have one to several latency cycles during which read data is read from the main flash memory array before transfer to the host. The number of latency cycles are determined by the latency code in the Configuration Register (CR1[7:6]). During the latency cycles, the host keeps RESET# HIGH and CS# LOW. The host may not drive the IO signals during these cycles. So that there is sufficient time for the host drivers to turn off before the memory begins to drive. This prevents driver conflict between host and memory when the signal direction changes. The memory has an option to drive all the IO signals with a data learning pattern (DLP) during the last 4 latency cycles. The DLP option should not be enabled when there are fewer than five latency cycles so that there is at least one cycle of high impedance for turn around of the IO signals before the memory begins driving the DLP. When there are more than 4 cycles of latency the memory does not drive the IO signals until the last four cycles of latency.

The next interface state following the last latency cycle is a DDR quad output cycle, depending on the instruction.

4.3.16 DDR quad output cycle — Memory to Host transfer

The DDR Quad I/O Read command returns bits to the host on all the IO signals. Eight bits are transferred on the rising edge of SCK and four bits on the falling edge in each cycle. The host keeps RESET# HIGH, and CS# LOW.

The next interface state continues to be DDR quad output cycle until the host returns CS# to HIGH ending the command.

infineon

Signal protocols

4.4 Configuration Register effects on the interface

The Configuration Register bits 7 and 6 (CR1[7:6]) select the latency code for all read commands. The latency code selects the number of mode bit and latency cycles for each type of instruction.

The Configuration Register Bit-1 (CR1[1]) selects whether Quad mode is enabled and allow Quad Page Program, Quad Output Read, and Quad I/O Read commands. Quad mode must also be selected to allow Read DDR Quad I/O commands. This Quad bit is set to '1' by default for Dual-Quad SPI.

4.5 Data protection

Some basic protection against unintended changes to stored data are provided and controlled purely by the hardware design. These are described in the "Data protection" on page 56. Other software managed protection methods are discussed in the "Software interface reference" on page 112 of this document.

4.5.1 Power-up

When the core supply voltage is at or below the V_{CC} (low) voltage, the device is considered to be powered off. The device does not react to external signals, and is prevented from performing any program or erase operation. Program and erase operations continue to be prevented during the power-on reset because no command is accepted until the exit from POR to the Interface Standby state.

4.5.2 Low power

When V_{CC} is less than V_{CC} (cut-off), the memory device will ignore commands to ensure that program and erase operations can not start when the core supply voltage is out of the operating range.

4.5.3 Clock pulse count

The device verifies that all program, erase, and Write Registers (WRR) commands consist of a clock pulse count that is a multiple of eight before executing them. A command not having a multiple of 8 clock pulse count is ignored and no error status is set for the command.

infineon

Electrical specifications

5 Electrical specifications

5.1 Absolute maximum ratings

Table 3 Absolute maximum ratings

| Storage temperature plastic packages | -65°C to +150°C |
|--|--------------------------------------|
| Ambient temperature with power applied | -65°C to +125°C |
| V _{CC} | -0.5 V to +4.0 V |
| Input Voltage with respect to ground (V _{SS}) ^[9] | -0.5 V to +(V _{IO} + 0.5 V) |
| Output short circuit current [10] | 100 mA |

5.2 Thermal resistance

Table 4 Thermal resistance

| Parameter | Description | Test condition | ZSA024 | Unit |
|-----------|---|--|--------|------|
| Theta JA | Thermal resistance (Junction to ambient) | Test conditions follow standard test methods and procedures for measuring thermal impedance in accordance with EIA/JESD51. with Still Air (0 m/s). | 38 | °C/W |
| Theta JB | Thermal resistance (Junction to board) | | 18 | °C/W |
| Theta JC | Thermal resistance (Junction to case) | | 13.78 | °C/W |

Notes

^{9.} See "Input signal overshoot" on page 26 for allowed maximums during signal transition.

^{10.}No more than one output may be shorted to ground at a time. Duration of the short circuit should not be greater than one second.

^{11.} Stresses above those listed under **Absolute maximum ratings** may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational sections of this datasheet is not implied. Exposure of the device to absolute maximum rating conditions for extended periods may affect device reliability.



Electrical specifications

5.3 Operating ranges

Operating ranges define those limits between which the functionality of the device is guaranteed.

5.3.1 Temperature ranges

Table 5 Recommended operating ranges

| Parameter | Symphol | Devices | Spec | | Unit |
|---------------------|----------------|-------------------------------------|------|------|-------|
| | Symbol | Devices | Min | Max | Oiiit |
| Ambient temperature | T _A | Industrial (I) | -40 | +85 | °C |
| | | Industrial Plus (V) ^[12] | -40 | +105 | |
| | | Automotive, AEC-Q100 grade 3 (A) | -40 | +85 | °C |
| | | Automotive, AEC-Q100 grade 2 (B) | -40 | +105 | |

5.3.2 Input signal overshoot

During DC conditions, input or I/O signals should remain equal to or between V_{SS} and V_{IO} . During voltage transitions, inputs or I/Os may overshoot V_{SS} to -2.0~V or overshoot to $V_{CC}+2.0~V$, for periods up to 20 ns.




Figure 11 Maximum negative overshoot waveform




Figure 12 Maximum positive overshoot waveform

Note

12. Operating and performance parameters will be determined by device characterization and may vary from standard industrial temperature range devices as currently shown in this specification.

infineon

Electrical specifications

5.4 Power-up and power-down

The device must not be selected at power-up or power-down (that is, CS# must follow the voltage applied on V_{CC}) until V_{CC} reaches the correct value as follows:

 V_{CC} (min) at power-up, and then for a further delay of t_{PU}

V_{SS} at power-down

A simple pull-up resistor (generally of the order of 100 k Ω) on Chip Select (CS#) can usually be used to insure safe and proper power-up and power-down.

The device ignores all instructions until a time delay of t_{PU} has elapsed after the moment that V_{CC} rises above the minimum V_{CC} threshold (see **Figure 13**). However, correct operation of the device is not guaranteed if V_{CC} returns below V_{CC} (min) during t_{PU} . No command should be sent to the device until the end of t_{PU} .

After power-up (t_{PU}) , the device is in Standby mode (not Deep Power Down mode), draws CMOS standby current (I_{SB}) , and the WEL bit is reset.

During power-down or voltage drops below V_{CC} (cut-off), the voltage must drop below V_{CC} (low) for a period of t_{PD} for the part to initialize correctly on power-up (see **Figure 14**). If during a voltage drop the V_{CC} stays above V_{CC} (cut-off) the part will stay initialized and will work correctly when V_{CC} is again above V_{CC} (min). In the event power-on reset did not complete correctly after power up, the assertion of the RESET# signal or receiving a software reset command (RESET) will restart the POR process.

Normal precautions must be taken for supply rail decoupling to stabilize the V_{CC} supply at the device. Each device in a system should have the V_{CC} rail decoupled by a suitable capacitor close to the package supply connection (this capacitor is generally of the order of 0.1 μ F).

Table 6 Power-up / power-down voltage and timing

| Symbol | Parameter | Min | Max | Unit |
|---------------------------|---|------------|-----|------|
| V _{CC} (min) | V _{CC} (minimum operation voltage) | 2.7 | _ | ٧ |
| V _{CC} (cut-off) | V _{CC} (cut 0ff where re-initialization is needed) | 2.4 | _ | V |
| V _{CC} (low) | V _{CC} (low voltage for initialization to occur) V _{CC} (low voltage for initialization to occur at embedded) | 1.0 2.3 | - | V |
| t _{PU} | V _{CC} (min) to Read operation | - | 300 | μs |
| t_{PD} | V _{CC} (low) time | 1.0 | _ | μs |



Electrical specifications




Figure 13 Power-up




Figure 14 Power-down and voltage drop

infineon

Electrical specifications

5.5 DC characteristics

Table 7 DC characteristics

| Symbol | Parameter | Test conditions | Min | Typ ^[13] | Max | Unit |
|---|--|--|------------------------|----------------------------|--|------|
| V _{IL} | Input low voltage | | -0.5 | _ | 0.2 × V _{CC} | ٧ |
| V _{IH} | Input high voltage | | $0.7 \times V_{CC}$ | _ | V _{CC} + 0.4 | ٧ |
| V _{OL} | Output low voltage | $I_{OL} = 1.6 \text{ mA}, V_{CC} = V_{CC} \text{ min}$ | _ | _ | 0.15 × V _{CC} | ٧ |
| V _{OH} | Output high voltage | I _{OH} = -0.1 mA | 0.85 × V _{CC} | _ | - | ٧ |
| I _{LI} | Input leakage current | $V_{CC} = V_{CC} \text{ max},$ $V_{IN} = V_{IH} \text{ or } V_{IL}$ | _ | _ | ±4 | μΑ |
| I _{LO} | Output leakage current | $V_{CC} = V_{CC} \text{ max},$ $V_{IN} = V_{IH} \text{ or } V_{IL}$ | - | _ | ±4 | μΑ |
| I _{CC1} | Active power supply current (READ) | Serial SDR @ 50 MHz Serial SDR @ 133 MHz Quad SDR @ 80 MHz Quad SDR @ 104 MHz Quad DDR @ 80 MHz Outputs unconnected during read data return [14] | - | - | 32 66/70 ^[15] 100 122 200 | mA |
| I _{CC2} | Active power supply current (Page Program) | CS# = V _{CC} | _ | _ | 200 | mA |
| I _{CC3} | Active power supply current (WRR) | CS# = V _{CC} | _ | _ | 200 | mA |
| I _{CC4} | Active power supply current (SE) | CS# = V _{CC} | _ | _ | 200 | mA |
| I _{CC5} | Active power supply current (BE) | CS# = V _{CC} | _ | _ | 200 | mA |
| I _{SB} (Industrial) | Standby current | RESET#, CS# = V _{CC} ; SI, SCK = V _{CC} or V _{SS} , Industrial Temperature | - | 140 | 200 | μΑ |
| I _{SB} (Industrial Plus) | Standby current | RESET#, CS# = V _{CC} ; SI, SCK = V _{CC} or V _{SS} , Industrial Plus Temperature | - | 140 | 600 | μΑ |
| | | | | | | |

5.5.1 Active power and standby power modes

The device is enabled and in the Active Power mode when Chip Select (CS#) is LOW. When CS# is HIGH, the device is disabled, but may still be in an Active Power mode until all program, erase, and write operations have completed. The device then goes into the Standby Power mode, and power consumption drops to I_{SB}.

Notes

13. Typical values are at T_{AI} = 25°C and V_{CC} = 3 V.

14. Outputs switching current is not included.

15.Industrial temperature range / Industrial Plus temperature range.



Timing specifications

6 Timing specifications

6.1 Key to switching waveforms




Figure 15 Waveform element meanings




Figure 16 Input, output, and timing reference levels



Timing specifications

6.2 AC test conditions




Figure 17 Test setup

Table 8 AC measurement conditions

| Symbol | Parameter | Mir | n I | Мах | Unit |
|----------------|---------------------------|----------|--|-----|------|
| C _L | Load capacitance | 30 15 | [19] | | pF |
| | Input rise and fall times | _ | 2 | 2.4 | ns |
| | Input pulse voltage | 0.2 | $0.2 \times V_{CC}$ to $0.8 \times V_{CC}$ | | ٧ |
| | Input timing ref voltage | 0.5 | × V _{CC} | | ٧ |
| | Output timing ref voltage | 0.5 | × V _{CC} | | ٧ |

6.2.1 Capacitance characteristics

Table 9 Capacitance

| Symbol | Parameter | Test conditions | Min | Max | Unit |
|------------------|---|-----------------|-----|-----|------|
| C _{IN} | Input capacitance (applies to SCK, CS#, RESET#) | 1 MHz | _ | 10 | pF |
| C _{OUT} | Output capacitance (applies to All I/O) | 1 MHz | - | 10 | pF |

Notes

16.Output High-Z is defined as the point where data is no longer driven.

17.Input slew rate: 1.5 V/ns.

18.AC characteristics tables assume clock and data signals have the same slew rate (slope).

19.DDR Operation.

20. For more information on capacitance, please consult the IBIS models.



Timing specifications

6.3 Reset

6.3.1 Power-on (cold) reset

The device executes a POR process until a time delay of t_{PU} has elapsed after the moment that V_{CC} rises above the minimum V_{CC} threshold. See **Figure 13**, **Table 6**, and **Table 10**. The device must not be selected (CS# to go HIGH with V_{IO}) during power-up (t_{PU}), i.e. no commands may be sent to the device until the end of t_{PU} . RESET# is ignored during POR. If RESET# is LOW during POR and remains LOW through and beyond the end of t_{PU} , CS# must remain HIGH until t_{RH} after RESET# returns HIGH. RESET# must return HIGH for greater than t_{RS} before returning LOW to initiate a hardware reset.




Figure 18 Reset LOW at the end of POR




Figure 19 Reset HIGH at the end of POR




Figure 20 POR followed by hardware reset

infineon

Timing specifications

6.3.2 Hardware (warm) reset

When the RESET# input transitions from V_{IL} to V_{IL} the device will reset register states in the same manner as POR but, does not go through the full reset process that is performed during POR. The hardware reset process requires a period of t_{RPH} to complete. If the POR process did not complete correctly for any reason during power-up (t_{PU}), RESET# going LOW will initiate the full POR process instead of the hardware reset process and will require t_{PU} to complete the POR process.

The RESET# input provides a hardware method of resetting the flash memory device to Standby state.

- RESET# must be HIGH for t_{RS} following t_{PU} or t_{RPH}, before going LOW again to initiate a hardware reset.
- When RESET# is driven LOW for at least a minimum period of time (t_{RP}), the device terminates any operation in progress, tri-states all outputs, and ignores all read/write commands for the duration of t_{RPH}. The device resets the interface to standby state.
- If CS# is LOW at the time RESET# is asserted, CS# must return HIGH during t_{RPH} before it can be asserted LOW
 again after t_{RH}.



Figure 21 Hardware reset

Table 10 Hardware reset parameters

| Parameter | Description | Limit | Time | Unit |
|------------------|---|-------|------|------|
| t _{RS} | Reset setup — prior reset end and RESET# HIGH before RESET# LOW | Min | 50 | ns |
| t _{RPH} | Reset pulse hold — RESET# LOW to CS# LOW | Min | 35 | μs |
| t _{RP} | RESET# pulse width | Min | 200 | ns |
| t _{RH} | Reset hold — RESET# HIGH before CS# LOW | Min | 50 | ns |

Notes

22. Sum of t_{RP} and t_{RH} must be equal to or greater than t_{RPH} .

^{21.}RESET# LOW is optional and ignored during power-up (t_{PU}). If RESET# is asserted during the end of t_{PU} , the device will remain in the Reset state and t_{RH} will determine when CS# may go LOW.

infineon

Timing specifications

6.4 SDR AC characteristics

Table 11 AC characteristics (V_{CC} 2.7 V to 3.6 V)

| Symbol | Parameter | Min | Тур | Max | Unit |
|--------------------------------------|--|----------------------|-----|--|------|
| F _{SCK, R} | SCK clock frequency for READ and 4READ instructions | DC | _ | 50 | MHz |
| F _{SCK, C} | SCK clock frequency for single commands as shown in Table 38 [27] | DC | - | 133 | MHz |
| F _{SCK, C} | SCK clock frequency for the following Dual and Quad commands: QOR, 4QOR, QIOR, 4QIOR | DC | - | 104 | MHz |
| F _{SCK, QPP} | SCK clock frequency for the QPP, 4QPP commands | DC | - | 80 | MHz |
| P _{SCK} | SCK clock period | 1/ F _{SCK} | _ | ∞ | |
| t _{WH} , t _{CH} | Clock HIGH time ^[23] | 45% P _{SCK} | _ | - | ns |
| t _{WL} , t _{CL} | Clock LOW time ^[23] | 45% P _{SCK} | _ | - | ns |
| t _{CRT} , t _{CLCH} | Clock rise time (slew rate) | 0.1 | _ | - | V/ns |
| t _{CFT} , t _{CHCL} | Clock fall time (slew rate) | 0.1 | _ | - | V/ns |
| t _{CS} | CS# HIGH time (read instructions) CS# HIGH time (program/erase) | 10 50 | - | - | ns |
| t _{CSS} | CS# active setup time (relative to SCK) | 3 | _ | - | ns |
| t _{CSH} | CS# active hold time (relative to SCK) | 3 | _ | - | ns |
| t _{SU} | Data in setup time | 1.5 | _ | 3000 [24] | ns |
| t _{HD} | Data in hold time | 2 | _ | - | ns |
| t _V | Clock LOW to output valid | - | - | 8.0 ^[25] 7.65 ^[26] 6.5 ^[27] | ns |
| t _{HO} | Output hold time | 2 | _ | - | ns |
| t _{DIS} | Output disable time | 0 | _ | 8 | ns |
| t _{WPS} | WP# setup time | 20 [28] | _ | - | ns |
| t _{WPH} | WP# hold time | 100 [28] | _ | - | ns |
| t _{HLCH} | HOLD# active setup time (relative to SCK) | 3 | _ | - | ns |
| t _{CHHH} | HOLD# active hold time (relative to SCK) | 3 | _ | - | ns |
| t _{HHCH} | HOLD# non active setup time (relative to SCK) | 3 | - | - | ns |
| t _{CHHL} | HOLD# non active hold time (relative to SCK) | 3 | _ | - | ns |
| t _{HZ} | HOLD# enable to output invalid | - | - | 8 | ns |
| t _{LZ} | HOLD# disable to output valid | _ | _ | 8 | ns |

Notes

23.±10% duty cycle is supported for frequencies ≤ 50 MHz.

24. Maximum value only applies during Program/Erase Suspend/Resume commands.

25.Full V_{CC} range (2.7 V–3.6 V) and CL = 30 pF.

26.Regulated V_{CC} range (3.0 V–3.6 V) and CL = 30 pF.

27.Regulated V_{CC} range (3.0 V–3.6 V) and CL = 15 pF.

28.Only applicable as a constraint for WRR instruction when SRWD is set to '1'.



Timing specifications

6.4.1 Clock timing




Figure 22 Clock timing

6.4.2 Input / output timing




Figure 23 SPI SDR dual-quad timing

infineon

Timing specifications

6.5 DDR AC characteristics

Table 12 AC characteristics DDR operation

| Symbol | Parameter | Min | Тур | Max | Unit |
|-----------------------------------|--|----------------------|-----|---------------------|------|
| F _{SCK, R} | SCK clock frequency for DDR READ instruction | DC | - | 80 | MHz |
| P _{SCK, R} | SCK clock period for DDR READ instruction | 10.75 | - | ∞ | ns |
| t _{WH} , t _{CH} | Clock HIGH time | 45% P _{SCK} | - | - | ns |
| t_{WL}, t_{CL} | Clock LOW time | 45% P _{SCK} | - | - | ns |
| t _{CS} | CS# HIGH time (Read Instructions) | 10 | - | - | ns |
| t _{CSS} | CS# active setup time (relative to SCK) | 3 | - | - | ns |
| t _{CSH} | CS# active hold time (relative to SCK) | 3 | - | - | ns |
| t _{SU} | IO in setup time | 1.5 | - | 3000 [29] | ns |
| t _{HD} | IO in hold time | 1.5 | - | - | ns |
| t _V | Clock LOW to output valid | 1.5 | - | 6.5 ^[30] | ns |
| t _{HO} | Output hold time | 1.5 | _ | | ns |
| t _{DIS} | Output disable time | - | - | 8 | ns |
| t _{LZ} | Clock to output LOW impedance | 0 | - | 8 | ns |
| t _{O_SKEW} | First output to last output data valid time | - | - | 600 | ps |

Notes

29. Maximum value only applies during Program/Erase Suspend/Resume commands. 30. Regulated V $_{\rm CC}$ range (3.0 V–3.6 V) and CL = 15 pF.



Timing specifications

6.5.1 DDR input timing




Figure 24 SPI DDR input timing

6.5.2 DDR output timing




Figure 25 SPI DDR output timing

Timing specifications




Figure 26 **SPI DDR data valid window**

Notes

- 31. t_{CLH} is the shorter duration of t_{CL} or t_{CH} .
- 32.t_{O_SKEW} is the maximum difference (delta) between the minimum and maximum t_V (output valid) across all IO signals.
- 33.t_{OTT} is the maximum output transition time from one valid data value to the next valid data value on each IO.
- 34.t_{OTT} is dependent on system level considerations including:
 - a. Memory device output impedance (drive strength).
 - b. System level parasitics on the IOs (primarily bus capacitance).

 - c. Host memory controller input V_{IH} and V_{IL} levels at which 0 to 1 and 1 to 0 transitions are recognized. d. As an example, assuming that the above considerations result a memory output slew rate of 2 V/ns and a 3 V transition (from 1 to 0 or 0 to 1) is required by the host, the t_{OTT} would be:

 $t_{OTT} = 3 \text{ V/(2 V/ns)} = 1.5 \text{ ns}$

- e. t_{OTT} is not a specification tested by Infineon, it is system dependent and must be derived by the system designer based on the above considerations.
- 35. The minimum data valid window (t_{DV}) can be calculated as follows:
 - a. As an example, assuming:
 - i. 80 MHz clock frequency = 12.5 ns clock period
 - ii. DDR operations are specified to have a duty cycle of 45% or higher
 - iii. $t_{CLH} = 0.45 \times PSCK = 0.45 \times 12.5 \text{ ns} = 5.625 \text{ ns}$

 - iv. $t_{O_SKEW} = 600 \text{ ps}$ v. $t_{OTT} = 1.5 \text{ ns}$ b. $t_{DV} = t_{CLH} t_{O_SKEW} t_{OTT}$ c. $t_{DV} = 5.625 \text{ ns} 600 \text{ ps} 1.5 \text{ ns} = 3.525 \text{ ns}$



Physical interface

7 Physical interface

| Table 13 | Model specific connections |
|----------|----------------------------|
|----------|----------------------------|

| | Versatile I/O or V_{CC} – V_{IO} functionality is not supported on S79FL01GS. This signal must be tied to V_{CC} on the PCB. |
|--------|--|
| RESET# | RESET# signal is bonded out and active on the S79FL01GS. The signal has an internal pull-up resistor and may be left unconnected in the host system if not used. |

7.1 Dual-Quad 24-ball BGA package (ZSA024)

7.1.1 Connection diagram




Figure 27 Dual-Quad 24-ball BGA, 5 x 5 ball footprint (ZSA024), top view

Notes

36.Refer to **Table 1** for signal descriptions.

37. The RESET# input has an internal pull-up and may be left unconnected in the system.

Physical interface

7.1.2 Physical diagram




Figure 28 24-ball FBGA (8.0 × 6.0 × 1.2 mm) package outline (PG-TFBGA-24), 002-15078

7.1.3 Special handling instructions for FBGA packages

Flash memory devices in BGA packages may be damaged if exposed to ultrasonic cleaning methods. The package and/or data integrity may be compromised if the package body is exposed to temperatures above 150°C for prolonged periods of time.

Address space maps

8 Address space maps

8.1 Overview

8.1.1 Extended address

The S79FL01GS device supports 32-bit addresses to enable higher density devices than allowed by previous generation (legacy) SPI devices that supported only 24-bit addresses. A 24-bit byte resolution address can access only 16 Mbytes (128 Mbits) of maximum density. A 32-bit byte resolution address allows direct addressing of up to a 4 Gbytes (32 Gbits) of address space.

Legacy commands continue to support 24-bit addresses for backward software compatibility. Extended 32-bit addresses are enabled in three ways:

- Bank Address register a software (command) loadable internal register that supplies the high order bits of address when legacy 24-bit addresses are in use.
- Extended Address mode a bank address register bit that changes all legacy commands to expect 32 bits of address supplied from the host system.
- New commands that perform both legacy and new functions, which expect 32-bit address.

The default condition at power-up and after reset, is the Bank address register loaded with zeros and the extended address mode set for 24-bit addresses. This enables legacy software compatible access to the first 128 Mbits of a device.

8.1.2 Multiple address spaces

Many commands operate on the main flash memory array. Some commands operate on address spaces separate from the main flash array. Each separate address space uses the full 32-bit address but may only define a small portion of the available address space.

8.2 Flash memory array

The main flash array is divided into erase units called sectors. The sectors are organized as uniform 512-kbyte sectors.

Table 14 S79FL01GS sector and memory address map, uniform 512-kbyte sectors

| Sector size (kbyte) | Sector count | Sector range | Address range (8-bit) | Notes |
|---------------------|--------------|--------------|-----------------------|-------------------------|
| 512 | 256 | SA00 | 00000000h-0003FFFFh | Sector starting address |
| | | : | : | _ |
| | | SA255 | 03FC0000h-03FFFFFFh | Sector ending address |

Note: This is a condensed table that uses a sector as a reference. There are address ranges that are not explicitly listed. All 512-kB sectors have the pattern XXXX0000h–XXXXFFFFh.

8.3 ID-CFI address space

The RDIDJ command (9Fh) reads information from a separate flash memory address space for device identification (ID) and common flash interface (CFI) information. See "Device ID and Common Flash Interface (ID-CFI) address map" on page 116 for the tables defining the contents of the ID-CFI address space. The ID-CFI address space is programmed by Infineon and read-only for the host system.

Address space maps

8.4 JEDEC JESD216 serial flash discoverable parameters (SFDP) space

The RSFDP command (5Ah) reads information from a separate Flash memory address space for device identification, feature, and configuration information, in accord with the JEDEC JESD216 standard for serial flash discoverable parameters. The ID-CFI address space is incorporated as one of the SFDP parameters.

See "Serial flash discoverable parameters (SFDP) address map" on page 112 for the table defining the contents of the SFDP address space. The SFDP address space is programmed by Infineon and is read-only for the host system

8.5 OTP address space

Each S79FL01GS memory device has a 2048-byte one time program (OTP) address space that is separate from the main flash array. The OTP area is divided into 64, individually lockable, 32-byte aligned and length regions. In the 64-byte region starting at address zero:

- The 16 lowest address bytes are programmed by Infineon with a 128-bit random number. Only Infineon is able to program these bytes.
- The next 4 higher address bytes (OTP lock bytes) are used to provide one bit per OTP region to permanently protect each region from programming. The bytes are erased when shipped from Infineon. After an OTP region is programmed, it can be locked to prevent further programming, by programming the related protection bit in the OTP lock bytes.
- The next higher 12 bytes of the lowest address region are Reserved for Future Use (RFU). The bits in these RFU bytes may be programmed by the host system but it must be understood that a future device may use those bits for protection of a larger OTP space. The bytes are erased when shipped from Infineon.

The remaining regions are erased when shipped from Infineon, and are available for programming of additional permanent data.

Refer to Figure 29 for a pictorial representation of the OTP memory space.

The OTP memory space is intended for increased system security. OTP values, such as the random number programmed by Infineon, can be used to "mate" a flash component with the system CPU/ASIC to prevent device substitution.

The configuration register FREEZE (CR1[0]) bit protects the entire OTP memory space from programming when set to '1'. This allows trusted boot code to control programming of OTP regions then set the FREEZE bit to prevent further OTP memory space programming during the remainder of normal power-on system operation.

During the programming of each OTP region, bits 0–3 are programmed on Quad SPI-1 via IO0–IO3, and bits 4–7 are programmed on Quad SPI-2 via IO4–IO7.




Figure 29 OTP address space — Quad SPI-1 and Quad SPI-2



Address space maps

Table 15 OTP address map for Quad SPI-1 and Quad SPI-2

| Region | Byte address range (Hex) | Contents | Initial delivery state (Hex) |
|-----------|--------------------------|--|-----------------------------------|
| Region 0 | 000 | Least Significant Byte of Infineon programmed random number | Infineon programmed random number |
| | | | |
| | 00F | Most Significant Byte of Infineon programmed random number | |
| | 010 to 013 | Region Locking Bits Byte 10 [bit 0] locks region 0 from programming when = 0 | All bytes = FF ^[38] |
| | | Byte 13 [bit 7] locks region 31 from programming when = 0 | |
| | 014 to 01F | Reserved for Future Use (RFU) | All bytes = FF |
| Region 1 | 020 to 03F | Available for user programming | All bytes = FF |
| Region 2 | 040 to 05F | Available for user programming | All bytes = FF |
| | | Available for user programming | All bytes = FF |
| Region 31 | 7E0 to 7FF | Available for user programming | All bytes = FF |

Note

38.It is recommended that the Lock Bytes for Quad SPI-1 and Quad SPI-2 be programmed with identical data.

Address space maps

8.6 Registers

Registers are small groups of memory cells used to configure how the S79FL01GS memory device operates or to report the status of device operations. The registers are accessed by specific commands. The commands (and hexadecimal instruction codes) used for each register are noted in each register description.

The S79FL01GS Dual-Quad SPI device has a register of each type, one for each individual die. These include the Status Register 1, Status Register 2, Configuration Register, AutoBoot Register, Bank Address Register, ASP Register, Password Register, PPB Lock Register, PPB Access Register, DYB Access Register, and DDR Data Learning Registers. Each register must be accessed by a command given in parallel to IOO-IO3 (Quad SPI-1) and for IO4-IO7 (Quad SPI-2). Reading and writing to each of these registers must also be done in parallel for IO0-IO3 (Quad SPI-1) and for IO4-IO7 (Quad SPI-2).

The individual register bits may be volatile, nonvolatile, or one time programmable (OTP). The type for each bit is noted in each register description. The default state shown for each bit refers to the state after power-on reset, hardware reset, or software reset if the bit is volatile. If the bit is nonvolatile or OTP, the default state is the value of the bit when the device is shipped from Infineon. Nonvolatile bits have the same cycling (erase and program) endurance as the main flash array.

Table 16 **Register descriptions**

| Register | Abbreviation | Туре | Bit location |
|---------------------------------|--------------|-----------------------|--------------|
| Status Register 1 | SR1[7:0] | Volatile | 7:0 |
| Configuration Register 1 | CR1[7:0] | Volatile | 7:0 |
| Status Register 2 | SR2[7:0] | RFU | 7:0 |
| AutoBoot Register | ABRD[31:0] | Nonvolatile | 31:0 |
| Bank Address Register | BRAC[7:0] | Volatile | 7:0 |
| ECC Status Register | ECCSR[7:0] | Volatile | 7:0 |
| ASP Register | ASPR[15:1] | OTP | 15:1 |
| ASP Register | ASPR[0] | RFU | 0 |
| Password Register | PASS[63:0] | Nonvolatile OTP | 63:0 |
| PPB Lock Register | PPBL[7:1] | Volatile | 7:1 |
| PPB Lock Register | PPBL[0] | Volatile Read Only | 0 |
| PPB Access Register | PPBAR[7:0] | Nonvolatile | 7:0 |
| DYB Access Register | DYBAR[7:0] | Volatile | 7:0 |
| SPI DDR Data Learning Registers | NVDLR[7:0] | Nonvolatile | 7:0 |
| SPI DDR Data Learning Registers | VDLR[7:0] | Volatile | 7:0 |

infineon

Address space maps

8.6.1 Status Register 1 (SR1)

Related Commands: Read Status Register (RDSR1 05h), Write Registers (WRR 01h), Write Enable (WREN 06h), Write Disable (WRDI 04h), Clear Status Register (CLSR 30h).

Table 17 Status Register 1 (SR1)

| Bits | Field name | Function | Туре | Default state | Description | |
|------|---------------|----------------------------------|--|-------------------------------------|--|------------------------|
| 7 | SRWD | Status Register Write Disable | Nonvolatile | 0 | 1 = Locks state of SRWD, BP, and Configuration Register bits when WP# is LOW by ignoring WRR command 0 = No protection, even when WP# is LOW | |
| 6 | P_ERR | Programming Error Occurred | Volatile, Read only | 0 | 1 = Error occurred 0 = No Error | |
| 5 | E_ERR | Erase Error Occurred | Volatile, Read only | 0 | 1 = Error occurred 0 = No Error | |
| 4 | BP2 | Block Protection | Volatile | 1 | Protects selected range of sectors (Block) | |
| 3 | BP1 | | if CR1[3] = 1, Nonvolatile if CR1[3] = 0 | | if CR1[3] = 1, | from Program or Erase. |
| 2 | BP0 | | | when shipped from Infineon | | |
| 1 | WEL | Write Enable Latch | Volatile | 0 | 1 = Device accepts Write Registers (WRR), Program or Erase commands 0 = Device ignores Write Registers (WRR), Program or Erase commands This bit is not affected by WRR, only WREN and WRDI commands affect this bit. | |
| 0 | WIP | Write in Progress | Volatile, Read only | 0 | 1 = Device Busy, a Write Registers (WRR), program, erase or other operation is in progress 0 = Ready Device is in Standby mode and can accept commands | |

The Status Register contains both status and control bits:

Status Register Write Disable (SRWD) SR1[7]: Places the device in the Hardware Protected mode when this bit is set to '1' and the WP# input is driven LOW. In this mode, the SRWD, BP2, BP1, and BP0 bits of the Status Register become read-only bits and the Write Registers (WRR) command is no longer accepted for execution. If WP# is HIGH, the SRWD bit and BP bits may be changed by the WRR command. If SRWD is '0', WP# has no effect and the SRWD bit and BP bits may be changed by the WRR command. The SRWD bit has the same nonvolatile endurance as the main flash array.

Program Error (P_ERR) SR1[6]: The Program Error Bit is used as a program operation success or failure indication. When the Program Error bit is set to '1', it indicates that there was an error in the last program operation. This bit will also be set when the user attempts to program within a protected main memory sector or locked OTP region. When the Program Error bit is set to '1', this bit can be reset to '0' with the Clear Status Register (CLSR) command. This is a read-only bit and is not affected by the WRR command.

Erase Error (E_ERR) SR1[5]: The Erase Error Bit is used as an Erase operation success or failure indication. When the Erase Error bit is set to '1', it indicates that there was an error in the last erase operation. This bit will also be set when the user attempts to erase an individual protected main memory sector. The Bulk Erase command will not set E_ERR if a protected sector is found during the command execution. When the Erase Error bit is set to '1', this bit can be reset to '0' with the Clear Status Register (CLSR) command. This is a read-only bit and is not affected by the WRR command.



Address space maps

Block Protection (BP2, BP1, BP0) SR1[4:2]: These bits define the main flash array area to be software-protected against program and erase commands. The BP bits are either volatile or nonvolatile, depending on the state of the BP nonvolatile bit (BPNV) in the configuration register. When one or more of the BP bits is set to '1', the relevant memory area is protected against program and erase. The Bulk Erase (BE) command can be executed only when the BP bits are cleared to 0's. See "**Block protection**" on page 57 for a description of how the BP bit values select the memory array area protected. The BP bits have the same nonvolatile endurance as the main flash array.

Write Enable Latch (WEL) SR1[1]: The WEL bit must be set to '1' to enable program, write, or erase operations as a means to provide protection against inadvertent changes to memory or register values. The Write Enable (WREN) command execution sets the Write Enable Latch to '1' to allow any program, erase, or write commands to execute afterwards. The Write Disable (WRDI) command can be used to set the Write Enable Latch to '0' to prevent all program, erase, and write commands from execution. The WEL bit is cleared to '0' at the end of any successful program, write, or erase operation. Following a failed operation the WEL bit may remain set and should be cleared with a WRDI command following a CLSR command. After a power down/power up sequence, hardware reset, or software reset, the Write Enable Latch is set to '0'. The WRR command does not affect this bit.

Write In Progress (WIP) SR1[0]: Indicates whether the device is performing a program, write, erase operation, or any other operation, during which a new operation command will be ignored. When the bit is set to '1', the device is busy performing an operation. While WIP is '1', only Read Status (RDSR1 or RDSR2), Erase Suspend (ERSP), Program Suspend (PGSP), Clear Status Register (CLSR), and Software Reset (RESET) commands may be accepted. ERSP and PGSP will only be accepted if memory array erase or program operations are in progress. The status register E_ERR and P_ERR bits are updated while WIP = 1. When P_ERR or E_ERR bits are set to '1', the WIP bit will remain set to one indicating the device remains busy and unable to receive new operation commands. A Clear Status Register (CLSR) command must be received to return the device to standby mode. When the WIP bit is cleared to 0 no operation is in progress. This is a read-only bit.

infineon

Address space maps

8.6.2 Configuration Register 1 (CR1)

Related Commands: Read Configuration Register (RDCR 35h), Write Registers (WRR 01h). The Configuration Register bits can be changed using the WRR command with sixteen input cycles.

The Configuration Register controls certain interface and data protection functions.

Table 18 Configuration Register 1 (CR1)

| Bits | Field name | Function | Туре | Default state | Description |
|------|------------|---|-------------|---------------|---|
| 7 | LC1 | Latency Code | Nonvolatile | 0 | Selects number of initial read latency |
| 6 | LC0 | | | 0 | cycles See Table 19 and Table 20 |
| 5 | TBPROT | Configures Start of Block Protection | OTP | 0 | 1 = BP starts at bottom (Low address) 0 = BP starts at top (High address) |
| 4 | DNU | DNU | DNU | 0 | Do Not Use |
| 3 | BPNV | Configures BP2–0 in Status Register | ОТР | 0 | 1 = Volatile 0 = Nonvolatile |
| 2 | RFU | RFU | RFU | 0 | Reserved for Future Use |
| 1 | QUAD | Puts the device into Quad I/O operation | Nonvolatile | 1 | 1 = Quad For the S79FL01GS Dual-Quad SPI device, the default state is set for QUAD and cannot be changed. |
| 0 | FREEZE | Lock current state of BP2–0 bits in Status Register, TBPROT in Configu- ration Register, and OTP regions | Volatile | 0 | 1 = Block Protection and OTP locked 0 = Block Protection and OTP unlocked |

Latency Code (LC) CR1[7:6]: The Latency Code selects the number of mode and dummy cycles between the end of address and the start of read data output for all read commands.

Some read commands send mode bits following the address to indicate that the next command will be of the same type with an implied, rather than an explicit, instruction. The next command thus does not provide an instruction byte, only a new address and mode bits. This reduces the time needed to send each command when the same command type is repeated in a sequence of commands.

Dummy cycles provide additional latency that is needed to complete the initial read access of the flash array before data can be returned to the host system. Some read commands require additional latency cycles as the SCK frequency is increased.

The following latency code tables provide different latency settings that are configured by Infineon.

Where mode or latency (dummy) cycles are shown in the tables as a dash, that read command is not supported at the frequency shown. Read is supported only up to 50 MHz but the same latency value is assigned in each latency code and the command may be used when the device is operated at ≤ 50 MHz with any latency code setting. Similarly, only the Fast Read command is supported up to 133 MHz but the same 10b latency code is used for Fast Read up to 133 MHz and for the other dual and quad read commands up to 104 MHz. It is not necessary to change the latency code from a higher to a lower frequency when operating at lower frequencies where a particular command is supported. The latency code values for a higher frequency can be used for accesses at lower frequencies.

The Enhanced High Performance settings provide latency options the same or faster than additional alternate source SPI memories.



Address space maps

Read DDR Data Learning Pattern (DLP) bits may be placed within the dummy cycles immediately before the start of read data, if there are five or more dummy cycles. See "Read Memory Array commands" on page 83 for more information on the DLP.

Table 19 Latency codes for SDR enhanced high performance

| _ | | Read | | Fast Read | Fast Read | | Read Quad Out | | Quad I/O Read | |
|-------------|----|------------|-------|-----------|------------|------|---------------|------|---------------|--|
| Freq. (MHz) | LC | (03h, 13h) | | (0Bh, 0Ch | (0Bh, 0Ch) | | (6Bh, 6Ch) | | (EBh, ECh) | |
| (, | | Mode | Dummy | Mode | Dummy | Mode | Dummy | Mode | Dummy | |
| ≤ 50 | 11 | 0 | 0 | 0 | 0 | 0 | 0 | 2 | 1 | |
| ≤ 80 | 00 | _ | _ | 0 | 8 | 0 | 8 | 2 | 4 | |
| ≤90 | 01 | _ | _ | 0 | 8 | 0 | 8 | 2 | 4 | |
| ≤ 104 | 10 | _ | _ | 0 | 8 | 0 | 8 | 2 | 5 | |
| ≤ 133 | 10 | _ | _ | 0 | 8 | _ | - | - | _ | |

Table 20 Latency codes for DDR enhanced high performance

| | | DDR Quad I/O Read (EDh, EEh) | | |
|-------------|----|------------------------------|-------|--|
| Freq. (MHz) | LC | | | |
| | | Mode | Dummy | |
| ≤ 50 | 11 | 1 | 3 | |
| ≤ 80 | 00 | 1 | 7 | |

Note

^{39.} When using DDR I/O commands with the data learning pattern (DLP) enabled, a latency code that provides five or more dummy cycles should be selected to allow one cycle of additional time for the host to stop driving before the memory starts driving the four cycle DLP. So it is recommended to use LC 00 for DDR Quad IO Read, if the data learning pattern (DLP) for DDR is used.



Address space maps

Top or Bottom Protection (TBPROT) CR1[5]: This bit defines the operation of the Block Protection bits BP2, BP1, and BP0 in the Status Register. As described in the status register section, the BP2–0 bits allow the user to optionally protect a portion of the array, ranging from 1/64, 1/4, 1/2, etc., up to the entire array. When TBPROT is set to '0', the Block Protection is defined to start from the top (maximum address) of the array. When TBPROT is set to '1', the Block Protection is defined to start from the bottom (zero address) of the array. The TBPROT bit is OTP and set to '0' when shipped from Infineon. If TBPROT is programmed to '1', an attempt to change it back to '0' will fail and set the Program Error bit (P_ERR in SR1[6]).

The desired state of TBPROT must be selected during the initial configuration of the device during system manufacture; before the first program or erase operation on the main flash array. TBPROT must not be programmed after programming or erasing is done in the main flash array.

CR1[4]: Reserved for Future Use

Block Protection Nonvolatile (BPNV) CR1[3]: The BPNV bit defines whether or not the BP2–0 bits in the Status Register are volatile or nonvolatile. The BPNV bit is OTP and cleared to a0 with the BP bits cleared to 000 when shipped from Infineon. When BPNV is set to '0', the BP2–0 bits in the Status Register are nonvolatile. When BPNV is set to '1', the BP2–0 bits in the Status Register are volatile and will be reset to binary 111 after POR, hardware reset, or command reset. If BPNV is programmed to '1', an attempt to change it back to '0' will fail and set the Program Error bit (P_ERR in SR1[6]).

CR1[2]: Reserved for Future Use.

Quad Data Width (QUAD) CR1[1]: When set to '1', this bit switches the data width of the device to 4-bit Quad mode. The commands for Serial Read still function normally. The QUAD bit in the S79FL01GS device is factory set to '1' and should not be changed.

Freeze Protection (FREEZE) CR1[0]: The Freeze Bit, when set to '1', locks the current state of the BP2–0 bits in Status Register, the TBPROT and TBPARM bits in the Configuration Register, and the OTP address space. This prevents writing, programming, or erasing these areas. As long as the FREEZE bit remains cleared to logic 0 the other bits of the Configuration Register, including FREEZE, are writable, and the OTP address space is programmable. Once the FREEZE bit has been written to a logic 1 it can only be cleared to a logic 0 by a power-off to power-on cycle or a hardware reset. Software reset will not affect the state of the FREEZE bit. The FREEZE bit is volatile and the default state of FREEZE after power-on is '0'. The FREEZE bit can be set in parallel with updating other values in CR1 by a single WRR command.

infineon

Address space maps

8.6.3 Status Register 2 (SR2)

Related Commands: Read Status Register 2 (RDSR2 07h).

Table 21 Status Register 2 (SR2)

| Bits | Field name | Function | Туре | Default state | Description |
|------|---------------|-----------------|------------------------|---------------|--|
| 7 | RFU | Reserved | _ | 0 | Reserved for Future Use |
| 6 | RFU | Reserved | _ | 0 | Reserved for Future Use |
| 5 | RFU | Reserved | - | 0 | Reserved for Future Use |
| 4 | RFU | Reserved | - | 0 | Reserved for Future Use |
| 3 | RFU | Reserved | - | 0 | Reserved for Future Use |
| 2 | RFU | Reserved | - | 0 | Reserved for Future Use |
| 1 | ES | Erase Suspend | Volatile, Read only | 0 | 1 = In Erase Suspend mode 0 = Not in Erase Suspend mode |
| 0 | PS | Program Suspend | Volatile, Read only | 0 | 1 = In Program Suspend mode 0 = Not in Program Suspend mode |

Erase Suspend (ES) SR2[1]: The Erase Suspend bit is used to determine when the device is in Erase Suspend mode. This is a status bit that cannot be written. When Erase Suspend bit is set to '1', the device is in erase suspend mode. When Erase Suspend bit is cleared to '0', the device is not in erase suspend mode. Refer to Erase Suspend and Resume Commands (75h) (7Ah) for details about the Erase Suspend/Resume commands.

Program Suspend (PS) SR2[0]: The Program Suspend bit is used to determine when the device is in Program Suspend mode. This is a status bit that cannot be written. When Program Suspend bit is set to '1', the device is in program suspend mode. When the Program Suspend bit is cleared to '0', the device is not in program suspend mode. Refer to "**Program Suspend (PGSP 85h) and Resume (PGRS 8Ah)"** on page 95 for details.

8.6.4 AutoBoot Register

Related Commands: AutoBoot Read (ABRD 14h) and AutoBoot Write (ABWR 15h).

The AutoBoot Register provides a means to automatically read boot code as part of the power on reset, hardware reset, or software reset process.

Table 22 AutoBoot Register

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|---------------------------|-------------|---------------|---|
| 31to9 | ABSA | AutoBoot Start Address | Nonvolatile | 000000h | 512 byte boundary address for the start of boot code access |
| 8 to 1 | ABSD | AutoBoot Start Delay | Nonvolatile | 00h | Number of initial delay cycles between CS# going LOW and the first bit of boot code being transferred |
| 0 | ABE | AutoBoot Enable | Nonvolatile | 0 | 1 = AutoBoot is enabled 0 = AutoBoot is not enabled |

infineon

Address space maps

8.6.5 Bank Address Register

Related Commands: Bank Register Access (BRAC B9h), Write Register (WRR 01h), Bank Register Read (BRRD 16h) and Bank Register Write (BRWR 17h).

The Bank Address register supplies additional high order bits of the main flash array byte boundary address for legacy commands that supply only the low order 24 bits of address. The Bank Address is used as the high bits of address (above A23) for all 3-byte address commands when EXTADD = 0. The Bank Address is not used when EXTADD = 1 and traditional 3-byte address commands are instead required to provide all four bytes of address.

Table 23 Bank Address Register (BAR)

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|----------------------------|----------|---------------|--|
| 7 | EXTADD | Extended Address Enable | Volatile | 0b | 1 = 4-byte (32-bits) addressing required from command. 0 = 3-byte (24-bits) addressing from command + Bank Address |
| 6 to 2 | RFU | Reserved | Volatile | 00000b | Reserved for Future Use |
| 1 | BA25 | Bank Address | Volatile | 0 | A25 for 1 Gb device |
| 0 | RFU | Bank Address | Volatile | 0 | RFU for lower density device |

Extended Address (EXTADD) BAR[7]: EXTADD controls the address field size for legacy SPI commands. By default (power up reset, hardware reset, and software reset), it is cleared to '0' for 3 bytes (24 bits) of address. When set to '1', the legacy commands will require 4 bytes (32 bits) for the address field. This is a volatile bit.

infineon

Address space maps

8.6.6 ECC Status Register (ECCSR)

Related Commands: ECC Read (ECCRD 18h). ECCSR does not have user programmable nonvolatile bits. All defined bits are volatile read only status. The default state of these bits are set by hardware. See "Automatic ECC" on page 92.

The status of ECC in each ECC unit is provided by the 8-bit ECC Status Register (ECCSR). The ECC Register Read command is written followed by an ECC unit address. The contents of the status register then indicates, for the selected ECC unit, whether there is an error in the ECC unit eight bit error correction code, the ECC unit of 16 Bytes of data, or that ECC is disabled for that ECC unit.

Table 24 ECC Status Register (ECCSR)

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|---------------------------|--|---------------|---|
| 7 to 3 | RFU | Reserved | | 0 | Reserved for Future Use |
| 2 | EECC | Error in ECC | Volatile, 0 1 = Single Bit Error found in the ECC eight bit error correction code 0 = No error | | • |
| 1 | EECCD | Error in ECC unit data | Volatile, 0 Read only | | 1 = Single Bit Error corrected in ECC unit data 0 = No error |
| 0 | ECCDI | ECC Disabled | Volatile, Read only | 0 | 1 = ECC is disabled in the selected ECC unit 0 = ECC is enabled in the selected ECC unit |

ECCSR[2] = 1 indicates an error was corrected in the ECC. ECCSR[1] = 1 indicates an error was corrected in the ECC unit data. ECCSR[0] = 1 indicates the ECC is disabled. The default state of '0' for all these bits indicates no failures and ECC is enabled.

ECCSR[7:3] are reserved. These have undefined high or low values that can change from one ECC status read to another. These bits should be treated as "don't care" and ignored by any software reading status.

infineon

Address space maps

8.6.7 ASP Register (ASPR)

Related Commands: ASP Read (ASPRD 2Bh) and ASP Program (ASPP 2Fh).

The ASP register is a 16-bit OTP memory location used to permanently configure the behavior of Advanced Sector Protection (ASP) features.

Table 25 ASP Register (ASPR)

| Bits | Field name | Function | Туре | Default state | Description | |
|-------|---------------|---|------|---------------|--|--|
| 15to9 | RFU | Reserved | ОТР | 1 | Reserved for Future Use | |
| 8 | RFU | Reserved | ОТР | Note 40 | Reserved for Future Use | |
| 7 | RFU | Reserved | ОТР | Note 40 | Reserved for Future Use | |
| 6 | RFU | Reserved | ОТР | 1 | Reserved for Future Use | |
| 5 | RFU | Reserved | ОТР | Note 40 | Reserved for Future Use | |
| 4 | RFU | Reserved | ОТР | Note 40 | Reserved for Future Use | |
| 3 | RFU | Reserved | ОТР | Note 40 | Reserved for Future Use | |
| 2 | PWDMLB | Password Protection Mode Lock Bit | ОТР | 1 | 0 = Password Protection Mode perma- nently enabled 1 = Password Protection Mode not perma- nently enabled | |
| 1 | PSTMLB | Persistent Protection Mode Lock Bit | ОТР | 1 | 0 = Persistent Protection Mode permanently enabled 1 = Persistent Protection Mode not permanently enabled | |
| 0 | RFU | Reserved | OTP | 1 | Reserved for Future Use | |

Reserved for Future Use (RFU) ASPR[15:3, 0].

Password Protection Mode Lock Bit (PWDMLB) ASPR[2]: When programmed to '0', the Password Protection Mode is permanently selected.

Persistent Protection Mode Lock Bit (PSTMLB) ASPR[1]: When programmed to '0', the Persistent Protection Mode is permanently selected. PWDMLB and PSTMLB are mutually exclusive, only one may be programmed to '0'.

Note

40. Default value depends on ordering part number, see "Initial delivery state" on page 138.

infineon

Address space maps

8.6.8 Password Register (PASS)

Related Commands: Password Read (PASSRD E7h) and Password Program (PASSP E8h).

Table 26 Password Register (PASS)

| Bits | Field name | Function | Туре | Default state | Description |
|-------|---------------|--------------------|------|-------------------|---|
| 63to0 | PWD | Hidden Password | ОТР | FFFFFFFF-FFFFFFFh | Nonvolatile OTP storage of 64-bit password. The password is no longer readable after the password protection mode is selected by programming ASP register bit 2 to '0'. |

8.6.9 PPB Lock Register (PPBL)

Related Commands: PPB Lock Read (PLBRD A7h, PLBWR A6h)

Table 27 PPB Lock Register (PPBL)

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|----------------------|----------|--|---|
| 7 to 1 | RFU | Reserved | Volatile | 00h | Reserved for Future Use |
| 0 | PPBLOCK | Protect PPB Array | Volatile | Persistent Protection Mode = 1 Password Protection Mode = 0 | 0 = PPB array protected until next power cycle or hardware reset 1 = PPB array may be programmed or erased. |

8.6.10 PPB Access Register (PPBAR)

Related Commands: PPB Read (PPBRD E2h)

Table 28 PPB Access Register (PPBAR)

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|-----------------------------------|-------------|---------------|--|
| 7 to 0 | PPB | Read or Program per sector PPB | Nonvolatile | FFh | 00h = PPB for the sector addressed by the PPBRD or PPBP command is programmed to '0', protecting that sector from program or erase operations. FFh = PPB for the sector addressed by the PPBRD or PPBP command is erased to '1', not protecting that sector from program or erase operations. |

infineon

Address space maps

8.6.11 DYB Access Register (DYBAR)

Related Commands: DYB Read (DYBRD E0h) and DYB Program (DYBP E1h).

Table 29 DYB Access Register (DYBAR)

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|---------------------------------|----------|---------------|--|
| 7 to 0 | DYB | Read or Write per sector DYB | Volatile | | 00h = DYB for the sector addressed by the DYBRD or DYBP command is cleared to '0', protecting that sector from program or erase operations. FFh = DYB for the sector addressed by the DYBRD or DYBP command is set to '1', not protecting that sector from program or erase operations. |

8.6.12 SPI DDR Data Learning Registers

Related Commands: Program NVDLR (PNVDLR 43h), Write VDLR (WVDLR 4Ah), Data Learning Pattern Read (DLPRD 41h).

The Data Learning Pattern (DLP) resides in an 8-bit Nonvolatile Data Learning Register (NVDLR) as well as an 8-bit Volatile Data Learning Register (VDLR). When shipped from Infineon, the NVDLR value is 00h. Once programmed, the NVDLR cannot be reprogrammed or erased; a copy of the data pattern in the NVDLR will also be written to the VDLR. The VDLR can be written to at any time, but on reset or power cycles the data pattern will revert back to what is in the NVDLR. During the learning phase described in the SPI DDR modes, the DLP will come from the VDLR. Each IO will output the same DLP value for every clock edge. For example, if the DLP is 34h (or binary 00110100) then during the first clock edge all IOs will output '0'; subsequently, the 2nd clock edge all I/O's will output '0', the 3rd will output '1', etc.

When the VDLR value is 00h, no preamble data pattern is presented during the dummy phase in the DDR commands.

Table 30 Nonvolatile Data Learning Register (NVDLR)

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|--------------------------------------|------|---------------|--|
| 7 to 0 | NVDLP | Nonvolatile Data Learning Pattern | ОТР | 00h | OTP value that may be transferred to the host during DDR read command latency (dummy) cycles to provide a training pattern to help the host more accurately center the data capture point in the received data bits. |

Table 31 Volatile Data Learning Register (NVDLR)

| Bits | Field name | Function | Туре | Default state | Description |
|--------|---------------|-----------------------------------|----------|--|--|
| 7 to 0 | VDLP | Volatile Data Learning Pattern | Volatile | Takes the value of NVDLR during POR or Reset | Volatile copy of the NVDLP used to enable and deliver the Data Learning Pattern (DLP) to the outputs. The VDLP may be changed by the host during system operation. |

infineon

Data protection

9 Data protection

9.1 Secure silicon region (OTP)

The device has a 2048-byte one time program (OTP) address space that is separate from the main flash array. The OTP area is divided into 32, individually lockable, 64-byte aligned and length regions.

The OTP memory space is intended for increased system security. OTP values can "mate" a flash component with the system CPU/ASIC to prevent device substitution. See "OTP address space" on page 42, "One Time Program Array commands" on page 100, and "OTP Read (OTPR 4Bh)" on page 101.

9.1.1 Reading OTP memory space

The OTP Read command uses the same protocol as Fast Read. OTP Read operations outside the valid 2-kB OTP address range will yield indeterminate data.

9.1.2 Programming OTP memory space

The protocol of the OTP programming command is the same as Page Program. The OTP Program command can be issued multiple times to any given OTP address, but this address space can never be erased. The valid address range for OTP Program is depicted in **Figure 29**. OTP Program operations outside the valid OTP address range will be ignored and the WEL in SR1 will remain high (set to '1'). OTP Program operations while FREEZE = 1 will fail with P_ERR in SR1 set to '1'.

9.1.3 Infineon programmed random number

Infineon standard practice is to program the low order 16 bytes of the OTP memory space (locations 0x0 to 0xF) with a 128-bit random number using the Linear Congruential Random Number method. The seed value for the algorithm is a random number concatenated with the day and time of tester insertion.

9.1.4 Lock bytes

The LSB of each Lock byte protects the lowest address region related to the byte, the MSB protects the highest address region related to the byte. The next higher address byte similarly protects the next higher 8 regions. The LSB bit of the lowest address Lock Byte protects the higher address 16 bytes of the lowest address region. In other words, the LSB of location 0x10 protects all the Lock Bytes and RFU bytes in the lowest address region from further programming. See "OTP address space" on page 42.

9.2 Write Enable command

The Write Enable (WREN) command must be written prior to any command that modifies nonvolatile data. The WREN command sets the Write Enable Latch (WEL) bit. The WEL bit is cleared to '0' (disables writes) during power-up, hardware reset, or after the device completes the following commands:

- Reset
- Page Program (PP)
- Sector Erase (SE)
- · Bulk Erase (BE)
- Write Disable (WRDI)
- Write Registers (WRR)
- Quad-input Page Programming (QPP)
- OTP Byte Programming (OTPP)

infineon

Data protection

9.3 Block protection

The Block Protect bits (Status Register bits BP2, BP1, BP0) in combination with the Configuration Register TBPROT bit can be used to protect an address range of the main flash array from program and erase operations. The size of the range is determined by the value of the BP bits and the upper or lower starting point of the range is selected by the TBPROT bit of the Configuration Register.

Table 32 Upper array start of protection (TBPROT = 0)

| Status register content | | ontent | | Protected memory (kbytes) | |
|-------------------------|-----|--------|------------------------------------|---------------------------|--|
| BP2 | BP1 | вро | Protected fraction of memory array | S79FL01GS 1024 Mb | |
| 0 | 0 | 0 | None | 0 | |
| 0 | 0 | 1 | Upper 64th | 2048 | |
| 0 | 1 | 0 | Upper 32nd | 4096 | |
| 0 | 1 | 1 | Upper 16th | 8192 | |
| 1 | 0 | 0 | Upper 8th | 16384 | |
| 1 | 0 | 1 | Upper 4th | 32768 | |
| 1 | 1 | 0 | Upper Half | 65536 | |
| 1 | 1 | 1 | All Sectors | 131072 | |

Table 33 Lower array start of protection (TBPROT = 1)

| Status register content | | ontent | | Protected memory (kbytes) |
|-------------------------|-----|--------|------------------------------------|---------------------------|
| BP2 | BP1 | BP0 | Protected fraction of memory array | S79FL01GS 1024 Mb |
| 0 | 0 | 0 | None | 0 |
| 0 | 0 | 1 | Lower 64th | 2048 |
| 0 | 1 | 0 | Lower 32nd | 4096 |
| 0 | 1 | 1 | Lower 16th | 8192 |
| 1 | 0 | 0 | Lower 8th | 16384 |
| 1 | 0 | 1 | Lower 4th | 32768 |
| 1 | 1 | 0 | Lower Half | 65536 |
| 1 | 1 | 1 | All Sectors | 131072 |

When Block Protection is enabled (i.e., any BP2–0 are set to '1'), advanced sector protection (ASP) can still be used to protect sectors not protected by the block protection scheme. In the case that both ASP and block protection are used on the same sector the logical OR of ASP and Block Protection related to the sector is used. Recommendation: ASP and block protection should not be used concurrently. Use one or the other, but not both.

9.3.1 Freeze bit

Bit 0 of the Configuration Register is the FREEZE bit. The FREEZE bit locks the BP2–0 bits in Status Register-1 and the TBPROT bit in the Configuration Register to their value at the time the FREEZE bit is set to '1'. Once the FREEZE bit has been written to a logic 1 it cannot be cleared to a logic 0 until a power-on-reset is executed. As long as the FREEZE bit is cleared to logic 0 the status register BP bits and the TBPROT bit of the Configuration Register are writable. The FREEZE bit also protects the entire OTP memory space from programming when set to '1'. Any attempt to change the BP bits with the WRR command while FREEZE = 1 is ignored and no error status is set.

Data protection

9.4 Advanced sector protection

Advanced sector protection (ASP) is the name used for a set of independent hardware and software methods used to disable or enable programming or erase operations, individually, in any or all sectors. An overview of these methods is shown in **Figure 30**.

Block Protection and ASP protection settings for each sector are logically OR'd to define the protection for each sector, i.e. if either mechanism is protecting a sector the sector cannot be programmed or erased. Refer to "Block protection" on page 57 for full details of the BP2–0 bits.




Figure 30 Advanced sector protection overview

Every main flash array sector has a nonvolatile (PPB) and a volatile (DYB) protection bit associated with it. When either bit is '0', the sector is protected from program and erase operations.

The PPB bits are protected from program and erase when the PPB Lock bit is '0'. There are two methods for managing the state of the PPB Lock bit, Persistent Protection and Password Protection.

The Persistent Protection method sets the PPB Lock bit to '1' during POR, or Hardware Reset so that the PPB bits are unprotected by a device reset. There is a command to clear the PPB Lock bit to '0' to protect the PPB. There is no command in the Persistent Protection method to set the PPB Lock bit to '1', therefore the PPB Lock bit will remain at '0' until the next power-off or hardware reset. The Persistent Protection method allows boot code the option of changing sector protection by programming or erasing the PPB, then protecting the PPB from further change for the remainder of normal system operation by clearing the PPB Lock bit to '0'. This is sometimes called Boot-code controlled sector protection.

The Password method clears the PPB Lock bit to '0' during POR, or Hardware Reset to protect the PPB. A 64-bit password may be permanently programmed and hidden for the password method. A command can be used to provide a password for comparison with the hidden password. If the password matches, the PPB Lock bit is set to '1' to unprotect the PPB. A command can be used to clear the PPB Lock bit to '0'. This method requires use of a password to control PPB protection.

The selection of the PPB Lock bit management method is made by programming OTP bits in the ASP Register so as to permanently select the method used.

infineon

Data protection

9.4.1 ASP register

The ASP register is used to permanently configure the behavior of Advanced Sector Protection (ASP) features. See **Table 25**.

As shipped from the factory, all devices default ASP to the Persistent Protection mode, with all sectors unprotected, when power is applied. The device programmer or host system must then choose which sector protection method to use. Programming either of the, one-time programmable, Protection Mode Lock Bits, locks the part permanently in the selected mode:

- ASPR[2:1] = 11 = No ASP mode selected, Persistent Protection Mode is the default.
- ASPR[2:1] = 10 = Persistent Protection Mode permanently selected.
- ASPR[2:1] = 01 = Password Protection Mode permanently selected.
- ASPR[2:1] = 00 = Illegal condition, attempting to program both bits to zero results in a programming failure. ASP register programming rules:
- If the password mode is chosen, the password must be programmed prior to setting the Protection Mode Lock Bits.
- Once the Protection Mode is selected, the Protection Mode Lock Bits are permanently protected from programming and no further changes to the ASP register is allowed.

The programming time of the ASP Register is the same as the typical page programming time. The system can determine the status of the ASP register programming operation by reading the WIP bit in the Status Register. See "Status Register 1 (SR1)" on page 45 for information on WIP.

After selecting a sector protection method, each sector can operate in each of the following states:

- Dynamically Locked A sector is protected and can be changed by a simple command.
- Persistently Locked A sector is protected and cannot be changed if its PPB Bit is '0'.
- Unlocked The sector is unprotected and can be changed by a simple command.

9.4.2 Persistent protection bits

The persistent protection bits (PPB) are located in a separate nonvolatile flash array. One of the PPB bits is related to each sector. When a PPB is '0', its related sector is protected from program and erase operations. The PPB are programmed individually but must be erased as a group, similar to the way individual words may be programmed in the main array but an entire sector must be erased at the same time. The PPB have the same program and erase endurance as the main flash memory array. Preprogramming and verification prior to erasure are handled by the device.

Programming a PPB bit requires the typical page programming time. Erasing all the PPBs requires typical sector erase time. During PPB bit programming and PPB bit erasing, status is available by reading the Status register. Reading of a PPB bit requires the initial access time of the device.

9.4.3 Dynamic protection bits

Dynamic protection bits are volatile and unique for each sector and can be individually modified. DYB only control the protection for sectors that have their PPB set to '1'. By issuing the DYB Write command, a DYB is cleared to '0' or set to '1', thus placing each sector in the protected or unprotected state respectively. This feature allows software to easily protect sectors against inadvertent changes, yet does not prevent the easy removal of protection when changes are needed. The DYBs can be set or cleared as often as needed as they are volatile bits.

Notes

- 41.Each PPB is individually programmed to '0' and all are erased to '1' in parallel.
- 42.If the PPB Lock bit is '0', the PPB Program or PPB Erase command does not execute and fails without programming or erasing the PPB.
- 43. The state of the PPB for a given sector can be verified by using the PPB Read command.

infineon

Data protection

9.4.4 PPB Lock Bit (PPBL[0])

The PPB Lock Bit is a volatile bit for protecting all PPB bits. When cleared to '0', it locks all PPBs and when set to '1', it allows the PPBs to be changed.

The PLBWR command is used to clear the PPB Lock bit to '0'. The PPB Lock Bit must be cleared to '0' only after all the PPBs are configured to the desired settings.

In Persistent Protection mode, the PPB Lock is set to '1' during POR or a hardware reset. When cleared to '0', no software command sequence can set the PPB Lock bit to '1', only another hardware reset or power-up can set the PPB Lock bit.

In the Password Protection mode, the PPB Lock bit is cleared to '0' during POR or a hardware reset. The PPB Lock bit can only be set to '1' by the Password Unlock command.

9.4.5 Sector protection states summary

Each sector can be in one of the following protection states:

- Unlocked The sector is unprotected and protection can be changed by a simple command. The protection state defaults to unprotected after a power cycle, software reset, or hardware reset.
- Dynamically Locked A sector is protected and protection can be changed by a simple command. The protection state is not saved across a power cycle or reset.
- Persistently Locked A sector is protected and protection can only be changed if the PPB Lock Bit is set to '1'. The protection state is nonvolatile and saved across a power cycle or reset. Changing the protection state requires programming and or erase of the PPB bits.

Table 34 Sector protection states

| Protection bit values | | | Control data | |
|-----------------------|-----|-----|---|--|
| PPB lock | PPB | DYB | Sector state | |
| 1 | 1 | 1 | Unprotected – PPB and DYB are changeable | |
| 1 | 1 | 0 | Protected – PPB and DYB are changeable | |
| 1 | 0 | 1 | Protected – PPB and DYB are changeable | |
| 1 | 0 | 0 | Protected – PPB and DYB are changeable | |
| 0 | 1 | 1 | Unprotected – PPB not changeable, DYB is changeable | |
| 0 | 1 | 0 | Protected – PPB not changeable, DYB is changeable | |
| 0 | 0 | 1 | Protected – PPB not changeable, DYB is changeable | |
| 0 | 0 | 0 | Protected – PPB not changeable, DYB is changeable | |

9.4.6 Persistent Protection mode

The Persistent Protection method sets the PPB Lock bit to '1' during POR or Hardware Reset so that the PPB bits are unprotected by a device hardware reset. Software reset does not affect the PPB Lock bit. The PLBWR command can clear the PPB Lock bit to '0' to protect the PPB. There is no command to set the PPB Lock bit therefore the PPB Lock bit will remain at '0' until the next power-off or hardware reset.

infineon

Data protection

9.4.7 Password Protection mode

Password Protection mode allows an even higher level of security than the Persistent Sector Protection mode, by requiring a 64-bit password for unlocking the PPB Lock bit. In addition to this password requirement, after power up and hardware reset, the PPB Lock bit is cleared to '0' to ensure protection at power-up. Successful execution of the Password Unlock command by entering the entire password clears the PPB Lock bit, allowing for sector PPB modifications.

Password protection notes:

- Once the Password is programmed and verified, the Password Mode (ASPR[2] = 0) must be set in order to prevent reading the password.
- The Password Program Command is only capable of programming '0's. Programming '1' after a cell is programmed as '0' results in the cell left as '0' with no programming error set.
- The password is all 1's when shipped from Infineon. It is located in its own memory space and is accessible through the use of the Password Program and Password Read commands.
- All 64-bit password combinations are valid as a password.
- The Password mode, once programmed, prevents reading the 64-bit password and further password programming. All further program and read commands to the password region are disabled and these commands are ignored. There is no means to verify what the password is after the Password Mode Lock Bit is selected. Password verification is only allowed before selecting the Password Protection mode.
- The Protection Mode Lock Bits are not erasable.
- The exact password must be entered in order for the unlocking function to occur. If the password unlock
 command provided password does not match the hidden internal password, the unlock operation fails in the
 same manner as a programming operation on a protected sector. The P_ERR bit is set to one and the WIP Bit
 remains set. In this case it is a failure to change the state of the PPB Lock bit because it is still protected by the
 lack of a valid password.
- The Password Unlock command cannot be accepted any faster than once every $100 \, \mu s \pm 20 \, \mu s$. This makes it take an unreasonably long time (58 million years) for a hacker to run through all the 64-bit combinations in an attempt to correctly match a password. The Read Status Register 1 command may be used to read the WIP bit to determine when the device has completed the password unlock command or is ready to accept a new password command. When a valid password is provided the password unlock command does not insert the $100 \, \mu s$ delay before returning the WIP bit to '0'.
- If the password is lost after selecting the Password mode, there is no way to set the PPB Lock bit.

infineon

Commands

10 Commands

All communication between the host system and the S79FL01GS memory device is in the form of units called commands.

All commands begin with an instruction that selects the type of information transfer or device operation to be performed. Commands may also have an address, instruction modifier, latency period, data transfer to the memory, or data transfer from the memory. All instruction, address, and data information is transferred serially between the host system and memory device.

All instructions are transferred from host to memory as a single bit serial sequence on the SI signal.

Single bit wide commands may provide an address or data sent only on the SI signal. Data may be sent back to the host serially on SO signal.

Quad Output commands provide an address sent to the memory only on the IOO and IO4 signal. Data will be returned to the host as a sequence of 8-bit (byte) groups on IOO–IO7.

Quad Input/Output (I/O) commands provide an address sent from the host as four-bit (nibble) groups on Quad SPI-1 IO0–IO3 and Quad SPI-2 IO4–IO7. Data is returned to the host similarly as 8-bit (byte) groups on IO0–IO7.

Commands are structured as follows:

- Each command begins with an eight bit (byte) instruction.
- The instruction may be stand alone or may be followed by address bits to select a location within one of several address spaces in the device. The address may be either a 24-bit or 32-bit byte boundary address.
- The S79FL01GS Serial Peripheral Interface with multiple IO provides the option for each transfer of address and data information to be done one, or four bits in parallel. This enables a trade off between the number of signal connections (IO bus width) and the speed of information transfer. If the host system can support a four-bit wide IO bus the memory performance can be increased by using the instructions that provide parallel four-bit (quad) transfers.
- The width of all transfers following the instruction are determined by the instruction sent.
- All single bits or parallel bit groups are transferred in most to least significant bit order.
- Some instructions send instruction modifier (mode) bits following the address to indicate that the next command will be of the same type with an implied, rather than an explicit, instruction. The next command thus does not provide an instruction byte, only a new address and mode bits. This reduces the time needed to send each command when the same command type is repeated in a sequence of commands.
- The address or mode bits may be followed by write data to be stored in the memory device or by a read latency period before read data is returned to the host.
- Read latency may be zero to several SCK cycles (also referred to as dummy cycles).
- All instruction, address, mode, and data information is transferred in byte granularity. Addresses are shifted into the device with the most significant byte first. All data is transferred with the lowest address byte sent first. Following bytes of data are sent in lowest to highest byte address order i.e. the byte address increments.
- All attempts to read the flash memory array during a program, erase, or a write cycle (embedded operations) are ignored. The embedded operation will continue to execute without any affect. A very limited set of commands are accepted during an embedded operation. These are discussed in the individual command descriptions. While a program, erase, or write operation is in progress, it is recommended to check that the Write-In Progress (WIP) bit is '0' before issuing most commands to the device, to ensure the new command can be accepted.
- Depending on the command, the time for execution varies. A command to read status information from an executing command is available to determine when the command completes execution and whether the command was successful.



Commands

- Although host software in some cases is used to directly control the SPI interface signals, the hardware interfaces of the host system and the memory device generally handle the details of signal relationships and timing. For this reason, signal relationships and timing are not covered in detail within this software interface focused section of the document. Instead, the focus is on the logical sequence of bits transferred in each command rather than the signal timing and relationships. Following are some general signal relationship descriptions to keep in mind. For additional information on the bit level format and signal timing relationships of commands, see "Command protocol" on page 16.
 - The host always controls the Chip Select (CS#), Serial Clock (SCK), and Serial Input (IO0 and IO4) for single-bit wide transfers. The memory drives the IO0–IO7 signals during transfers.
 - All commands begin with the host selecting the memory by driving CS# LOW before the first rising edge of SCK. CS# is kept LOW throughout a command and when CS# is returned HIGH the command ends. Generally, CS# remains LOW for eight bit transfer multiples to transfer byte granularity information. Some commands will not be accepted if CS# is returned HIGH not at an 8-bit boundary.

10.1 Command set summary

The S79FL01GS Dual-Quad SPI device contains two Quad SPI devices (Quad SPI-1 and Quad SPI-2)) stacked in a Dual Die Package (DDP). Both devices are selected to decode each command instruction and address when the CS# signal, shared by both devices, goes low. Quad SPI-1 device responds to commands, address, data in and data out on IO0–IO3. Quad SPI-2 device responds to commands, address, data in and data out on IO4–IO7. All commands are executed by both devices in parallel.

Both Quad SPI devices must be configured, by writing to the various status and configuration registers in parallel, to define the same overall sector map and behavior of both devices, selected by each CS# for the DDP.

10.1.1 Extended addressing

To accommodate addressing above 256 Mb, there are three options:

1. New instructions are provided with 4-byte address, used to access up to 32 Gb of memory.

Table 35 Instructions and corresponding details

| Instruction name | Description | Code (Hex) |
|------------------|------------------------------------|------------|
| 4FAST_READ | Read Fast (4-byte Address) | 0C |
| 4READ | Read (4-byte Address) | 13 |
| 4QOR | Read Quad Out (4-byte Address) | 6C |
| 4QIOR | Quad I/O Read (4-byte Address) | EC |
| 4DDRQIOR | DDR Quad I/O Read (4-byte Address) | EE |
| 4PP | Page Program (4-byte Address) | 12 |
| 4QPP | Quad Page Program (4-byte Address) | 34 |
| 4SE | Erase 512 kB (4-byte Address) | DC |



Commands

2. For backward compatibility to the 3-byte address instructions, the standard instructions can be used in conjunction with the EXTADD Bit in the Bank Address Register (BAR[7]). By default BAR[7] is cleared to '0' (following power up and hardware reset), to enable 3-byte (24-bit) addressing. When set to '1', the legacy commands are changed to require 4 bytes (32 bits) for the address field. The following instructions can be used in conjunction with EXTADD bit to switch from 3 bytes to 4 bytes of address field.

Table 36 Instructions and corresponding details

| Instruction name | Description | Code (Hex) |
|------------------|------------------------------------|------------|
| READ | Read (3-byte Address) | 03 |
| FAST_READ | Read Fast (3-byte Address) | 0B |
| QOR | Read Quad Out (3-byte Address) | 6B |
| QIOR | Quad I/O Read (3-byte Address) | ЕВ |
| DDRQIOR | DDR Quad I/O Read (3-byte Address) | ED |
| PP | Page Program (3-byte Address) | 02 |
| QPP | Quad Page Program (3-byte Address) | 32 |
| SE | Erase 512 kB (3-byte Address) | D8 |

- 3. For backward compatibility to the 3-byte addressing, the standard instructions can be used in conjunction with the Bank Address Register:
 - a. The Bank Address Register is used to switch between 128-Mbit (16-Mbyte) banks of memory, The standard 3-byte address selects an address within the bank selected by the Bank Address Register.
 - i. The host system writes the Bank Address Register to access beyond the first 128 Mbits of memory.
 - ii. This applies to read, erase, and program commands.
 - b. The Bank Register provides the high order (4th) byte of address, which is used to address the available memory at addresses greater than 16 Mbytes.
- c. Bank Register bits are volatile.
 - i. On power up, the default is Bank 0 (the lowest address 16 Mbytes).
- d. For Read, the device will continuously transfer out data until the end of the array.
 - i. There is no bank to bank delay.
 - ii. The Bank Address Register is not updated.
 - iii. The Bank Address Register value is used only for the initial address of an access.

Table 37 Bank address map

| Bank address register bits | | Doub. | Memory array address range (Hex) | | |
|----------------------------|-------|-------|----------------------------------|---------------------|--|
| Bit 1 | Bit 0 | Bank | memory array | address range (Hex) | |
| 0 | 0 | 0 | 00000000 | 00FFFFF | |
| 0 | 1 | 1 | 01000000 | 01FFFFFF | |
| 1 | 0 | 2 | 02000000 | 02FFFFF | |
| 1 | 1 | 3 | 03000000 | 03FFFFFF | |

infineon

Commands

Table 38 S79FL01GS command set (sorted by function)

| Function | Command name | Command description | Instruction value (Hex) | Maximum frequency (MHz) |
|---------------------------------|-------------------|---|-------------------------|--|
| Read Device Identi- fication | READ_ID (REMS) | Read Electronic Manufacturer Signature | 90 | 133 |
| | RDID | Read ID (JEDEC Manufacturer ID and JEDEC CFI) | 9F | 133 |
| | RES | Read Electronic Signature | AB | 50 |
| | RSFDP | Read Serial Flash Discoverable Parameters | 5A | 133 |
| Register Access | RDSR1 | Read Status Register 1 | 05 | 133 |
| | RDSR2 | Read Status Register 2 | 07 | 133 |
| | RDCR | Read Configuration Register 1 | 35 | 133 |
| | WRR | Write Register (Status 1, Configuration 1) | 01 | 133 |
| | WRDI | Write Disable | 04 | 133 |
| | WREN | Write Enable | 06 | 133 |
| | CLSR | Clear Status Register 1 – Erase/Program Fail Reset | 30 | 133 |
| | ABRD | AutoBoot Register Read | 14 | 133 (QUAD = 0) 104 (QUAD = 1) |
| | ABWR | AutoBoot Register Write | 15 | 133 |
| | BRRD | Bank Register Read | 16 | 133 |
| | BRWR | Bank Register Write | 17 | 133 |
| | BRAC | Bank Register Access (Legacy Command formerly used for Deep Power Down) | B9 | 133 |
| | DLPRD | Data Learning Pattern Read | 41 | 133 |
| | PNVDLR | Program NV Data Learning Register | 43 | 133 |
| | WVDLR | Write Volatile Data Learning Register | 4A | 133 |
| Read Flash Array | READ | Read (3- or 4-byte address) | 03 | 50 |
| | 4READ | Read (4-byte address) | 13 | 50 |
| | FAST_READ | Fast Read (3- or 4-byte address) | 0B | 133 |
| | 4FAST_READ | Fast Read (4-byte address) | 0C | 133 |
| | QOR | Read Quad Out (3- or 4-byte address) | 6B | 104 |
| | 4QOR | Read Quad Out (4-byte address) | 6C | 104 |
| | QIOR | Quad I/O Read (3- or 4-byte address) | EB | 104 |
| | 4QIOR | Quad I/O Read (4-byte address) | EC | 104 |
| | DDRQIOR | DDR Quad I/O Read (3- or 4-byte address) | ED | 80 |
| | 4DDRQIOR | DDR Quad I/O Read (4-byte address) | EE | 80 |

1 Gb (128 MB) Dual-Quad FL-S Flash SPI Multi-I/O, $3.0\,\mathrm{V}$

infineon

Commands

 Table 38
 S79FL01GS command set (sorted by function) (Continued)

| Function | Command name | Command description | Instruction value (Hex) | Maximum frequency (MHz) |
|----------------------------|--------------|--|-------------------------|-------------------------|
| Program Flash Array | PP | Page Program (3- or 4-byte address) | 02 | 133 |
| | 4PP | Page Program (4-byte address) | 12 | 133 |
| | QPP | Quad Page Program (3- or 4-byte address) | 32 | 80 |
| | QPP | Quad Page Program - Alternate instruction (3- or 4-byte address) | 38 | 80 |
| | 4QPP | Quad Page Program (4-byte address) | 34 | 80 |
| | PGSP | Program Suspend | 85 | 133 |
| | PGRS | Program Resume | 8A | 133 |
| Erase Flash Array | BE | Bulk Erase | 60 | 133 |
| | BE | Bulk Erase (alternate command) | C7 | 133 |
| | SE | Erase 512 kB (3- or 4-byte address) | D8 | 133 |
| | 4SE | Erase 512 kB (4-byte address) | DC | 133 |
| | ERSP | Erase Suspend | 75 | 133 |
| | ERRS | Erase Resume | 7A | 133 |
| One Time Program | OTPP | OTP Program | 42 | 133 |
| Array | OTPR | OTP Read | 4B | 133 |
| Advanced Sector | DYBRD | DYB Read | E0 | 133 |
| Protection | DYBWR | DYB Write | E1 | 133 |
| | PPBRD | PPB Read | E2 | 133 |
| | PPBP | PPB Program | E3 | 133 |
| | PPBE | PPB Erase | E4 | 133 |
| | ASPRD | ASP Read | 2B | 133 |
| | ASPP | ASP Program | 2F | 133 |
| | PLBRD | PPB Lock Bit Read | A7 | 133 |
| | PLBWR | PPB Lock Bit Write | A6 | 133 |
| | PASSRD | Password Read | E7 | 133 |
| | PASSP | Password Program | E8 | 133 |
| | PASSU | Password Unlock | E9 | 133 |
| Reset | RESET | Software Reset | F0 | 133 |
| | MBR | Mode Bit Reset | FF | 133 |
| Reserved for Future Use | MPM | Reserved for Multi-I/O-High Performance Mode (MPM) | A3 | 133 |
| RFU | Reserved-18 | Reserved | 18 | _ |
| RFU | Reserved-E5 | Reserved | E5 | _ |
| RFU | Reserved-E6 | Reserved | E6 | _ |

infineon

Commands

10.1.2 Read Device identification

There are multiple commands to read information about the device manufacturer, device type, and device features. SPI memories from different vendors have used different commands and formats for reading information about the memories. The S79FL01GS device supports the three most common device information commands.

10.1.3 Register read or write

There are multiple registers for reporting embedded operation status or controlling device configuration options. There are commands for reading or writing these registers. Registers contain both volatile and nonvolatile bits. Nonvolatile bits in registers are automatically erased and programmed as a single (write) operation.

10.1.3.1 Monitoring operation status

The host system can determine when a write, program, erase, suspend or other embedded operation is complete by monitoring the Write in Progress (WIP) bit in the Status Register. The Read from Status Register 1 command provides the state of the WIP bit. The program error (P_ERR) and erase error (E_ERR) bits in the status register indicate whether the most recent program or erase command has not completed successfully. When P_ERR or E_ERR bits are set to one, the WIP bit will remain set to one indicating the device remains busy. Under this condition, only the CLSR, WRDI, RDSR1, RDSR2, and software RESET commands are valid commands. A Clear Status Register (CLSR) followed by a Write Disable (WRDI) command must be sent to return the device to standby state. CLSR clears the WIP, P_ERR, and E_ERR bits. WRDI clears the WEL bit. Alternatively, Hardware Reset, or Software Reset (RESET) may be used to return the device to standby state.

10.1.3.2 Configuration

There are commands to read, write, and protect registers that control interface path width, interface timing, interface address length, and some aspects of data protection.

10.1.4 Read flash array

Data may be read from the memory starting at any byte boundary. Data bytes are sequentially read from incrementally higher byte addresses until the host ends the data transfer by driving CS# input HIGH. If the byte address reaches the maximum address of the memory array, the read will continue at address zero of the array.

There are several different read commands to specify different access latency and data path widths. Double Data Rate (DDR) commands also define the address and data bit relationship to both SCK edges:

- The Read command provides a single address bit per SCK rising edge on the IO0 and IO4 signal with read data
 returning a single bit per SCK falling edge on the IO1 and IO5 signal. This command has zero latency between
 the address and the returning data but is limited to a maximum SCK rate of 50 MHz.
- Other read commands have a latency period between the address and returning data but can operate at higher SCK frequencies. The latency depends on the Configuration Register latency code.
- The Fast Read command provides a single address bit per SCK rising edge on the IO0 and IO4 signal with read data returning a single bit per SCK falling edge on the IO1 and IO5 signal and may operate up to 133 MHz.
- Quad Output read commands provide address a single bit per SCK rising edge on the IOO and IO4 signal with read data returning four bits of data per SCK falling edge on the IOO–IO7 signals.
- Quad I/O Read commands provide address four bits per SCK rising edge with read data returning four bits of data per SCK falling edge on the IOO–IO7 signals.
- Quad Double Data Rate read commands provide address four bits per every SCK edge with read data returning
 eight bits of data per every SCK edge on the IO0–IO7 signals. Double Data Rate (DDR) operation is only supported
 for core and I/O voltages of 3 V to 3.6 V.

infineon

Commands

10.1.5 Program flash array

Programming data requires two commands: Write Enable (WREN), and Page Program (PP or QPP). The Page Program command accepts from 1 byte up to 512 consecutive bytes of data (page) to be programmed in one operation. Programming means that bits can either be left at '1', or programmed from '1' to '0'. Changing bits from '0' to '1' requires an erase operation.

10.1.6 Erase flash array

The Sector Erase (SE) and Bulk Erase (BE) commands set all the bits in a sector or the entire memory array to '1'. A bit needs to be first erased to '1' before programming can change it to '0'. While bits can be individually programmed from '1' to '0', erasing bits from '0' to '1' must be done on a sector-wide (SE) or array-wide (BE) level.

10.1.7 OTP, block protection, and advanced sector protection

There are commands to read and program a separate one time programmable (OTP) array for permanent data such as a serial number. There are commands to control a contiguous group (block) of flash memory array sectors that are protected from program and erase operations. There are commands to control which individual flash memory array sectors are protected from program and erase operations.

10.1.8 Reset

There is a command to reset to the default conditions present after power on to the device. There is a command to reset (exit from) the Enhanced Performance Read modes.

10.1.9 Reserved

Some instructions are reserved for future use. In this generation of the S79FL01GS some of these command instructions may be unused and not affect device operation, some may have undefined results.

Some commands are reserved to ensure that a legacy or alternate source device command is allowed without affect. This allows legacy software to issue some commands that are not relevant for the current generation S79FL01GS device with the assurance these commands do not cause some unexpected action.

Some commands are reserved for use in special versions of the FL-S not addressed by this document or for a future generation. This allows new host memory controller designs to plan the flexibility to issue these command instructions. The command format is defined if known at the time this document revision is published.

Commands

10.2 Identification commands

10.2.1 Read Identification — REMS (Read_ID or REMS 90h)

The READ_ID command identifies the Device Manufacturer ID and the Device ID. The command is also referred to as Read Electronic Manufacturer and device Signature (REMS). READ-ID (REMS) is only supported for backward compatibility and should not be used for new software designs. New software designs should instead make use of the RDID command.

The command is initiated by shifting on SI the instruction code "90h" followed by a 24-bit address of 00000h. Following this, the Manufacturer ID and the Device ID are shifted out on SO starting at the falling edge of SCK after address. The Manufacturer ID and the Device ID are always shifted out with the MSB first. If the 24-bit address is set to 000001h, then the Device ID is read out first followed by the Manufacturer ID. The Manufacturer ID and Device ID output data toggles between address 000000H and 000001H until terminated by a low to high transition on CS# input. The maximum clock frequency for the READ_ID command is 133 MHz.

For the Dual-Quad SPI device the Read Identification (REMS) instruction and data read is only done on Quad SPI-1 using IO0 and IO1.




Figure 31 READ_ID (90h) command sequence

Table 39 Read_ID values

| Device | Manufacturer ID (Hex) | Device ID (Hex) |
|-----------|-----------------------|-----------------|
| S79FL01GS | 01 | 21 |

infineon

Commands

10.2.2 Read Identification (RDID 9Fh)

The Read Identification (RDID) command provides read access to manufacturer identification, device identification, and common flash interface (CFI) information. The manufacturer identification is assigned by JEDEC. The CFI structure is defined by JEDEC standard. The device identification and CFI values are assigned by Infineon.

The JEDEC common flash interface (CFI) specification defines a device information structure, which allows a vendor-specified software flash management program (driver) to be used for entire families of flash devices. Software support can then be device-independent, JEDEC manufacturer ID independent, forward and backward-compatible for the specified flash device families. System vendors can standardize their flash drivers for long-term software compatibility by using the CFI values to configure a family driver from the CFI information of the device in use.

Any RDID command issued while a program, erase, or write cycle is in progress is ignored and has no effect on execution of the program, erase, or write cycle that is in progress.

The RDID instruction is shifted on SI. After the last bit of the RDID instruction is shifted into the device, a byte of manufacturer identification, two bytes of device identification, extended device identification, and CFI information will be shifted sequentially out on SO. As a whole this information is referred to as ID-CFI. See "ID-CFI address space" on page 41 for the detail description of the ID-CFI contents.

Continued shifting of output beyond the end of the defined ID-CFI address space will provide undefined data. The RDID command sequence is terminated by driving CS# to the logic HIGH state anytime during data output.

For the S79FL01GS Dual-Quad SPI device, the Read Identification (RDID) instruction and data read is only done on Quad SPI-1 using IO0 and IO1. The maximum clock frequency for the RDID command is 133 MHz.




Figure 32 Read Identification (RDID 9Fh) command sequence

Commands

Table 40

10.2.3 Read Electronic Signature (RES) (ABh)

The RES command is used to read a single byte Electronic Signature from SO. RES is only supported for backward compatibility and should not be used for new software designs. New software designs should instead make use of the RDID command.

The RES instruction is shifted in followed by three dummy bytes onto SI. After the last bit of the three dummy bytes are shifted into the device, a byte of Electronic Signature will be shifted out of SO. Each bit is shifted out by the falling edge of SCK. The maximum clock frequency for the RES command is 50 MHz.

The Electronic Signature can be read repeatedly by applying multiples of eight clock cycles.

The RES command sequence is terminated by driving CS# to the logic HIGH state anytime during data output. For the S79FL01GS Dual-Quad SPI device, the Read Electronic Signature (RES) instruction and data read is only done on Quad SPI-1 using IO0 and IO1.




Figure 33 Read Electronic Signature (RES ABh) command sequence

| Table 40 RES values | | |
|---------------------|-----------------|--|
| Device | Device ID (Hex) | |
| S79FL01GS | 21 | |

10.2.4 Read serial flash discoverable parameters (RSFDP 5Ah)

The command is initiated by shifting on SI the instruction code '5Ah', followed by a 24-bit address of 000000h, followed by eight dummy cycles. The SFDP bytes are then shifted out on SO starting at the falling edge of SCK after the eight dummy cycles. The SFDP bytes are always shifted out with the MSB first. If the 24-bit address is set to any other value, the selected location in the SFDP space is the starting point of the data read. This enables random access to any parameter in the SFDP space. The maximum clock frequency for the RSFDP command is 133 MHz.

For the S79FL01GS Dual-Quad device the Read Serial Flash Discoverable Parameters (RSFDP) instruction and data read is only done on Quad SPI-1 using IO0 and IO1.




Figure 34 RSFDP command sequence

DEC values

Commands

10.3 Register Access commands

10.3.1 Read Status Register 1 (RDSR1 05h)

The Read Status Register 1 (RDSR1) command allows the Status Register 1 contents of Quad SPI-1 to be read from IO1 and Quad SPI-2 to be read from IO5. The Status Register 1 contents may be read at any time, even while a program, erase, or write operation is in progress. It is possible to read the Status Register 1 continuously by providing multiples of eight clock cycles. The status is updated for each eight cycle read. The maximum clock frequency for the RDSR1 (05h) command is 133 MHz.




Figure 35 Dual-Quad Read Status Register 1 (RDSR1 05h) command sequence

10.3.2 Read Status Register 2 (RDSR2 07h)

The Read Status Register 2 (RDSR2) command allows the Status Register 2 contents of Quad SPI-1 to be read from IO1 and Quad SPI-2 to be read from IO5. The Status Register 2 contents may be read at any time, even while a program, erase, or write operation is in progress. It is possible to read the Status Register 2 continuously by providing multiples of eight clock cycles. The status is updated for each eight cycle read. The maximum clock frequency for the RDSR2 command is 133 MHz.




Figure 36 Dual-Quad Read Status Register 2 (RDSR2 07h) command sequence

Commands

10.3.3 Read Configuration Register (RDCR 35h)

The Read Configuration Register (RDCR) command allows the Configuration Register contents of Quad SPI-1 to be read from IO1 and Quad SPI-2 to be read from IO5. It is possible to read the Configuration Register continuously by providing multiples of eight clock cycles. The Configuration Register contents may be read at any time, even while a program, erase, or write operation is in progress.




Figure 37 Dual-Quad Read Configuration Register (RDCR 35h) command sequence

10.3.4 Bank Register Read (BRRD 16h)

The Read the Bank Register (BRRD) command allows the Bank address Register contents to be read from SO. The instruction is first shifted in from SI. Then the 8-bit Bank Register is shifted out on SO. It is possible to read the Bank Register continuously by providing multiples of eight clock cycles. The maximum operating clock frequency for the BRRD command is 133 MHz.




Figure 38 Read Bank Register (BRRD 16h) command

infineon

Commands

10.3.5 Bank Register Write (BRWR 17h)

The Bank Register Write (BRWR) command is used to write address bits above A23, into the Bank Address Register (BAR). The command is also used to write the Extended address control bit (EXTADD) that is also in BAR[7]. BAR provides the high order addresses needed by devices having more than 128 Mbits (16 Mbytes), when using 3-byte address commands without extended addressing enabled (BAR[7] EXTADD = 0). Because this command is part of the addressing method and is not changing data in the flash memory, this command does not require the WREN command to precede it.

The BRWR instruction is entered, followed by the data byte on SI. The Bank Register is one data byte in length. The BRWR command has no effect on the P_ERR, E_ERR or WIP bits of the Status and Configuration Registers. Any bank address bit reserved for the future should always be written as '0'.




Figure 39 Bank Register Write (BRWR 17h) command

Commands

10.3.6 Bank Register Access (BRAC B9h)

The Bank Register Read and Write commands provide full access to the Bank Address Register (BAR) but they are both commands that are not present in legacy SPI memory devices. Host system SPI memory controller interfaces may not be able to easily support such new commands. The Bank Register Access (BRAC) command uses the same command code and format as the Deep Power Down (DPD) command that is available in legacy SPI memories. The FL-S family does not support a DPD feature but assigns this legacy command code to the BRAC command to enable write access to the Bank Address Register for legacy systems that are able to send the legacy DPD (B9h) command.

When the BRAC command is sent, the S79FL-S family device will then interpret an immediately following Write Register (WRR) command as a write to the lower address bits of the BAR. A WREN command is not used between the BRAC and WRR commands. Only the lower two bits of the first data byte following the WRR command code are used to load BAR[1:0]. The upper bits of that byte and the content of the optional WRR command second data byte are ignored. Following the WRR command the access to BAR is closed and the device interface returns to the standby state. The combined BRAC followed by WRR command sequence has no affect on the value of the ExtAdd bit (BAR[7]).

Commands other than WRR may immediately follow BRAC and execute normally. However, any command other than WRR, or any other sequence in which CS# goes low and returns high, following a BRAC command, will close the access to BAR and return to the normal interpretation of a WRR command as a write to Status Register 1 and the Configuration Register.

The BRAC + WRR sequence is allowed only when the device is in standby, program suspend, or erase suspend states. This command sequence is illegal when the device is performing an embedded algorithm or when the program (P_ERR) or erase (E_ERR) status bits are set to '1'.




Figure 40 BRAC (B9h) command sequence

Commands

10.3.7 Write Registers (WRR 01h)

The Write Registers (WRR) command allows new values to be written to both the Status Register 1 and Configuration Register. Before the Write Registers (WRR) command can be accepted by the device, a Write Enable (WREN) command must be received. After the Write Enable (WREN) command has been decoded successfully, the device will set the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The Write Registers (WRR) command is entered by shifting the instruction and the data bytes for Quad SPI-1 on IO0 and for Quad SPI-2 on IO4. The Status Register is one data byte in length.

The Write Registers (WRR) command will set the P_ERR or E_ERR bits if there is a failure in the WRR operation. Any Status or Configuration Register bit reserved for the future must be written as '0'.

CS# must be driven to the logic HIGH state after the eighth or sixteenth bit of data has been latched. If not, the Write Registers (WRR) command is not executed. If CS# is driven HIGH after the eighth cycle then only the Status Register 1 is written; otherwise, after the sixteenth cycle both the Status and Configuration Registers are written. When the configuration register QUAD bit CR[1] is '1', only the WRR command format with 16 data bits may be used.

As soon as CS# is driven to the logic HIGH state, the self-timed Write Registers (WRR) operation is initiated. While the Write Registers (WRR) operation is in progress, the Status Register may still be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed Write Registers (WRR) operation, and is '0' when it is completed. When the Write Registers (WRR) operation is completed, the Write Enable Latch (WEL) is set to '0'. The maximum clock frequency for the WRR command is 133 MHz.




Figure 41 Dual-Quad Write Registers




Figure 42 Dual-Quad Write Registers (WRR 01h) command sequence

The Write Registers (WRR) command allows the user to change the values of the Block Protect (BP2, BP1, and BP0) bits to define the size of the area that is to be treated as read-only. The Write Registers (WRR) command also allows the user to set the Status Register Write Disable (SRWD) bit to '1' or '0'. The Status Register Write Disable (SRWD) bit allows the BP bits to be hardware protected.



Commands

When the Status Register Write Disable (SRWD) bit of the Status Register is '0' (its initial delivery state), it is possible to write to the Status Register provided that the Write Enable Latch (WEL) bit has previously been set by a Write Enable (WREN) command.

The WRR command has an alternate function of loading the Bank Address Register if the command immediately follows a BRAC command. See "Bank Register Access (BRAC B9h)" on page 75.

10.3.8 Write Enable (WREN 06h)

The Write Enable (WREN) command sets the Write Enable Latch (WEL) bit of the Status Register 1 (SR1[1]) to '1'. The Write Enable Latch (WEL) bit must be set to '1' by issuing the Write Enable (WREN) command to enable write, program and erase commands.

CS# must be driven into the logic HIGH state after the eighth bit of the instruction byte has been latched in on IOO for Quad SPI-1 and IO4 for Quad SPI-2. Without CS# being driven to the logic HIGH state after the eighth bit of the instruction byte has been latched in on IOO for Quad SPI-1 and IO4 for Quad SPI-2, the write enable operation will not be executed.




Figure 43 Dual-Quad Write Enable (WREN 06h) command sequence

10.3.9 Write Disable (WRDI 04h)

The Write Disable (WRDI) command sets the Write Enable Latch (WEL) bit of the Status Register 1 (SR1[1]) to '0'.

The Write Enable Latch (WEL) bit may be set to '0' by issuing the Write Disable (WRDI) command to disable Page Program (PP), Sector Erase (SE), Bulk Erase (BE), Write Registers (WRR), OTP Program (OTPP), and other commands, that require WEL be set to '1' for execution. The WRDI command can be used by the user to protect memory areas against inadvertent writes that can possibly corrupt the contents of the memory. The WRDI command is ignored during an embedded operation while WIP bit = 1.

CS# must be driven into the logic HIGH state after the eighth bit of the instruction byte has been latched in on IO0 for Quad SPI-1 and IO4 for Quad SPI-2. Without CS# being driven to the logic HIGH state after the eighth bit of the instruction byte has been latched in on IO0 for Quad SPI-1 and IO4 for Quad SPI-2, the write disable operation will not be executed.




Figure 44 Dual-Quad Write Disable (WRDI 04h) command sequence

Commands

10.3.10 Clear Status Register (CLSR 30h)

The Clear Status Register command resets bit SR1[5] (Erase Fail Flag) and bit SR1[6] (Program Fail Flag). It is not necessary to set the WEL bit before the Clear SR command is executed. The Clear SR command will be accepted even when the device remains busy with WIP set to '1', as the device does remain busy when either error bit is set. The WEL bit will be unchanged after this command is executed.




Figure 45 Dual-Quad Clear Status Register (CLSR 30h) command sequence

10.3.11 ECC Status Register Read (ECCRD 18h)

To read the ECC Status Register, the command is followed by the ECC unit (32 bit) address, the four least significant bits (LSB) of address must be set to zero. This is followed by eight dummy cycles. Then the 8-bit contents of the ECC Register, for the ECC unit selected, are shifted out on SO 16 times, once for each byte in the ECC Unit. If CS# remains low the next ECC unit status is sent through SO 16 times, once for each byte in the ECC Unit, this continues until CS# goes high. The maximum operating clock frequency for the ECC READ command is 133 MHz. See "Automatic ECC" on page 92 for details on ECC unit.




Figure 46 ECC Status Register Read command sequence

Note

44. Data Out for Quad SPI-1 is IO1, Quad SPI-2 is IO5.

infineon

Commands

10.3.12 AutoBoot

SPI devices normally require 32 or more cycles of command and address shifting to initiate a read command. And, in order to read boot code from an SPI device, the host memory controller or processor must supply the read command from a hardwired state machine or from some host processor internal ROM code.

Parallel NOR devices need only an initial address, supplied in parallel in a single cycle, and initial access time to start reading boot code.

The AutoBoot feature allows the host memory controller to take boot code from a S79FL01GS device immediately after the end of reset, without having to send a read command. This saves 32 or more cycles and simplifies the logic needed to initiate the reading of boot code.

- As part of the power up reset, hardware reset, or command reset process the AutoBoot feature automatically starts a read access from a pre-specified address. At the time the reset process is completed, the device is ready to deliver code from the starting address. The host memory controller only needs to drive CS# signal from HIGH to LOW and begin toggling the SCK signal. The S79FL01GS device will delay code output for a pre-specified number of clock cycles before code streams out.
 - The Auto Boot Start Delay (ABSD) field of the AutoBoot register specifies the initial delay if any is needed by the host.
 - The host cannot send commands during this time.
 - If ABSD = 0, the maximum SCK frequency is 50 MHz.
 - If ABSD > 0, the maximum SCK frequency is 133 MHz if the QUAD bit CR1[1] is '0' or 104 MHz if the QUAD bit is '1'.
- The starting address of the boot code is selected by the value programmed into the AutoBoot Start Address (ABSA) field of the AutoBoot Register which specifies a 512 byte boundary aligned location; the default address is 00000000h.
 - Data will continuously shift out until CS# returns HIGH.
- At any point after the first data byte is transferred, when CS# returns HIGH, the SPI device will reset to standard SPI mode; able to accept normal command operations.
 - A minimum of one byte must be transferred.
 - AutoBoot mode will not initiate again until another power cycle or a reset occurs.
- An AutoBoot Enable bit (ABE) is set to enable the AutoBoot feature.

The AutoBoot register bits are nonvolatile and provide:

- The starting address (512-byte boundary), set by the AutoBoot Start Address (ABSA). The size of the ABSA field is 23 bits for devices up to 32-Gbit.
- The number of initial delay cycles, set by the AutoBoot Start Delay (ABSD) 8-bit count value.
- The AutoBoot Enable.

With the configuration register QUAD bit CR1[1] is set to '1', the boot code will be provided 4 bits per cycle in the same manner as a Read Quad Out command.




Figure 47 AutoBoot sequence (CR1[1] = 1)

Commands

10.3.13 AutoBoot Register Read (ABRD 14h)

The AutoBoot Register Read command is shifted into SI. Then the 32-bit AutoBoot Register is shifted out on SO, least significant byte first, most significant bit of each byte first. It is possible to read the AutoBoot Register continuously by providing multiples of 32 clock cycles. The maximum operating clock frequency for ABRD command is 104 MHz.




Figure 48 AutoBoot Register Read (ABRD 14h) command

10.3.14 AutoBoot Register Write (ABWR 15h)

Before the ABWR command can be accepted, a Write Enable (WREN) command must be issued and decoded by the device, which sets the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The ABWR command is entered by shifting the instruction and the data bytes on SI, least significant byte first, most significant bit of each byte first. The ABWR data is 32 bits in length.

The ABWR command has status reported in Status Register 1 as both an erase and a programming operation. An E_ERR or a P_ERR may be set depending on whether the erase or programming phase of updating the register fails.

CS# must be driven to the logic HIGH state after the 32nd bit of data has been latched. If not, the ABWR command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed ABWR operation is initiated. While the ABWR operation is in progress, Status Register 1 may be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed ABWR operation, and is '0' when it is completed. When the ABWR cycle is completed, the Write Enable Latch (WEL) is set to '0'. The maximum clock frequency for the ABWR command is 133 MHz.




Figure 49 AutoBoot Register Write (ABWR) command

Commands

10.3.15 Program NVDLR (PNVDLR 43h)

Before the Program NVDLR (PNVDLR) command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device. After the Write Enable (WREN) command has been decoded successfully, the device will set the Write Enable Latch (WEL) to enable the PNVDLR operation.

The PNVDLR command is entered by shifting the instruction and the data byte on SI-IO0 for Quad SPI-1 and IO4 for Quad SPI-2.

CS# must be driven to the logic HIGH state after the eighth (8th) bit of data has been latched. If not, the PNVDLR command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed PNVDLR operation is initiated. While the PNVDLR operation is in progress, the Status Register may be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed PNVDLR cycle, and is a '0' when it is completed. The PNVDLR operation can report a program error in the P_ERR bit of the status register. When the PNVDLR operation is completed, the Write Enable Latch (WEL) is set to '0'. The maximum clock frequency for the PNVDLR command is 133 MHz.




Figure 50 Program NVDLR (PNVDLR 43h) command sequence

10.3.16 Write VDLR (WVDLR 4Ah)

Before the Write VDLR (WVDLR) command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device. After the Write Enable (WREN) command has been decoded successfully, the device will set the Write Enable Latch (WEL) to enable WVDLR operation.

The WVDLR command is entered by shifting the instruction and the data byte on SI-IO0 for Quad SPI-1 and IO4 for Quad SPI-2.

CS# must be driven to the logic HIGH state after the eighth (8th) bit of data has been latched. If not, the WVDLR command is not executed. As soon as CS# is driven to the logic HIGH state, the WVDLR operation is initiated with no delays. The maximum clock frequency for the PNVDLR command is 133 MHz.




Figure 51 Write VDLR (WVDLR 4Ah) command sequence



Commands

10.3.17 Data Learning Pattern Read (DLPRD 41h)

The instruction is shifted on SI_IO0, then the 8-bit DLP is shifted out on SO_IO1 and IO5. It is possible to read the DLP continuously by providing multiples of eight clock cycles. The maximum operating clock frequency for the DLPRD command is 133 MHz.




Figure 52 Dual-Quad DLP Read (DLPRD 41h) command sequence

infineon

Commands

10.4 Read Memory Array commands

Read commands for the main flash array provide many options for prior generation SPI compatibility or enhanced performance SPI:

- Some commands transfer address or data on each rising edge of SCK. These are called Single Data Rate commands (SDR).
- Some SDR commands transfer address one bit per rising edge of SCK and return data 2, or 8 bits of data per rising edge of SCK. These are called Read or Fast Read for 2-bit data; Quad Output for 8-bit data.
- Some SDR commands transfer both address and data 8 bits per rising edge of SCK. These are called Quad I/O
 for 8 bit.
- Some commands transfer address and data on both the rising edge and falling edge of SCK. These are called Double Data Rate (DDR) commands.
- There are DDR commands for 1, or 4 bits of address per each die or 8 bit data per SCK edge. These are called Fast DDR for 1-bit, and Quad I/O DDR for 8-bit per edge transfer.

All of these commands begin with an instruction code that is transferred one bit per SCK rising edge. The instruction is followed by either a 3- or 4-byte address transferred at SDR or DDR. Commands transferring address or data 4-bits per clock edge per die are called Multiple I/O (MIO) commands. For FL-S devices at 256 Mbits or higher density, the traditional SPI 3-byte addresses are unable to directly address all locations in the memory array. These device have a bank address register that is used with 3-byte address commands to supply the high order address bits beyond the address from the host system. The default bank address is '0'. Commands are provided to load and read the bank address register. These devices may also be configured to take a 4-byte address from the host system with the traditional 3-byte address commands. The 4-byte address mode for traditional commands is activated by setting the External Address (EXTADD) bit in the bank address register to '1'.

The Quad I/O commands provide a performance improvement option controlled by mode bits that are sent following the address bits. The mode bits indicate whether the command following the end of the current read will be another read of the same type, without an instruction at the beginning of the read. These mode bits give the option to eliminate the instruction cycles when doing a series of Quad I/O read accesses.

Some commands require delay cycles following the address or mode bits to allow time to access the memory array. The delay cycles are traditionally called dummy cycles. The dummy cycles are ignored by the memory thus any data provided by the host during these cycles is 'don't care' and the host may also leave the SI signal at high impedance during the dummy cycles. When MIO commands are used the host must stop driving the IO signals (outputs are high impedance) before the end of last dummy cycle. When DDR commands are used the host must not drive the I/O signals during any dummy cycle. The number of dummy cycles varies with the SCK frequency or performance option selected via the Configuration Register 1 (CR1) Latency Code (LC). Dummy cycles are measured from SCK falling edge to next SCK falling edge. SPI outputs are traditionally driven to a new value on the falling edge of each SCK. Zero dummy cycles means the returning data is driven by the memory on the same falling edge of SCK that the host stops driving address or mode bits.

The DDR commands may optionally have an 8-edge Data Learning Pattern (DLP) driven by the memory, on all data outputs, in the dummy cycles immediately before the start of data. The DLP can help the host memory controller determine the phase shift from SCK to data edges so that the memory controller can capture data at the center of the data eye.

When using SDR I/O commands at higher SCK frequencies (>50 MHz), an LC that provides one or more dummy cycles should be selected to allow additional time for the host to stop driving before the memory starts driving data, to minimize I/O driver conflict. When using DDR I/O commands with the DLP enabled, an LC that provides five or more dummy cycles should be selected to allow one cycle of additional time for the host to stop driving before the memory starts driving the 4 cycle DLP.

Each read command ends when CS# is returned HIGH at any point during data return. CS# must not be returned HIGH during the mode or dummy cycles before data returns as this may cause mode bits to be captured incorrectly; making it indeterminate as to whether the device remains in enhanced high performance read mode.

Commands

10.4.1 Read (Read 03h or 4READ 13h)

The instruction

- 03h (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- 03h (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- 13h is followed by a 4-byte address (A31–A0)

Then the memory contents, at the address given, are shifted out on IO1 and IO5. The maximum operating clock frequency for the READ command is 50 MHz.

The address can start at any byte location of the memory array. The address is automatically incremented to the next higher address in sequential order after each byte of data is shifted out. The entire memory can therefore be read out with one single read instruction and address 000000h provided. When the highest address is reached, the address counter will wrap around and roll back to 000000h, allowing the read sequence to be continued indefinitely.




Figure 53 Dual-Quad Read command sequence (READ 03h or 13h)

Note

45.A = MSB of address = 23 for command 03h, or 31 for command 13h.

Commands

10.4.2 Fast Read (FAST_READ 0Bh or 4FAST_READ 0Ch)

The instruction

- 0Bh (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- 0Bh (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- 0Ch is followed by a 4-byte address (A31-A0)

The address is followed by zero or eight dummy cycles depending on the latency code set in the Configuration Register. The dummy cycles allow the device internal circuits additional time for accessing the initial address location. During the dummy cycles the data value on IO1 and IO5 is 'don't care' and may be high impedance. Then the memory contents, at the address given, are shifted out on IO1 and IO5.

The maximum operating clock frequency for FAST READ command is 133 MHz.

The address can start at any byte location of the memory array. The address is automatically incremented to the next higher address in sequential order after each byte of data is shifted out. The entire memory can therefore be read out with one single read instruction and address 000000h provided. When the highest address is reached, the address counter will wrap around and roll back to 000000h, allowing the read sequence to be continued indefinitely.




Figure 54 Dual-Quad SPI Fast Read (FAST_READ) command sequence

Commands

10.4.3 Quad Output Read (QOR 6Bh or 4QOR 6Ch)

The instruction

- 6Bh (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- 6Bh (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- 6Ch is followed by a 4-byte address (A31-A0)

Then the memory contents, at the address given, is shifted out eight bits at a time through IOO–IO7. Each nibble (4 bits) is shifted out at the SCK frequency by the falling edge of the SCK signal.

The maximum operating clock frequency for Quad Output Read command is 104 MHz. For Quad Output Read Mode, there may be dummy cycles required after the last address bit is shifted into SI before data begins shifting out of IOO–IO3. This latency period (i.e., dummy cycles) allows the device's internal circuitry enough time to set up for the initial address. During the dummy cycles, the data value on IOO–IO7 is 'don't care' and may be high impedance. The number of dummy cycles is determined by the frequency of SCK (refer to **Table 19**).

The address can start at any byte location of the memory array. The address is automatically incremented to the next higher address in sequential order after each byte of data is shifted out. The entire memory can therefore be read out with one single read instruction and address 000000h provided. When the highest address is reached, the address counter will wrap around and roll back to 000000h, allowing the read sequence to be continued indefinitely.




Figure 55 Dual-Quad, Quad Output Read (QOR 6Bh or 4QOR 6Ch) command sequence

Note

46.A = MSB of address = 23 for command 6Bh, or 31 for command 6Ch.

infineon

Commands

10.4.4 Quad I/O Read (QIOR EBh or 4QIOR ECh)

The instruction

- EBh (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- EBh (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- ECh is followed by a 4-byte address (A31-A0)

The Quad I/O Read command improves throughput with eight I/O signals — IOO–IO7. It is similar to the Quad Output Read command but allows input of the address bits eight bits per serial SCK clock. In some applications, the reduced instruction overhead might allow for code execution (XIP) directly from the S79FL01GS device.

The maximum operating clock frequency for Quad I/O Read is 104 MHz.

For the Quad I/O Read command, there is a latency required after the mode bits (described below) before data begins shifting out of IOO–IO7. This latency period (i.e., dummy cycles) allows the device's internal circuitry enough time to access data at the initial address. During latency cycles, the data value on IOO–IO7 are 'don't care' and may be high impedance. The number of dummy cycles is determined by the frequency of SCK and the latency code table (refer to **Table 19**). The number of dummy cycles is set by the LC bits in the Configuration Register (CR1). However, both latency code tables use the same latency values for the Quad I/O Read command.

Following the latency period, the memory contents at the address given, is shifted out eight bits at a time through IOO–IO7. Each byte (8 bits) is shifted out at the SCK frequency by the falling edge of the SCK signal.

The address can start at any byte location of the memory array. The address is automatically incremented to the next higher address in sequential order after each byte of data is shifted out. The entire memory can therefore be read out with one single read instruction and address 000000h provided. When the highest address is reached, the address counter will wrap around and roll back to 000000h, allowing the read sequence to be continued indefinitely.

Address jumps can be done without the need for additional Quad I/O Read instructions. This is controlled through the setting of the Mode bits (after the address sequence, as shown in **Figure 56** or **Figure 57**). This added feature removes the need for the instruction sequence and greatly improves code execution (XIP). The upper nibble (bits 7–4) of the Mode bits control the length of the next Quad I/O instruction through the inclusion or exclusion of the first byte instruction code. The lower nibble (bits 3–0) of the Mode bits are 'don't care' (x). If the Mode bits equal Axh, then the device remains in Quad I/O High Performance Read Mode and the next address can be entered (after CS# is raised high and then asserted low) without requiring the EBh or ECh instruction, as shown in **Figure 56**; thus, eliminating eight cycles for the command sequence. The following sequences will release the device from Quad I/O High Performance Read mode; after which, the device can accept standard SPI commands:

1. During the Quad I/O Read Command Sequence, if the Mode bits are any value other than Axh, then the next time CS# is raised HIGH the device will be released from Quad I/O High Performance Read mode.

During any operation, if CS# toggles HIGH to LOW to high for eight cycles (or less) and data input (IO0–IO3) are not set for a valid instruction sequence, then the device will be released from Quad I/O High Performance Read mode. Note that the two mode bit clock cycles and additional wait states (i.e., dummy cycles) allow the device's internal circuitry latency time to access the initial address after the last address cycle that is clocked into IO0–IO3.

It is important that the IOO–IO7 signals be set to high-impedance at or before the falling edge of the first data out clock. At higher clock speeds the time available to turn off the host outputs before the memory device begins to drive (bus turn around) is diminished. It is allowed and may be helpful in preventing IOO–IO7 signal contention, for the host system to turn off the IOO–IO7 signal outputs (make them high impedance) during the last 'don't care' mode cycle or during any dummy cycles.

CS# should not be driven HIGH during mode or dummy bits as this may make the mode bits indeterminate.



Commands




Figure 56 Dual-Quad I/O Read command sequence (3-Byte Address, EBh [ExtAdd = 0], LC = 00b)




Figure 57 Dual-Quad Continuous Quad I/O Read command sequence (3-Byte Address), LC = 00b

Note

47.A = MSB of address = 23 for command EBh, or 31 for command ECh.

infineon

Commands

10.4.5 DDR Quad I/O Read (EDh, EEh)

The Read DDR Quad I/O command is similar to the Quad I/O Read command but allows input of the address four bits on every edge of the clock. In some applications, the reduced instruction overhead might allow for code execution (XIP) directly from the S79FL01GS device. The QUAD bit of the Configuration Register is set (CR[1] = 1) to enable the Quad capability in the S79FL01GS device.

The instruction

- EDh (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- EDh (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- EEh is followed by a 4-byte address (A31–A0)

The address is followed by mode bits. Then the memory contents, at the address given, is shifted out, in a DDR fashion, with four bits at a time on each clock edge through IO0–IO7.

The maximum operating clock frequency for Read DDR Quad I/O command is 80 MHz.

For Read DDR Quad I/O, there is a latency required after the last address and mode bits are shifted into the IOO–IO7 signals before data begins shifting out of IOO–IO7. This latency period (dummy cycles) allows the device's internal circuitry enough time to access the initial address. During these latency cycles, the data value on IOO–IO7 are 'don't care' and may be high impedance. When the Data Learning Pattern (DLP) is enabled the host system must not drive the IO signals during the dummy cycles. The IO signals must be left high impedance by the host so that the memory device can drive the DLP during the dummy cycles.

The number of dummy cycles is determined by the frequency of SCK. The number of dummy cycles is set by the LC bits in the Configuration Register (CR1).

Both latency tables provide cycles for mode bits so a series of Quad I/O DDR commands may eliminate the 8-bit instruction after the first command sends a complementary mode bit pattern, as shown in **Figure 58**. This feature removes the need for the eight bit SDR instruction sequence and dramatically reduces initial access times (improves XIP performance). The Mode bits control the length of the next Read DDR Quad I/O operation through the inclusion or exclusion of the first byte instruction code. If the upper nibble (IO[7:4]) and lower nibble (IO[3:0]) of the Mode bits are complementary (i.e. 5h and Ah) the device transitions to Continuous Read DDR Quad I/O Mode and the next address can be entered (after CS# is raised HIGH and then asserted LOW) without requiring the EDh or EEh instruction, as shown in **Figure 59** thus, eliminating eight cycles from the command sequence. The following sequences will release the device from Continuous Read DDR Quad I/O mode; after which, the device can accept standard SPI commands:

- 1. During the Read DDR Quad I/O Command Sequence, if the Mode bits are not complementary the next time CS# is raised HIGH and then asserted LOW the device will be released from Read DDR Quad I/O mode.
- 2. During any operation, if CS# toggles HIGH to LOW to HIGH for eight cycles (or less) and data input (IO0–IO7) are not set for a valid instruction sequence, then the device will be released from Read DDR Quad I/O mode.

The address can start at any byte location of the memory array. The address is automatically incremented to the next higher address in sequential order after each byte of data is shifted out. The entire memory can therefore be read out with one single read instruction and address 000000h provided. When the highest address is reached, the address counter will wrap around and roll back to 000000h, allowing the read sequence to be continued indefinitely.

CS# should not be driven HIGH during mode or dummy bits as this may make the mode bits indeterminate. The HOLD function is not valid during Quad I/O DDR commands.

Note that the memory devices drive the IOs with a preamble prior to the first data value. The preamble is a pattern that is used by the host controller to optimize data capture at higher frequencies. The preamble drives the IO bus for the four clock cycles immediately before data is output. The host must be sure to stop driving the IO bus prior to the time that the memory starts outputting the preamble.



Commands

The preamble is intended to give the host controller an indication about the round trip time from when the host drives a clock edge to when the corresponding data value returns from the memory device. The host controller will skew the data capture point during the preamble period to optimize timing margins and then use the same skew time to capture the data during the rest of the read operation. The optimized capture point will be determined during the preamble period of every read operation. This optimization strategy is intended to compensate for both the PVT (process, voltage, temperature) of both the memory device and the host controller as well as any system level delays caused by flight time on the PCB.

Although the data learning pattern (DLP) is programmable, the following example shows example of the DLP of 34h. The DLP 34h (or 00110100) will be driven on each of the active outputs (i.e. all eight IOs). This pattern was chosen to cover both DC and AC data transition scenarios. The two DC transition scenarios include data low for a long period of time (two half clocks) followed by a high going transition (001) and the complementary low going transition (110). The two AC transition scenarios include data low for a short period of time (one half clock) followed by a high going transition (101) and the complementary low going transition (010). The DC transitions will typically occur with a starting point closer to the supply rail than the AC transitions that may not have fully settled to their steady state (DC) levels. In many cases the DC transitions will bound the beginning of the data valid period and the AC transitions will bound the ending of the data valid period. These transitions will allow the host controller to identify the beginning and ending of the valid data eye. Once the data eye has been characterized the optimal data capture point can be chosen. See "SPI DDR Data Learning Registers" on page 55 for more details.




Figure 58 Dual-Quad SPI DDR Quad I/O Read Initial Access

Notes

48.A = MSB of address = 23 for command EDh, or 31 for command EEh. 49.Example DLP of 34h (or 00110100).



Commands




Figure 59 Dual-Quad Continuous DDR Quad I/O Read Subsequent Access

Notes

50.A = MSB of address = 23 for command EDh, or 31 for command EEh. 51.Example DLP of 34h (or 00110100).

infineon

Commands

10.5 Program Flash Array commands

10.5.1 Program granularity

10.5.1.1 Automatic ECC

Each 16 byte aligned and 16 byte length Programming Block has a hidden error correction code (ECC) value. The data block plus ECC form an ECC unit. In combination with EDC logic the ECC is used to detect and correct any single bit error found during a read access. When data is first programmed within an ECC unit the ECC value is set for the entire ECC unit. If the same ECC unit is programmed more than once the ECC value is changed to disable the error detection and correction (EDC) function. A sector erase is needed to again enable Automatic ECC on that Programming Block. The 16 byte Program Block is the smallest program granularity on which Automatic ECC is enabled.

These are automatic operations transparent to the user. The transparency of the Automatic ECC feature enhances data accuracy for typical programming operations which write data once to each ECC unit but, facilitates software compatibility to previous generations of FL-S family of products by allowing for single byte programming and bit walking in which the same ECC unit is programmed more than once. When an ECC unit has Automatic ECC disabled, EDC is not done on data read from the ECC unit location.

An ECC status register is provided for determining if ECC is enabled on an ECC unit and whether any errors have been detected and corrected in the ECC unit data or the ECC (See "ECC Status Register (ECCSR)" on page 52.) The ECC Status Register Read (ECCRD) command is used to read the ECC status on any ECC unit.

EDC is applied to all parts of the Flash address spaces other than registers. An ECC is calculated for each group of bytes protected and the ECC is stored in a hidden area related to the group of bytes. The group of protected bytes and the related ECC are together called an ECC unit.

ECC is calculated for each 16 byte aligned and length ECC unit.

- Single Bit EDC is supported with 8 ECC bits per ECC unit, plus 1-bit for an ECC disable Flag.
- Sector erase resets all ECC bits and ECC disable flags in a sector to the default state (enabled).
- ECC is programmed as part of the standard Program commands operation.
- ECC is disabled automatically if multiple programming operations are done on the same ECC unit.
- Single byte programming or bit walking is allowed but disables ECC on the second program to the same 16-byte ECC unit.
- The ECC disable flag is programmed when ECC is disabled.
- To re-enable ECC for an ECC unit that has been disabled, the Sector that includes the ECC unit must be erased.
- To ensure the best data integrity provided by EDC, each ECC unit should be programmed only once so that ECC is stored for that unit and not disabled.
- The calculation, programming, and disabling of ECC is done automatically as part of a programming operation. The detection and correction, if needed, is done automatically as part of read operations. The host system sees only corrected data from a read operation.
- ECC protects the OTP region however a second program operation on the same ECC unit will disable ECC permanently on that ECC unit (OTP is one time programmable, hence an erase operation to re-enable the ECC enable/indicator bit is prohibited).

Commands

10.5.1.2 Page programming

Page programming is done by loading a Page Buffer with data to be programmed and issuing a programming command to move data from the buffer to the memory array. This sets an upper limit on the amount of data that can be programmed with a single programming command. Page programming allows up to a page size (1024 bytes) to be programmed in one operation. The page is aligned on the page size address boundary. It is possible to program from one bit up to a page size in each Page programming operation. It is recommended that a multiple of 16 byte length and aligned Program Blocks be written. For the very best performance, programming should be done in full pages of 512 bytes aligned on 512-byte boundaries with each Page being programmed only once.

10.5.1.3 Single byte programming

Single byte programming allows full backward compatibility to the standard SPI page programming (PP) command by allowing a single byte to be programmed anywhere in the memory array.

10.5.2 Page Program (PP 02h or 4PP 12h)

The Page Program (PP) commands allows bytes to be programmed in the memory (changing bits from '1' to '0'). Before the Page Program (PP) commands can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device. After the Write Enable (WREN) command has been decoded successfully, the device sets the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The instruction

- 02h (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- 02h (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- 12h is followed by a 4-byte address (A31–A0)

and at least one data byte on IO0 and IO4. Up to a page can be provided on IO0 and IO4 after the 3-byte address with instruction 02h or 4-byte address with instruction 12h has been provided. If the 9 least significant address bits (A8–A0) are not all zero, all transmitted data that goes beyond the end of the current page are programmed from the start address of the same page (from the address whose 9 least significant bits (A8–A0) are all zero) i.e. the address wraps within the page aligned address boundaries. This is a result of only requiring the user to enter one single page address to cover the entire page boundary.

If less than a page of data is sent to the device, these data bytes will be programmed in sequence, starting at the provided address within the page, without having any affect on the other bytes of the same page.

For optimized timings, using the Page Program (PP) command to load the entire page size program buffer within the page boundary will save overall programming time versus loading less than a page size into the program buffer.

The programming process is managed by the flash memory device internal control logic. After a programming command is issued, the programming operation status can be checked using the Read Status Register 1 command. The WIP bit (SR1[0]) will indicate when the programming operation is completed. The P_ERR bit (SR1[6]) will indicate if an error occurs in the programming operation that prevents successful completion of programming.




Figure 60 Dual-Quad Page Program (PP 02h or 4PP 12h) command sequence

Commands

10.5.3 Quad Page Program (QPP 32h or 38h, or 4QPP 34h)

The Quad-input Page Program (QPP) command allows bytes to be programmed in the memory (changing bits from '1' to '0'). The Quad-input Page Program (QPP) command allows up to a page size (512 bytes) of data to be loaded into the Page Buffer using eight signals: IO0–IO7. QPP can improve performance for PROM Programmer and applications that have slower clock speeds (< 12 MHz) by loading 8 bits of data per clock cycle. Systems with faster clock speeds do not realize as much benefit for the QPP command since the inherent page program time becomes greater than the time it takes to clock-in the data. The maximum frequency for the QPP command is 80 MHz.

To use Quad Page Program the Quad Enable Bit in the Configuration Register must be set (QUAD = 1). A Write Enable command must be executed before the device will accept the QPP command (Status Register-1, WEL = 1). The instruction

- 32h (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- 32h (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- 38h (ExtAdd = 0) is followed by a 3-byte address (A23-A0) or
- 38h (ExtAdd = 1) is followed by a 4-byte address (A31-A0) or
- 34h is followed by a 4-byte address (A31-A0)

and at least two data bytes, into the IO signals. Data must be programmed at previously erased (FFh) memory locations.

QPP requires programming to be done one full page at a time. While less than a full page of data may be loaded for programming, the entire page is considered programmed, any locations not filled with data will be left as ones, the same page must not be programmed more than once.

All other functions of QPP are identical to Page Program. The QPP command sequence is shown in the Figure 61.




Figure 61 Dual-Quad, Quad Page Program command sequence

Note

52.A = MSB of address = A23 for PP 02h, or A31 for PP 02h, or for 4PP 12h.

Commands

10.5.4 Program Suspend (PGSP 85h) and Resume (PGRS 8Ah)

The Program Suspend command allows the system to interrupt a programming operation and then read from any other non-erase-suspended sector or non-program-suspended-page. Program Suspend is valid only during a programming operation.

Commands allowed after the Program Suspend command is issued:

- Read Status Register 1 (RDSR1 05h)
- Read Status Register 2 (RDSR2 07h)

The Write in Progress (WIP) bit in Status Register 1 (SR1[0]) must be checked to know when the programming operation has stopped. The Program Suspend Status bit in the Status Register 2 (SR2[0]) can be used to determine if a programming operation has been suspended or was completed at the time WIP changes to '0'. The time required for the suspend operation to complete is t_{PSL} , see **Table 43**.

See **Table 41** for the commands allowed while programming is suspend.

The Program Resume command 8Ah must be written to resume the programming operation after a Program Suspend. If the programming operation was completed during the suspend operation, a resume command is not needed and has no effect if issued. Program Resume commands will be ignored unless a Program operation is suspended.

After a Program Resume command is issued, the WIP bit in the Status Register 1 will be set to '1' and the programming operation will resume. Program operations may be interrupted as often as necessary e.g. a program suspend command could immediately follow a program resume command but, in order for a program operation to progress to completion there must be some periods of time between resume and the next suspend command greater than or equal to t_{PRS}. See **Table 43**.




Figure 62 Dual-Quad Program Suspend command sequence




Figure 63 Dual_Quad Program Resume command sequence

Commands

10.6 Erase Flash Array commands

10.6.1 Sector Erase (SE D8h or 4SE DCh)

The Sector Erase (SE) command sets all bits in the addressed sector to '1' (all bytes are FFh). Before the Sector Erase (SE) command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device, which sets the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The instruction

- D8h [ExtAdd = 0] is followed by a 3-byte address (A23-A0), or
- D8h [ExtAdd = 1] is followed by a 4-byte address (A31-A0), or
- DCh is followed by a 4-byte address (A31-A0)

CS# must be driven into the logic HIGH state after the twenty-fourth or thirty-second bit of address has been latched in on IOO and IO4. This will initiate the erase cycle, which involves the pre-programming and erase of the chosen sector. If CS# is not driven HIGH after the last bit of address, the sector erase operation will not be executed.

As soon as CS# is driven into the logic HIGH state, the internal erase cycle will be initiated. With the internal erase cycle in progress, the user can read the value of the Write-In Progress (WIP) bit to check if the operation has been completed. The WIP bit will indicate '1' when the erase cycle is in progress and '0' when the erase cycle has been completed.

A Sector Erase (SE) command applied to a sector that has been Write Protected through the Block Protection bits or ASP, will not be executed and will set the E_ERR status.

ASP has a PPB and a DYB protection bit for each sector.




Figure 64 Dual-Quad Sector Erase (SE 20h or 4SE 21h) command sequence

Commands

10.6.2 Bulk Erase (BE 60h or C7h)

The Bulk Erase (BE) command sets all bits to '1' (all bytes are FFh) inside the entire flash memory array. Before the BE command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device, which sets the Write Enable Latch (WEL) in the Status Register to enable any write operations.

CS# must be driven into the logic HIGH state after the eighth bit of the instruction byte has been latched in on IOO and IO4. This will initiate the erase cycle, which involves the pre-programming and erase of the entire flash memory array. If CS# is not driven HIGH after the last bit of instruction, the BE operation will not be executed.

As soon as CS# is driven into the logic HIGH state, the erase cycle will be initiated. With the erase cycle in progress, the user can read the value of the Write-In Progress (WIP) bit to determine when the operation has been completed. The WIP bit will indicate '1' when the erase cycle is in progress and '0' when the erase cycle has been completed.

A BE command can be executed only when the Block Protection (BP2, BP1, BP0) bits are set to 0's. If the BP bits are not '0', the BE command is not executed and E_ERR is not set. The BE command will skip any sectors protected by the DYB or PPB and the E_ERR status will not be set.




Figure 65 Bulk Erase command sequence

infineon

Commands

10.6.3 Erase Suspend and Resume commands (ERSP 75h or ERRS 7Ah)

The Erase Suspend command, allows the system to interrupt a sector erase operation and then read from or program data to, any other sector. Erase Suspend is valid only during a sector erase operation. The Erase Suspend command is ignored if written during the Bulk Erase operation.

When the Erase Suspend command is written during the sector erase operation, the device requires a maximum of t_{ESL} (erase suspend latency) to suspend the erase operation and update the status bits. See **Table 44**.

Commands allowed after the Erase Suspend command is issued:

- Read Status Register 1 (RDSR1 05h)
- Read Status Register 2 (RDSR2 07h)

The Write in Progress (WIP) bit in Status Register 1 (SR1[0]) must be checked to know when the erase operation has stopped. The Erase Suspend bit in Status Register 2 (SR2[1]) can be used to determine if an erase operation has been suspended or was completed at the time WIP changes to '0'.

If the erase operation was completed during the suspend operation, a resume command is not needed and has no effect if issued. Erase Resume commands will be ignored unless an Erase operation is suspended.

See **Table 41** for the commands allowed while erase is suspend.

After the erase operation has been suspended, the sector enters the erase-suspend mode. The system can read data from or program data to the device. Reading at any address within an erase-suspended sector produces undetermined data.

A WREN command is required before any command that will change nonvolatile data, even during erase suspend.

The WRR and PPB Erase commands are not allowed during Erase Suspend, it is therefore not possible to alter the Block Protection or PPB bits during Erase Suspend. If there are sectors that may need programming during Erase suspend, these sectors should be protected only by DYB bits that can be turned off during Erase Suspend. However, WRR is allowed immediately following the BRAC command; in this special case the WRR is interpreted as a write to the Bank Address Register, not a write to SR1 or CR1.

If a program command is sent for a location within an erase suspended sector the program operation will fail with the P_ERR bit set.

After an erase-suspended program operation is complete, the device returns to the erase-suspend mode. The system can determine the status of the program operation by reading the WIP bit in the Status Register, just as in the standard program operation.

The Erase Resume command 7Ah must be written to resume the erase operation if an Erase is suspend. Erase Resume commands will be ignored unless an Erase is Suspend.

After an Erase Resume command is sent, the WIP bit in the status register will be set to '1' and the erase operation will continue. Further Resume commands are ignored.

Erase operations may be interrupted as often as necessary e.g. an erase suspend command could immediately follow an erase resume command but, in order for an erase operation to progress to completion there must be some periods of time between resume and the next suspend command greater than or equal to t_{ERS} . See **Table 44**.




Figure 66 Dual-Quad Erase Suspend command sequence

infineon

Commands




Figure 67 Dual-Quad Erase Resume command sequence

Table 41 Commands allowed during Program or Erase Suspend

| Instruction name | Instruction Code (Hex) | Allowed during erase suspend | Allowed during program suspend | Comment |
|------------------|------------------------------|------------------------------------|--------------------------------|--|
| BRAC | B9 | X | Х | Bank address register may need to be changed during a suspend to reach a sector for read or program. |
| BRRD | 16 | X | Х | Bank address register may need to be changed during a suspend to reach a sector for read or program. |
| BRWR | 17 | X | Х | Bank address register may need to be changed during a suspend to reach a sector for read or program. |
| CLSR | 30 | Х | - | Clear status may be used if a program operation fails during erase suspend. |
| DYBRD | E0 | X | - | It may be necessary to remove and restore dynamic protection during erase suspend to allow programming during erase suspend. |
| DYBWR | E1 | X | _ | It may be necessary to remove and restore dynamic protection during erase suspend to allow programming during erase suspend. |
| ERRS | 7A | Х | | Required to resume from erase suspend. |
| FAST_READ | 0B | Х | X | All array reads allowed in suspend. |
| 4FAST_READ | 0C | Х | Х | All array reads allowed in suspend. |
| MBR | FF | Х | Х | May need to reset a read operation during suspend. |
| PGRS | 8A | Х | Х | Needed to resume a program operation. A program resume may also be used during nested program suspend within an erase suspend. |
| PGSP | 85 | Х | - | Program suspend allowed during erase suspend. |
| PP | 02 | Х | - | Required for array program during erase suspend. |
| 4PP | 12 | Х | - | Required for array program during erase suspend. |

Commands

Table 41 **Commands allowed during Program or Erase Suspend (Continued)**

| Instruction name | Instruction Code (Hex) | Allowed during erase suspend | Allowed during program suspend | Comment |
|------------------|------------------------------|------------------------------------|--------------------------------|---|
| PPBRD | E2 | X | _ | Allowed for checking persistent protection before attempting a program command during erase suspend. |
| QPP | 32, 38 | X | - | Required for array program during erase suspend. |
| 4QPP | 34 | Х | - | Required for array program during erase suspend. |
| 4READ | 13 | Х | X | All array reads allowed in suspend. |
| RDCR | 35 | Х | X | - |
| DDRQIOR | ED | Х | X | All array reads allowed in suspend. |
| DDRQIOR4 | EE | Х | X | All array reads allowed in suspend. |
| QIOR | EB | Х | X | All array reads allowed in suspend. |
| 4QIOR | EC | Х | X | All array reads allowed in suspend. |
| QOR | 6B | Х | X | All array reads allowed in suspend. |
| 4QOR | 6C | Х | X | All array reads allowed in suspend. |
| RDSR1 | 05 | Х | Х | Needed to read WIP to determine end of suspend process. |
| RDSR2 | 07 | X | Х | Needed to read suspend status to determine whether the operation is suspended or complete. |
| READ | 03 | Х | X | All array reads allowed in suspend. |
| RESET | F0 | Х | X | Reset allowed anytime. |
| WREN | 06 | Х | | Required for program command within erase suspend. |
| WRR | 01 | Х | Х | Bank register may need to be changed during a suspend to reach a sector needed for read or program. WRR is allowed when following BRAC. |

10.7 **One Time Program Array commands**

OTP Program (OTPP 42h) 10.7.1

The OTP Program command programs data in the One Time Program region, which is in a different address space from the main array data. The OTP region is 2048 bytes so, the address bits from A25 to A10 must be zero for this command. Refer to "OTP address space" on page 42 for details on the OTP region. The protocol of the OTP Program command is the same as the Page Program command. Before the OTP Program command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device, which sets the Write Enable Latch (WEL) in the Status Register to enable any write operations.

To program the OTP array in bit granularity, the rest of the bits within a data byte can be set to '1'.

Each region in the OTP memory space can be programmed one or more times, provided that the region is not locked. Attempting to program zeros in a region that is locked will fail with the P_ERR bit in SR1 set to '1' Programming ones, even in a protected area does not cause an error and does not set P_ERR. Subsequent OTP programming can be performed only on the un-programmed bits (that is, 1 data). The protocol of the OTP Program command is the same as the Page Program command. See "Page Program (PP 02h or 4PP 12h)" on page 93 for the command sequence.

Commands

10.7.2 OTP Read (OTPR 4Bh)

The OTP Read command reads data from the OTP region. The OTP region is 2048 bytes so, the address bits from A25 to A10 must be zero for this command. Refer to "OTP address space" on page 42 for details on the OTP region. The protocol of the OTP Read command is similar to the Fast Read command except that it will not wrap to the starting address after the OTP address is at its maximum; instead, the data beyond the maximum OTP address will be undefined. Also, the OTP Read command is not affected by the latency code. The OTP read command always has one dummy byte of latency as shown in Figure 68.




Figure 68 Read OTP (OTPR 4Bh) command sequence

Commands

10.8 Advanced Sector Protection commands

10.8.1 ASP Read (ASPRD 2Bh)

The ASP Read instruction 2Bh is shifted into SI by the rising edge of the SCK signal. Then the 16-bit ASP register contents is shifted out on the serial output SO, least significant byte first. Each bit is shifted out at the SCK frequency by the falling edge of the SCK signal. It is possible to read the ASP register continuously by providing multiples of 16 clock cycles. The maximum operating clock frequency for the ASP Read (ASPRD) command is 133 MHz.




Figure 69 Dual-Quad SPI ASPRD command sequence

10.8.2 ASP Program (ASPP 2Fh)

Before the ASP Program (ASPP) command can be accepted by the device, a Write Enable (WREN) command must be issued. After the Write Enable (WREN) command has been decoded, the device will set the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The ASPP command is entered by driving CS# to the logic LOW state, followed by the instruction and two data bytes on SI, least significant byte first. The ASP Register is two data bytes in length.

 $The ASPP command affects the P_ERR and WIP bits of the Status and Configuration Registers in the same manner as any other programming operation.\\$

CS# input must be driven to the logic HIGH state after the sixteenth bit of data has been latched in. If not, the ASPP command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed ASPP operation is initiated. While the ASPP operation is in progress, the Status Register may be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed ASPP operation, and is '0' when it is completed. When the ASPP operation is completed, the Write Enable Latch (WEL) is set to '0'.




Figure 70 ASPP (2Fh) command

Commands

10.8.3 DYB Read (DYBRD E0h)

The instruction E0h is latched into SI by the rising edge of the SCK signal. Followed by the 32-bit address selecting location zero within the desired sector (note, the high order address bits not used by a particular density device must be zero). Then the 8-bit DYB access register contents are shifted out on the serial output SO. Each bit is shifted out at the SCK frequency by the falling edge of the SCK signal. It is possible to read the same DYB access register continuously by providing multiples of eight clock cycles. The address of the DYB register does not increment so this is not a means to read the entire DYB array. Each location must be read with a separate DYB Read command. The maximum operating clock frequency for READ command is 133 MHz.




Figure 71 DYBRD command sequence

10.8.4 DYB Write (DYBWR E1h)

Before the DYB Write (DYBWR) command can be accepted by the device, a Write Enable (WREN) command must be issued. After the Write Enable (WREN) command has been decoded, the device will set the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The DYBWR command is entered by driving CS# to the logic LOW state, followed by the instruction, the 32-bit address selecting location zero within the desired sector (note, the high order address bits not used by a particular density device must be zero), then the data byte on SI. The DYB Access Register is one data byte in length.

The DYBWR command affects the P_ERR and WIP bits of the Status and Configuration Registers in the same manner as any other programming operation. CS# must be driven to the logic HIGH state after the eighth bit of data has been latched in. If not, the DYBWR command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed DYBWR operation is initiated. While the DYBWR operation is in progress, the Status Register may be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed DYBWR operation, and is '0' when it is completed. When the DYBWR operation is completed, the Write Enable Latch (WEL) is set to '0'.




Figure 72 DYBWR (E1h) command sequence

Commands

10.8.5 PPB Read (PPBRD E2h)

The instruction E2h is shifted into SI by the rising edges of the SCK signal, followed by the 32-bit address selecting location zero within the desired sector (note, the high order address bits not used by a particular density device must be zero) Then the 8-bit PPB access register contents are shifted out on SO.

It is possible to read the same PPB access register continuously by providing multiples of eight clock cycles. The address of the PPB register does not increment so this is not a means to read the entire PPB array. Each location must be read with a separate PPB Read command. The maximum operating clock frequency for the PPB Read command is 133 MHz.




Figure 73 PPBRD (E2h) command sequence

10.8.6 PPB Program (PPBP E3h)

Before the PPB Program (PPBP) command can be accepted by the device, a Write Enable (WREN) command must be issued. After the Write Enable (WREN) command has been decoded, the device will set the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The PPBP command is entered by driving CS# to the logic LOW state, followed by the instruction, followed by the 32-bit address selecting location zero within the desired sector (note, the high order address bits not used by a particular density device must be zero).

The PPBP command affects the P_ERR and WIP bits of the Status and Configuration Registers in the same manner as any other programming operation.

CS# must be driven to the logic HIGH state after the last bit of address has been latched in. If not, the PPBP command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed PPBP operation is initiated. While the PPBP operation is in progress, the Status Register may be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed PPBP operation, and is '0' when it is completed. When the PPBP operation is completed, the Write Enable Latch (WEL) is set to '0'.




Figure 74 PPBP (E3h) command sequence

Commands

10.8.7 PPB Erase (PPBE E4h)

The PPB Erase (PPBE) command sets all PPB bits to '1'. Before the PPB Erase command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device, which sets the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The instruction E4h is shifted into SI by the rising edges of the SCK signal.

CS# must be driven into the logic HIGH state after the eighth bit of the instruction byte has been latched in on SI. This will initiate the beginning of internal erase cycle, which involves the pre-programming and erase of the entire PPB memory array. Without CS# being driven to the logic HIGH state after the eighth bit of the instruction, the PPB erase operation will not be executed.

With the internal erase cycle in progress, the user can read the value of the Write-In Progress (WIP) bit to check if the operation has been completed. The WIP bit will indicate '1', when the erase cycle is in progress and '0', when the erase cycle has been completed. Erase suspend is not allowed during PPB Erase.




Figure 75 PPB Erase (PPBE E4h) command sequence

10.8.8 PPB Lock Bit Read (PLBRD A7h)

The PPB Lock Bit Read (PLBRD) command allows the PPB Lock Register contents to be read out of SO. It is possible to read the PPB lock register continuously by providing multiples of eight clock cycles. The PPB Lock Register contents may only be read when the device is in standby state with no other operation in progress. It is recommended to check the Write-In Progress (WIP) bit of the Status Register before issuing a new command to the device.




Figure 76 PPB Lock Register Read command sequence

Commands

10.8.9 PPB Lock Bit Write (PLBWR A6h)

The PPB Lock Bit Write (PLBWR) command clears the PPB Lock Register to '0'. Before the PLBWR command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device, which sets the Write Enable Latch (WEL) in the Status Register to enable any write operations.

The PLBWR command is entered by driving CS# to the logic LOW state, followed by the instruction.

CS# must be driven to the logic HIGH state after the eighth bit of instruction has been latched in. If not, the PLBWR command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed PLBWR operation is initiated. While the PLBWR operation is in progress, the Status Register may still be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed PLBWR operation, and is '0' when it is completed. When the PLBWR operation is completed, the Write Enable Latch (WEL) is set to '0'. The maximum clock frequency for the PLBWR command is 133 MHz.




Figure 77 PPB Lock Bit Write (PLBWR A6h) command sequence

10.8.10 Password Read (PASSRD E7h)

The correct password value may be read only after it is programmed and before the Password Mode has been selected by programming the Password Protection Mode bit to '0' in the ASP Register (ASP[2]). After the Password Protection Mode is selected the PASSRD command is ignored.

The PASSRD command is shifted into SI. Then the 64-bit Password is shifted out on the serial output SO, least significant byte first, most significant bit of each byte first. Each bit is shifted out at the SCK frequency by the falling edge of the SCK signal. It is possible to read the Password continuously by providing multiples of 64 clock cycles. The maximum operating clock frequency for the PASSRD command is 133 MHz.




Figure 78 Password Read (PASSRD E7h) command sequence

Commands

10.8.11 Password Program (PASSP E8h)

Before the Password Program (PASSP) command can be accepted by the device, a Write Enable (WREN) command must be issued and decoded by the device. After the Write Enable (WREN) command has been decoded, the device sets the Write Enable Latch (WEL) to enable the PASSP operation.

The password can only be programmed before the Password Mode is selected by programming the Password Protection Mode bit to '0' in the ASP Register (ASP[2]). After the Password Protection Mode is selected the PASSP command is ignored.

The PASSP command is entered by driving CS# to the logic LOW state, followed by the instruction and the password data bytes on SI, least significant byte first, most significant bit of each byte first. The password is sixty-four (64) bits in length.

CS# must be driven to the logic HIGH state after the sixty-fourth (64th) bit of data has been latched. If not, the PASSP command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed PASSP operation is initiated. While the PASSP operation is in progress, the Status Register may be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed PASSP cycle, and is '0' when it is completed. The PASSP command can report a program error in the P_ERR bit of the status register. When the PASSP operation is completed, the Write Enable Latch (WEL) is set to '0'. The maximum clock frequency for the PASSP command is 133 MHz.




Figure 79 Password Program (PASSP E8h) command sequence

Commands

10.8.12 Password Unlock (PASSU E9h)

The PASSU command is entered by driving CS# to the logic LOW state, followed by the instruction and the password data bytes on SI, least significant byte first, most significant bit of each byte first. The password is sixty-four (64) bits in length.

CS# must be driven to the logic HIGH state after the sixty-fourth (64th) bit of data has been latched. If not, the PASSU command is not executed. As soon as CS# is driven to the logic HIGH state, the self-timed PASSU operation is initiated. While the PASSU operation is in progress, the Status Register may be read to check the value of the Write-In Progress (WIP) bit. The Write-In Progress (WIP) bit is '1' during the self-timed PASSU cycle, and is '0' when it is completed.

If the PASSU command supplied password does not match the hidden password in the Password Register, an error is reported by setting the P_ERR bit to '1'. The WIP bit of the status register also remains set to '1'. It is necessary to use the CLSR command to clear the status register, the RESET command to software reset the device, or drive the RESET# input LOW to initiate a hardware reset, in order to return the P_ERR and WIP bits to '0'. This returns the device to standby state, ready for new commands such as a retry of the PASSU command.

If the password does match, the PPB Lock bit is set to '1'. The maximum clock frequency for the PASSU command is 133 MHz.




Figure 80 Password Unlock (PASSU E9h) command sequence

infineon

Commands

10.9 Reset commands

10.9.1 Software Reset command (RESET F0h)

The Software Reset command (RESET) restores the device to its initial power up state, except for the volatile FREEZE bit in the Configuration register CR1[1] and the volatile PPB Lock bit in the PPB Lock Register. The Freeze bit and the PPB Lock bit will remain set at their last value prior to the software reset. To clear the FREEZE bit and set the PPB Lock bit to its protection mode selected power on state, a full power-on-reset sequence or hardware reset must be done. Note that the nonvolatile bits in the configuration register, TBPROT, TBPARM, and BPNV, retain their previous state after a Software Reset. The Block Protection bits BP2, BP1, and BP0, in the status register will only be reset if they are configured as volatile via the BPNV bit in the Configuration Register (CR1[3]) and FREEZE is cleared to '0'. The software reset cannot be used to circumvent the FREEZE or PPB Lock bit protection mechanisms for the other security configuration bits. The reset command is executed when CS# is brought to HIGH state and requires t_{RPH} time to execute.




Figure 81 Dual-Quad Software Reset (RESET F0h) command sequence

10.9.2 Mode Bit Reset (MBR FFh)

The Mode Bit Reset (MBR) command can be used to return the device from continuous high performance read mode back to normal standby awaiting any new command. Because some device packages lack a hardware RESET# input and a device that is in a continuous high performance read mode may not recognize any normal SPI command, a system hardware reset or software reset command may not be recognized by the device. It is recommended to use the MBR command after a system reset when the RESET# signal is not available or, before sending a software reset, to ensure the device is released from continuous high performance read mode.

The MBR command sends Ones on IO0 and IO4 for 8 SCK cycles. IO1–IO3 and IO5–IO7 are 'don't care' during these cycles.




Figure 82 Dual-Quad SPI Mode Bit (MBR FFh) Reset command sequence

infineon

Commands

10.10 Embedded algorithm performance tables

Table 42 Program and erase performance

| Symbol | Parameter | Min | Typ [53] | Max ^[54] | Unit |
|-----------------|--|-----|-----------------|------------------------------|------|
| t _W | WRR write time | _ | 560 | 2000 | ms |
| t _{PP} | Page programming (1024 bytes) | _ | 340 | 750/1300 ^[55, 56] | μs |
| t _{SE} | Sector erase time (512-kB logical sectors = 4 x 128-kB physical sectors) | - | 520 | 2600 | ms |
| t _{BE} | Bulk erase time | _ | 103 | 460 | sec |

Table 43 Program suspend AC parameters

| Parameter | Min | Тур | Max | Unit | Comments |
|---|------|-----|-----|------|---|
| Program Suspend Latency (t _{PSL}) | _ | - | 40 | μs | The time from Program Suspend command until the WIP bit is '0'. |
| Program Resume to next Program Suspend (t _{PRS}) | 0.06 | 100 | - | μs | Minimum is the time needed to issue the next Program Suspend command but ≥ typical periods are needed for Program to progress to completion |

Table 44 Erase suspend AC parameters

| Parameter | Min | Тур | Max | Unit | Comments |
|--|------|-----|-----|------|---|
| Erase Suspend Latency (t _{ESL}) | _ | _ | 45 | μs | The time from Erase Suspend command until the WIP bit is '0'. |
| Erase Resume to next Erase Suspend (t _{ERS)} | 0.06 | 100 | - | μs | Minimum is the time needed to issue the next Erase Suspend command but ≥ typical periods are needed for the Erase to progress to completion |

Notes

^{53.} Typical program and erase times assume the following conditions: 25° C, $V_{CC} = 3.0$ V; random data pattern. 54. Under worst case conditions of 90° C; 100,000 cycles max.

^{55.}Industrial temperature range / Industrial Plus temperature range.

^{56.} Maximum value also applies to OTPP, PPBP, ASPP, PASSP, ABWR, and PNVDLR programming commands.



Data integrity

11 Data integrity

11.1 Erase endurance

Table 45 Erase endurance

| Parameter | Minimum | Unit |
|---|---------|-----------|
| Program/erase cycles per main Flash array sectors | 100K | P/E cycle |
| Program/erase cycles per PPB array or nonvolatile register array [57] | 100K | P/E cycle |

11.2 Data retention

Table 46 Data retention

| Parameter | Test conditions | Minimum time | Unit |
|---------------------|---------------------------|--------------|-------|
| Data retention time | 10K program/erase cycles | 20 | Years |
| | 100K program/erase cycles | 2 | Years |

Note

57. Each write command to a nonvolatile register causes a P/E cycle on the entire nonvolatile register array. OTP bits and registers internally reside in a separate array that is not P/E cycled.

infineon

Software interface reference

12 Software interface reference

12.1 Serial flash discoverable parameters (SFDP) address map

The SFDP address space has a header starting at address zero that identifies the SFDP data structure and provides a pointer to each parameter. One Basic Flash parameter is mandated by the JEDEC JESD216B standard. Two optional parameter tables for Sector Map and 4 Byte Address Instructions follow the Basic Flash table. Infineon provides an additional parameter by pointing to the ID-CFI address space i.e. the ID-CFI address space is a sub-set of the SFDP address space. The parameter tables portion of the SFDP data structure are located within the ID-CFI address space and is thus both a CFI parameter and an SFDP parameter. In this way both SFDP and ID-CFI information can be accessed by either the RSFDP or RDID commands.

Table 47 SFDP overview map

| Byte address | Description |
|--------------|--|
| 0000h | Location zero within JEDEC JESD216B SFDP space — start of SFDP header |
| ,,, | Remainder of SFDP header followed by undefined space |
| 1000h | Location zero within ID-CFI space — start of ID-CFI parameter tables |
| ••• | ID-CFI parameters |
| 1120h | Start of SFDP parameter which is also one of the CFI parameter tables |
| | Remainder of SFDP parameter tables followed by either more CFI parameters or undefined space |

Software interface reference

12.1.1 **Field definitions**

Table 48 **SFDP** header

| Relative byte address | SFDPDword address | Data | Description |
|-----------------------|------------------------------------|------|---|
| 00h | SFDP Header | 53h | This is the entry point for Read SFDP (5Ah) command i.e. location zero within SFDP space ASCII "S" |
| 01h | 1st DWORD | 46h | ASCII "F" |
| 02h | | 44h | ASCII "D" |
| 03h | | 50h | ASCII "P" |
| 04h | SFDP Header 2nd DWORD | 06h | SFDP Minor Revision (06h = JEDEC JESD216 Revision B) This revision is backward compatible with all prior minor revisions. Minor revisions are changes that define previously reserved fields, add fields to the end, or that clarify definitions of existing fields. Increments of the minor revision value indicate that previously reserved parameter fields may have been assigned a new definition or entire Dwords may have been added to the parameter table. However, the definition of previously existing fields is unchanged and therefore remain backward compatible with earlier SFDP parameter table revisions. Software can safely ignore increments of the minor revision number, as long as only those parameters the software was designed to support are used i.e. previously reserved fields and additional Dwords must be masked or ignored. Do not do a simple compare on the minor revision number, looking only for a match with the revision number that the software is designed to handle. There is no problem with using a higher number minor revision. |
| 05h | | 01h | SFDP Major Revision This is the original major revision. This major revision is compatible with all SFDP reading and parsing software. |
| 06h | - | 05h | Number of Parameter Headers (zero based, 05h = 6 parameters) |
| 07h | = | FFh | Unused |
| 08h | Parameter | 00h | Parameter ID LSB (00h = JEDEC SFDP Basic SPI Flash Parameter) |
| 09h | Header 0 1st DWORD | 00h | Parameter Minor Revision (00h = JESD216) — This older revision parameter header is provided for any legacy SFDP reading and parsing software that requires seeing a minor revision 0 parameter header. SFDP software designed to handle later minor revisions should continue reading parameter headers looking for a higher numbered minor revision that contains additional parameters for that software revision. |
| 0Ah | | 01h | Parameter Major Revision (01h = The original major revision — all SFDP software is compatible with this major revision. |
| 0Bh | 1 | 09h | Parameter Table Length (in double words = Dwords = 4 byte units) 09h = 9 Dwords |
| 0Ch | Parameter Header 0 2nd DWORD | 20h | Parameter Table Pointer Byte 0 (Dword = 4 byte aligned) JEDEC Basic SPI Flash parameter byte offset = 1120h |
| 0Dh | | 11h | Parameter Table Pointer Byte 1 |
| 0Eh | | 00h | Parameter Table Pointer Byte 2 |
| 0Fh | | FFh | Parameter ID MSB (FFh = JEDEC defined legacy Parameter ID) |



SFDP header (Continued) Table 48

| Relative byte address | SFDPDword address | Data | Description |
|-----------------------|------------------------------------|------|--|
| 10h | Parameter | 00h | Parameter ID LSB (00h = JEDEC SFDP Basic SPI Flash Parameter) |
| 11h | Header 1 1st DWORD | 05h | Parameter Minor Revision (05h = JESD216 Revision A) — This older revision parameter header is provided for any legacy SFDP reading and parsing software that requires seeing a minor revision 5 parameter header. SFDP software designed to handle later minor revisions should continue reading parameter headers looking for a later minor revision that contains additional parameters. |
| 12h | | 01h | Parameter Major Revision (01h = The original major revision — all SFDP software is compatible with this major revision. |
| 13h | 1 | 10h | Parameter Table Length (in double words = Dwords = 4 byte units) 10h = 16 Dwords |
| 14h | Parameter Header 1 | 20h | Parameter Table Pointer Byte 0 (Dword = 4 byte aligned) JEDEC Basic SPI Flash parameter byte offset = 1120h address |
| 15h | 2nd DWORD | 11h | Parameter Table Pointer Byte 1 |
| 16h | | 00h | Parameter Table Pointer Byte 2 |
| 17h | | FFh | Parameter ID MSB (FFh = JEDEC defined Parameter) |
| 18h | Parameter Header 2 1st DWORD | 00h | Parameter ID LSB (00h = JEDEC SFDP Basic SPI Flash Parameter) |
| 19h | | 06h | Parameter Minor Revision (06h = JESD216 Revision B) |
| 1Ah | | 01h | Parameter Major Revision (01h = The original major revision - all SFDP software is compatible with this major revision. |
| 1Bh | | 10h | Parameter Table Length (in double words = Dwords = 4 byte units) 10h = 16 Dwords |
| 1Ch | Parameter Header 2 | 20h | Parameter Table Pointer Byte 0 (Dword = 4 byte aligned) JEDEC Basic SPI Flash parameter byte offset = 1120h address |
| 1Dh | 2nd DWORD | 11h | Parameter Table Pointer Byte 1 |
| 1Eh | | 00h | Parameter Table Pointer Byte 2 |
| 1Fh | | FFh | Parameter ID MSB (FFh = JEDEC defined Parameter) |
| 20h | Parameter | 81h | Parameter ID LSB (81h = SFDP Sector Map Parameter) |
| 21h | Header 3 1st DWORD | 00h | Parameter Minor Revision (00h = Initial version as defined in JESD216 Revision B) |
| 22h | | 01h | Parameter Major Revision (01h = The original major revision — all SFDP software that recognizes this parameter's ID is compatible with this major revision. |
| 23h | _ | 02h | Parameter Table Length (in double words = Dwords = 4 byte units) 02h = 2 Dwords |
| 24h | Parameter Header 3 | 60h | Parameter Table Pointer Byte 0 (Dword = 4 byte aligned) JEDEC parameter byte offset = 1160h |
| 25h | 2nd DWORD | 11h | Parameter Table Pointer Byte 1 |
| 26h | | 00h | Parameter Table Pointer Byte 2 |
| 27h |] | FFh | Parameter ID MSB (FFh = JEDEC defined Parameter) |



SFDP header (Continued) Table 48

| Table 40 | SEDE HEAUEI | (Continued) | |
|-----------------------|------------------------------------|-------------|--|
| Relative byte address | SFDPDword address | Data | Description |
| 28h | Parameter Header 4 1st DWORD | 84h | Parameter ID LSB (00h = SFDP 4 Byte Address Instructions Parameter) |
| 29h | | 00h | Parameter Minor Revision (00h = Initial version as defined in JESD216 Revision B) |
| 2Ah | | 01h | Parameter Major Revision (01h = The original major revision - all SFDP software that recognizes this parameter's ID is compatible with this major revision. |
| 2Bh | | 02h | Parameter Table Length (in double words = Dwords = 4 byte units) (2h = 2 Dwords) |
| 2Ch | Parameter Header 4 | 68h | Parameter Table Pointer Byte 0 (Dword = 4 byte aligned) JEDEC parameter byte offset = 1168h |
| 2Dh | 2nd DWORD | 11h | Parameter Table Pointer Byte 1 |
| 2Eh | | 00h | Parameter Table Pointer Byte 2 |
| 2Fh | | FFh | Parameter ID MSB (FFh = JEDEC defined Parameter) |
| 30h | Parameter Header 5 | 01h | Parameter ID LSB (Infineon Vendor Specific ID-CFI parameter) Legacy Manufacturer ID 01h = AMD / Infineon |
| 31h | 1st DWORD | 01h | Parameter Minor Revision (01h = ID-CFI updated with SFDP Rev B table) |
| 32h | | 01h | Parameter Major Revision (01h = The original major revision - all SFDP software that recognizes this parameter's ID is compatible with this major revision. |
| 33h | | 5Ch | Parameter Table Length (in double words = Dwords = 4 byte units) CFI starts at 1000h, the final SFDP parameter (CFI ID = A5) starts at 111Eh (SFDP starting point of 1120h - 2hB of CFI parameter header), for a length of 11EhB excluding the CFI A5 parameter. The final CFI A5 parameter adds an additional 52hB for a total of 11Eh + 82h = 170hB. 170hB/4 = 5Ch Dwords. |
| 34h | Parameter Header 5 2nd DWORD | 00h | Parameter Table Pointer Byte 0 (Dword = 4 byte aligned) Entry point for ID-CFI parameter is byte offset = 1000h relative to SFDP location zero. |
| 35h | | 10h | Parameter Table Pointer Byte 1 |
| 36h | | 00h | Parameter Table Pointer Byte 2 |
| 37h | | 01h | Parameter ID MSB (01h = JEDEC JEP106 Bank Number 1) |

infineon

Software interface reference

12.2 Device ID and Common Flash Interface (ID-CFI) address map

12.2.1 Field definitions

Table 49 Manufacturer and Device ID

| Byte address | Data | Description |
|--------------|---------------------------------|---|
| 00h | 01h | Manufacturer ID for Infineon |
| 01h | 79h | Device ID Most Significant Byte — Memory Interface Type |
| 02h | 21h | Device ID Least Significant Byte — Density |
| 03h | 4Eh | ID-CFI Length — number bytes following. Adding this value to the current location of 03h gives the address of the last valid location in the ID-CFI address map. A value of 00h indicates the entire 512-byte ID-CFI space must be read because the actual length of the ID-CFI information is longer than can be indicated by this legacy single byte field. The value is OPN dependent. |
| 04h | 00h (Uniform 512-kB sectors) | Sector Architecture |
| 05h | 80h (FL-S Family) | Family ID |
| 06h | xxh | ASCII characters for Model |
| 07h | xxh | Refer to "Ordering information" on page 139 for the model number definitions. |
| 08h | xxh | Reserved |
| 09h | xxh | Reserved |
| 0Ah | xxh | Reserved |
| 0Bh | xxh | Reserved |
| 0Ch | xxh | Reserved |
| 0Dh | xxh | Reserved |
| 0Eh | xxh | Reserved |
| 0Fh | xxh | Reserved |

Table 50 CFI query identification string

| Byte address | Data | Description |
|-------------------|-------------------|--|
| 10h 11h 12h | 51h 52h 59h | Query Unique ASCII string "QRY" |
| 13h 14h | 02h 00h | Primary OEM Command Set FL-P backward compatible command set ID |
| 15h 16h | 40h 00h | Address for Primary Extended Table |
| 17h 18h | 53h 46h | Alternate OEM Command Set ASCII characters "FS" for SPI (F) interface, S Technology |
| 19h 1Ah | 51h 00h | Address for Alternate OEM Extended Table |



Table 51 **CFI system interface string**

| Byte address | Data | Description |
|--------------|-----------------|---|
| 1Bh | 27h | V _{CC} Min. (erase/program): 100 millivolts |
| 1Ch | 36h | V _{CC} Max. (erase/program): 100 millivolts |
| 1Dh | 00h | V _{PP} Min. voltage (00h = no V _{PP} present) |
| 1Eh | 00h | V _{PP} Max. voltage (00h = no V _{PP} present) |
| 1Fh | 06h | Typical timeout per single byte program 2 ^N μs |
| 20h | 09h (512B page) | Typical timeout for Min. size Page program 2 ^N μs (00h = not supported) |
| 21h | 09h (512 kB) | Typical timeout per individual sector erase 2 ^N ms |
| 22h | 11h (1024 Mb) | Typical timeout for full chip erase 2 ^N ms (00h = not supported) |
| 23h | 02h | Max. timeout for byte program 2 ^N times typical |
| 24h | 02h | Max. timeout for page program 2 ^N times typical |
| 25h | 03h | Max. timeout per individual sector erase 2 ^N times typical |
| 26h | 03h | Max. timeout for full chip erase 2 ^N times typical (00h = not supported) |

Device geometry definition for 1024-Mbit device Table 52

| Byte address | Data | Description |
|--------------|---------------|--|
| 27h | 1Bh (1024 Mb) | Device Size = 2 ^N bytes; |
| 28h 29h | 03h 01h | Flash Device Interface Description; 0000h = x8 only 0001h = x16 only 0002h = x8/x16 capable 0003h = x32 only 0004h = Single I/O SPI, 3-byte address 0005h = Multi I/O SPI, 3-byte address 0102h = Multi I/O SPI, 3- or 4-byte address 0103h = Dual-Quad SPI, 3 or 4-byte address |
| 2Ah 2Bh | 0Ah 00h | Max. number of bytes in multi-byte write = 2 ^N (0000 = not supported 0009h = 512B page 000Ah = 1024B page) |
| 2Ch | 01h | Number of Erase Block Regions within device 1 = Uniform Device, 2 = Boot Device |
| 2Dh | FFh | Erase Block Region 1 Information (refer to JEDEC JEP137) |
| 2Eh | 00h | 256 sectors = 256-1 = 00FFh |
| 2Fh | 00h | 512-kB sectors = 256 bytes x 0800h |
| 30h | 08h | |
| 31h thru 3Fh | FFh | RFU |



CFI primary vendor-specific extended query Table 53

| Byte address | Data | Description |
|--------------|------|--|
| 40h | 50h | Query-unique ASCII string "PRI" |
| 41h | 52h | |
| 42h | 49h | |
| 43h | 31h | Major version number = 1, ASCII |
| 44h | 33h | Minor version number = 3, ASCII |
| 45h | 21h | Address Sensitive Unlock (Bits 1–0) 00b = Required 01b = Not Required Process Technology (Bits 5–2) 0000b = 0.23 μm Floating Gate 0001b = 0.17 μm Floating Gate 0010b = 0.23 μm MIRRORBIT TM 0011b = 0.11 μm Floating Gate 0100b = 0.11 μm MIRRORBIT TM 0101b = 0.09 μm MIRRORBIT TM 1000b = 0.065 μm MIRRORBIT TM |
| 46h | 02h | Erase Suspend 0 = Not Supported 1 = Read Only 2 = Read and Program |
| 47h | 01h | Sector Protect 00 = Not Supported X = Number of sectors in group |
| 48h | 00h | Temporary Sector Unprotect 00 = Not Supported 01 = Supported |
| 49h | 08h | Sector Protect/Unprotect Scheme 04 = High Voltage Method 05 = Software Command Locking Method 08 = Advanced Sector Protection Method 09 = Secure |
| 4Ah | 00h | Simultaneous Operation 00 = Not Supported X = Number of Sectors |
| 4Bh | 01h | Burst Mode (Synchronous sequential read) support 00 = Not Supported 01 = Supported |
| 4Ch | 05h | Page Mode Type, model dependent 00 = Not Supported 01 = 4 Word Read Page 02 = 8 Read Word Page 03 = 256-Byte Program Page 04 = 512-Byte Program Page 05 = 1024-Byte Program Page |
| 4Dh | 00h | ACC (Acceleration) Supply Minimum 00 = Not Supported, 100 mV |
| 4Eh | 00h | ACC (Acceleration) Supply Maximum 00 = Not Supported, 100 mV |

infineon

Software interface reference

Table 53 CFI primary vendor-specific extended query (Continued)

| Byte address | Data | Description |
|--------------|------|--|
| 4Fh | 00h | WP# Protection 00 = None 01 = Whole Chip 04 = Uniform Device with Bottom WP Protect 05 = Uniform Device with Top WP Protect 07 = Uniform Device with Top or Bottom Write Protect (user select) |
| 50h | 01h | Program Suspend 00 = Not Supported 01 = Supported |

The alternate vendor-specific extended query provides information related to the expanded command set provided by the S79FL-S family. The alternate query parameters use a format in which each parameter begins with an identifier byte and a parameter length byte. Driver software can check each parameter ID and can use the length value to skip to the next parameter if the parameter is not needed or not recognized by the software.

Table 54 CFI alternate vendor-specific extended query header

| Byte address | Data | Description |
|--------------|------|---------------------------------|
| 51h | 41h | Query-unique ASCII string "ALT" |
| 52h | 4Ch | |
| 53h | 54h | |
| 54h | 32h | Major version number = 2, ASCII |
| 55h | 30h | Minor version number = 0, ASCII |



CFI alternate vendor-specific extended query parameter 0 Table 55

| Parameter relative byte address offset | Data | Description |
|--|------------|--|
| 00h | 00h | Parameter ID (ordering part number) |
| 01h | 10h | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | 53h | ASCII "S" for manufacturer (Infineon) |
| 03h | 37h | ASCII "79" for Product Characters (Dual-Quad SPI) |
| 04h | 39h | |
| 05h | 46h | ASCII "FL" for Interface Characters (SPI 3 Volt) |
| 06h | 4Ch | |
| 07h | 30h (1 Gb) | ASCII characters for density |
| 08h | 31h (1 Gb) | |
| 09h | 47h (1 Gb) | |
| 0Ah | 53h | ASCII "S" for technology (65-nm MIRRORBIT™) |
| 0Bh | xxh | Reserved for Future Use (RFU) |
| 0Ch | xxh | |
| 0Dh | xxh | |
| 0Eh | xxh | |
| 0Fh | xxh | |
| 10h | xxh | |
| 11h | xxh | |

Table 56 CFI alternate vendor-specific extended query parameter 80h address options

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 00h | 80h | Parameter ID (ordering part number) |
| 01h | 01h | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | F0h | Bits 7:4 - Reserved = 1111b Bit 3 - AutoBoot support - Yes= 0b, No = 1b Bit 2 - 4-byte address instructions supported - Yes = 0b, No = 1b Bit 1 - Bank address + 3-byte address instructions supported - Yes = 0b, No = 1b Bit 0 - 3-byte address instructions supported - Yes = 0b, No = 1b |



Table 57 CFI alternate vendor-specific extended query parameter 84h suspend commands

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 00h | 84h | Parameter ID (Suspend Commands) |
| 01h | 08h | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | 85h | Program suspend instruction code |
| 03h | 28h | Program suspend latency maximum (μs) |
| 04h | 8Ah | Program resume instruction code |
| 05h | 64h | Program resume to next suspend typical (μs) |
| 06h | 75h | Erase suspend instruction code |
| 07h | 2Dh | Erase suspend latency maximum (μs) |
| 08h | 7Ah | Erase resume instruction code |
| 09h | 64h | Erase resume to next suspend typical (μs) |

Table 58 CFI alternate vendor-specific extended query parameter 88h data protection

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 00h | 88h | Parameter ID (Data Protection) |
| 01h | 04h | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | 0Bh | OTP size 2 ^N bytes, FFh = not supported |
| 03h | 01h | OTP address map format, 01h = FL-S format, FFh = not supported |
| 04h | xxh | Block Protect Type, model dependent 00h = FL-P, FL-S, FFh = not supported |
| 05h | 01h | Advanced Sector Protection type, model dependent 01h = FL-S ASP |

Table 59 CFI alternate vendor-specific extended query parameter 8Ch reset timing

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 00h | 8Ch | Parameter ID (Reset Timing) |
| 01h | 06h | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | 96h | POR maximum value |
| 03h | 01h | POR maximum exponent 2 ^N μs |
| 04h | 23h | Hardware Reset maximum value, FFh = not supported |
| 05h | 00h | Hardware Reset maximum exponent 2 ^N μs |
| 06h | 23h | Software Reset maximum value, FFh = not supported |
| 07h | 00h | Software Reset maximum exponent 2 ^N μs |

CFI alternate vendor-specific extended query parameter 90h — EHPLC (SDR) Table 60

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 00h | 90h | Parameter ID (Latency Code Table) |
| 01h | 56h | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | 06h | Number of rows |
| 03h | 0Eh | Row length in bytes |
| 04h | 46h | Start of header (row 1), ASCII "F" for frequency column header |
| 05h | 43h | ASCII "C" for Code column header |
| 06h | 03h | Read 3-byte address instruction |
| 07h | 13h | Read 4-byte address instruction |
| 08h | 0Bh | Read Fast 3-byte address instruction |
| 09h | 0Ch | Read Fast 4-byte address instruction |
| 0Ah | FFh | Read Dual Out 3-byte address instruction |
| 0Bh | FFh | Read Dual Out 3-byte address instruction |
| 0Ch | 6Bh | Read Quad Out 3-byte address instruction |
| 0Dh | 6Ch | Read Quad Out 4-byte address instruction |
| 0Eh | FFh | Dual I/O Read 3-byte address instruction |
| 0Fh | FFh | Dual I/O Read 4-byte address instruction |
| 10h | EBh | Quad I/O Read 3-byte address instruction |
| 11h | ECh | Quad I/O Read 4-byte address instruction |
| 12h | 32h | Start of row 2, SCK frequency limit for this row (50 MHz) |
| 13h | 03h | Latency Code for this row (11b) |
| 14h | 00h | Read mode cycles |
| 15h | 00h | Read latency cycles |
| 16h | 00h | Read Fast mode cycles |
| 17h | 00h | Read Fast latency cycles |
| 18h | FFh | Read Dual Out mode cycles |
| 19h | FFh | Read Dual Out mode cycles |
| 1Ah | 00h | Read Quad Out mode cycles |
| 1Bh | 00h | Read Quad Out latency cycles |
| 1Ch | FFh | Dual I/O Read mode cycles |
| 1Dh | FFh | Dual I/O Read latency cycles |
| 1Eh | 02h | Quad I/O Read mode cycles |
| 1Fh | 01h | Quad I/O Read latency cycles |
| 20h | 50h | Start of row 3, SCK frequency limit for this row (80 MHz) |
| 21h | 00h | Latency Code for this row (00b) |
| 22h | FFh | Read mode cycles (FFh = command not supported at this frequency) |
| 23h | FFh | Read latency cycles |

infineon

Table 60 CFI alternate vendor-specific extended query parameter 90h — EHPLC (SDR) (Continued)

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 24h | 00h | Read Fast mode cycles |
| 25h | 08h | Read Fast latency cycles |
| 26h | FFh | Read Dual Out mode cycles |
| 27h | FFh | Read Dual Out latency cycles |
| 28h | 00h | Read Quad Out mode cycles |
| 29h | 08h | Read Quad Out latency cycles |
| 2Ah | FFh | Dual I/O Read mode cycles |
| 2Bh | FFh | Dual I/O Read latency cycles |
| 2Ch | 02h | Quad I/O Read mode cycles |
| 2Dh | 04h | Quad I/O Read latency cycles |
| 2Eh | 5Ah | Start of row 4, SCK frequency limit for this row (90 MHz) |
| 2Fh | 01h | Latency Code for this row (01b) |
| 30h | FFh | Read mode cycles (FFh = command not supported at this frequency) |
| 31h | FFh | Read latency cycles |
| 32h | 00h | Read Fast mode cycles |
| 33h | 08h | Read Fast latency cycles |
| 34h | FFh | Read Dual Out mode cycles |
| 35h | FFh | Read Dual Out latency cycles |
| 36h | 00h | Read Quad Out mode cycles |
| 37h | 08h | Read Quad Out latency cycles |
| 38h | FFh | Dual I/O Read mode cycles |
| 39h | FFh | Dual I/O Read latency cycles |
| 3Ah | 02h | Quad I/O Read mode cycles |
| 3Bh | 04h | Quad I/O Read latency cycles |
| 3Ch | 68h | Start of row 5, SCK frequency limit for this row (104 MHz) |
| 3Dh | 02h | Latency Code for this row (10b) |
| 3Eh | FFh | Read mode cycles (FFh = command not supported at this frequency) |
| 3Fh | FFh | Read latency cycles |
| 40h | 00h | Read Fast mode cycles |
| 41h | 08h | Read Fast latency cycles |
| 42h | FFh | Read Dual Out mode cycles |
| 43h | FFh | Read Dual Out latency cycles |
| 44h | 00h | Read Quad Out mode cycles |
| 45h | 08h | Read Quad Out latency cycles |
| 46h | FFh | Dual I/O Read mode cycles |
| 47h | FFh | Dual I/O Read latency cycles |
| 48h | 02h | Quad I/O Read mode cycles |



Software interface reference

Table 60 CFI alternate vendor-specific extended query parameter 90h — EHPLC (SDR) (Continued)

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 49h | 05h | Quad I/O Read latency cycles |
| 4Ah | 85h | Start of row 6, SCK frequency limit for this row (133 MHz) |
| 4Bh | 02h | Latency Code for this row (10b) |
| 4Ch | FFh | Read mode cycles (FFh = command not supported at this frequency) |
| 4Dh | FFh | Read latency cycles |
| 4Eh | 00h | Read Fast mode cycles |
| 4Fh | 08h | Read Fast latency cycles |
| 50h | FFh | Read Dual Out mode cycles |
| 51h | FFh | Read Dual Out latency cycles |
| 52h | FFh | Read Quad Out mode cycles |
| 53h | FFh | Read Quad Out latency cycles |
| 54h | FFh | Dual I/O Read mode cycles |
| 55h | FFh | Dual I/O Read latency cycles |
| 56h | FFh | Quad I/O Read mode cycles |
| 57h | FFh | Quad I/O Read latency cycles |

Note:

FFh = Not supported.

CFI alternate vendor-specific extended query parameter 9Ah — EHPLC (DDR) Table 61

| Parameter relative byte address offset Data | | Description | | |
|---|-----|--|--|--|
| 00h | 9Ah | Parameter ID (Latency Code Table) | | |
| 01h | 2Ah | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) | | |
| 02h | 05h | Number of rows | | |
| 03h | 08h | Row length in bytes | | |
| 04h | 46h | Start of header (row 1), ASCII "F" for frequency column header | | |
| 05h | 43h | ASCII "C" for Code column header | | |
| 06h | FFh | Read Fast DDR 3-byte address instruction | | |
| 07h | FFh | Read Fast DDR 4-byte address instruction | | |
| 08h | FFh | DDR Dual I/O Read 3-byte address instruction | | |
| 09h | FFh | DDR Dual I/O Read 4-byte address instruction | | |
| 0Ah | EDh | Read DDR Quad I/O 3-byte address instruction | | |
| 0Bh | EEh | Read DDR Quad I/O 4-byte address instruction | | |
| 0Ch | 32h | Start of row 2, SCK frequency limit for this row (50 MHz) | | |
| 0Dh | 03h | Latency Code for this row (11b) | | |
| 0Eh | FFh | Read Fast DDR mode cycles | | |
| 0Fh | FFh | Read Fast DDR latency cycles | | |
| 10h | FFh | DDR Dual I/O Read mode cycles | | |
| 11h | FFh | DDR Dual I/O Read latency cycles | | |
| 12h | 01h | Read DDR Quad I/O mode cycles | | |
| 13h | 03h | Read DDR Quad I/O latency cycles | | |
| 14h | 50h | Start of row 3, SCK frequency limit for this row (80 MHz) | | |
| 15h | 00h | Latency Code for this row (00b) | | |
| 16h | FFh | Read Fast DDR mode cycles | | |
| 17h | FFh | Read Fast DDR latency cycles | | |
| 18h | FFh | DDR Dual I/O Read mode cycles | | |
| 19h | FFh | DDR Dual I/O Read latency cycles | | |
| 1Ah | 01h | Read DDR Quad I/O mode cycles | | |
| 1Bh | 06h | Read DDR Quad I/O latency cycles | | |
| 1Ch | FFh | Start of row 4, SCK frequency limit for this row (66 MHz) | | |
| 1Dh | FFh | Latency Code for this row (01b) | | |
| 1Eh | FFh | Read Fast DDR mode cycles | | |
| 1Fh | FFh | Read Fast DDR latency cycles | | |
| 20h | FFh | DDR Dual I/O Read mode cycles | | |
| 21h | FFh | DDR Dual I/O Read latency cycles | | |
| 22h | FFh | Read DDR Quad I/O mode cycles | | |
| 23h | FFh | Read DDR Quad I/O latency cycles | | |



Software interface reference

Table 61 CFI alternate vendor-specific extended query parameter 9Ah — EHPLC (DDR) (Continued)

| Parameter relative byte address offset | Data | Description | |
|--|------|---|--|
| 24h | FFh | Start of row 5, SCK frequency limit for this row (66 MHz) | |
| 25h | FFh | Latency Code for this row (10b) | |
| 26h | FFh | Read Fast DDR mode cycles | |
| 27h | FFh | Read Fast DDR latency cycles | |
| 28h | FFh | DDR Dual I/O Read mode cycles | |
| 29h | FFh | DDR Dual I/O Read latency cycles | |
| 2Ah | FFh | Read DDR Quad I/O mode cycles | |
| 2Bh | FFh | Read DDR Quad I/O latency cycles | |

Note:

FFh = Not supported.

infineon

Software interface reference

Table 62 CFI alternate vendor-specific extended query parameter F0h RFU

| Parameter relative byte address offset | Data | Description |
|--|------|--|
| 00h | F0h | Parameter ID (RFU) |
| 01h | 0Fh | Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | FFh | RFU |
| | FFh | RFU |
| 10h | FFh | RFU |

This parameter type (Parameter ID F0h) may appear multiple times and have a different length each time. The parameter is used to reserve space in the ID-CFI map or to force space (pad) to align a following parameter to a required boundary.

Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|--|------|--|
| 00h | _ | N/A | A5h | CFI Parameter ID (JEDEC SFDP) |
| 01h | _ | N/A | 50h | CFI Parameter Length (The number of following bytes in this parameter. Adding this value to the current location value + 1 = the first byte of the next parameter) |
| 02h | 00h | JEDEC Basic Flash Parameter Dword-1 | E7h | Start of SFDP JEDEC parameter, located at 1120h in the overall SFDP address space. Bits 7:5 = unused = 111b Bits 4:3 = 06h is status register write instruction and status register is default nonvolatile = 00b Bit 2 = Program Buffer > 64 bytes = 1 Bits 1:0 = Uniform 4-kB erase unavailable = 11b |
| 03h | 01h | | FFh | Bits 15:8 = Uniform 4-kB erase opcode = not supported = FFh |
| 04h | 02h | | EAh | Bit 23 = Unused = 1b Bit 22 = Supports Quad Out Read = Yes = 1b Bit 21 = Supports Quad I/O Read = Yes = 1b Bit 20 = Supports Dual I/O Read = Yes = 1b Bit19 = Supports DDR 0 = No, 1 = Yes Bits 18:17 = Number of Address Bytes, 3 or 4 = 01b Bit 16 = Supports Dual Out Read = Yes = 1b |
| 05h | 03h | | FFh | Bits 31:24 = unused = FFh |
| 06h | 04h | JEDEC Basic | FFh | Density in bits, zero based, 1 Gb = |
| 07h | 05h | Flash Parameter | FFh | 3FFFFFFh |
| 08h | 06h | Dword-2 | FFh | |
| 09h | 07h | | 3Fh | |



Software interface reference

Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CEI neversate: | CEDD marramata: | | 1. 71 | | | | | |
|--|---|--|-------|---|--|--|-----|--|
| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description | | | | |
| 0Ah | 08h | JEDEC Basic Flash Parameter Dword-3 | 44h | Bits 7:5 = number of Quad I/O Mode cycles = 010b Bits 4:0 = number of Quad I/O Dummy cycles = 00100b for default latency code 00b | | | | |
| 0Bh | 09h | | EBh | Quad I/O instruction code | | | | |
| 0Ch | 0Ah | | 08h | Bits 23:21 = number of Quad Out Mode cycles = 000b Bits 20:16 = number of Quad Out Dummy cycles = 01000b | | | | |
| 0Dh | 0Bh | | 6Bh | Quad Out instruction code | | | | |
| 0Eh | 0Ch | JEDEC Basic Flash Parameter Dword-4 | 00h | Bits 7:5 = number of Dual Out Mode cycles (not supported) = 000b Bits 4:0 = number of Dual Out Dummy cycles (not supported) = 00000b for default latency code | | | | |
| 0Fh | 0Dh | | FFh | Dual Out instruction code (not supported) = FFh | | | | |
| 10h | 0Eh | | | | | | 00h | Bits 23:21 = number of Dual I/O Mode cycles (not supported) = 000b for HPLC Bits 20:16 = number of Dual I/O Dummy cycles (not supported) = 00000b for EHPLC or 00100b for HPLC Default Latency code = 00b (not supported) |
| 11h | 0Fh | | FFh | Dual I/O instruction code (not supported) = FFh | | | | |
| 12h | 10h | JEDEC Basic Flash Parameter Dword-5 | EEh | Bits 7:5 RFU = 111b Bit 4 = QPI (supported) = No = 0b Bits 3:1 RFU = 111b Bit 0 = Dual All (not supported) = 0b | | | | |
| 13h | 11h | | FFh | Bits 15:8 = RFU = FFh | | | | |
| 14h | 12h | | FFh | Bits 23:16 = RFU = FFh | | | | |
| 15h | 13h | | FFh | Bits 31:24 = RFU = FFh | | | | |
| 16h | 14h | JEDEC Basic | FFh | Bits 7:0 = RFU = FFh | | | | |
| 17h | 15h | Flash Parameter | FFh | Bits 15:8 = RFU = FFh | | | | |
| 18h | 16h | - Parameter Dword-6 | 00h | Bits 23:21 = number of Dual All Mode cycles (not supported) = 000b Bits 20:16 = number of Dual All Dummy cycles (not supported) = 00000b | | | | |
| 19h | 17h | | FFh | Dual All instruction code (not supported) = FFh | | | | |



Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|------------------------|------|---|
| 1Ah | 18h | JEDEC Basic | FFh | Bits 7:0 = RFU = FFh |
| 1Bh | 19h | ☐ Flash — Parameter | FFh | Bits 15:8 = RFU = FFh |
| 1Ch | 1Ah | Dword-7 | 00h | Bits 23:21 = number of QPI cycles (not supported) = 000b Bits 20:16 = number of QPI Dummy cycles (not supported) = 00000b |
| 1Dh | 1Bh | | FFh | Bits 31:24 (4-4-4) (not supported) = FFh |
| 1Eh | 1Ch | JEDEC Basic Flash | 00h | Erase type 1 size 2 ^N bytes (not supported) = 00h |
| 1Fh | 1Dh | Parameter Dword-8 | FFh | Erase type 1 instruction (not supported) = FFh |
| 20h | 1Eh | | 00h | Erase type 2 size 2 ^N bytes (not supported) = 00h |
| 21h | 1Fh | | FFh | Erase type 2 instruction (not supported) = FFh |
| 22h | 20h | JEDEC Basic | 13h | Erase type 3 size 2 ^N bytes = 512 kB = 13h |
| 23h | 21h | ☐ Flash — Parameter | D8h | Erase type 3 instruction |
| 24h | 22h | Dword-9 | 00h | Erase type 4 size 2 ^N bytes (not supported) = 00h |
| 25h | 23h | | FFh | Erase type 4 instruction (not supported) = FFh |



Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|--------------------|------|--|
| 26h | 24h | JEDEC Basic | F2h | Bits 31:30 = Erase type 4 Erase, Typical time |
| 27h | 25h | Flash | FFh | units (00b: 1 ms, 01b: 16 ms, 10b: 128 ms, |
| 28h | 26h | Parameter Dword-10 | 0Fh | 11b: 1 s) = RFU = 11b Bits 29:25 = Erase type 4 Erase, Typical time |
| 29h | 27h | _ DWord-10 | FFh | count = RFU = 11111b (typical erase time = (count + 1) * units = RFU) Bits 24:23 = Erase type 3 Erase, Typical time units (00b: 1 ms, 01b: 16 ms, 10b: 128 ms, 11b: 1 s) = 128 ms = 10b Bits 22:18 = Erase type 3 Erase, Typical time count = 00011b (typical erase time = (count + 1) * units = 4*128 ms = 512 ms) Bits 17:16 = Erase type 2 Erase, Typical time units (00b: 1 ms, 01b: 16 ms, 10b: 128 ms, 11b: 1 s) = RFU = 11b Bits 15:11 = Erase type 2 Erase, Typical time count = RFU = 11111b (typical erase time = (count + 1) * units = RFU) Bits 10:9 = Erase type 1 Erase, Typical time units (00b: 1 ms, 01b: 16 ms, 10b: 128 ms, 11b: 1 s) = RFU = 11b Bits 8:4 = Erase type 1 Erase, Typical time count = RFU = 11111b (typical erase time = (count + 1) * units = RFU) Bits 3:0 = Multiplier from typical erase time to maximum erase time = 2*(N+1), N=2h = 6x multiplier Binary Fields: 11-1111-10-00011-11-11111-11111-1010 0 Nibble Format: 1111_1111_0000_1111_1111_1111_1111_0010 Hex Format: FF_0F_FF_F2 |



Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|-------------------------|---|---|
| 2Ah | 28h | JEDEC Basic | A1h | Bit 31 Reserved = 1b |
| 2Bh | 29h | Flash | 1/311 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 | Bits 30:29 = Chip Erase, Typical time units |
| 2Ch | 2Ah | - Parameter Dword-11 | 07h | (00b: 16 ms, 01b: 256 ms, 10b: 4 s, 11b: 64 s) = 4s = 10b |
| 2Dh | 2Bh | DWOI'd-II | D9h | Bits 28:24 = Chip Erase, Typical time count, (count + 1)* units, count = 11001b, (typical program time = (count + 1) * units = 26*.4 μs = 104s Bit 23 = Byte Program Typical time, additional byte units (0b:1 μs, 1b:8 μs) = 1 μs = 0b Bits 22:19 = Byte Program Typical time, additional byte count, (count + 1)* units, count = 0000b, (typical program time = (count + 1) * units = 1*1 μs = 1 μs Bit 18 = Byte Program Typical time, first byte units (0b:1 μs, 1b:8 μs) = 8 μs = 1b Bits 17:14 = Byte Program Typical time, first byte count, (count + 1)* units, count = 1100b, (typical program time = (count + 1) * units = 13*8 μs = 104 μs Bit 13 = Page Program Typical time units (0b:8 μs, 1b:64 μs) = 64 μs = 1b Bits 12:8 = Page Program Typical time count, (count + 1)* units, count = 00101b, (typical program time = (count + 1) * units = 6*64 μs = 384 μs) Bits 7:4 = Page size 2 ^N , N=9h, = 512B page Bits 3:0 = Multiplier from typical time to maximum for Page or Byte program = 2*(N+1), N=1h = 4x multiplier Binary Fields: 1-10-11001-0-0000-1-11001-00101-1001-0 001 Nibble Format: 1101_1001_0101_1001_0 001 Hex Format: D9 07 25 91 |



CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued) Table 63

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|--------------------|------|---|
| 2Eh | 2Ch | JEDEC Basic | ECh | Bit 31 = Suspend and Resume supported = |
| 2Fh | 2Dh | Flash Parameter | 83h | 0b |
| 30h | 2Eh | Dword-12 | 18h | Bits 30:29 = Suspend in-progress erase max latency units (00b: 128 ns, 01b: 1 µs, 10b: 8 |
| 31h | 2Fh | | 45h | μs, 11b: 64 μs) = 8 μs = 10b Bits 28:24 = Suspend in-progress erase max latency count = 00101b, max erase suspend latency = (count + 1) * units = 6*8 μs = 48 μs Bits 23:20 = Erase resume to suspend interval count = 0001b, interval = (count + 1) * 64 μs = 2 * 64 μs = 128 μs Bits 19:18 = Suspend in-progress program max latency units (00b: 128 ns, 01b: 1 μs, 10b: 8 μs, 11b: 64 μs) = 8 μs = 10b Bits 17:13 = Suspend in-progress program max latency count = 00100b, max erase suspend latency = (count + 1) * units = 5*8 μs = 40 μs Bits 12:9 = Program resume to suspend interval count = 0001b, interval = (count + 1) * 64 μs = 2 * 64 μs = 128 μs Bit 8 = RFU = 1b Bits 7:4 = Prohibited operations during erase suspend = xxx0b: May not initiate a new erase anywhere (erase nesting not permitted) + xx1xb: May not initiate a page program in the erase suspended sector size + x1xxb: May not initiate a read in the erase and program restrictions in bits 5:4 are sufficient = 1110b Bits 3:0 = Prohibited Operations During Program Suspend = xxx0b: May not initiate a new erase anywhere (erase nesting not permitted) + xx0xb: May not initiate a new page program anywhere (program nesting not permitted) + x1xxb: May not initiate a read in the program suspended page size + 1xxxb: The erase and program restrictions in bits 1:0 are sufficient = 1100b Binary Fields: 0-10-00101-0001-10-00100-0001-1-1110-11 00 Nibble Format: 0100_0101_0001_1000_1000_0011_1110_1 100 Hex Format: 45_18_83_EC |
| 32h | 30h | JEDEC Basic | 8Ah | Bits 31:24 = Erase Suspend Instruction = 75h |
| 33h | 31h | Flash Parameter | 85h | Bits 23:16 = Erase Resume Instruction = 7Ah Bits 15:8 = Program Suspend Instruction = |
| 34h | 32h | Dword-13 | 7Ah | 85h |
| 35h | 33h | | 75h | Bits 7:0 = Program Resume Instruction = 8Ah |

infineon

Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|--------------------|------|--|
| 36h | 34h | JEDEC Basic | F7h | Bit 31 = Deep Power Down Supported (not |
| 37h | 35h | Flash Parameter | FFh | supported) = 1 Bits 30:23 = Enter Deep Power Down |
| 38h | 36h | Dword-14 | FFh | Instruction (not supported) = FFh |
| 39h | 37h | | FFh | Bits 22:15 = Exit Deep Power Down Instruction (not supported) = FFh Bits 14:13 = Exit Deep Power Down to next operation delay units = (00b: 128 ns, 01b: 1 µs, 10b: 8 µs, 11b: 64 µs) = 64 µs = 11b Bits 12:8 = Exit Deep Power Down to next operation delay count = 11111b, Exit Deep Power Down to next operation delay = (count+1)*units (not supported) Bits 7:4 = RFU = Fh Bits 3:2 = Status Register Polling Device Busy = 01b: Legacy status polling supported = Use legacy polling by reading the Status Register with 05h instruction and checking WIP bit[0] (0 = ready; 1=busy). Bits 1:0 = RFU = 11b Binary Fields: 1-1111111-11111111-1111-1111-1111 1 Nibble Format: 1111_1111_1111_1111_1111_1111 Hex Format: FF_FF_FF_FF |
| 3Ah | 38h | JEDEC Basic | 00h | Bits 31:24 = RFU = FFh |
| 3Bh | 39h | Flash | F6h | Bit 23 = Hold and WP Disable = not |
| 3Ch | 3Ah | Parameter Dword-15 | 5Dh | supported = 0b Bits 22:20 = Quad Enable Requirements = |
| 3Dh | 3Bh | 2 | FFh | 101b: QE is bit 1 of the Status Register 2. Status Register 1 is read using Read Status instruction 05h. Status Register 2 is read using instruction 35h. QE is set via Write Status instruction 01h with two data bytes where bit 1 of the second byte is one. It is cleared via Write Status with two data bytes where bit 1 of the second byte is zero. Bits 19:16 0-4-4 Mode Entry Method = xxxx1b: Mode Bits[7:0] = A5h Note: QE must be set prior to using this mode + x1xxb: Mode Bits[7:0] = Axh + 1xxxb: RFU = 1101b Bits 15:10 0-4-4 Mode Exit Method = xx_xxxx1b: Mode Bits[7:0] = 00h will terminate this mode at the end of the current read operation + xx_1xxxb: Input Fh (mode bit reset) on DQ0-DQ3 for 8 clocks. This will terminate the mode prior to the next read operation. + x1_xxxxb: Mode Bit[7:0]!= Axh + 1x_x1xx: RFU |



CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued) Table 63

| CFI parameter relative byte address offsetSFDP Dword nameDescription3Eh3ChJEDEC Basic Flash Parameter Dword-16F0hBits 31:24 = Enter 4-byte Addressing = xxxxx_1xxxb: 8-bit volatile bank register use to define A[30:A24] bits. MSB (bit[7]) is use to enable/disable 4-byte address mode.41h3FhA8hWhen MSB is set to '1', 4-byte address mode is active and A[30:24] bits are don't care. Read with instruction 16h. Write instruction is 17h with 1 byte of data. When MSB is cleared to '0', select the active 128-Mbit | CFI parameter |
|--|---------------|
| Flash Parameter Dword-16 Flash Parameter Dword-16 FAh A8h Flash Parameter Dword-16 FAh A8h Xxxxx_1xxxb: 8-bit volatile bank register use to define A[30:A24] bits. MSB (bit[7]) is use to enable/disable 4-byte address mode. When MSB is set to '1', 4-byte address mode is active and A[30:24] bits are don't care. Read with instruction 16h. Write instruction is 17h with 1 byte of data. When MSB is | relative byte |
| Parameter Dword-16 Parameter Dword-16 Parameter Dword-16 Parameter Dword-16 Parameter Dword-16 FAh to define A[30:A24] bits. MSB (bit[7]) is use to enable/disable 4-byte address mode. When MSB is set to '1', 4-byte address mode is active and A[30:24] bits are don't care. Read with instruction 16h. Write instruction is 17h with 1 byte of data. When MSB is | 3Eh |
| 40h 3Eh Dword-16 FAh to enable/disable 4-byte address mode. 41h 3Fh When MSB is set to '1', 4-byte address mode is active and A[30:24] bits are don't care. Read with instruction 16h. Write instruction is 17h with 1 byte of data. When MSB is | 3Fh |
| A8h A8h When MSB is set to '1', 4-byte address mode is active and A[30:24] bits are don't care. Read with instruction 16h. Write instruction is 17h with 1 byte of data. When MSB is | 40h |
| is active and A[30:24] bits are don't care. Read with instruction 16h. Write instruction is 17h with 1 byte of data. When MSB is | |
| segment by setting the appropriate A[30:2 bits and use 3-byte addressing. + xxlx_xxxxb: Supports dedicated 4-byte address instruction set. Consult vendor data sheet for the instruction set definitio or look for 4 byte Address Parameter Tabil + 1xxx_xxxxb: Reserved = 10101000b Bits 23:14 = Exit 4-byte Addressing = xx_xxxx_lxxxb: 8-bit volatile bank registe used to define A[30:A24] bits. MSB (bit[7]) used to enable/disable 4-byte address mode. When MSB is cleared to '0; 3-byte address mode is active and A30:A24 are used to select the active 128-Mbit memor segment. Read with instruction 16h. Write instruction is 17h, data length is 1 byte. + xx_xxix_xxxxb: Software reset (see bits 13:8 in thin DWORD) + xx_1xxx_xxxxb: Power cycle + xx_xxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxxx | 41h |



Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|---------------------------------|------|--|
| 42h | 40h | JEDEC Sector | FFh | Bits 31:24 = RFU = FFh |
| 43h | 41h | Map Parameter | 00h | Bits 23:16 = Region count (Dwords -1) = 00h: One region |
| 44h | 42h | Dword-1 | 00h | Bits 15:8 = Configuration ID = 00h: Uniform |
| 45h | 43h | Config-0 Header | FFh | 256 kB sectors Bits 7:2 = RFU = 1111111b Bit 1 = Map Descriptor = 1 Bit 0 = The end descriptor = 1 |
| 46h | 44h | JEDEC Sector | F4h | Bits 31:8 = Region size = 00FFFFh: Region |
| 47h | 45h | Map Parameter | FFh | size as count-1 of 256 byte units = 64 MB/256 = 256K Count = 262144, value = count -1 = |
| 48h | 46h | Dword-2 | FE | 262144 -1 = 262143 = 3FFFFh |
| 49h | 47h | Dword-2 Config-0 Region-0 | 7Fh | Bits 4:7 = RFU = Fh Erase Type not supported = 0/ supported = 1 Bit 3 = Erase Type 4 support = 0b — Erase Type 4 is not defined Bit 2 = Erase Type 3 support = 1b — Erase Type 3 is 512 kB erase and is supported in the 512-kB sector region Bit 1 = Erase Type 2 support = 0b — Erase Type 2 is 64 kB erase and is not supported in the 256-kB sector region Bit 0 = Erase Type 1 support = 0b — Erase Type 1 is 4 kB erase and is not supported in the 256-kB sector region |



Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description |
|--|---|-------------------|------------|---|
| 4Ah | 48h | JEDEC 4 Byte | F3h | Supported = 1, Not Supported = 0 |
| 4Bh | 49h | Address | 88h | Bits 31:20 = RFU = FFFh |
| 4Ch | 4Ah | Instructions | FFh | Bit 19 = Support for nonvolatile individual |
| | 4Bh | _ | | Instruction=E3h = 1 |
| 4Ch 4Dh | 4Ah 4Bh | Parameter Dword-1 | FFh FFh | sector lock write command, |
| | | | | Bit 1 = Support for (1-1-1) FAST_READ Command, Instruction = 0Ch = 1 Bit 0 = Support for (1-1-1) READ Command, Instruction = 13h = 1 |

infineon

Software interface reference

Table 63 CFI alternate vendor-specific extended query parameter A5h, JEDEC SFDP Rev B (Continued)

| CFI parameter relative byte address offset | SFDP parameter relative byte address offset | SFDP Dword name | Data | Description | |
|--|---|--|------|---|---|
| 4Eh | 4Ch | JEDEC 4 Byte | FFh | Bits 31:24 = FFh = Instruction for Erase Type | |
| 4Fh | 4Dh | Address Instructions Parameter Dword-2 | FFh | 4: RFU Bits 23:16 = DCh = Instruction for Erase Type | |
| 50h | 4Eh | | l i | D.C.L. | 3 |
| 51h | 4Fh | | FFh | Bits 15:8 = FFh = Instruction for Erase Type 2: RFU Bits 7:0 = FFh = Instruction for Erase Type 1: RFU | |

12.3 Device ID and Common Flash Interface (ID-CFI) ASO map — automotive only

The CFI Primary Vendor-Specific Extended Query is extended to include Electronic Marking information for device traceability.

Table 64 Device ID and Common Flash Interface (ID-CFI) map automotive only

| Address | Data field | # of bytes | Data format | Example of actual data | Hex read out of example data |
|--------------|-----------------------------------|---------------|-------------|------------------------|---|
| (SA) + 0180h | Size of Electronic Marking | 1 | Hex | 20 | 14h |
| (SA) + 0181h | Revision of Electronic Marking | 1 | Hex | 1 | 01h |
| (SA) + 0182h | Fab Lot # | 8 | ASCII | LD87270 | 4Ch, 44h, 38h, 37h, 32h, 37h, 30h, FFh |
| (SA) + 018Ah | Wafer # | 1 | Hex | 23 | 17h |
| (SA) + 018Bh | Die X Coordinate | 1 | Hex | 10 | 0Ah |
| (SA) + 018Ch | Die Y Coordinate | 1 | Hex | 15 | 0Fh |
| (SA) + 018Dh | Class Lot # | 7 | ASCII | BR33150 | 42h, 52h, 33h, 33h, 31h, 35h, 30h |
| (SA) + 0194h | Reserved for Future | 12 | N/A | N/A | FFh, FFh, FFh, FFh, FFh, FFh, FFh, FFh, |

Fab Lot # + Wafer # + Die X Coordinate + Die Y Coordinate gives a unique ID for each device.

infineon

Software interface reference

12.4 Initial delivery state

The device is shipped from Infineon with nonvolatile bits set as follows:

- The entire memory array is erased: i.e. all bits are set to '1' (each byte contains FFh).
- The OTP address space has the first 16 bytes programmed to a random number. All other bytes are erased to FFh.
- The SFDP address space contains the values as defined in the description of the SFDP address space.
- The ID-CFI address space contains the values as defined in the description of the ID-CFI address space.
- The Status Register 1 contains 00h (all SR1 bits are cleared to 0's).
- The Configuration Register 1 contains 02h.
- The Autoboot register contains 00h.
- The Password Register contains FFFFFFFFFFFFh.
- All PPB bits are '1'.
- The ASP Register contents are shown here.

Table 65 ASP Register content


| Ordering part number model | ASPR default value | |
|----------------------------|--------------------|--|
| C1 | FE7Fh | |

infineon

Ordering information

13 Ordering information

The ordering part number is formed by a valid combination of the following:



infineon

Ordering information

13.1 Valid combinations — standard

Valid Combinations list configurations planned to be supported in volume for this device. Consult your local sales office to confirm availability of specific valid combinations and to check on newly released combinations.

Table 66 Valid combinations — standard

| Product | Speed option | Package and temperature | Model number | Packing type | Package marking [60] |
|-----------|--------------|-------------------------|-----------------|--------------|---|
| S79FL01GS | DS | BHV | C1 | 0, 3 | 79FL01GS + S + (Temp) + H + (Model Number) |

13.2 Valid combinations — automotive grade / AEC-Q100

Table 67 lists configurations that are automotive grade / AEC-Q100 qualified and are planned to be available in volume. The table will be updated as new combinations are released. Contact your local sales representative to confirm availability of specific combinations and to check on newly released combinations.

Production part approval process (PPAP) support is only provided for AEC-Q100 grade products.

Products to be used in end-use applications that require ISO/TS-16949 compliance must be AEC-Q100 grade products in combination with PPAP. Non-AEC-Q100 grade products are not manufactured or documented in full compliance with ISO/TS-16949 requirements.

AEC-Q100 grade products are also offered without PPAP support for end-use applications that do not require ISO/TS-16949 compliance.

Table 67 Valid combinations — automotive grade / AEC-Q100

| Product | Speed option | Package and temperature | Model number | Packing type | Package marking |
|-----------|--------------|-------------------------|-----------------|-----------------|---------------------------------------|
| S79FL01GS | DS | вна, внв | C1 | 0, 3 | 79FL01GS+S+(Temp)+H+(Model Number) |

Notes

58.EHPLC = Enhanced High Performance Latency Code table. 59.Uniform 512-kB sectors = All sectors are uniform 512-kB with a 1024B programming buffer.

60.Example, S79FL01GSDSBHVC10 package marking would be 79FL01GSSVHC1.

infineon

Revision history

Revision history

| Document revision | Date | Description of changes | |
|-------------------|------------|--|--|
| ** | 2014-10-15 | Initial release. | |
| *A | 2015-02-04 | Global: Promoted data sheet from Advance Information to Preliminary Command Set Summary: S79FL01GS Command Set (sorted by function) table: corrected 'Maximum Frequency (MHz)' for DDRQIOR and 4DDRQIOR Serial Flash Discoverable Parameters (SFDP) Address Map: Updated paragraph, updated SFDP Overview Map table Field Definitions: Updated SFDP Header table Device ID and Common Flash Interface (ID-CFI) Address Map: Manufacturer and Device ID table: corrected 03h Data CFI Alternate Vendor-Specific Extended Query Parameter 84h Suspend Commands table: corrected 07h Data Added table: CFI Alternate Vendor-Specific Extended Query Parameter A5h, JEDEC SFDP Rev B | |
| *B | 2016-02-01 | Changed maximum value of "SCK Clock Frequency for DDR READ" from 80 MHz to 93 MHz in all instances across the document. Updated to Cypress template. | |
| *C | 2017-01-05 | Changed maximum value of "SCK Clock Frequency for DDR READ" from 93 MHz to 80 MHz in all instances across the document. Added Automotive Temperature Range related information in all instances across the document. Updated Electrical specifications: Added Thermal resistance. Updated Address space maps: Updated Registers: Added ECC Status Register (ECCSR). Updated Commands: Updated Register Access commands: Added ECC Status Register Read (ECCRD 18h). Updated Program Flash Array commands: Updated Program granularity: Added Automatic ECC. Added Data integrity. Updated Software interface reference: Added Device ID and Common Flash Interface (ID-CFI) ASO map—automotive only. Updated Ordering information: Updated Ordering Information S79FL01GS: Added Automotive Grade Temperature Range related information. Added Valid combinations — automotive grade / AEC-Q100. Updated to new template. | |
| *D | 2017-03-22 | Updated Timing specifications: Updated SDR AC characteristics: Updated Table 11: Changed minimum value of t _{SU} parameter from 3 ns to 1.5 ns. Updated to new template. | |



Revision history

| Document revision | Date | Description of changes |
|-------------------|------------|--|
| *E | 2017-06-08 | Replaced "FAB024" with "ZSA024" in all instances across the document. Updated Address space maps: Updated Registers: Updated Configuration Register 1 (CR1): Updated details corresponding to Bit 4 (Replaced "RFU" with "DNU"). Updated PDF properties data. |
| *F | 2018-01-29 | Updated to new template. Completing Sunset Review. |
| *G | 2018-03-21 | Updated Timing specifications: Updated SDR AC characteristics: Updated Table 11: Removed typical value of t _{CSH} parameter. Added "3000 ns" as maximum value of t _{SU} parameter. |
| *H | 2022-07-19 | Updated Document Title to read as "S79FL01GS, 1 Gb (128 MB) Dual-Quad FL-S Flash SPI Multi-I/O, 3.0 V". Updated Overview: Removed "Glossary". Removed "Other resources". Updated SPI with multiple input / output (SPI-MIO) dual-quad: Replaced "Hardware interface" with "SPI with multiple input / output (SPI-MIO) Dual-Quad" in heading. Updated Electrical specifications: Updated Thermal resistance: Updated Table 4. Removed "Software interface". Updated Data integrity: Updated Data retention: Updated description. Migrated to Infineon template. |
| * | 2023-11-24 | Updated Table 11 . Updated template. |

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-11-24 Published by Infineon Technologies AG 81726 Munich, Germany

© 2023 Infineon Technologies AG. All Rights Reserved.

Do you have a question about this document?

Go to www.infineon.com/support

Document reference 002-00466 Rev. *I

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.