

BGA735N16

BGA735N16 for 3G/HSPA/LTE  
Applications Supporting Bands  
3, 7 and 20

with Reference Resistor  $R_{ref} = 27 \text{ k}\Omega$

Application Note AN233

Revision: Rev. 1.0  
2010-08-24

**Edition 2010-08-24**

**Published by  
Infineon Technologies AG  
81726 Munich, Germany**

**© 2010 Infineon Technologies AG  
All Rights Reserved.**

#### **Legal Disclaimer**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

#### **Information**

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

#### **Warnings**

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

**Application Note AN233**

**Revision History: 2010-08-24**

**Previous Revision:**

Page	Subjects (major changes since last revision)

**Trademarks of Infineon Technologies AG**

A-GOLD™, BlueMoon™, COMNEON™, CONVERGATE™, COSIC™, C166™, CROSSAVE™, CanPAK™, CIPOS™, CoolMOS™, CoolSET™, CONVERPATH™, CORECONTROL™, DAVE™, DUALFALC™, DUSLIC™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPACK™, EconoPIM™, E-GOLD™, EiceDRIVER™, EUPEC™, ELIC™, EPIC™, FALC™, FCOS™, FLEXISLIC™, GEMINAX™, GOLDMOS™, HITFET™, HybridPACK™, INCA™, ISAC™, ISOFACE™, IsoPACK™, IWORX™, M-GOLD™, MIPAQ™, ModSTACK™, MUSLIC™, my-d™, NovalithIC™, OCTALFALC™, OCTAT™, OmniTune™, OmniVia™, OptiMOS™, OPTIVERSE™, ORIGA™, PROFET™, PRO-SIL™, PrimePACK™, QUADFALC™, RASIC™, ReverSave™, SatRIC™, SCEPTRE™, SCOUT™, S-GOLD™, SensoNor™, SEROCCO™, SICOFI™, SIEGET™, SINDRION™, SLIC™, SMARTi™, SmartLEWIS™, SMINT™, SOCRATES™, TEMPFET™, thinQ!™, TrueNTRY™, TriCore™, TRENCHSTOP™, VINAX™, VINETIC™, VIONTIC™, WildPass™, X-GOLD™, XMM™, X-PMU™, XPOSYS™, XWAY™.

**Other Trademarks**

AMBA™, ARM™, MULTI-ICE™, PRIMECELL™, REALVIEW™, THUMB™ of ARM Limited, UK. AUTOSAR™ is licensed by AUTOSAR development partnership. Bluetooth™ of Bluetooth SIG Inc. CAT-iq™ of DECT Forum. COLOSSUS™, FirstGPS™ of Trimble Navigation Ltd. EMV™ of EMVCo, LLC (Visa Holdings Inc.). EPCOS™ of Epcos AG. FLEXGO™ of Microsoft Corporation. FlexRay™ is licensed by FlexRay Consortium. HYPERTERMINAL™ of Hilgraeve Incorporated. IEC™ of Commission Electrotechnique Internationale. IrDA™ of Infrared Data Association Corporation. ISO™ of INTERNATIONAL ORGANIZATION FOR STANDARDIZATION. MATLAB™ of MathWorks, Inc. MAXIM™ of Maxim Integrated Products, Inc. MICROTEC™, NUCLEUS™ of Mentor Graphics Corporation. Mifare™ of NXP. MIPI™ of MIPI Alliance, Inc. MIPS™ of MIPS Technologies, Inc., USA. muRata™ of MURATA MANUFACTURING CO. OmniVision™ of OmniVision Technologies, Inc. Openwave™ Openwave Systems Inc. RED HAT™ Red Hat, Inc. RFMD™ RF Micro Devices, Inc. SIRIUS™ of Sirius Sattelite Radio Inc. SOLARIS™ of Sun Microsystems, Inc. SPANSION™ of Spansion LLC Ltd. Symbian™ of Symbian Software Limited. TAIYO YUDEN™ of Taiyo Yuden Co. TEAKLITE™ of CEVA, Inc. TEKTRONIX™ of Tektronix Inc. TOKO™ of TOKO KABUSHIKI KAISHA TA. UNIX™ of X/Open Company Limited. VERILOG™, PALLADIUM™ of Cadence Design Systems, Inc. VLYNQ™ of Texas Instruments Incorporated. VXWORKS™, WIND RIVER™ of WIND RIVER SYSTEMS, INC. ZETEX™ of Diodes Zetex Limited.

Last Trademarks Update 2009-10-19

## Table of Content

1	<b>Introduction .....</b>	<b>6</b>
2	<b>Infineon LNA BGA735N16 for 3G and 4G Applications.....</b>	<b>11</b>
3	<b>Description.....</b>	<b>12</b>
4	<b>Application Information .....</b>	<b>14</b>
5	<b>Typical Measurement Results.....</b>	<b>16</b>
6	<b>Measured Graphs .....</b>	<b>19</b>
7	<b>Evaluation Board and Layout Information .....</b>	<b>31</b>
	<b>Authors.....</b>	<b>33</b>

## List of Figures

Figure 1	Application Diagram of a 3-band RF front-end for 3G and 4G systems.....	8
Figure 2	BGA735N16 in TSNP-16 Package .....	11
Figure 3	Block diagram and pin assignment of BGA735N16 (topview) .....	12
Figure 4	Schematics of the application circuit of BGA735N16 for bands 3, 7 and 20 .....	14
Figure 5	Measured Power Gain of BGA735N16 in Band 3 with Rref= 27 kΩ.....	19
Figure 6	Measured Noise Figure of BGA735N16 in Band 3 with Rref= 27 kΩ.....	19
Figure 7	Measured input insertion loss of BGA735N16 in Band 3 with Rref= 27 kΩ.....	20
Figure 8	Measured output insertion loss of BGA735N16 in Band 3 with Rref= 27 kΩ .....	20
Figure 9	Measured reverse isolation of BGA735N16 in Band 3 with Rref= 27 kΩ .....	21
Figure 10	Measured stability factor of BGA735N16 in Band 3 with Rref= 27 kΩ .....	21
Figure 11	Measured input IP3 of BGA735N16 in middle of Band 3 with Rref= 27 kΩ (High Gain Mode) .....	22
Figure 12	Measured Power Gain of BGA735N16 in Band 7 with Rref= 27 kΩ.....	23
Figure 13	Measured Noise Figure of BGA735N16 in Band 7 with Rref= 27 kΩ .....	23
Figure 14	Measured input insertion loss of BGA735N16 in Band 7 with Rref= 27 kΩ.....	24
Figure 15	Measured output insertion loss of BGA735N16 in Band 7 with Rref= 27 kΩ .....	24
Figure 16	Measured reverse isolation of BGA735N16 in Band 7 with Rref= 27 kΩ .....	25
Figure 17	Measured stability factor of BGA735N16 in Band 7 with Rref= 27 kΩ .....	25
Figure 18	Measured input IP3 of BGA735N16 in middle of Band 7 with Rref= 27 kΩ (High Gain Mode) .....	26
Figure 19	Measured Power Gain of BGA735N16 in Band 20 with Rref= 27 kΩ.....	27
Figure 20	Measured Noise Figure of BGA735N16 in Band 20 with Rref= 27 kΩ.....	27
Figure 21	Measured input insertion loss of BGA735N16 in Band 20 with Rref= 27 kΩ.....	28
Figure 22	Measured output insertion loss of BGA735N16 in Band 20 with Rref= 27 kΩ .....	28
Figure 23	Measured reverse isolation of BGA735N16 in Band 20 with Rref= 27 kΩ .....	29
Figure 24	Measured stability factor of BGA735N16 in Band 20 with Rref= 27 kΩ .....	29
Figure 25	Measured input IP3 of BGA735N16 in middle of Band 20 with Rref= 27 kΩ (High Gain Mode) .....	30
Figure 26	Photo Picture of Evaluation Board of BGA735N16.....	31
Figure 27	PCB Layer Information of BGA735N16.....	31

## List of Tables

Table 1	UMTS/WCDMA Band Assignment.....	6
Table 2	LTE Band Assignment .....	7
Table 3	Infineon Product Portfolio of LNAs for 3G and 4G Applications (Stand July 2010) .....	10
Table 4	Pin Assignment of BGA735N16 .....	13
Table 5	13	
Table 6	Gain control Truth table(Vcc=2.8V).....	13
Table 7	Bill-of-Materials.....	15
Table 8	Electrical Characteristics Band 3 (at room temperature) .....	16
Table 9	Electrical Characteristics Band 7 (at room temperature) .....	17
Table 10	Electrical Characteristics Band 20 (at room temperature) .....	18

## 1 Introduction

### 1.1 About 3G and 4G Applications

Recently, demand for wireless data service is growing faster than ever before. Starting from the first 3G technology, Universal Mobile Telecommunications System (UMTS), also known as Wideband Code Division Multiple Access (WCDMA) to the 3.5G technologies, High Speed Downlink Packet Access (HSDPA), High Speed Uplink Packet Access (HSUPA), and the combined technology HSPA and HSPA+, the wireless data rate through mobile phone networks increase dramatically. Ever since the rollout of HSDPA networks and flat-rate pricing plans, the wireless industry has seen amazing growth in mobile broadband average revenue per user.

Since middle 2009, further enhancements of the HSPA technology, defines a new OFDMA-based technology through the Long Term Evolution (LTE) start to ramp in the market. The ability of LTE to support bandwidths up to 20MHz and to have more spectral efficiency by using better modulation methods like QAM-64, is of particular importance as the demand for higher wireless data speeds continues to grow fast.

Countries all over the world have released various frequencies bands for the 3G and 4G applications. [Table 1](#) and [Table 2](#) show the band assignment for the UMTS and LTE bands worldwide.

**Table 1 UMTS/WCDMA Band Assignment**

Band No.	Uplink Frequencies (TX)	Downlink Frequencies (RX)	Comment
1	1920 - 1980 MHz	2110 - 2170 MHz	
2	1850 - 1910 MHz	1930 - 1990 MHz	
3	1850 - 1915 MHz	1930 - 1995 MHz	
4	1850 - 1920 MHz	1930 - 2000 MHz	
5	1710 - 1785 MHz	1805 - 1880 MHz	
6	1710 - 1755 MHz	2110 - 2155 MHz	
7	824 - 849 MHz	869 - 894 MHz	
8	830 - 840 MHz	875 - 885 MHz	
9	2500 - 2570 MHz	2620 - 2690 MHz	
10	880 - 915 MHz	925 - 960 MHz	

**Table 2      LTE Band Assignment**


<b>Band No.</b>	<b>Uplink Frequency Range</b>	<b>Downlink Frequency Range</b>	<b>Comment</b>
1	1920 - 1980 MHz	2110 - 2170 MHz	
2	1850 - 1910 MHz	1930 - 1990 MHz	
3	1710 - 1785 MHz	1805 - 1880 MHz	
4	1710 - 1755 MHz	2110 - 2155 MHz	
5	824 - 849 MHz	869 - 894 MHz	
7	2500 - 2570 MHz	2620 - 2690 MHz	
8	880 - 915 MHz	925 - 960 MHz	
9	1749.9 - 1784.9 MHz	1844.9 - 1879.9 MHz	
10	1710 - 1770 MHz	2110 - 2170 MHz	
11	1427.9 - 1452.9 MHz	1475.9 - 1500.9 MHz	
12	698 - 716 MHz	728 - 746 MHz	
13	777 - 787 MHz	746 - 756 MHz	
14	788 - 798 MHz	758 - 768 MHz	
17	704 - 716 MHz	734 - 746 MHz	
18	815 - 830 MHz	860 - 875 MHz	
19	830 - 845 MHz	875 - 890 MHz	
20	832 - 862 MHz	791 - 821 MHz	
21	1447.9 - 1462.9 MHz	1495.9 - 1510.9 MHz	
33	1900 -1920 MHz	1900 -1920 MHz	
34	2010 - 2025 MHz	2010 - 2025 MHz	
35	1850 - 1910 MHz	1850 - 1910 MHz	
36	1930 - 1990 MHz	1930 - 1990 MHz	
37	1910 - 1930 MHz	1910 - 1930 MHz	
38	2570 - 2620 MHz	2570 - 2620 MHz	
39	1880 - 1920 MHz	1880 - 1920 MHz	
40	2300 - 2400 MHz	2300 - 2400 MHz	

In order to cover different countries with a unique device, mobile phones and 3G data cards are usually equipped with more than one band. Some typical examples are the triple band combination of band 1, 2 and 5 or quad band combination of band 1, 2, 5 and 8. Since last year, some 700MHz bands are released in the US, so that band combination like 4, 13 and 17 are also well visible in the market.

## 1.2 Applications

**Figure 1** shows an example of the block diagram of the front-end of a 3G modem. A SPnT switch connects on one side the modem antenna and on the other sides several duplexers for different 3G bands. Every duplexer is connected to the transmitting (TX) and receiving (RX) paths of each band. The external LNA, here for example BGA735N16, is placed on the RX path between the duplex and the bandpass SAW filter. The output of the SAW filter is connected to the receiver input of the transceiver IC.

Depending on the number of bands designed in a device, various numbers of LNAs are required in a system. It can be 1-, 2-, 3-, or 4-bands. Recently, even mobile devices with 6 bands are under discussion.



**Figure 1** Example of Application Diagram of a 3-band RF front-end for 3G and 4G systems.

Besides low noise amplifiers, Infineon Technologies also offers system designers solutions for high power highly linear antenna switches as well as power detection diodes for power amplifiers.



### 1.3 Infineon LNAs for 3G and 4G Applications

With the increasing wireless data speed and with the extended link distance of mobile phones and 3G data cards, the requirements on the sensitivity are much higher. Infineon offers different kind of low noise amplifiers (LNAs) to support the customers for mobile phones and data cards of 3G and 4G to improve their system performance to meet the requirements coming from the networks/service providers.

The benefits to use external LNAs in an equipment for 3G and 4G applications are:

- Flexible design to place the front-end components: due to the size constraint, the modem antenna and the front-end can not be always put close to the transceiver IC. The path loss in front of the integrated LNA on the transceiver IC increases the system noise figure noticeable. An external LNA physically close to the ANT can help to eliminate the path loss and reduce the system noise figure. Therefore the sensitivity can be improved by several dB.
- Boost the sensitivity by reducing the system noise figure: external LNA has lower noise figure than the integrated LNA on the transceiver IC.
- Bug fix to help the transceiver ICs to fulfill the system requirements.
- Increase the dynamic range of the power handling.

Infineon Technologies is the leading company with broad product portfolio to offer high performance SiGe:C bipolar transistor LNAs and MMIC LNAs for various wireless applications by using the industrial standard silicon process.

**Table 3** shows a list of the MMIC LNA portfolio from Infineon Technologies for the applications of 3G and 4G applications (stand July 2010). Depending on the applications, LNAs with different band combinations are available:

- Single-band LNAs like BGA711L7 for high-band (HB, 1700MHz-2300MHz), BGA777L7 for high-band (2300MHz-2700MHz) or BGA751L7 for low-band (LB, 700-1000MHz) are available. BGA713L7 is designed for the special LTE bands 12, 13, 14, 17, 18, 19 and 20 in the US.
- Triple-band LNAs BGA734N16, BGA735N16 and BGA736N16 are available to cover the most bands. All of the three triple-band LNAs can support designs covering 2x high-bands and 1x low-band.

- Both BGA748N16 and BGA749N16 are quad-band LNAs. BGA748N16 can cover 2x high- and 2x low-bands and BGA749N16 can cover 1x high-band and 3x low-bands. BGA747N16 can cover 3x high-bands and 1x low-band. All of these quad-bands LNAs can support all designs with 3 to 4 bands.

The broad product portfolio with highest integration and best features in noise figure, switchable gain level and flexible band selection helps designers of mobile phones and data cards to achieve outstanding performance. Therefore Infineon LNAs are widely used by major mobile phone vendors.

**Table 3 Infineon Product Portfolio of LNAs for 3G and 4G Applications (Stand July 2010)**

Frequency Range	700 MHz – 1 GHz	1400MHz – 2200MHz	2100 MHz – 2700 MHz	Comment
<b>Single-Band LNA</b>				
BGA711L7		x		
BGA751L7	x			
BGA777L7			x	
BGA728L7	x	x		
BGA713L7	x			
<b>Triple Band LNA</b>				
BGA734L16	x	x	x	
BGA735N16	x	x	x	
BGA736N16	x	x	x	
<b>Quad-band LNA</b>				
BGA747N16	x	x	x	
BGA748N16	x	x	x	
BGA749N16	x	x	x	

## 2 Infineon LNA BGA735N16 for 3G and 4G Applications

This application note focuses on the Infineon's Tri-band LNA BGA735N16 tuned for the band combination of **band 3, 7 and 20**. It presents the performance of BGA735N16 **with an external reference resistor of 27 k $\Omega$**  which enables the device to work with a current of **4.4 mA** at single supply voltage of 2.8 V. All the measurements are executed with the standard evaluation board presented at the end of this application note.

### 2.1 Features of BGA735N16

- High gain and low gain modes
- Low noise figure
- Tunable supply current with external Rref
- Standby mode (< 2  $\mu$ A typ.)
- Output internally matched to 50  $\Omega$ .
- Inputs pre-matched to 50  $\Omega$ .
- 2 kV HBM ESD protection
- Low external component count
- Small leadless TSNP-16-1 package (2.3 x 2.3 x 0.39 mm<sup>3</sup>)
- Pb-free (RoHS compliant) device




Figure 2 BGA735N16 in TSNP-16 Package




### 3 Description

**Figure 3** shows the internal block diagram of BGA735N16 with the topview of the TSNP-16 and the pin assignment. **Table 4** is the pin assignment of BGA735N16 with the description of their functions accordingly. As shown in the block diagram, BGA735N16 includes 4 LNAs into one device. Each of the LNA can be switched to the high-gain and the low-gain mode. The gain switch can be easily done by switching the VGS pin to Vcc (high-gain mode) or 0 V (low-gain mode). Furthermore, the following functions are integrated into BGA735N16:

- Smart active biasing circuit: to enable the circuit performance over temperature and supply voltage variation.
- Output matching circuits for the standard bands (bands 1, 2 and 5 for BGA735N16)
- Current setting with only one external resistor Rref.
- Band selection with the two pins VEN1 and VEN2 ([Fehler! Verweisquelle konnte nicht gefunden werden.](#)).
- On/off switch of the whole device with one single pin VON (**Table 6**).
- All the digital control pins VON, VEN1, VEN2 and VGS are CMOS 2.8V logic compliant.
- ESD protection circuit allaround the device for 2kV HBM.

The RF input pins of the LNAs are connected directly with the base of the major SiGe:C RF transistors to achieve the best noise figure performance. In addition, the input and the output matching circuits can be tuned to different bands if required.



**Figure 3** Block diagram and pin assignment of BGA735N16 (topview)

**Table 4 Pin Assignment of BGA735N16**

Pin No.	Symbol	Function
0	GND	Package paddle; ground connection for low band LNA and control circuitry
1	n/c	Not connected
2	VGS	Gain step control
3	VCC	Supply Voltage
4	RFGNDH	High Band LNA emitter ground
5	n/c	Not connected
6	RFINM	Mid Band LNA input UMTS Band 3 (1840 MHz)
7	RFINH	High Band LNA input UMTS Band 7 (2660 MHz)
8	RFGNDM	Mid band LNA emitter ground
9	n/c	Not connected
10	RFINL	Low Band LNA input UMTS Band 20 (805 MHz)
11	VEN2	Band select control
12	VEN1	Band select control
13	RREF	Bias current reference resistor (high gain mode)
14	RFOUTL	Low band LNA output, UMTS Band 20 (805 MHz)
15	RFOUTH	High band LNA output, UMTS Band 7 (2100 MHz)
16	RFOUTM	Mid band LNA output, UMTS Band 3(1840 MHz)

**Table 5**

Pin control	Band 3	Band 7	Band 20	Stand-by
VEN1	H	H	L	L
VEN2	L	H	H	L

**Table 6 Gain control Truth table(Vcc=2.8V)**

Pin control	High Gain	Low Gain
VGS	H	L

## 4 Application Information

Figure 4 shows the application circuit of BGA735N16 for bands 3, 7 and 20.

### 4.1 Schematics




Figure 4 Schematics of the application circuit of BGA735N16 for bands 3, 7 and 20

**Table 7 Bill-of-Materials**

Symbol	Value	Unit	Size	Manufacturer	Comment
C1	22	pF	0402	Murata GRM15	Input matching / DC block
L1	4.3	nH	0402	Murata LQW15A	Input matching
C2	22	pF	0402	Murata GRM15	Input matching
C3	2.4	pF	0402	Murata GRM15	Input matching / DC block
L2	3.9	nH	0402	Murata LQW15A	Input matching
L3	3.9	nH	0402	Murata LQW15A	Input matching
C4	3	pF	0402	Murata GRM15	Input matching / DC block
L4	11	nH	0402	Murata LQW15A	Input matching
C5	15	pF	0402	Murata GRM15	Input matching
C6	1.5	pF	0402	Murata GRM15	Output matching
L5	1.5	nH	0402	Murata LQW15A	Output matching
C7	0.5	pF	0402	Murata GRM15	Output matching
L6	3.9	nH	0402	Murata LQW15A	Output matching
C8	3.9	pF	0402	Murata GRM15	Output matching
L7	6.2	nH	0402	Murata LQW15A	Output matching
C9	10	nF	0402	Murata GRM15	HF to ground
R <sub>REF</sub>	27	kΩ	0402	Various	Current settings
Q1	BGA735N16		TSNP-16-1	Infineon	SiGe MMIC LNA BGA735N16

## 5 Typical Measurement Results

### 5.1 Results of Band 3

**Table 8 Electrical Characteristics Band 3 (at room temperature)**

VGS = 0V for low gain mode, VGS = 2.8V for high gain mode

Parameter	Symbol	Value		Unit	Comment/Test Condition
Frequency Range	Freq	1805 - 1880		MHz	
DC Supply Voltage	Vcc	2.8		V	
Gain Mode	-	High Gain	Low Gain		
DC Current	Icc	3.5	0.65	mA	
Gain	G	16	-9.3	dB	
Noise Figure	NF	1.1	8.7	dB	SMA and PCB losses of 0.2 excluded
Input Return Loss	RLin	16.6	16.2	dB	
Output Return Loss	RLout	17.7	11.5	dB	
Reverse Isolation	IRev	36.9	9.3	dB	Power@Port2: -30dBm
Input P1dB	IP1dB	-7.7	-6	dBm	
Output P1dB	OP1dB	7.3	-17.3	dBm	
Input IP3	IIP3	-7.6	2.5	dBm	f1=1840MHz; f2=1841MHz Pin=-30dBm high gain mode Pin=-20dBm Low gain mode
Output IP3	OIP3	8.4	-6.8	dBm	
Stability	k	> 1		--	Unconditionnally stably from DC to 10 GHz



## 5.2 Results of Band 7

**Table 9 Electrical Characteristics Band 7 (at room temperature)**

VGS = 0V for low gain mode, VGS = 2.8V for high gain mode

Parameter	Symbol	Value		Unit	Comment/Test Condition
Frequency Range	Freq	2620 - 2690		MHz	
DC Supply Voltage	Vcc	2.8		V	
Gain Mode	-	High Gain	Low Gain		
DC Current	Icc	4.4	0.65	mA	
Gain	G	14.9	-6.2	dB	
Noise Figure	NF	1.3	6.5	dB	SMA and PCB losses of 0.25 excluded
Input Return Loss	RLin	11.5	14.3	dB	
Output Return Loss	RLout	10.4	11.5	dB	
Reverse Isolation	IRev	32.3	6.2	dB	Power@Port2: -30dBm
Input P1dB	IP1dB	-9	-1.6	dBm	
Output P1dB	OP1dB	4.9	-8.8	dBm	
Input IP3	IIP3	-5.7	8.5	dBm	f1=2660MHz; f2=2661MHz Pin=-30dBm high gain mode Pin=-20dBm Low gain mode
Output IP3	OIP3	9.2	2.3	dBm	
Stability	K	> 1		--	Unconditionnally stably from DC to 10 GHz

### 5.3 Results of Band 20


**Table 10 Electrical Characteristics Band 20 (at room temperature)**

VGS = 2.8 V for low gain mode, VGS = 0 V for high gain mode


Parameter	Symbol	Value		Unit	Comment/Test Condition
Frequency Range	Freq	791 - 821		MHz	
DC Supply Voltage	Vcc	2.8		V	
Gain Mode	-	High Gain	Low Gain		
DC Current	Icc	3.5	0.65	mA	
Gain	G	16	-9.3	dB	
Noise Figure	NF	1.0	8.7	dB	SMA and PCB losses of 0.2 excluded
Input Return Loss	RLin	16.6	16.2	dB	
Output Return Loss	RLout	17.7	11.5	dB	
Reverse Isolation	IRev	36.9	9.3	dB	Power@Port2: -30dBm
Input P1dB	IP1dB	-7.7	-6	dBm	
Output P1dB	OP1dB	7.3	-17.3	dBm	
Input IP3	IIP3	-7.6	2.5	dBm	f1=805MHz; f2=806MHz Pin=-30dBm high gain mode Pin=-20dBm Low gain mode
Output IP3	OIP3	8.4	-6.8	dBm	
Stability	k	> 1		--	Unconditionnally stably from DC to 10 GHz

## 6 Measured Graphs


### 6.1 Graphs of Band 3




**Figure 5 Measured Power Gain of BGA735N16 in Band 3 with Rref= 27 k $\Omega$**




**Figure 6 Measured Noise Figure of BGA735N16 in Band 3 with Rref= 27 k $\Omega$**




**Figure 7** Measured input insertion loss of BGA735N16 in Band 3 with Rref= 27 kΩ



**Figure 8** Measured output insertion loss of BGA735N16 in Band 3 with Rref= 27 kΩ



**Figure 9** Measured reverse isolation of BGA735N16 in Band 3 with Rref= 27 k $\Omega$



**Figure 10** Measured stability factor of BGA735N16 in Band 3 with Rref= 27 k $\Omega$






Figure 11 Measured input IP3 of BGA735N16 in middle of Band 3 with Rref= 27 kΩ (High Gain Mode)


## 6.2 Graphs of Band 7




**Figure 12 Measured Power Gain of BGA735N16 in Band 7 with Rref= 27 kΩ**



**Figure 13 Measured Noise Figure of BGA735N16 in Band 7 with Rref= 27 kΩ**



**Figure 14** Measured input insertion loss of BGA735N16 in Band 7 with Rref= 27 kΩ



**Figure 15** Measured output insertion loss of BGA735N16 in Band 7 with Rref= 27 kΩ






Figure 16 Measured reverse isolation of BGA735N16 in Band 7 with Rref= 27 kΩ




Figure 17 Measured stability factor of BGA735N16 in Band 7 with Rref= 27 kΩ






Figure 18 Measured input IP3 of BGA735N16 in middle of Band 7 with Rref= 27 k $\Omega$  (High Gain Mode)

### 6.3 Graphs of Band 20



**Figure 19 Measured Power Gain of BGA735N16 in Band 20 with Rref= 27 kΩ**



**Figure 20 Measured Noise Figure of BGA735N16 in Band 20 with Rref= 27 kΩ**




Figure 21 Measured input insertion loss of BGA735N16 in Band 20 with Rref= 27 kΩ




Figure 22 Measured output insertion loss of BGA735N16 in Band 20 with Rref= 27 kΩ




Figure 23 Measured reverse isolation of BGA735N16 in Band 20 with Rref= 27 kΩ




Figure 24 Measured stability factor of BGA735N16 in Band 20 with Rref= 27 kΩ




Figure 25 Measured input IP3 of BGA735N16 in middle of Band 20 with Rref= 27 kΩ (High Gain Mode)

## 7 Evaluation Board and Layout Information




Figure 26 Photo Picture of Evaluation Board of BGA735N16


0.017 mm	Copper	
0.100 mm	Prepreg FR4	
0.100 mm	Prepreg FR4	
0.035 mm	Copper	
0.460 mm	FR4	
0.100 mm	Prepreg FR4	
0.100 mm	Prepreg FR4	
0.017 mm	Copper	

Figure 27 PCB Layer Information of BGA735N16





## **Authors**

André Dewai, RF Engineer of Business Unit “RF and Protection Devices”

Dr.Chih-I Lin, Senior Staff engineer of Business Unit “RF and Protection Devices”

Anthony Thomas, RF Engineer of Business Unit “RF and Protection Devices”

[www.infineon.com](http://www.infineon.com)