

## BGA824N6

BGA824N6 with improved immunity,  
against out-of-band jammers (LTE  
Band-13, GSM850/900/1800, UMTS,  
WLAN)

## Application Note AN326

Revision: Rev.1.0  
2013-06-03

**Edition 2013-06-03**

**Published by  
Infineon Technologies AG  
81726 Munich, Germany**

**© 2013 Infineon Technologies AG  
All Rights Reserved.**

### **Legal Disclaimer**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

### **Information**

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

### **Warnings**

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.



**Application Note AN326**

**Revision History: 2013-06-03**

**Previous Revision: None**

Page	Subjects (major changes since last revision)

**Trademarks of Infineon Technologies AG**

AURIX™, C166™, CanPAK™, CIPOS™, CIPURSE™, EconoPACK™, CoolMOS™, CoolSET™, CORECONTROL™, CROSSAVE™, DAVE™, DI-POL™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPIM™, EconoPACK™, EiceDRIVER™, eupec™, FCOS™, HITFET™, HybridPACK™, I<sup>2</sup>RF™, ISOFACE™, IsoPACK™, MIPAQ™, ModSTACK™, my-d™, NovalithIC™, OptiMOS™, ORIGA™, POWERCODE™, PRIMARION™, PrimePACK™, PrimeSTACK™, PRO-SIL™, PROFET™, RASIC™, ReverSave™, SatRIC™, SIEGET™, SINDRION™, SIPMOS™, SmartLEWIS™, SOLID FLASH™, TEMPFET™, thinQ!™, TRENCHSTOP™, TriCore™.

**Other Trademarks**

Advance Design System™ (ADS) of Agilent Technologies, AMBA™, ARM™, MULTI-ICE™, KEIL™, PRIMECELL™, REALVIEW™, THUMB™, μVision™ of ARM Limited, UK. AUTOSAR™ is licensed by AUTOSAR development partnership. Bluetooth™ of Bluetooth SIG Inc. CAT-iq™ of DECT Forum. COLOSSUS™, FirstGPS™ of Trimble Navigation Ltd. EMV™ of EMVCo, LLC (Visa Holdings Inc.). EPCOS™ of Epcos AG. FLEXGO™ of Microsoft Corporation. FlexRay™ is licensed by FlexRay Consortium. HYPERTERMINAL™ of Hilgraeve Incorporated. IEC™ of Commission Electrotechnique Internationale. IrDA™ of Infrared Data Association Corporation. ISO™ of INTERNATIONAL ORGANIZATION FOR STANDARDIZATION. MATLAB™ of MathWorks, Inc. MAXIM™ of Maxim Integrated Products, Inc. MICROTEC™, NUCLEUS™ of Mentor Graphics Corporation. MIPI™ of MIPI Alliance, Inc. MIPS™ of MIPS Technologies, Inc., USA. muRata™ of MURATA MANUFACTURING CO., MICROWAVE OFFICE™ (MWO) of Applied Wave Research Inc., OmniVision™ of OmniVision Technologies, Inc. Openwave™ Openwave Systems Inc. RED HAT™ Red Hat, Inc. RFMD™ RF Micro Devices, Inc. SIRIUS™ of Sirius Satellite Radio Inc. SOLARIS™ of Sun Microsystems, Inc. SPANSION™ of Spansion LLC Ltd. Symbian™ of Symbian Software Limited. TAIYO YUDEN™ of Taiyo Yuden Co. TEAKLITE™ of CEVA, Inc. TEKTRONIX™ of Tektronix Inc. TOKO™ of TOKO KABUSHIKI KAISHA TA. UNIX™ of X/Open Company Limited. VERILOG™, PALLADIUM™ of Cadence Design Systems, Inc. VLYNQ™ of Texas Instruments Incorporated. VXWORKS™, WIND RIVER™ of WIND RIVER SYSTEMS, INC. ZETEX™ of Diodes Zetex Limited.

Last Trademarks Update 2011-11-11

## Table of Content

<b>1</b>	<b>Introduction of Global Navigation Satellite Systems (GNSS)</b> .....	<b>5</b>
<b>2</b>	<b>BGA824N6 Overview</b> .....	<b>8</b>
2.1	Features .....	8
2.2	Key Applications of BGA824N6 .....	8
2.3	Description .....	9
<b>3</b>	<b>Application Circuit and Performance Overview</b> .....	<b>10</b>
3.1	Summary of Measurement Results.....	10
3.2	Summary BGA824N6 as 1550-1615 MHz LNA for GNSS.....	12
3.3	Schematics and Bill-of-Materials.....	13
<b>4</b>	<b>Measurement Graphs</b> .....	<b>14</b>
<b>5</b>	<b>Evaluation Board and Layout Information</b> .....	<b>22</b>
<b>6</b>	<b>Authors</b> .....	<b>24</b>
<b>7</b>	<b>Remark</b> .....	<b>24</b>

## List of Figures

Figure 1	BGA824N6 TSNP-6-2 leadless Package size .....	6
Figure 2	BGA824N6 in TSNP-6-2 .....	8
Figure 3	Equivalent Circuit Block diagram of BGA824N6 .....	9
Figure 4	Package and pin connections of BGA824N6.....	9
Figure 5	Schematic of the BGA824N6 Application Circuit .....	13
Figure 6	Power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands .....	14
Figure 7	Narrowband power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands .....	14
Figure 8	Noise figure of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands .....	15
Figure 9	Input matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands.....	15
Figure 10	Input matching smith chart for COMPASS, Galileo, GPS and GLONASS bands .....	16
Figure 11	Output matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands .....	16
Figure 12	Output matching smith chart for COMPASS, Galileo, GPS and GLONASS bands .....	17
Figure 13	Reverse isolation of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands.....	17
Figure 14	Stability factor $k$ of BGA824N6 upto 10 GHz .....	18
Figure 15	Stability factor $\mu_1$ of BGA824N6 upto 10 GHz .....	18
Figure 16	Stability factor $\mu_2$ of BGA824N6 upto 10 GHz .....	19
Figure 17	Input 1 dB compression point of BGA824N6 at supply voltage of 1.8 V for COMPASS, Galileo, GPS and GLONASS bands .....	19
Figure 18	Input 1 dB compression point of BGA824N6 at supply voltage of 2.8 V for COMPASS, Galileo, GPS and GLONASS bands .....	20
Figure 19	Carrier and intermodulation products of BGA824N6 for GPS band .....	20
Figure 20	Carrier and intermodulation products of BGA824N6 for GLONASS band .....	21
Figure 21	Picture of Evaluation Board (overview) .....	22
Figure 22	Picture of Evaluation Board (detailed view) .....	22
Figure 23	PCB Layer Information .....	23

## List of Tables

Table 1	Pin Assignment of BGA824N6 .....	9
Table 2	Pin Assignment of BGA824N6 .....	9
Table 3	Electrical Characteristics for COMPASS/Galileo at $V_{cc} = V_{pon} = 1.8\text{ V}$ .....	10
Table 4	Electrical Characteristics for COMPASS/Galileo at $V_{cc} = V_{pon} = 2.8\text{ V}$ .....	11
Table 5	Bill-of-Materials.....	13


## 1 Introduction of Global Navigation Satellite Systems (GNSS)

The BGA824N6 is a front-end Low Noise Amplifier (LNA) for Global Navigation Satellite Systems (GNSS) application. It is based on Infineon Technologies' B7HF Silicon-Germanium (SiGe) technology, enabling a cost-effective solution in a TSNP-6-2 leadless package with ultra low noise figure, high linearity, low current consumption and high gain, over a wide range of supply voltages from 1.5 V up to 3.6 V. All these features make BGA824N6 an excellent choice for GNSS LNA as it improves sensitivity, provide better immunity against out-of-band jammer signals, reduces filtering requirement and hence the overall cost of the GNSS receiver.

The GNSS satellites are at an orbit altitude of more than 20,000 km away from earth's surface and transmit power in the range of +47 dBm. After taking losses (atmospheric, antenna etc.) into account, the received signal strength at the GNSS device input is very low in the range of -130 dBm. The ability of the GNSS device to receive such low signal strength and provide meaningful information to the end-user depends strongly on the noise figure of the GNSS receiver chain. This ability which is called receiver sensitivity can be improved by using a low-noise amplifier with low noise figure and high gain at the input of the receiver chain. The improved sensitivity results in a shorter Time-To-First-Fix (TTFF), which is the time required for a GNSS receiver to acquire satellite signals and navigation data, and calculate a position. Noise figure of the LNA defines the overall noise figure of the GNSS receiver system. This is where BGA824N6 excels by providing noise figure as low as 0.55 dB and high gain of 17 dB, thereby improving the receiver sensitivity significantly.

The ever growing demand to integrate more and more functionality into one device leads to many challenges when transmitter/receiver has to work simultaneously without degrading the performance of each other. In today's smart-phones a GNSS receiver simultaneously co-exists with transceivers in the GSM/EDGE/UMTS/LTE bands. These 3G/4G transceivers transmit high power in the range of +24 dBm which due to insufficient isolation couple to the GNSS receiver. The cellular signals can mix to produce Intermodulation products exactly in the GNSS receiver frequency band. For example, GSM 1712.7 MHz mixes with UMTS 1850 MHz to produce third-order-product exactly at GPS band. To quantify the effect, BGA824N6

shows out-of-band input IP3 at GPS band of +7 dBm, as a result of frequency mixing between GSM 1712.7 MHz and UMTS 1850 MHz with power levels of -20 dBm. Due to this high out-of-band input 3<sup>rd</sup> order intercept point (IIP3), BGA824N6 is especially suitable for the GPS function in mobile phones.



**Figure 1 BGA824N6 TSNP-6-2 leadless Package size**

As the industry inclines toward assembly miniaturization and also surface mount technology matures, there is a desire to have smaller and thinner components. This is especially the case with portable electronics where higher circuit density allows device design flexibility and also optimum use of the limited space available. BGA824N6 has a small package with dimensions of 0.70mm x 1.1mm x 0.375mm and it requires only one external component at its input, the inductor providing the input matching. The DC block at input is optional as it is usually provided by the pre-filter before the LNA in many GPS applications. All the device/phone manufacturers implement very good power supply filtering on their boards so that the RF bypass capacitor mentioned in this application circuit may not be needed in the end. The minimal number of external SMD components reduces the application bill of materials, assembly complexity and the PCB area thus making it an ideal solution for compact and cost-effective GNSS LNA. The output of the BGA824N6 is internally matched to  $50 \Omega$ , and a DC blocking capacitor is integrated on-chip, thus no external component is required at the output

The device also integrates an on-chip ESD protection which can resist until 2 kV (referenced to human body model) in all pins. The integrated power on/off feature provides for low power consumption and increased stand-by time for GNSS handsets. Moreover, the low current consumption (3.8 mA) makes the device suitable for portable technology like GNSS receivers and mobiles phones.


The Internal circuit block diagram of the BGA824N6 is presented in Figure 3. Table 1 shows the pin assignment of BGA824N6. Table 2 shows the truth table to turn on/off BGA824N6 by applying different voltage to the PON pin.



## 2 BGA824N6 Overview

### 2.1 Features

- High insertion power gain: 17.0 dB
- Out-of-band input 3rd order intercept point: +7 dBm
- Input 1 dB compression point: -6 dBm
- Low noise figure: 0.55 dB
- Low current consumption: 3.8 mA
- Operating frequencies: 1550 - 1615 MHz
- Supply voltage: 1.5 V to 3.6 V
- Digital on/off switch (1 V logic high level)
- Ultra small TSNP-6-2 leadless package (footprint: 0.7 x 1.1 mm<sup>2</sup>)
- B7HF Silicon Germanium technology
- RF output internally matched to 50 Ω
- Only 1 external SMD component necessary
- 2 kV HBM ESD protection (including AI-pin)
- Pb-free (RoHS compliant) package



**Figure 2 BGA824N6 in TSNP-6-2**



### 2.2 Key Applications of BGA824N6


- Ideal for all Global Navigation Satellite Systems (GNSS) like
  - GPS (Global Positioning System) working in the L1 band at 1575.42 MHz
  - GLONASS (Russian GNSS) working in the L1 band from 1598.06 MHz to 1605.38 MHz
  - Galileo<sup>1</sup> (European GNSS) working in the E2-L1-E1 band from 1559 MHz to 1592 MHz
  - COMPASS<sup>1</sup> (Chinese Beidou Navigation System) working in E2 band at 1561.10 MHz and E1 band at 1589.74 MHz

<sup>1</sup>The application circuit (Figure 5) proposed in this Application Note is suitable for GPS and GLONASS bands




### 2.3 Description

The BGA824N6 is a front-end low noise amplifier for Global Navigation Satellite Systems (GNSS) from 1550 MHz to 1615 MHz like GPS, GLONASS, Beidou, Galileo and others. The LNA provides 17.0 dB gain and 0.55 dB noise figure at a current consumption of 3.8 mA in the application configuration described in **Chapter 3**. The BGA824N6 is based upon Infineon Technologies B7HF Silicon Germanium technology. It operates from 1.5 V to 3.6 V supply voltage.



**Figure 3** Equivalent Circuit Block diagram of BGA824N6



**Figure 4** Package and pin connections of BGA824N6

**Table 1** Pin Assignment of BGA824N6

Pin No.	Symbol	Function
1	GND	Ground
2	VCC	DC supply
3	AO	LNA output
4	GND	Ground
5	AI	LNA input
6	PON	Power on control

**Table 2** Pin Assignment of BGA824N6

LNA Mode	Symbol	ON/OFF Control Voltage at PON pin	
		Min	Max
ON	PON, on	1.0 V	VCC
OFF	PON, off	0 V	0.4 V

### 3 Application Circuit and Performance Overview

**Device:** BGA824N6

**Application:** BGA824N6 with improved immunity, against out-of-band jammers  
(LTE Band-13, GSM850/900/1800, UMTS, WLAN)

**PCB Marking:** BGA824N6

#### 3.1 Summary of Measurement Results

**Table 3 Electrical Characteristics for COMPASS/Galileo at Vcc = Vpon = 1.8 V**

Parameter	Symbol	Value		Unit	Comment/Test Condition
DC Voltage	Vcc	1.8		V	
DC Current	Icc	3.9		mA	
Navigation System	Sys	GPS	GLONASS		
Frequency Range	Freq	1575.42	1598-1606	MHz	
Gain	G	15.3	15	dB	
Noise Figure	NF	1.97	2.31	dB	PCB and SMA losses 0.06dB are subtracted
Input Return Loss	RLin	10.3	14.2	dB	
Output Return Loss	RLout	24.3	13.1	dB	
Reverse Isolation	IRev	24.6	24.6	dB	
Input P1dB	IP1dB	-8.3	-8	dBm	F <sub>gps</sub> = 1575.42 MHz F <sub>GLONASS</sub> = 1605 MHz
Output P1dB	OP1dB	6	6	dBm	
Input IP3 In-band	IIP3	-4.9	-3.6	dBm	
Output IP3 In-band	OIP3	10.4	11.4	dBm	f <sub>1gps</sub> = 1575.42 MHz, f <sub>2gps</sub> = 1576.42 MHz F <sub>1GLONASS</sub> = 1602 MHz, F <sub>2GLONASS</sub> = 1603 MHz Input power= -30 dBm
LTE band-13 2 <sup>nd</sup> Harmonic	H2	-88.6			f <sub>IN</sub> = 787.76 MHz, P <sub>IN</sub> = +15 dBm; f <sub>H2</sub> = 1575.52 MHz
Output IM2 Out-of-band	IM2	-104.7			f <sub>1</sub> = 827 MHz, P <sub>1IN</sub> = +12 dBm; f <sub>2</sub> = 2402 MHz, P <sub>2IN</sub> = +8 dBm ; f <sub>IM2</sub> = 1575 MHz
Output IM2 Out-of-band	IM2	-109.7			f <sub>1</sub> = 897 MHz, P <sub>1IN</sub> = +12 dBm; f <sub>2</sub> = 2472 MHz, P <sub>2IN</sub> = +8 dBm ; f <sub>IM2</sub> = 1575 MHz
Input IP3 Out-of-band	IIP3 <sub>OOB</sub>	67.4			f <sub>1</sub> = 1712.7 MHz, P <sub>1IN</sub> = +10 dBm; f <sub>2</sub> = 1850 MHz, P <sub>2IN</sub> = +10 dBm; f <sub>IIP3</sub> = 1575.4 MHz
Stability	k	>1		--	Unconditionnally Stable from 0 to 10GHz

**Table 4 Electrical Characteristics for COMPASS/Galileo at Vcc = Vpon = 2.8 V**

Parameter	Symbol	Value		Unit	Comment/Test Condition
DC Voltage	Vcc	2.8		V	
DC Current	Icc	4.1		mA	
Navigation System	Sys	GPS	GLONASS		
Frequency Range	Freq	1575.42	1598-1606	MHz	
Gain	G	15.4	15.2	dB	
Noise Figure	NF	1.99	2.33	dB	PCB and SMA losses 0.06dB are subtracted
Input Return Loss	RLin	10.4	14.8	dB	
Output Return Loss	RLout	28.7	14.2	dB	
Reverse Isolation	IRev	25	25	dB	
Input P1dB	IP1dB	-5.2	-4.8	dBm	F <sub>gps</sub> = 1575.42 MHz F <sub>GLONASS</sub> = 1605 MHz
Output P1dB	OP1dB	9.2	9.4	dBm	
Input IP3 In-band	IIP3	-4.9	-3.5	dBm	
Output IP3 In-band	OIP3	10.5	11.7	dBm	f <sub>1gps</sub> = 1575.42 MHz, f <sub>2gps</sub> = 1576.42 MHz F <sub>1GLONASS</sub> = 1602 MHz, F <sub>2GLONASS</sub> = 1603 MHz Input power= -30 dBm
LTE band-13 2 <sup>nd</sup> Harmonic	H2	-89			f <sub>IN</sub> = 787.76 MHz, P <sub>IN</sub> = +15 dBm; f <sub>H2</sub> = 1575.52 MHz
Output IM2 Out-of-band	IM2	-105			f <sub>1</sub> = 827 MHz, P <sub>1IN</sub> = +12 dBm; f <sub>2</sub> = 2402 MHz, P <sub>2IN</sub> = +8 dBm ; f <sub>IM2</sub> = 1575 MHz
Output IM2 Out-of-band	IM2	-110			f <sub>1</sub> = 897 MHz, P <sub>1IN</sub> = +12 dBm; f <sub>2</sub> = 2472 MHz, P <sub>2IN</sub> = +8 dBm ; f <sub>IM2</sub> = 1575 MHz
Input IP3 Out-of-band	IIP3 <sub>OOB</sub>	67.5			f <sub>1</sub> = 1712.7 MHz, P <sub>1IN</sub> = +10 dBm; f <sub>2</sub> = 1850 MHz, P <sub>2IN</sub> = +10 dBm; f <sub>IIP3</sub> = 1575.4 MHz
Stability	k	>1		--	Unconditionally Stable from 0 to 10GHz

### 3.2 Summary BGA824N6 as 1550-1615 MHz LNA for GNSS


This application note addresses the issue of out-of-band jammers and improving the immunity of BGA824N6 against LTE Band-13, GSM850/900/1800, UMTS and WLAN jammers.

The jamming resistance of BGA824N6 against these jammers is improved by increasing the attenuation of the circuit at these specific out-of-band frequencies (787 MHz, 827 MHz, 897 MHz, 1712 MHz, 1850 MHz, 2402 MHz, and 2472 MHz). This is achieved by using external SMDs and a SAW filter before BGA824N6. In some applications where more rejection is required at special frequencies and SAW filter alone cannot provide sufficient attenuation, some external notches can be designed for those frequencies. The notches L1-C1/L2-C2 and L3-C3 are designed for 750-950 MHz range and 2.45 GHz respectively. The component values are fine tuned so as to have optimal noise figure, jammer rejection, gain and input matching.

The circuit requires only eight 0402 passive components including the notch filters. It has in band gain of 15 dB. The circuit achieves input return loss better than 10.3 dB, as well as output return loss better than 13.1 dB. At room temperature the noise figure is 1.97 dB (SMA and PCB losses are subtracted) for the GPS frequency. Furthermore, the circuit is unconditionally stable till 10 GHz.

At 1575.42 MHz, using two tones spacing of 1 MHz, the output third order intercept point OIP3 reaches 10.5 dBm. And for the GLONASS frequency band, OIP3 reaches 11.7 dBm. Input P1dB of the GNSS LNA is about -5.2 dBm for the GPS frequency and -4.8 dBm for GLONASS frequency band. The out of band IIP3 reaches 67.5 dBm at room temperature at 1575.4 MHz frequency. And this circuit shows very good H2 performance of -89 dBm for GPS frequency.

### 3.3 Schematics and Bill-of-Materials




**Figure 5 Schematic of the BGA824N6 Application Circuit**


**Table 5 Bill-of-Materials**

Symbol	Value	Unit	Size	Manufacturer	Comment
L1	4.3	nH	0201	Murata LQP type	750-950 MHz Notch
C1	9	pF	0201	Various	750-950 MHz Notch
L2	4.7	nH	0201	Murata LQP type	750-950 MHz Notch
C2	7	pF	0201	Various	750-950 MHz Notch
L3	2.9	nH	0201	Murata LQP type	2.45 GHz Notch
C3	1.2	pF	0201	Various	2.45 GHz Notch
L4	6.8	nH	0201	Murata LQP type	Matching between SAW and LNA
C4 (optional)	10	nF	0201	Various	RF bypass
N1	BGA824N6		TSNP-6-2	Infineon	SiGe LNA
N2	SAW		TSNP-7-10		SAW filter of BGM1033N7 used in this application circuit


## 4 Measurement Graphs




**Figure 6** Power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands



**Figure 7** Narrowband power gain of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




**Figure 8** Noise figure of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




**Figure 9** Input matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands







**Figure 10** Input matching smith chart for COMPASS, Galileo, GPS and GLONASS bands




**Figure 11** Output matching of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




**Figure 12** Output matching smith chart for COMPASS, Galileo, GPS and GLONASS bands




**Figure 13** Reverse isolation of BGA824N6 for COMPASS, Galileo, GPS and GLONASS bands




**Figure 14** Stability factor  $k$  of BGA824N6 upto 10 GHz




**Figure 15** Stability factor  $\mu_1$  of BGA824N6 upto 10 GHz




**Figure 16** Stability factor  $\mu_2$  of BGA824N6 upto 10 GHz




**Figure 17** Input 1 dB compression point of BGA824N6 at supply voltage of 1.8 V for COMPASS, Galileo, GPS and GLONASS bands



**Figure 18** Input 1 dB compression point of BGA824N6 at supply voltage of 2.8 V for COMPASS, Galileo, GPS and GLONASS bands



**Figure 19** Carrier and intermodulation products of BGA824N6 for GPS band



**Figure 20 Carrier and intermodulation products of BGA824N6 for GLONASS band**

## 5 Evaluation Board and Layout Information

In this application note, the following PCB is used:

PCB material: FR4

$\epsilon_r$  of PCB material: 4.3




Figure 21 Picture of Evaluation Board (overview)




Figure 22 Picture of Evaluation Board (detailed view)






Figure 23 PCB Layer Information

## **6 Authors**

Moakhkhurul Islam, Application Engineer of Business Unit “RF and Protection Devices”.  
Jagjit Singh Bal, Application Engineer of Business Unit “RF and Protection Devices”

## **7 Remark**

The graphs are generated with the simulation program AWR Microwave Office®.

[www.infineon.com](http://www.infineon.com)