

Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as "Cypress" document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.





High-Performance Programmable Oscillators

Features


- Low-noise PLL for integrated crystal applications
- Differential Clock Output: re-configurable through I²C
- Output frequency support from 15 MHz to 2.1 GHz
- Fractional N PLL with fully integrated VCO
- Works on an integrated fixed frequency crystal
- LVPECL, LVDS, HCSL, and CML output standards available
- Compatible with 3.3 V, 2.5 V, and 1.8 V supply
- 150 fs typical integrated jitter performance (12 kHz to 20 MHz frequency offsets) for outputs greater than 150 MHz
- VCXO functionality provided with tunable Total Pull Range (TPR) from ±50 ppm to ±275 ppm
- 8-pin LCC package 7.0 × 5.0 (CY2941x) or 5.0 × 3.2 (CY2942x) mm

Functional Description

The CY2941x/CY2942x is a programmable PLL-based crystal oscillator solution with flexible output frequency options. It is field or factory-programmable for any output frequency between 15 MHz and 2.1 GHz. Other frequency options can be configured with the I^2C interface. Using advanced design technology, it provides excellent jitter performance across the entire output frequency range, working reliably at supply voltages from 1.8 V to 3.3 V for ambient temperatures from -40 °C to +105 °C. This makes it ideally suited for communications applications (for example, OTN, SONET/SDH, xDSL, GbE, networking, wireless infrastructure), test and instrumentation applications, and high-speed data converters. Additionally, the VCXO function enables use of the CY2941x/CY2942x series in applications requiring a clock source with voltage control, and in discrete clocking solutions for synchronous timing applications.

The CY2941x/CY2942x device configuration can be created using ClockWizard 2.1. For programming support, contact Cypress technical support or send an email to clocks@cypress.com.

For a complete list of related documentation, click here.



Logic Block Diagram




Contents


Pin Diagrams	3
Pin Description	3
Functional Overview	-
Programmable Features	4
Architecture Overview	4
Internal State Diagram	4
Small/Large Change	5
Programming Support	5
Programmable OE Polarity	5
Programmable VCXO	5
Power Supply Sequencing	5
I2C Interface	5
Memory Map	5
Absolute Maximum Ratings	6
Recommended Operating Conditions	
DC Electrical Specifications	
DC Specifications for LVDS Output	
DC Specifications for LVPECL Output	
DC Specifications for CML Output	
DC Specifications for HCSL Output	7
VCXO Specific Parameters	8
AC Electrical Specifications	
for LVPECL, LVDS, CML Outputs	9

AC Electrical Specifications for HCSL Output	10
Timing Parameters	10
Phase Jitter Characteristics	
I2C Bus Timing Specifications	
Frequency Stability	
Voltage and Timing Definitions	
Phase Noise Plots	
Ordering Information	18
Ordering Code Definitions	
Package Diagrams	
Acronyms	
Document Conventions	
Units of Measure	
Document History Page	
Sales, Solutions, and Legal Information	
Worldwide Sales and Design Support	
Products	
PSoC® Solutions	
Cypress Developer Community	
Technical Support	



Pin Diagrams





Pin Description

Name	Pin Number	Description
CY29411/CY29421 (8-pin LCC)	
OE	1	Output Enable input
NC	2	Not connected
GND	3	Supply ground
CLKN	4	Complement clock output
CLKP	5	True clock output
V _{DD}	6	Power supply
SDA	7	Serial data input/output
SCL	8	Serial clock input for I ² C
CY29412/CY29422 (8-pin LCC)	
VC ^[1]	1	Input voltage for VCXO
OE	2	Output enable input
GND	3	Supply ground
CLKN	4	Complement clock output
CLKP	5	True clock output
V _{DD}	6	Power supply
SDA	7	Serial data input/output
SCL	8	Serial clock input for I ² C

^{1.} If VC is unused, do not leave it floating; connect it to VDD or GND.



Functional Overview

Programmable Features

Table 1. Programmable Features

Feature	Details		
Frequency	Frequency for the PLL		
Tuning	Oscillator tuning (load capacitance values)		
Function	OE Polarity, I ² C Address		
Power Supply V _{DD} (1.8, 2.5, or 3.3 V)			
	Enable/Disable VCXO		
vcxo	Kv Polarity		
VCAO	TPR		
	Modulation Bandwidth		
Output Standard	LVPECL, LVDS, HCSL, CML		

Architecture Overview

The CY2941x/CY2942x devices are high-performance programmable PLL crystal oscillators supporting multiple functions and multiple output standards. The device has internal one-time programmable (OTP) nonvolatile memory (NVM) that can be partitioned into Common Device Configurations and Output frequency-related information (see Figure 2). The Common Device Configurations do not change with output frequency and consist of chip power supply, OE polarity, I^2C device address, input reference, output standard, and VCXO. The CY2941x/CY2942x devices also contain volatile memory (shown as "NVMCopy" in Figure 1) that stores an exact copy of the NVM at the release of reset on Power ON. The Chip settings depend on the contents of the volatile memory and the output frequency depends on the configurations stored in it, as explained in Figure 1. The volatile memory can be accessed through the I²C bus and modified.







Figure 2 shows the conceptual internal memory structure that consists of Frequency Profile and Common Device Configuration settings.

Figure 2. Memory Structure



Description of Settings for the Memory Structure

- FS0: Contains frequency information
- VCXO Function: Contains parameters related to VCXO functionality, enable/disable, TPR, modulation bandwidth and Kv (Slope for VC vs. Frequency) information
- V_{DD}: 1.8-/2.5-/3.3-V range information
- I²C address: I²C address (programmable) information
- Output Standard: LVPECL, LVDS, HCSL or CML
- LOCK: 2-bit pattern to indicate NVM lock
- Input Reference: Information is Fixed, cannot be modified by the user

Internal State Diagram

The CY2941x/CY2942x contains a state machine which controls the device behavior. The state machine loads the "eFuse" contents to "NVMCopy" after reset as indicated in the Figure 3 on page 5. The state machine enters one of the following states: "Command Wait state" or "Active state" according to the value of LOCK. In the "Command Wait state" state, user may access all the registers and read/write the "NVMCopy" contents. The following commands can be used in the "Command Wait state":


The LOCK state is determined by a 2-bit pattern: 00, 01, 10, or 11. When the Power rail reaches a value within the specified range, the device comes out of the Reset state.

The blank device has LOCK="00" (NVM not locked) in Figure 3 on page 5 so that it goes to the "Command Wait state" after coming out of Reset. The State machine will wait for the following commands:

- Write to volatile memory
- Program Non-Volatile memory (NVM)
- Loop Lock



Figure 3. State Diagram



When the LOCK is programmed to "10" or "01", the device will go to the "Active state" and the device will perform at the programmed frequency.

In the "Command Wait state", you can configure the device with or without writing to the NVM. The use case scenarios are as follows:

Test output frequency

- $\ensuremath{\square}$ Write to volatile memory and selectively write to NVM if needed
- Proceed to Loop Lock can optionally be done for testing purpose

In the NVM locked state, the NVM cannot be reprogrammed. If needed, the output frequency may be changed using Large or Small change commands.

Small/Large Change

Small Change indicates that the frequency is changing within ± 500 ppm. The frequency information will be loaded through I²C and the output frequency will change without any glitch from its original frequency to the new frequency. For more information, see AC Electrical Specifications for LVPECL, LVDS, CML Outputs.

Large Change indicates that the frequency is changing more than ± 500 ppm and is done through the I²C interface.The device will recalibrate and reconfigure the PLL. The output will be differential Low synchronously until this process is completed.

Programming Support

The CY2941x/CY2942x is a software-configurable solution, in which Cypress provides programming software to users to configure the programmable features of the device based on their requirements.

Programmable OE Polarity

The CY2941x/CY2942x contains a bit for OE polarity setting (default is active low). You can choose active-high or active-low polarity for the OE function. The output will be differential Low synchronously when OE is deasserted.

Programmable VCXO

The device incorporates a proprietary technique for modulating frequency by modifying the VCO frequency based on the VC control voltage. The pull profile is linear and accurate compared to pulling the crystal reference. Also, the VCXO characteristics are very stable and do not vary over temperature, supply voltage, or process variations.

Kv (Slope for frequency vs. VC), TPR VC bandwidth, and VCXO on/off are programmable.

Power Supply Sequencing

The CY2941x/CY2942x does not require any specific sequencing for startup. Startup requires a monotonic V_{DD} ramp specified in the datasheet. After the ramp up, V_{DD} has to be maintained within the limits specified for it in the Recommended Operating Conditions. Brownout detection and protection has to be implemented elsewhere in the system.

Other input signals can power up earlier or later than V_{DD} , there is no timing requirement for the input signals with reference to V_{DD} . The device will operate normally when all the input signals are settled to the configured state.

I²C Interface

The CY2941x/CY2942x supports two-wire serial interface (l^2C) in Fast Mode (400 kbps) and 7-bit addressing. The device address is programmable and is 55h by default. It supports single-byte access only. The first l^2C access to the device will be available at 5 ms (minimum) after VDD reaches its minimum specified voltage.

Memory Map

Table 2. Common Configurations

Memory Address	Descriptions
50h–57h	Device configurations

Table 3. FS0: Frequency Configurations

Memory Address	Descriptions
10h	DIVO
11h	DIVO, DIVN_INT
12h	ICP,DIVN_INT, PLL_MODE
13h	DIVN_FRAC_L
14h	DIVN_FRAC_M
15h	DIVN_FRAC_H

Table 4. Misc information

Memory Address	Description
00h (Read only)	Device ID (= 51h)
D4h–D6h	User configurable information

The user must write all the contents created by the Configuration tool. Partial updates to the device is not allowed. Access to locations other than those described here may cause fatal error in device operation.



Absolute Maximum Ratings

Exceeding maximum ratings^[2] may shorten the useful life of the device. User guidelines are not tested.

Supply voltage to ground potential–0.5 V to + 3.8 V
Input voltage0.5 V to + 3.8 V
Storage temperature (non-condensing) –55 °C to +150 °C
Junction temperature40 °C to +125 °C
Programming temperature 0 °C to +125 °C

Recommended Operating Conditions

Programming voltage	2.5V ±0.1 V
Supply Current for eFuse Programming	50 mA
Data retention at T _J = 100 °C	> 10 years
Maximum programming cycles	1
ESD HBM (JEDEC JS-001-2012)	2000 V
ESD MM (JEDEC JESD22-A115B)	
ESD CDM (JEDEC JESD22-C101E)	400 V
Latch-up current	±140 mA

Parameter	Description		Max	Unit
	Core supply voltage, 1.8-V operating range, 1.8 V ± 5%	1.71	1.89	
V _{DD}	Core supply voltage, 2.5-V operating range, 2.5 V ± 10%	2.25	2.75	V
	Core supply voltage, 3.3-V operating range, 3.3 V ± 10%	2.97	3.63	
T _A	mbient temperature		+105	°C
UL-94	Flammability rating. V-0 at 1/8 in.	-	10	ppm
f _{RES}	Frequency resolution	-	2	ppb
T _{PLLHOLD}	PLL Hold Temperature Range	_	125	°C

DC Electrical Specifications

Parameter	Description	Test Conditions	Min	Тур	Max	Unit
	Supply current, LVPECL	V_{DD} = 3.3 V/2.5 V, 50 Ω to V _{TT} (V _{DD} – 2.0 V), with common mode current	-	93	106	
	Supply current, LVPECL	V_{DD} = 3.3 V/2.5 V, 50 Ω to V _{TT} (V _{DD} – 2.0 V), without common mode current ^[3]	-	81	94	
IDD	Supply current, LVDS	V_{DD} = 3.3 V/2.5 V/1.8 V, 100 Ω between CLKP and CLKN	-	69	81	mA
	Supply current, HCSL	V_{DD} = 3.3 V/2.5 V/1.8 V, 33 Ω and 49.9 Ω to GND	-	80	93	
	Supply current, CML	V_{DD} = 3.3 V/2.5 V/1.8 V, 50 Ω to V _{DD}	-	73	86	
	Supply current, PLL only	V _{DD} = 3.3 V/2.5 V/1.8 V	-	59	70	
I _{IH}	Input high current	Logic input, Input = V _{DD}	-	30	50	μA
I _{IL}	Input low current	Logic input, Input = GND	-	30	50	μA
V _{IH} ^[4]	Input high voltage	OE, SCL, SDA logic level = 1	0.7 × V _{DD}	_	_	V
V _{IL} ^[4]	Input low voltage	OE, SCL, SDA logic level = 0	_	_	$0.3 \times V_{DD}$	V
V _{IN}	Input voltage level	All input, relative to GND	-0.5	_	3.8	V
R _P	Internal pull-up resistance	OE, configured active High	-	200	-	kΩ
R _D	Internal pull-down resistance	OE, configured active Low	-	200	-	kΩ

Notes

Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or at any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to Absolute-Maximum-Rated conditions for extended periods may affect device reliability or cause permanent device damage.
 In ClockWizard 2.1, setting the output standard to LVPECL2 configures the output to "LVPECL without common mode current". Refer to AN210253 for LVPECL terminations for different use case configurations.

4. I²C operation applicable for V_DD of 1.8 \breve{V} and 2.5 V only.



DC Specifications for LVDS Output

(V_{DD} = 1.8-V, 2.5-V, or 3.3-V range)

Parameter	Description	Conditions	Min	Тур	Max	Units
V _{OCM} ^[5]	Output common-mode voltage	V _{DD} = 2.5-V or 3.3-V range	1.125	1.200	1.375	V
	Change in V _{OCM} between complementary output states	_	_	-	50	mV
I _{OZ}	Output leakage current	Output off, V _{OUT} = 0.75 V to 1.75 V	-20	-	20	μA

DC Specifications for LVPECL Output

(V_{DD} = 2.5-V or 3.3-V range, with common mode current)

Parameter	Description	Conditions	Min	Тур	Max	Units
V _{OH}	Output high voltage	R-term = 50 Ω to V _{TT} (V _{DD} – 2.0 V)	V _{DD} – 1.165	-	V _{DD} – 0.800	V
V _{OL}	Output low voltage	R-term = 50 Ω to V _{TT} (V _{DD} – 2.0 V)	$V_{DD} - 2.0$	-	V _{DD} – 1.55	V

DC Specifications for CML Output

(V_{DD} = 1.8-V, 2.5-V or 3.3-V range)

Parameter	Description	Conditions	Min	Тур	Мах	Units
V _{OH}	Output high voltage	R-term = 50 Ω to V _{DD}	V _{DD} – 0.085	V _{DD} – 0.01	V _{DD}	V
V _{OL}	Output low voltage	R-term = 50 Ω to V _{DD}	V _{DD} – 0.6	V _{DD} – 0.4	V _{DD} - 0.32	V

DC Specifications for HCSL Output

(V_{DD} = 1.8-V, 2.5-V, or 3.3-V range)

Parameter	Description	Conditions	Min	Тур	Max	Units
V _{MAX} ^[6]	Max output high voltage	Measurement taken from single-ended waveform	_	-	1150	mV
V _{MIN} ^[6]	Min output low voltage	Measurement taken from single-ended waveform	-300	-	_	mV
V _{OHDIFF}	Differential output high voltage	Measurement taken from differential waveform	150	_	_	mV
V _{OLDIFF}	Differential output low voltage	Measurement taken from differential waveform	_	-	-150	mV
V _{CROSS} ^[6]	Absolute crossing point voltage	Measurement taken from single-ended waveform	250	_	600	mV
V _{CROSSDELTA} ^[6]	Variation of V _{CROSS} over all rising clock edges	Measurement taken from single-ended waveform	_	-	140	mV

Notes

Requires external AC coupling for V_{DD} = 1.8-V range, as indicated in Figure 9.
 Parameters are guaranteed by design and characterization. Not 100% tested in production.



V_{CXO} Specific Parameters

Parameter ^[7]	Description	Condition	Min	Тур	Max	Units
TPR	Total Pull Range	VC range 0.1 × V_{DD} to 0.9 × V_{DD}	±50	-	±275	ppm
K _{BSL}	Best-fit Straight Line (BSL) linearity	Deviation from BSL line	-5	-	5	%
K _{INC}	Incremental linearity	Kv slope deviation	-10	-	10	%
K _{BW}	Bandwidth of Kv modulation	Programmable	5	10	20	kHz
K _{RANGE}	Voltage range	Permissible voltage range	0	-	V _{DD}	V
		V _{DD} configuration = 1.8 V	-	0.9	-	V
V _{CTYP}	Nominal center VC control voltage	V _{DD} configuration = 2.5 V	-	1.25	-	V
		V _{DD} configuration = 3.3 V	-	1.65	-	V
R _{VCIN} ^[8]	Input resistance for VC	_	5	-	-	MΩ
V _{RANGE}	Input voltage range	Linearity guaranteed range	$0.1 \times V_{DD}$	_	$0.9 \times V_{DD}$	V

Notes7. Parameters are guaranteed by design and characterization. Not 100% tested in production.8. RVCIN is 100% tested.



AC Electrical Specifications for LVPECL, LVDS, CML Outputs

(V_{DD} = 3.3 V and 2.5 V for LVPECL, with common mode current, and V_{DD} = 3.3 V, 2.5 V, and 1.8 V for LVDS and CML outputs)

Parameter ^[9]	Description	Details/Conditions	Min	Тур	Max	Unit
		LVPECL, CML, LVDS output		קני		
f _{OUT}	Clock Output Frequency	standards	15	-	2100	MHz
	LVPECL Output Rise/Fall Time	20% to 80% of AC levels. Measured at 156.25 MHz for PECL outputs.	_	-	350	ps
t _{RF}	CML Output Rise/Fall Time	20% to 80% of AC levels. Measured at 156.25 MHz for CML outputs.	_	_	350	ps
	LVDS Output Rise/Fall Time	20% to 80% of AC levels. Measured at 156.25 MHz for LVDS outputs.	-	_	350	ps
t _{ODC}	Output Duty Cycle	Measured at differential 50% level, 156.25 MHz.	45	50	55	%
V _P	LVDS output differential peak	15 MHz to 700 MHz	247	_	454	mV
V _P	LVDS output differential peak	700 MHz to 2100 MHz	150	_	454	mV
ΔV _P	Change in VP between complementary output states	-	_	-	50	mV
V _P		f _{OUT} = 15 MHz to 325 MHz	450	_	_	mV
V _P	LVPECL output differential peak	f _{OUT} = 325 MHz to 700 MHz	350	-	-	mV
V _P		f _{OUT} = 700 MHz to 2100 MHz	250	-	-	mv
V _P	CML output differential peak	f _{OUT} = 15 MHz to 700 MHz	250	-	600	mV
V _P	CML output differential peak	f _{OUT} = 700 MHz to 2100 MHz	200	-	600	mV
t _{CCJ}	Cycle to Cycle Jitter	pk, measured at differential signal, 156.25 MHz, over 10k cycles, 100 MHz–130 MHz crystal	_	_	50	ps
t _{PJ}	Period Jitter	pk-pk, measured at differential signal, 156.25 MHz, over 10k cycles, 100 MHz–130 MHz crystal	_	_	50	ps
J _{RMS}	RMS Phase Jitter	f _{OUT} = 156.25 MHz, 12 kHz–20 MHz offset, non-VCXO mode	-	150	250	fs
Non-VCXO Mo	de	·				•
PN1k	Phase Noise, 1 kHz Offset	100-130 MHz crystal reference, f _{OUT} = 156.25 MHz	-	-	-113	dBc/Hz
PN10k	Phase Noise, 10 kHz Offset	100-130 MHz crystal reference, f _{OUT} = 156.25 MHz	-	-	-127	dBc/Hz
PN100k	Phase Noise, 100 kHz Offset	100-130 MHz crystal reference, f _{OUT} = 156.25 MHz	-	-	-135	dBc/Hz
PN1M	Phase Noise, 1MHz Offset	100-130 MHz crystal reference, f _{OUT} = 156.25 MHz	-	-	-144	dBc/Hz
PN10M	Phase Noise, 10 MHz Offset	100-130 MHz crystal reference, f _{OUT} = 156.25 MHz	-	-	-152	dBc/Hz
PN-SPUR	Spur	At frequency offsets equal to and greater than the update rate of the PLL	_	_	-65	dBc/Hz

Note9. Parameters are guaranteed by design and characterization. Not 100% tested in production.



AC Electrical Specifications for HCSL Output

Parameter ^[10]	Description	Test Conditions	Min	Тур	Max	Units
f _{OUT}	Output frequency	HCSL	15	-	700	MHz
E _R	Rising edge rate	Measured taken from differential waveform, –150 mV to +150 mV	0.6	-	5.7 ^[11]	V/ns
E _F	Falling edge rate	Measured taken from differential waveform, –150 mV to +150 mV	0.6	-	5.7 ^[11]	V/ns
t _{STABLE}	Time before voltage ring back (VRB) is allowed	Measured taken from differential waveform, –150 mV to +150 mV	500	-	-	ps
R-F_MATCHING	Rise-Fall matching	Measured taken from single-ended waveform, rising edge rate to falling edge rate matching, 100 MHz	-100	_	100	ps
t _{DC}	Output duty cycle	Measured taken from differential waveform, f _{OUT} = 100 MHz	45	-	55	%
t _{CCJ}	Cycle to Cycle Jitter	Measured taken from differential waveform, 100 MHz	-	-	50	ps
J _{RMSPCIE}	Random jitter, PCIE Specification 3.0	100 MHz–130 MHz crystal	_	_	1	ps (RMS)

Timing Parameters

Parameter ^[10]	Description		Max	Unit
t _{PU}	Supply ramp time (0.5 V to V _{DD(min)}). Power ramp must be monotonic.	0.01	3000	ms
t _{WAKEUP}	Time from minimum specified power supply to < ±0.1 ppm accurate output irequency clock		10	ms
t _{OEEN}	Time from OE edge to output enable	-	2.5	ms
t _{OEDIS}	Time for OE edge to output disable	-	10	μs
t _{FSMALL}	Frequency change time for small trigger ($\leq \pm 500$ ppm) with $\pm 1\%$ target frequency		20	μs
t _{FLARGE}	Frequency change time for large trigger (> ±500 ppm)	-	2.5	ms

Notes

Parameters are guaranteed by design and characterization. Not 100% tested in production.
 Edge rates are higher than 4 V/ns due to jitter performance requirements.



Phase Jitter Characteristics

12 kHz to 20 MHz Integration Bandwidth

Parameter ^[12]	Description	Condition	Min	Тур	Max	Units			
Non VCXO function	Ion VCXO functionality								
J _{RMS}	RMS jitter	F _{OUT} = 644.53 MHz	-	110	-	fs			
J _{RMS}	RMS jitter	F _{OUT} = 622.08 MHz	-	120	-	fs			
J _{RMS}	RMS jitter	F _{OUT} = 156.25 MHz	-	145	-	fs			
J _{RMS}	RMS jitter	F _{OUT} = 2.105 GHz	_	145	_	fs			
Modulation bandw	vidth = 10 kHz, V _{DD} = 3.3 V, F _O	_{UT} = 622.08 MHz							
J _{RMS}	RMS jitter	TPR = 50 ppm, Kv = 37.9 ppm/V	_	151	_	fs			
J _{RMS}	RMS jitter	TPR = 155 ppm, Kv = 117.4 ppm/V	-	158	-	fs			
J _{RMS}	RMS jitter	TPR = 275 ppm, Kv = 208.3 ppm/V	-	170	-	fs			
Modulation bandw	vidth = 10 kHz, V _{DD} = 2.5 V, F _O	_{UT} = 622.08 MHz							
J _{RMS}	RMS jitter	TPR = 50 ppm, Kv = 50 ppm/V	-	152	-	fs			
J _{RMS}	RMS jitter	TPR = 155 ppm, Kv = 155 ppm/V	_	160	_	fs			
J _{RMS}	RMS jitter	TPR = 275 ppm, Kv = 275 ppm/V	-	175	-	fs			
Modulation bandw	vidth = 10 kHz, V _{DD} = 1.8 V, F _O	_{UT} = 622.08 MHz							
J _{RMS}	RMS jitter	TPR = 50 ppm, Kv = 69.4 ppm/V	_	153	_	fs			
J _{RMS}	RMS jitter	TPR = 155 ppm, Kv = 215.3 ppm/V	-	166	-	fs			
J _{RMS}	RMS jitter	TPR = 275 ppm, Kv = 381.9 ppm/V	_	190	-	fs			

I²C Bus Timing Specifications

Parameter ^[12, 13]	Description	Min	Тур	Max	Units
f _{SCL}	SCL clock frequency	-	-	400	kHz
t _{HD:STA}	Hold time START condition	0.6	-	-	μs
t _{LOW}	Low period of SCL	1.3	-	-	μs
t _{HIGH}	High period of SCL	0.6	-	-	μs
t _{SU:STA}	Setup time for a repeated START condition	0.6	-	-	μs
t _{HD:DAT}	Data hold time	0	-	-	μs
t _{SU:DAT}	Data setup time	100	-	-	ns
t _R	Rise time	-	-	300	ns
t _F	Fall time	-	-	300	ns
t _{SU:STO}	Setup time for STOP condition	0.6	-	-	μs
t _{BUF}	Bus-free time between STOP and START conditions	1.3	_	_	μs

Notes 12. Parameters are guaranteed by design and characterization. Not 100% tested in production. 13. I²C operation applicable for V_{DD} of 1.8 V and 2.5 V only.



Frequency Stability

Parameter	Description	Test Conditions	Min	Тур	Max	Units
fTOLERANCE	Frequency Tolerance	V _{DD} = min to max, T _A = +25 °C	-20	-	+20	ppm
f _{TC}	Temperature Characteristics	V _{DD} = min to max, T _A = –40 °C to +85 °C	-20	-	+20	ppm
f _{TC}	Temperature Characteristics	V _{DD} = min to max, T _A = –40 °C to +105 °C	-30	-	+30	ppm
f _{AGE}	Frequency Aging		-5	_	+5	ppm/year



Voltage and Timing Definitions

Figure 4. Differential Output Definitions




Figure 5. Output Enable/Disable Timing




Figure 6. Power Ramp and PLL Lock Time






Figure 7. Output Termination Circuit





Note

14. The termination circuit shown in this figure is specific to the LVDS output standard for V_{DD} =1.8-V operation. This needs AC coupling (100-nF series capacitor). The 50-ohm termination resistors along with the bias voltage (V_{OCM}) is required to be set at the destination circuit as shown in the figure.



Figure 9. HCSL: Single-ended Measurement Points for Absolute Crossing Point





Figure 10. HCSL: Single-ended Measurement Points for Delta Crossing Point










Figure 12. HCSL: Differential Measurement Points for Ringback









Phase Noise Plots




Figure 14. Typical Phase Noise at 156.25 MHz (12 kHz–20 MHz)






Figure 15. Typical Phase Noise at 622.08 MHz (12 kHz–20 MHz)







Figure 16. Typical Phase Noise at 644.53 MHz (12 kHz-20 MHz)




Ordering Information

Ordering Code	Configuration	Package Description	Product Flow
CY29411FLXIT	Field-programmable	8-pin LCC 7.0 × 5.0 mm – Tape and Reel	Industrial, –40 °C to +105 °C
CY29411LXIxxxT	Factory-configured ^[15]	8-pin LCC 7.0 × 5.0 mm – Tape and Reel	Industrial, –40 °C to +105 °C
CY29412FLXIT	Field-programmable	8-pin LCC 7.0 × 5.0 mm – Tape and Reel	Industrial, –40 °C to +105 °C
CY29412LXIxxxT	Factory-configured ^[15]	8-pin LCC 7.0 × 5.0 mm – Tape and Reel	Industrial, –40 °C to +105 °C
CY29421FLXIT	Field-programmable	8-pin LCC 5.0 × 3.2 mm – Tape and Reel	Industrial, –40 °C to +105 °C
CY29421LXIxxxT	Factory-configured ^[15]	8-pin LCC 5.0 × 3.2 mm – Tape and Reel	Industrial, –40 °C to +105 °C
CY29422FLXIT	Field-programmable	8-pin LCC 5.0 × 3.2 mm – Tape and Reel	Industrial, –40 °C to +105 °C
CY29422LXIxxxT	Factory-configured ^[15]	8-pin LCC 5.0 × 3.2 mm – Tape and Reel	Industrial, –40 °C to +105 °C


Ordering Code Definitions







Package Diagrams



DIMENSIONS SYMBOL MIN. NOM. MAX. А 1.65 1.75 _ A3 0.70 REF D 5.00 BSC 7.00 BSC Е 1.00 bD 1.40 bE 1.18 LD LE 1.28 κ 0.13 2.54 BSC е Ν 8 ND 1 3 NE

NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. N IS THE TOTAL NUMBER OF TERMINALS.
- 3. ND IS THE NUMBER OF TERMINALS ON "D" DIMENSION.
- 4. NE IS THE NUMBER OF TERMINALS ON "E" DIMENSION.

5. PIN #1 ID ON TOP WILL BE LOCATED WITHIN THE INDICATED ZONE.

002-10174 *A

- K

2

3

9

ŧ






Figure 18. 8-pin Ceramic LCC (3.2 × 5.0 × 1.45 mm) Package Outline, 002-10273

TOP VIEW

SIDE VIEW

BOTTOM VIEW

bD 🗵

8

LE


0.32 R INDEX

		DIMENSIONS				
SYMBOL	MIN.	NOM.	MAX.			
А	1.35	-	1.45			
A3		0.60 REF				
D		3.20 BSC				
E		5.00 BSC				
bD	0.64					
bE		0.64				
LD		0.70				
LE		0.90				
К		0.10				
е		1.27 BSC				
N	8					
ND	1					
NE	3					

NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. N IS THE TOTAL NUMBER OF TERMINALS.
- 3. ND IS THE NUMBER OF TERMINALS ON "D" DIMENSION.
- 4. NE IS THE NUMBER OF TERMINALS ON "E" DIMENSION.
- <u>5.</u> PIN #1 ID ON TOP WILL BE LOCATED WITHIN THE INDICATED ZONE.

002-10273 *A





Acronyms

Table 5. Acronyms Used in this Document


Acronym	Description		
AC	alternating current		
ADC	analog-to-digital converter		
BCL	best-fit straight line		
CML	current mode logic		
DC	direct current		
ESD	electrostatic discharge		
FS	frequency select		
HCSL	high-speed current steering logic		
I ² C	inter-integrated circuit		
JEDEC	Joint Electron Device Engineering Council		
LDO	low dropout (regulator)		
LVCMOS	low voltage complementary metal oxide semiconductor		
LVDS	low-voltage differential signals		
LVPECL	low-voltage positive emitter-coupled logic		
NVM	non-volatile memory		
OE	output enable		
PLL	phase-locked loop		
POR	power-on reset		
PSoC [®]	Programmable System-on-Chip		
QFN	quad flat no-lead		
RMS	root mean square		
SCL	serial I ² C clock		
SDA	serial I ² C data		
VCXO	voltage controlled crystal oscillator		
VRB	voltage ring back		
XTAL	crystal		
OTP	one time programmable		

Document Conventions

Units of Measure

Table 6. Units of Measure

Symbol	Unit of Measure		
°C	Degrees Celsius		
fs	femtoseconds		
GHz	gigahertz		
kΩ	kilohms		
kHz	kilohertz		
MHz	megahertz		
MΩ	megaohms		
μA	microamperes		
μm	micrometer		
μs	microseconds		
μW	microwatts		
mA	milliamperes		
mm	millimeter		
mΩ	milliohms		
ms	milliseconds		
mV	millivolts		
nH	nanohenry		
ns	nanoseconds		
Ω	ohms		
%	percent		
pF	picofarads		
ps	picoseconds		
ppm	parts per million		
ppb	parts per billion		
V	volts		





Document History Page

Document Title: CY2941x/CY2942x, High-Performance Programmable Oscillators Document Number: 001-97768					
Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change	
*C	5320399	MGPL	07/18/2016	Changed status from Preliminary to Final.	
*D	5429121	MGPL	09/07/2016	Updated Absolute Maximum Ratings: Added "Supply Current for eFuse Programming". Replaced "> 2000 V" with "2000 V" in value corresponding to "ESD HBM". Replaced "> 200 V" with "200 V" in value corresponding to "ESD MM". Replaced ">500V" with "400 V" in value corresponding to "ESD CDM". Updated to new template.	
*E	5518357	MGPL / PSR	11/15/2016	Updated Voltage and Timing Definitions: Added Figure 8.	
*F	5613574	PSR	02/03/2017	Updated Functional Description: Updated description. Added "For a complete list of related documentation, click here." at the end. Updated DC Electrical Specifications: Updated details in "Test Conditions" columns corresponding to I _{DD} parameter having description "Supply current, LVPECL". Updated AC Electrical Specifications for LVPECL, LVDS, CML Outputs: Added note below heading (clarifying voltage range). Updated Ordering Information: Updated part numbers.	
*G	5682054	PSR	04/03/2017	Replaced V_{DDO} with V_{DD} in all instances across the document. Updated to new template.	
*Н	5757596	PSR	05/31/2017	Updated VCXO Specific Parameters: Updated details in all columns corresponding to V _{CTYP} parameter. Updated to new template.	
*	6178001	XHT	05/31/2018	Updated Voltage and Timing Definitions: Updated Figure 5. Updated Functional Overview: Updated Small/Large Change: Updated description. Updated I2C Interface: Updated description. Updated to new template.	
*J	6372083	ХНТ	10/31/2018	Updated Functional Overview: Updated Small/Large Change: Updated description.	



Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

Products

Arm [®] Cortex [®] Microcontrollers	cypress.com/arm
Automotive	cypress.com/automotive
Clocks & Buffers	cypress.com/clocks
Interface	cypress.com/interface
Internet of Things	cypress.com/iot
Memory	cypress.com/memory
Microcontrollers	cypress.com/mcu
PSoC	cypress.com/psoc
Power Management ICs	cypress.com/pmic
Touch Sensing	cypress.com/touch
USB Controllers	cypress.com/usb
Wireless Connectivity	cypress.com/wireless

PSoC[®] Solutions

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP | PSoC 6 MCU

Cypress Developer Community Community | Projects | Video | Blogs | Training | Components

Technical Support cypress.com/support

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.

[©] Cypress Semiconductor Corporation, 2015–2018. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. No computing device can be absolutely secure. Therefore, despite security measures implemented in Cypress hardware or software products, Cypress does not assume any liability arising out of any security breach, such as unauthorized access to or use of a Cypress product. In addition, the products described in these materials may contain design defects or errors known as errata which may cause the product to deviate from published specifications. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or system, could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or reflectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to any Unintended Uses of Cypress products.